

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100.0	0.01	46.2	46.3
200.0	0.03	42.8	42.8
300.0	0.04	40.3	40.5
400.0	0.05	39.3	39.6
500.0	0.05	39.0	39.3
600.0	0.06	39.3	39.4
700.0	0.06	40.1	40.4
800.0	0.06	41.4	42.0
900.0	0.07	43.1	44.2
1000.0	0.07	45.2	47.8
1100.0	0.08	47.8	55.1
1300.0	0.08	48.9	50.8
1400.0	0.09	44.9	44.4
1500.0	0.09	41.5	40.8
1600.0	0.09	38.8	38.1
1700.0	0.09	36.6	36.0
1800.0	0.09	34.9	34.4
1900.0	0.10	33.6	33.1
2000.0	0.10	32.7	32.2
2500.0	0.11	30.0	29.9
3000.0	0.12	31.8	31.9
3500.0	0.12	45.8	45.2
4000.0	0.13	34.3	33.9
4500.0	0.14	28.1	28.0
5000.0	0.14	27.3	27.3
5500.0	0.14	30.5	30.3
6000.0	0.15	39.2	35.7
6500.0	0.15	43.5	34.0
7000.0	0.15	38.6	33.3
7500.0	0.15	41.3	38.5
8000.0	0.16	39.4	50.1
8500.0	0.16	39.4	37.2
9000.0	0.16	37.5	32.3
9500.0	0.17	29.0	27.8
10000.0	0.18	25.6	25.5
10500.0	0.18	26.7	26.8
11000.0	0.18	33.6	33.1
11500.0	0.19	28.9	28.9
12000.0	0.22	21.9	22.1
12500.0	0.23	20.2	20.5
13000.0	0.21	23.1	23.1
13500.0	0.20	33.6	29.2
14000.0	0.24	24.2	23.4
14500.0	0.29	18.8	19.0
15000.0	0.28	18.8	19.4
15500.0	0.23	24.0	25.1
16000.0	0.22	29.5	29.0
16500.0	0.28	21.4	21.4
17000.0	0.32	18.9	19.3
17500.0	0.29	21.1	21.6
18000.0	0.25	28.6	28.2

