

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
10.0	0.02	51.09	53.35
50.0	0.04	46.66	46.90
100.0	0.04	44.27	44.30
200.0	0.06	43.15	43.26
300.0	0.08	45.29	43.83
400.0	0.09	44.99	43.31
500.0	0.10	41.69	41.52
600.0	0.11	41.52	41.56
700.0	0.12	43.61	44.60
800.0	0.13	46.28	46.19
900.0	0.14	44.04	42.96
1000.0	0.15	40.12	39.63
1100.0	0.15	38.62	38.61
1250.0	0.16	41.11	40.70
1500.0	0.18	42.28	41.70
1750.0	0.20	36.91	36.44
2000.0	0.21	49.41	52.45
2001.0	0.21	49.23	52.19
2250.0	0.22	36.26	35.27
2500.0	0.24	51.38	61.03
2750.0	0.25	35.02	34.14
3000.0	0.26	47.15	47.02
3250.0	0.27	35.52	35.62
3500.0	0.28	41.29	41.95
3750.0	0.30	38.83	39.68
4000.0	0.31	35.72	35.30
4250.0	0.32	51.09	47.28
4500.0	0.33	33.23	32.42
5000.0	0.35	33.39	32.59
5500.0	0.37	35.55	36.39
6000.0	0.38	38.99	53.29
6500.0	0.40	35.42	37.38
7000.0	0.42	34.76	34.86
7500.0	0.44	32.91	32.77
8000.0	0.45	33.09	32.75
8500.0	0.47	31.51	33.11
9000.0	0.48	32.55	33.58
9500.0	0.49	35.09	33.85
10000.0	0.50	44.62	40.48
10500.0	0.51	51.40	54.54
11000.0	0.53	38.53	37.14
11500.0	0.55	29.72	29.92
12000.0	0.56	26.96	27.35
12500.0	0.60	26.14	25.48
13000.0	0.64	25.75	24.20
13500.0	0.71	23.80	22.68
14000.0	0.70	23.45	23.68
14500.0	0.70	24.90	23.87
15000.0	0.69	28.92	26.05
15500.0	0.72	21.21	23.02
16000.0	0.71	23.27	25.48
16500.0	0.70	29.02	28.55
17000.0	0.73	29.85	25.86
17500.0	0.76	31.18	26.38
18000.0	0.78	30.11	27.96