

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.01	40.2	43.4
200.0	0.02	35.8	36.3
300.0	0.03	33.2	33.4
400.0	0.04	32.5	33.3
500.0	0.04	33.1	33.8
600.0	0.05	35.9	36.6
700.0	0.05	42.2	44.3
800.0	0.05	50.8	47.0
900.0	0.06	39.2	38.6
1000.0	0.06	35.5	34.7
1100.0	0.07	34.8	34.5
1250.0	0.07	37.7	38.0
1500.0	0.08	40.8	38.9
1750.0	0.09	32.1	31.8
2000.0	0.09	33.9	33.5
2250.0	0.10	37.8	35.7
2500.0	0.10	35.2	35.0
2750.0	0.10	43.2	45.2
3000.0	0.11	39.3	36.2
3250.0	0.12	37.7	37.8
3500.0	0.13	42.2	38.7
3750.0	0.14	31.5	29.7
4000.0	0.15	30.3	30.2
4250.0	0.15	37.2	41.8
4500.0	0.16	32.2	29.8
5000.0	0.16	33.6	39.9
5500.0	0.18	29.0	29.3
6000.0	0.18	37.1	31.0
6500.0	0.19	29.2	36.0
7000.0	0.20	32.9	31.3
7500.0	0.21	33.2	30.3
8000.0	0.22	27.0	32.1
8500.0	0.22	28.8	26.6
9000.0	0.25	23.8	25.0
9500.0	0.25	30.8	32.3
10000.0	0.25	22.4	22.2
10500.0	0.28	22.6	22.7
11000.0	0.26	35.7	35.1
11500.0	0.29	21.0	21.4
12000.0	0.30	24.5	23.4
12500.0	0.30	24.0	24.9
13000.0	0.30	25.1	25.3
13500.0	0.31	31.2	28.8
14000.0	0.33	25.9	24.8
14500.0	0.33	32.1	27.1
15000.0	0.33	34.2	40.0
15500.0	0.34	25.5	22.3
16000.0	0.35	30.7	25.8
16500.0	0.35	27.8	30.2
17000.0	0.35	27.6	23.6
17500.0	0.41	21.3	21.7
18000.0	0.38	32.9	37.7