

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.02	48.3	47.8
200.0	0.03	42.8	43.0
300.0	0.04	40.3	41.2
400.0	0.04	40.1	40.5
500.0	0.05	41.5	42.1
600.0	0.05	46.4	46.0
700.0	0.06	50.6	60.3
800.0	0.06	44.9	49.5
900.0	0.07	41.5	43.9
1000.0	0.07	40.6	42.2
1100.0	0.08	42.6	43.5
1250.0	0.08	51.0	51.7
1500.0	0.09	38.5	41.1
1750.0	0.10	36.2	36.5
2000.0	0.11	40.0	40.6
2250.0	0.11	42.4	48.7
2500.0	0.12	42.0	41.3
2750.0	0.12	42.7	49.8
3000.0	0.13	37.0	36.7
3250.0	0.14	33.4	32.8
3500.0	0.14	38.8	39.6
3750.0	0.15	42.0	40.4
4000.0	0.16	36.6	35.9
4250.0	0.16	51.9	60.9
4500.0	0.17	35.0	33.9
5000.0	0.18	65.3	52.7
5500.0	0.19	43.6	43.8
6000.0	0.20	31.2	30.8
6500.0	0.21	31.7	31.1
7000.0	0.22	33.2	33.0
7500.0	0.23	39.3	39.8
8000.0	0.24	33.4	32.0
8500.0	0.25	30.4	29.5
9000.0	0.27	24.7	24.4
9500.0	0.27	31.9	32.0
10000.0	0.27	38.5	39.6
10500.0	0.29	33.6	33.0
11000.0	0.30	38.2	34.7
11500.0	0.31	36.7	33.4
12000.0	0.31	52.7	37.2
12500.0	0.30	32.2	31.1
13000.0	0.31	26.4	26.5
13500.0	0.32	25.8	25.2
14000.0	0.32	35.9	34.1
14500.0	0.31	30.9	28.3
15000.0	0.33	23.5	24.5
15500.0	0.36	20.4	19.8
16000.0	0.38	22.8	21.6
16500.0	0.37	29.2	26.0
17000.0	0.36	30.0	31.9
17500.0	0.39	22.0	23.5
18000.0	0.43	19.4	19.2