

*Typical Performance Data*

FREQUENCY (MHz)	AVERAGE INSERTION LOSS (dB)	INPUT RETURN LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE <sup>(1)</sup> (deg.)
4900	0.86	12.50	0.91	2.29
4926	0.83	13.00	0.91	2.37
4952	0.80	13.53	0.91	2.41
4978	0.77	14.17	0.91	2.49
5005	0.74	14.91	0.91	2.62
5031	0.71	15.59	0.91	2.67
5057	0.68	16.34	0.91	2.74
5084	0.66	17.26	0.91	2.79
5110	0.64	18.29	0.92	2.85
5136	0.62	19.37	0.92	2.94
5163	0.60	20.61	0.92	3.02
5189	0.58	22.07	0.92	3.07
5215	0.57	23.78	0.92	3.10
5242	0.56	25.72	0.92	3.18
5268	0.55	27.53	0.92	3.27
5294	0.54	28.57	0.92	3.31
5321	0.54	28.09	0.93	3.36
5347	0.53	26.60	0.92	3.41
5373	0.53	24.91	0.91	3.47
5400	0.54	23.13	0.91	3.54
5426	0.54	21.43	0.92	3.56
5452	0.55	20.01	0.91	3.62
5478	0.56	18.95	0.90	3.69
5505	0.56	18.02	0.90	3.71
5531	0.58	17.01	0.89	3.76
5557	0.59	16.03	0.88	3.80
5584	0.61	15.21	0.87	3.83
5610	0.62	14.60	0.85	3.89
5636	0.64	14.02	0.85	3.90
5663	0.67	13.35	0.85	3.91
5689	0.69	12.77	0.84	3.93
5715	0.71	12.30	0.83	4.00
5742	0.73	11.88	0.82	4.05
5768	0.76	11.45	0.81	4.05
5794	0.79	11.00	0.79	4.08
5821	0.82	10.59	0.77	4.12
5847	0.84	10.24	0.76	4.18
5873	0.87	9.94	0.74	4.19
5900	0.90	9.64	0.71	4.17
5950	0.96	9.10	0.67	4.19

<sup>(1)</sup>Relative to 180°