

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT VSWR (:1)	OUTPUT VSWR (:1)
2000	18.63	43.86	15.55
2400	21.32	27.79	11.73
2420	21.77	27.33	11.52
2440	22.29	26.81	11.29
2460	22.88	26.36	11.11
2480	23.53	25.94	11.01
2500	24.26	25.50	10.91
2600	28.96	22.70	10.17
2800	19.91	17.32	8.67
3000	12.51	12.38	7.62
3200	8.46	8.57	6.50
3400	6.04	6.11	5.34
3600	4.50	4.56	4.33
3800	3.44	3.53	3.49
4000	2.67	2.78	2.79
4200	2.09	2.18	2.24
4400	1.65	1.72	1.81
4600	1.38	1.37	1.49
4800	1.23	1.11	1.31
4900	1.20	1.04	1.28
5000	1.19	1.10	1.28
5100	1.21	1.19	1.32
5200	1.23	1.28	1.36
5300	1.25	1.35	1.40
5400	1.28	1.41	1.43
5500	1.30	1.45	1.45
5600	1.33	1.47	1.46
5700	1.34	1.48	1.45
5800	1.36	1.46	1.42
5900	1.36	1.42	1.37
5950	1.37	1.40	1.33
6000	1.38	1.37	1.29
6200	1.43	1.26	1.13
6400	1.57	1.26	1.14
6600	1.87	1.49	1.42
6800	2.44	1.93	1.81
7000	3.70	2.70	2.02
7200	4.55	3.81	2.84
7400	5.25	4.86	4.13
7600	6.34	6.17	5.26
7800	7.54	7.59	6.31
8000	8.82	8.83	7.07
8200	10.16	9.61	7.59
8400	11.57	9.77	8.01
8600	13.12	9.37	8.34
8800	14.83	8.63	8.70
9000	16.79	7.87	9.32
9200	19.06	7.35	10.17
9400	21.73	7.16	11.48
9600	24.90	7.39	13.30
9800	28.76	8.08	15.72
10000	33.62	9.30	19.03
10400	42.53	13.88	27.28
10800	36.46	22.42	34.69
11200	33.51	36.46	35.31
11600	31.80	49.08	26.06
11900	30.65	47.41	18.35
12000	30.28	44.46	15.86
12500	28.21	24.02	8.01
13000	26.29	10.37	4.75
13500	25.92	4.61	5.24
14000	28.41	3.84	10.06
14500	33.38	7.82	23.33
14700	35.63	11.35	34.20
15000	38.97	20.44	58.93
15500	43.29	59.77	113.04
16000	45.22	160.16	54.11
16500	45.06	89.21	16.99
17000	44.26	23.79	5.15
17500	37.61	6.50	1.93
18000	33.53	1.75	4.18