

# Fixed Attenuator

# BW-20N250W+

## Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)	
		N-Male	N-Female
10	19.65	1.02	1.03
100	19.70	1.03	1.03
500	19.74	1.04	1.05
1000	19.77	1.03	1.07
1200	19.80	1.02	1.08
1400	19.84	1.03	1.09
1600	19.85	1.04	1.09
1800	19.86	1.04	1.10
2000	19.88	1.04	1.10
2200	19.90	1.06	1.11
2400	19.93	1.08	1.11
2600	19.96	1.06	1.11
2800	19.98	1.06	1.11
3000	20.02	1.10	1.11
3200	20.05	1.10	1.12
3400	20.09	1.08	1.13
3600	20.09	1.16	1.14
3800	20.16	1.18	1.16
4000	20.18	1.15	1.17
4200	20.20	1.21	1.18
4400	20.22	1.21	1.19
4600	20.24	1.16	1.20
4800	20.27	1.17	1.21
5000	20.31	1.18	1.21
5200	20.34	1.18	1.20
5400	20.35	1.14	1.19
5600	20.38	1.12	1.17
5800	20.42	1.08	1.16
6000	20.47	1.10	1.15
6200	20.52	1.13	1.14
6400	20.55	1.11	1.13
6600	20.58	1.08	1.14
6800	20.64	1.06	1.15
7000	20.70	1.08	1.17
7200	20.75	1.10	1.20
7400	20.77	1.08	1.22
7600	20.78	1.09	1.23
7800	20.80	1.11	1.24
8000	20.85	1.10	1.24