


Digital Step Attenuator


Typical Performance Curves

DAT-31A-PN+


Thru Loss




Step Attenuation (1dB)




Step Attenuation (2dB)




Step Attenuation (4dB)



Step Attenuation (8dB)



Step Attenuation (16dB)




Digital Step Attenuator


Typical Performance Curves

DAT-31A-PN+


Input Return Loss (0dB)




Input Return Loss (1dB)




Input Return Loss(2dB)




Input Return Loss (4dB)



Input Return Loss (8dB)



Input Return Loss (16dB)




Digital Step Attenuator


Typical Performance Curves

DAT-31A-PN+


Output Return Loss (0dB)




Output Return Loss (1dB)




Output Return Loss (2dB)



Output Return Loss (4dB)



Output Return Loss (8dB)



Output Return Loss (16dB)

