

*Typical Performance Data*

Control Voltage: 0V/-5V										
RF FREQ (MHz)	INSERTION LOSS*		ISOLATION*				VSWR*			
	(dB)		(dB)				(:1)			
	RF IN-RF OUT1	RF IN-RF OUT2	RF IN-RF OUT1	RF IN-RF OUT2	RF OUT1-RFOUT2	RF OUT1-RFOUT2	RF IN	RF IN	RF OUT1	RF OUT2
	RF OUT1 ON	RF OUT2 ON	RF OUT2 ON	RF OUT1 ON	RF OUT1 ON	RF OUT2 ON	RF OUT1 ON	RF OUT2 ON	RF OUT1 ON	RF OUT2 ON
0.3	0.52	0.52	95.48	81.93	86.02	93.30	1.10	1.11	1.11	1.11
0.5	0.53	0.53	93.50	96.98	96.30	91.99	1.10	1.11	1.10	1.10
1.0	0.52	0.53	105.84	97.26	96.68	97.90	1.10	1.10	1.10	1.10
2.0	0.51	0.52	101.67	87.07	90.87	90.04	1.10	1.10	1.10	1.10
4.0	0.51	0.52	97.05	83.22	85.19	99.29	1.09	1.10	1.10	1.10
6.0	0.52	0.53	94.91	81.38	81.93	95.21	1.09	1.09	1.10	1.09
8.0	0.52	0.53	96.45	78.15	80.53	90.19	1.09	1.09	1.09	1.09
10.0	0.53	0.54	93.59	79.27	79.61	95.56	1.09	1.09	1.09	1.09
20.0	0.54	0.55	97.15	72.12	73.11	83.11	1.08	1.08	1.08	1.08
40.0	0.54	0.55	86.74	65.62	68.68	74.42	1.07	1.08	1.08	1.08
60.0	0.55	0.56	76.78	63.45	63.80	77.41	1.07	1.07	1.08	1.08
80.0	0.55	0.57	73.08	61.19	61.30	77.00	1.07	1.07	1.08	1.07
100.0	0.56	0.57	71.49	59.31	59.31	73.94	1.07	1.07	1.08	1.07
200.0	0.57	0.57	63.48	53.23	53.10	64.89	1.07	1.07	1.07	1.07
300.0	0.57	0.57	57.82	49.47	49.25	58.85	1.07	1.06	1.07	1.07
400.0	0.57	0.57	53.43	46.44	46.44	53.61	1.07	1.06	1.07	1.07
500.0	0.58	0.58	49.82	44.05	43.87	50.36	1.07	1.06	1.07	1.06
600.0	0.58	0.57	46.77	41.90	41.82	47.22	1.07	1.06	1.07	1.06
700.0	0.58	0.57	44.21	39.98	39.93	44.58	1.07	1.05	1.07	1.06
800.0	0.58	0.58	41.94	38.20	38.18	42.30	1.07	1.05	1.07	1.07
900.0	0.58	0.58	39.92	36.54	36.60	40.21	1.06	1.05	1.07	1.08
1000.0	0.59	0.59	38.14	35.06	35.13	38.40	1.06	1.04	1.08	1.09
1100.0	0.59	0.59	36.48	33.66	33.71	36.75	1.05	1.04	1.08	1.10
1200.0	0.59	0.60	34.98	32.36	32.37	35.21	1.04	1.05	1.09	1.10
1300.0	0.60	0.61	33.58	31.14	31.11	33.81	1.04	1.05	1.09	1.11
1400.0	0.61	0.62	32.26	29.98	29.93	32.49	1.04	1.05	1.09	1.11
1500.0	0.63	0.64	31.10	28.91	28.59	31.14	1.03	1.05	1.09	1.11
1600.0	0.66	0.65	30.09	28.12	27.78	29.80	1.03	1.06	1.08	1.11
1700.0	0.72	0.69	29.12	27.92	27.10	28.17	1.03	1.06	1.08	1.12
1800.0	0.70	0.72	25.49	24.70	26.69	29.05	1.04	1.06	1.07	1.12
1900.0	0.66	0.67	24.59	22.96	24.52	26.48	1.06	1.10	1.06	1.12
2000.0	0.64	0.65	25.38	23.40	24.07	25.43	1.06	1.12	1.07	1.13

\*Note:

CONTROL LOGIC			
Control Ports		RF Outputs	
1	2	1	2
0	-5V	Off	On
-5V	0	On	Off



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

**IF/RF MICROWAVE COMPONENTS**

*Typical Performance Data*

Control Voltage: 0V/-8V										
RF FREQ (MHz)	INSERTION LOSS*		ISOLATION*				VSWR*			
	(dB)		(dB)				(:1)			
	RF IN-RF OUT1	RF IN-RF OUT2	RF IN-RF OUT1	RF IN-RF OUT2	RF OUT1-RFOUT2	RF OUT1-RFOUT2	RF IN	RF IN	RF OUT1	RF OUT2
	RF OUT1 ON	RF OUT2 ON	RF OUT2 ON	RF OUT1 ON	RF OUT1 ON	RF OUT2 ON	RF OUT1 ON	RF OUT2 ON	RF OUT1 ON	RF OUT2 ON
0.3	0.51	0.51	95.40	105.54	89.64	89.08	1.10	1.10	1.10	1.10
0.5	0.52	0.52	94.63	103.91	97.58	97.84	1.10	1.10	1.10	1.10
1.0	0.51	0.52	102.70	92.24	90.34	99.32	1.09	1.10	1.10	1.09
2.0	0.51	0.51	104.71	87.07	87.58	103.27	1.09	1.09	1.10	1.09
4.0	0.51	0.51	94.84	81.94	83.44	97.72	1.09	1.09	1.09	1.09
6.0	0.51	0.52	94.84	80.61	80.79	93.61	1.08	1.09	1.09	1.09
8.0	0.51	0.52	94.08	77.54	79.83	88.22	1.08	1.08	1.09	1.09
10.0	0.52	0.53	89.72	76.32	78.21	101.29	1.08	1.08	1.09	1.09
20.0	0.53	0.54	94.25	71.90	72.61	82.50	1.08	1.08	1.08	1.08
40.0	0.53	0.54	87.03	65.49	68.56	74.53	1.07	1.08	1.08	1.08
60.0	0.54	0.55	76.80	63.29	63.67	76.71	1.07	1.07	1.08	1.07
80.0	0.54	0.56	73.40	61.03	61.09	77.25	1.07	1.07	1.08	1.07
100.0	0.55	0.56	71.10	59.20	59.18	74.62	1.07	1.07	1.08	1.07
200.0	0.56	0.56	63.57	53.14	52.93	65.45	1.07	1.07	1.07	1.07
300.0	0.56	0.57	57.98	49.41	49.16	59.34	1.07	1.06	1.07	1.07
400.0	0.56	0.56	53.69	46.41	46.35	53.93	1.07	1.06	1.07	1.07
500.0	0.57	0.57	50.06	44.07	43.85	50.72	1.07	1.06	1.07	1.06
600.0	0.57	0.56	47.02	41.97	41.79	47.57	1.07	1.06	1.07	1.06
700.0	0.57	0.56	44.46	40.08	39.94	44.94	1.07	1.05	1.07	1.06
800.0	0.57	0.57	42.21	38.34	38.22	42.64	1.07	1.05	1.07	1.07
900.0	0.57	0.57	40.19	36.71	36.67	40.56	1.06	1.05	1.08	1.08
1000.0	0.58	0.58	38.42	35.25	35.23	38.75	1.06	1.04	1.08	1.08
1100.0	0.58	0.58	36.76	33.86	33.83	37.09	1.05	1.04	1.09	1.09
1200.0	0.58	0.59	35.25	32.58	32.51	35.56	1.05	1.04	1.09	1.10
1300.0	0.59	0.60	33.85	31.37	31.26	34.15	1.04	1.03	1.09	1.10
1400.0	0.60	0.61	32.53	30.21	30.04	32.83	1.04	1.04	1.09	1.10
1500.0	0.61	0.63	31.39	29.16	28.75	31.49	1.03	1.03	1.09	1.10
1600.0	0.64	0.64	30.35	28.37	27.91	30.09	1.03	1.04	1.09	1.10
1700.0	0.71	0.67	29.40	28.30	27.30	28.54	1.04	1.04	1.08	1.10
1800.0	0.69	0.70	25.66	24.95	26.88	29.31	1.04	1.04	1.06	1.10
1900.0	0.64	0.65	24.81	23.19	24.66	26.77	1.04	1.07	1.06	1.09
2000.0	0.63	0.63	25.59	23.61	24.24	25.69	1.04	1.09	1.07	1.10

\*Note:

CONTROL LOGIC			
Control Ports		RF Outputs	
1	2	1	2
0	-8V	Off	On
-8V	0	On	Off



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

**IF/RF MICROWAVE COMPONENTS**