


Outline Dimensions



| CASE# | A | B | C | D | E | F | G | H | J | K | L | M |
|--------|-----------------|-----------------|----------------|----------------|----------------|----------------|----------------|----------------|-----------------|-----------------|----------------|----------------|
| KS1509 | .625 (15.88) | .880 (22.35) | .225 (5.71) | .160 (4.06) | .120 (3.05) | .077 (1.96) | .070 (1.78) | .160 (4.06) | .665 (16.89) | .920 (23.37) | .100 (2.54) | .140 (3.56) |

| CASE# | N | P | Q | R | S | T | U | V | WT, GRAMS |
|--------|----------------|----------------|----------------|----------------|-----------------|----------------|----------------|----------------|-----------|
| KS1509 | .305 (7.75) | .180 (4.57) | .205 (5.21) | .115 (2.92) | .620 (15.75) | .365 (9.27) | .110 (2.79) | .180 (4.57) | 4.4 |

Dimensions are in inches (mm). Tolerances: 2PL. $\pm .03$; 3PL. $\pm .015$