

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMP-FEMALE RETURN LOSS (dB)	SMA-MALE RETURN LOSS (dB)
100	0.12	32.5	32.1
200	0.18	29.7	29.4
300	0.21	35.0	34.8
400	0.24	39.7	39.4
500	0.27	29.6	29.5
600	0.31	29.3	29.3
700	0.33	37.4	37.7
800	0.35	36.0	36.0
900	0.38	30.6	30.6
1000	0.40	33.9	34.1
1100	0.41	39.1	39.0
1200	0.43	30.0	30.1
1300	0.45	29.8	30.0
1400	0.47	41.1	42.4
1500	0.49	32.3	32.1
1600	0.53	27.1	27.0
1800	0.54	43.4	44.6
2000	0.59	28.0	28.0
2500	0.63	36.2	36.2
3000	0.69	29.1	30.4
3500	0.75	26.2	26.6
4000	0.81	30.9	32.0
4500	0.86	26.3	28.3
5000	0.93	27.1	27.3
5500	0.99	26.2	28.3
6000	1.01	27.0	29.5
6500	1.07	26.7	28.0
7000	1.13	29.0	32.8
7500	1.16	25.9	29.7
8000	1.21	26.2	28.6
8500	1.25	27.0	31.4
9000	1.28	29.6	41.4
9500	1.31	29.1	31.2
10000	1.37	26.3	26.2
10500	1.39	35.6	29.1
11000	1.41	31.1	32.3
11500	1.54	25.9	31.4
12000	1.45	31.0	30.3
12500	1.63	25.5	34.3
13000	1.44	28.1	28.1
13500	1.65	32.5	33.4
14000	1.70	25.0	30.7
14500	1.58	18.7	19.7
15000	1.82	21.9	22.6
15500	1.87	27.7	24.0
16000	1.85	22.5	23.8
16500	1.84	25.1	29.5
17000	1.81	24.6	29.5
17500	1.83	26.5	32.6
18000	1.64	19.7	26.1