

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMP-FEMALE 1 RETURN LOSS (dB)	SMP-FEMALE 2 RETURN LOSS (dB)
100	0.06	35.1	34.6
200	0.09	29.5	29.0
300	0.11	27.3	26.8
400	0.14	27.1	26.6
500	0.14	28.8	28.2
600	0.16	33.5	32.9
700	0.17	57.2	50.7
800	0.18	34.2	34.2
900	0.20	28.6	28.4
1000	0.21	26.3	26.1
1100	0.23	25.8	25.5
1200	0.25	26.7	26.4
1300	0.24	29.4	29.0
1400	0.24	35.0	34.3
1500	0.25	40.5	39.9
1600	0.26	33.7	33.6
1800	0.29	29.4	28.9
2000	0.31	32.8	31.0
2500	0.35	26.9	26.6
3000	0.37	31.2	29.7
3500	0.36	28.4	25.7
4000	0.42	31.4	29.7
4500	0.45	34.2	30.1
5000	0.48	25.6	22.4
5500	0.49	27.6	28.4
6000	0.52	33.2	31.6
6500	0.55	27.8	25.5
7000	0.56	29.9	29.5
7500	0.58	35.9	34.6
8000	0.60	28.3	31.5
8500	0.61	36.1	35.7
9000	0.64	60.7	31.3
9500	0.67	26.9	40.9
10000	0.65	29.1	26.3
10500	0.64	26.2	42.0
11000	0.66	33.2	23.6
11500	0.70	25.1	24.8
12000	0.66	22.7	26.7
12500	0.80	29.1	23.5
13000	0.75	22.2	22.1
13500	0.86	22.0	26.8
14000	0.84	30.8	30.4
14500	0.68	22.1	22.3
15000	0.89	23.5	24.9
15500	0.92	32.4	26.9
16000	0.90	30.1	31.1
16500	0.90	36.5	26.2
17000	0.86	24.1	23.0
17500	0.80	24.2	23.7
18000	0.57	22.9	25.0