

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.05	41.6	42.0
200.0	0.05	41.6	42.0
300.0	0.07	44.1	44.2
400.0	0.07	44.1	44.2
500.0	0.09	44.5	45.1
600.0	0.09	44.5	45.1
700.0	0.11	45.6	49.7
800.0	0.11	45.6	49.7
900.0	0.13	44.4	48.7
1000.0	0.13	44.4	48.7
1100.0	0.14	43.5	47.7
1250.0	0.14	43.5	47.7
1500.0	0.17	42.1	44.2
1750.0	0.18	41.2	43.3
2000.0	0.19	40.1	41.8
2250.0	0.20	38.7	40.5
2500.0	0.23	37.2	38.0
2750.0	0.23	36.7	37.6
3000.0	0.24	36.5	37.0
3250.0	0.25	36.0	36.1
3500.0	0.27	35.8	35.7
3750.0	0.28	35.4	34.8
4000.0	0.28	34.6	34.2
4250.0	0.29	35.3	34.2
4500.0	0.30	35.3	33.9
5000.0	0.32	36.0	33.6
5500.0	0.33	36.3	32.4
6000.0	0.34	38.0	34.5
6500.0	0.36	38.6	35.1
7000.0	0.37	39.9	34.1
7500.0	0.39	34.4	32.5
8000.0	0.40	37.5	36.4
8500.0	0.41	38.0	35.4
9000.0	0.42	36.1	33.4
9500.0	0.44	35.2	33.6
10000.0	0.44	34.3	34.9
10500.0	0.46	36.1	40.2
11000.0	0.47	29.7	30.9
11500.0	0.49	27.1	28.5
12000.0	0.50	27.6	28.9
12500.0	0.52	26.2	27.2
13000.0	0.53	24.8	29.2
13500.0	0.56	22.9	24.1
14000.0	0.56	24.1	25.0
14500.0	0.58	23.1	24.3
15000.0	0.59	23.0	25.5
15500.0	0.60	24.6	24.9
16000.0	0.62	23.2	23.6
16500.0	0.63	22.4	25.9
17000.0	0.63	22.7	24.3
17500.0	0.64	23.6	24.1
18100.0	0.66	22.7	24.6