

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	SMA-FEMALE BULKHEAD RETURN LOSS (dB)
100.0	0.05	39.4	38.1
500.0	0.13	44.0	41.9
1000.0	0.18	42.4	39.8
1100.0	0.19	38.5	35.6
1200.0	0.21	36.6	35.8
1300.0	0.21	37.3	39.8
1400.0	0.22	41.6	55.1
1500.0	0.23	42.3	40.3
1600.0	0.23	37.0	36.4
1700.0	0.25	35.3	36.9
1800.0	0.25	37.6	41.8
1900.0	0.26	43.9	52.6
2000.0	0.27	39.5	39.0
2400.0	0.29	42.7	48.2
3000.0	0.33	34.2	35.2
4000.0	0.39	30.9	32.1
5000.0	0.45	30.0	30.3
5500.0	0.47	28.3	28.8
6000.0	0.50	25.8	26.0
6500.0	0.52	26.5	26.8
7000.0	0.53	26.9	27.0
7500.0	0.56	25.9	26.1
8000.0	0.57	26.2	26.2
8500.0	0.59	25.5	25.0
9000.0	0.61	25.2	24.9
9500.0	0.62	28.0	26.9
10000.0	0.63	29.2	28.9
10500.0	0.64	31.5	31.3
11000.0	0.66	36.6	41.3
11500.0	0.68	30.0	40.0
12000.0	0.73	32.0	48.5
12500.0	0.69	33.4	34.4
13000.0	0.77	29.1	39.0
13500.0	0.74	32.2	32.0
14000.0	0.80	28.1	30.3
14500.0	0.87	24.4	24.7
15000.0	0.88	27.8	28.2
15500.0	0.90	26.1	24.8
16000.0	0.91	23.1	23.2
16500.0	0.93	24.3	22.5
17000.0	0.92	24.0	22.0
17500.0	0.95	23.3	20.8
18000.0	0.96	26.0	23.1