

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-FEMALE BULKHEAD RETURN LOSS (dB)
100.0	0.07	39.2	41.1
200.0	0.10	56.7	52.8
400.0	0.15	43.0	47.4
600.0	0.19	42.0	44.4
800.0	0.22	37.6	41.1
900.0	0.24	39.3	37.3
1000.0	0.25	34.9	36.2
1200.0	0.28	32.7	33.1
1400.0	0.30	33.1	32.7
1600.0	0.33	33.9	32.5
1800.0	0.35	36.4	34.3
2000.0	0.37	40.7	36.8
2200.0	0.38	46.7	39.9
2400.0	0.40	54.0	42.5
2600.0	0.42	44.7	48.0
2800.0	0.44	42.1	41.6
3000.0	0.45	41.2	38.5
3200.0	0.47	42.2	36.5
3400.0	0.49	40.0	35.1
3600.0	0.50	35.7	34.8
3800.0	0.52	30.9	31.5
4000.0	0.54	33.0	32.9
4200.0	0.56	29.5	29.9
4400.0	0.57	27.4	27.5
4600.0	0.59	28.9	28.5
4800.0	0.60	30.5	29.5
5000.0	0.61	30.3	28.7
5500.0	0.65	26.1	25.4
6000.0	0.70	23.5	23.5
6500.0	0.74	22.7	21.7
7000.0	0.76	24.7	22.4
7500.0	0.80	23.2	21.7
8000.0	0.82	24.3	23.2
8500.0	0.85	23.7	22.1
9000.0	0.89	24.9	22.6
9500.0	0.90	26.7	26.5
10000.0	0.93	30.5	32.1
10500.0	0.95	32.1	30.6
11000.0	1.03	29.4	31.3
11500.0	1.07	25.7	24.5
12000.0	1.10	26.9	24.3
12500.0	1.13	22.0	20.9