

*Typical Performance Data*

V <sub>DS</sub> (V)	I <sub>DS</sub> (mA)					
	V <sub>GS</sub> = 0.7V	V <sub>GS</sub> = 0.6V	V <sub>GS</sub> = 0.5V	V <sub>GS</sub> = 0.4V	V <sub>GS</sub> = 0.3V	V <sub>GS</sub> = 0.2V
0.0	0.09	0.10	0.08	0.08	0.04	0.01
0.1	23.61	21.95	18.97	12.61	3.65	0.27
0.2	46.35	42.39	34.57	18.82	4.15	0.29
0.3	68.02	60.56	45.11	20.58	4.34	0.30
0.4	88.05	75.24	50.24	21.37	4.50	0.33
0.5	105.70	85.18	52.30	21.90	4.65	0.34
0.6	120.00	90.38	53.38	22.33	4.85	0.34
0.7		92.66	54.18	22.76	4.99	0.36
0.8		93.88	54.89	23.24	5.13	0.38
0.9		94.80	55.49	23.62	5.25	0.40
1.0		95.53	56.03	23.97	5.38	0.42
1.1		96.14	56.51	24.29	5.51	0.43
1.2		96.68	56.97	24.61	5.63	0.45
1.3		97.18	57.39	24.91	5.75	0.45
1.4		97.65	57.82	25.22	5.86	0.47
1.5		98.08	58.21	25.50	5.98	0.48
1.6		98.49	58.60	25.77	6.10	0.52
1.7		98.89	58.97	26.04	6.21	0.53
1.8		99.30	59.33	26.32	6.32	0.55
1.9		99.68	59.70	26.58	6.45	0.57
2.0		100.07	60.08	26.87	6.55	0.55
2.1		100.48	60.50	27.17	6.69	0.58
2.2		100.97	60.97	27.51	6.82	0.60
2.3		101.50	61.47	27.89	6.99	0.63
2.4		102.12	62.05	28.29	7.17	0.64
2.5		102.78	62.68	28.74	7.34	0.67
2.6		103.50	63.32	29.19	7.52	0.70
2.7		104.22	63.99	29.65	7.69	0.71
2.8		104.94	64.64	30.15	7.90	0.73
2.9		105.64	65.31	30.62	8.10	0.76
3.0		106.33	65.99	31.13	8.34	0.82
3.1		107.02	66.65	31.63	8.56	0.84
3.2		107.70	67.32	32.17	8.79	0.87
3.3		108.37	68.02	32.72	9.03	0.90
3.4		109.02	68.69	33.28	9.30	0.92
3.5		109.67	69.41	33.87	9.58	0.95
3.6		110.34	70.12	34.46	9.89	1.01
3.7		111.00	70.81	35.06	10.20	1.06
3.8		111.64	71.53	35.67	10.53	1.10
3.9		112.30	72.24	36.29	10.86	1.14
4.0		112.96	72.93	36.89	11.21	1.14
4.1		113.60	73.65	37.51	11.55	1.30
4.2		114.25	74.35	38.13	11.90	1.37
4.3		114.88	75.03	38.74	12.26	1.45
4.4		115.53	75.76	39.36	12.63	1.54
4.5		116.18	76.47	39.99	13.00	1.62
4.6		116.80	77.15	40.62	13.38	1.69
4.7		117.44	77.86	41.23	13.76	1.78
4.8		118.06	78.56	41.86	14.14	1.90
4.9		118.67	79.26	42.50	14.53	1.98
5.0		119.30	79.96	43.13	14.94	2.07

*Typical Performance Data*

FREQ (MHz)	GAIN vs. FREQ & TEMPERATURE <sup>(1)</sup> @ V <sub>DS</sub> =+3V, I <sub>DS</sub> =60mA			NOISE FIGURE vs. FREQ & TEMPERATURE <sup>(1)</sup> @ V <sub>DS</sub> =+3V, I <sub>DS</sub> =60mA			OUTPUT RETURN LOSS vs. FREQ & TEMPERATURE <sup>(1)</sup> @ V <sub>DS</sub> =+3V, I <sub>DS</sub> =60mA		
	dB			dB			dB		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
70	29.2	29.2	28.9	0.4	0.6	0.8	6.2	6.0	5.8
80	29.2	29.2	28.9	0.3	0.5	0.7	6.2	6.0	5.8
90	29.2	29.2	28.9	0.2	0.5	0.6	6.2	6.1	5.9
100	29.1	29.1	28.9	0.3	0.5	0.6	6.2	6.1	5.9
200	28.8	28.8	28.5	0.3	0.5	0.6	6.4	6.4	6.2
300	28.4	28.3	28.0	0.4	0.5	0.6	6.8	6.8	6.7
400	27.8	27.7	27.4	0.5	0.5	0.7	7.3	7.3	7.1
500	27.1	27.0	26.7	0.3	0.5	0.5	7.8	7.9	7.7
600	26.5	26.3	26.0	0.3	0.5	0.5	8.2	8.4	8.2
700	25.7	25.6	25.2	0.3	0.6	0.5	8.7	8.9	8.8
800	25.1	24.9	24.6	0.2	0.4	0.5	9.1	9.3	9.3
900	24.4	24.2	23.9	0.2	0.4	0.4	9.4	9.8	9.8
1000	23.8	23.6	23.2	0.2	0.5	0.4	9.8	10.2	10.2
1100	23.2	23.0	22.6	0.2	0.4	0.4	10.2	10.6	10.7
1200	22.6	22.4	22.1	0.2	0.4	0.5	10.5	11.0	11.1
1300	22.1	21.8	21.5	0.2	0.4	0.4	10.8	11.3	11.5
1400	21.6	21.3	21.0	0.1	0.4	0.4	11.1	11.6	11.8
1500	21.1	20.8	20.5	0.2	0.4	0.5	11.4	11.9	12.1
1600	20.6	20.3	20.0	0.2	0.4	0.5	11.7	12.2	12.3
1700	20.1	19.8	19.6	0.2	0.5	0.5	11.9	12.5	12.6
1800	19.7	19.4	19.1	0.2	0.5	0.5	12.1	12.7	12.8
1900	19.3	19.0	18.7	0.2	0.6	0.5	12.3	12.9	13.1
2000	18.9	18.6	18.3	0.2	0.6	0.5	12.4	13.1	13.3
2100	18.5	18.2	18.0	0.1	0.5	0.5	12.6	13.3	13.5
2200	18.2	17.9	17.6	0.2	0.5	0.6	12.8	13.4	13.7
2300	17.9	17.5	17.3	0.2	0.6	0.5	13.0	13.6	13.8
2400	17.5	17.2	17.0	0.2	0.5	0.6	13.0	13.7	14.0
2500	17.2	16.9	16.6	0.3	0.6	0.6	13.0	13.9	14.2
2600	16.9	16.6	16.3	0.4	0.5	0.7	13.1	14.0	14.3
2700	16.6	16.3	16.0	0.2	0.7	0.6	13.1	14.1	14.4
2800	16.3	16.0	15.8	0.2	0.7	0.6	13.2	14.2	14.5
2900	16.1	15.7	15.5	0.3	0.7	0.7	13.3	14.2	14.6
3000	15.8	15.4	15.2	0.2	0.6	0.6	13.4	14.2	14.7
3100	15.6	15.2	15.0	0.4	0.8	0.8	13.4	14.3	14.7
3200	15.3	14.9	14.7	0.4	0.8	0.9	13.5	14.3	14.8
3300	15.1	14.7	14.5	0.4	0.7	0.9	13.6	14.4	14.8
3400	14.8	14.4	14.2	0.4	0.8	0.9	13.6	14.5	14.9
3500	14.6	14.2	14.0	0.4	0.8	0.9	13.7	14.5	15.0
3600	14.4	14.0	13.8	0.4	0.9	0.9	13.7	14.5	15.0
3700	14.2	13.7	13.6	0.4	0.8	0.9	13.7	14.5	15.0
3800	13.9	13.5	13.3	0.4	0.9	1.0	13.6	14.5	15.0
3900	13.7	13.3	13.1	0.4	1.0	1.0	13.6	14.5	15.0
4000	13.5	13.1	12.9	0.5	1.0	1.1	13.5	14.4	15.0
4100	13.3	12.9	12.7	0.5	1.0	1.1	13.4	14.3	14.9
4200	13.1	12.7	12.5	0.5	0.9	1.1	13.3	14.2	14.9
4300	12.9	12.4	12.2	0.5	1.0	1.1	13.2	14.1	14.8
4400	12.7	12.2	12.0	0.6	1.1	1.2	13.1	14.0	14.7
4500	12.5	12.0	11.8	0.5	1.1	1.2	12.9	13.8	14.5
4600	12.3	11.8	11.6	0.6	1.1	1.2	12.8	13.7	14.4
4700	12.0	11.6	11.4	0.6	1.1	1.2	12.6	13.5	14.2
4800	11.8	11.4	11.2	0.6	1.3	1.3	12.3	13.3	14.0
4900	11.6	11.2	11.0	0.6	1.2	1.3	12.1	13.1	13.8
5000	11.4	11.0	10.7	0.6	1.1	1.4	11.9	12.9	13.5
5100	11.2	10.8	10.5	0.7	1.3	1.4	11.8	12.6	13.3
5200	10.9	10.6	10.3	0.7	1.5	1.5	11.6	12.4	13.1
5300	10.7	10.4	10.1	0.8	1.3	1.5	11.4	12.3	12.9
5400	10.5	10.2	9.9	0.8	1.5	1.6	11.2	12.1	12.7
5500	10.3	10.0	9.7	0.8	1.3	1.6	11.1	12.0	12.6
5600	10.1	9.8	9.5	0.9	1.3	1.6	11.0	11.8	12.4
5700	9.9	9.6	9.3	0.9	1.5	1.7	10.9	11.7	12.2
5800	9.7	9.4	9.1	0.9	1.4	1.8	10.6	11.6	12.1
5900	9.5	9.2	8.9	1.0	1.5	1.9	10.5	11.4	11.8
6000	9.3	9.0	8.7	1.0	1.5	1.9	10.4	11.2	11.6

(1) Includes test board loss

*Typical Performance Data*

FREQ (MHz)	OIP3 vs FREQ & TEMPERATURE <sup>(1)</sup> @ V <sub>DS</sub> =+3V, I <sub>DS</sub> =60mA			P1dB vs FREQ & TEMPERATURE <sup>(1,2)</sup> @ V <sub>DS</sub> =+3V, I <sub>DS</sub> =60mA		
	dBm			dBm		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
70	32.8	31.6	30.5	17.2	17.8	17.8
80	32.7	33.6	30.6	17.4	17.7	17.9
90	32.7	32.1	30.5	17.5	18.0	18.0
100	32.4	32.0	30.6	17.3	18.1	17.8
200	31.7	32.6	31.0	17.4	17.8	17.8
300	31.1	32.0	30.9	17.8	17.7	18.1
400	31.3	32.6	31.5	17.7	18.0	18.0
500	31.0	32.4	31.7	17.4	17.6	17.7
600	31.2	32.3	32.0	17.8	17.9	18.1
700	30.7	32.2	32.2	17.8	18.0	18.0
800	31.1	31.4	32.5	17.8	18.1	18.1
900	30.6	31.6	32.4	18.0	18.1	18.3
1000	31.6	32.2	32.8	18.1	18.3	18.5
1100	30.6	32.2	33.0	18.1	18.1	18.5
1200	31.2	31.5	33.2	18.1	18.0	18.4
1300	31.9	31.1	33.6	17.9	18.1	18.3
1400	31.4	31.8	33.7	18.0	18.2	18.4
1500	31.4	31.9	34.0	18.1	18.0	18.5
1600	31.3	32.7	34.2	17.9	18.4	18.4
1700	30.4	31.0	34.0	17.7	18.0	18.1
1800	31.4	32.1	34.7	18.2	18.4	18.6
1900	32.1	32.8	34.4	18.1	18.2	18.6
2000	31.9	31.1	34.6	18.1	18.3	18.6
2100	32.3	32.3	34.9	18.1	18.5	18.5
2200	31.5	32.7	34.9	18.1	18.3	18.6
2300	32.7	31.4	35.1	18.0	18.3	18.4
2400	33.1	32.5	35.0	17.7	18.7	18.1
2500	31.7	31.8	35.3	18.2	18.3	18.6
2600	32.6	32.0	35.5	18.3	18.5	18.8
2700	32.0	30.6	35.7	18.1	18.4	18.5
2800	31.4	31.6	35.9	18.0	18.4	18.4
2900	31.7	32.4	35.5	17.9	18.5	18.4
3000	32.5	32.1	35.7	18.1	18.4	18.6
3100	32.8	32.4	35.8	18.0	18.4	18.6
3200	32.7	32.7	35.8	18.4	18.4	19.0
3300	31.9	32.7	36.0	17.9	18.6	18.5
3400	32.9	32.6	35.9	17.9	18.6	18.3
3500	32.2	32.5	36.1	18.2	18.6	18.7
3600	31.2	31.9	35.7	18.2	18.7	18.7
3700	31.0	32.1	36.3	18.3	18.4	18.9
3800	31.4	31.9	36.3	18.2	18.4	18.8
3900	32.3	32.3	36.7	18.1	18.4	18.7
4000	30.4	31.6	36.6	17.8	18.1	18.4
4100	31.9	32.8	36.6	18.0	18.6	18.6
4200	32.6	31.8	36.8	18.1	18.3	18.8
4300	29.9	32.2	36.1	17.9	18.4	18.6
4400	31.6	31.9	37.0	18.0	18.5	18.8
4500	31.6	31.5	36.8	17.9	18.1	18.6
4600	30.3	32.1	36.2	17.8	18.5	18.6
4700	31.9	32.0	37.1	17.9	18.5	18.6
4800	29.9	31.4	35.4	18.0	18.2	18.8
4900	30.0	31.6	35.5	18.0	18.5	18.8
5000	31.4	32.6	36.5	17.8	18.5	18.5
5100	30.6	31.7	36.9	17.9	18.3	18.5
5200	31.6	31.7	37.5	17.7	18.2	18.4
5300	31.8	31.9	37.8	17.8	18.2	18.5
5400	30.1	31.8	36.4	17.8	18.0	18.5
5500	30.8	30.7	34.6	18.1	17.8	18.9
5600	31.3	31.3	36.9	17.7	18.1	18.3
5700	30.4	32.1	35.5	17.6	18.1	18.2
5800	31.7	31.6	36.9	17.7	18.1	18.4
5900	30.5	31.1	36.5	17.6	18.3	18.2
6000	30.8	31.8	35.9	17.6	18.2	18.2

(1) Includes test board loss

(2) Drain current was allowed to increase during compression measurement

*Typical Performance Data*

FREQ (MHz)	GAIN vs. FREQ & TEMPERATURE <sup>(1)</sup> @ V <sub>DS</sub> =+4V, I <sub>DS</sub> =60mA			NOISE FIGURE vs. FREQ & TEMPERATURE <sup>(1)</sup> @ V <sub>DS</sub> =+4V, I <sub>DS</sub> =60mA			OUTPUT RETURN LOSS vs. FREQ & TEMPERATURE <sup>(1)</sup> @ V <sub>DS</sub> =+4V, I <sub>DS</sub> =60mA		
	dB			dB			dB		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
70	29.3	29.2	29.0	0.5	0.6	0.8	5.8	5.5	5.3
80	29.3	29.2	29.0	0.4	0.5	0.7	5.8	5.5	5.3
90	29.3	29.2	29.0	0.3	0.6	0.6	5.8	5.6	5.3
100	29.3	29.2	29.0	0.4	0.5	0.6	5.9	5.6	5.4
200	28.9	28.8	28.6	0.3	0.5	0.6	6.1	6.0	5.8
300	28.5	28.3	28.0	0.4	0.5	0.6	6.6	6.5	6.3
400	27.9	27.6	27.4	0.5	0.5	0.7	7.1	7.0	6.8
500	27.2	26.9	26.7	0.3	0.6	0.5	7.7	7.6	7.3
600	26.5	26.2	26.0	0.3	0.6	0.5	8.2	8.2	8.0
700	25.8	25.5	25.3	0.3	0.6	0.6	8.7	8.7	8.6
800	25.1	24.8	24.6	0.3	0.5	0.5	9.1	9.2	9.1
900	24.4	24.1	23.9	0.2	0.5	0.4	9.5	9.7	9.7
1000	23.8	23.5	23.3	0.2	0.5	0.5	10.0	10.2	10.1
1100	23.2	22.9	22.6	0.2	0.4	0.5	10.4	10.7	10.6
1200	22.6	22.3	22.1	0.2	0.4	0.5	10.8	11.1	11.1
1300	22.1	21.7	21.5	0.2	0.5	0.4	11.1	11.5	11.5
1400	21.6	21.2	21.0	0.2	0.5	0.5	11.4	11.8	11.9
1500	21.1	20.7	20.5	0.2	0.4	0.5	11.8	12.1	12.2
1600	20.6	20.2	20.0	0.2	0.5	0.5	12.1	12.5	12.5
1700	20.1	19.8	19.6	0.2	0.5	0.5	12.4	12.8	12.8
1800	19.7	19.4	19.1	0.2	0.5	0.5	12.6	13.0	13.1
1900	19.3	18.9	18.7	0.2	0.6	0.5	12.8	13.3	13.4
2000	18.9	18.6	18.3	0.2	0.6	0.5	12.9	13.5	13.6
2100	18.5	18.2	18.0	0.2	0.6	0.5	13.2	13.8	13.9
2200	18.2	17.8	17.6	0.2	0.6	0.6	13.4	13.9	14.1
2300	17.8	17.5	17.3	0.2	0.7	0.6	13.6	14.1	14.3
2400	17.5	17.2	16.9	0.2	0.6	0.7	13.7	14.3	14.4
2500	17.2	16.9	16.6	0.2	0.7	0.7	13.7	14.5	14.7
2600	16.9	16.6	16.3	0.3	0.6	0.7	13.7	14.6	14.8
2700	16.6	16.3	16.0	0.2	0.7	0.6	13.8	14.7	15.0
2800	16.3	16.0	15.8	0.2	0.7	0.6	13.9	14.8	15.1
2900	16.1	15.7	15.5	0.3	0.7	0.7	14.0	14.8	15.2
3000	15.8	15.4	15.2	0.2	0.6	0.7	14.1	14.9	15.3
3100	15.6	15.2	15.0	0.4	0.8	0.9	14.2	15.0	15.3
3200	15.3	14.9	14.7	0.4	0.8	0.9	14.3	15.1	15.4
3300	15.1	14.7	14.5	0.4	0.8	0.9	14.4	15.1	15.5
3400	14.8	14.5	14.2	0.4	0.9	0.9	14.5	15.2	15.6
3500	14.6	14.2	14.0	0.4	0.8	0.9	14.5	15.3	15.7
3600	14.4	14.0	13.8	0.4	0.9	0.9	14.5	15.3	15.7
3700	14.1	13.8	13.5	0.4	0.9	1.0	14.5	15.4	15.8
3800	13.9	13.5	13.3	0.4	0.9	1.0	14.5	15.3	15.8
3900	13.7	13.3	13.1	0.4	1.0	1.0	14.4	15.3	15.8
4000	13.5	13.1	12.9	0.5	1.0	1.1	14.4	15.3	15.8
4100	13.3	12.9	12.7	0.5	1.0	1.1	14.3	15.2	15.8
4200	13.1	12.7	12.5	0.5	1.0	1.1	14.2	15.2	15.8
4300	12.9	12.5	12.2	0.5	1.0	1.1	14.1	15.0	15.7
4400	12.7	12.3	12.0	0.5	1.1	1.2	14.0	14.9	15.6
4500	12.4	12.0	11.8	0.5	1.1	1.2	13.8	14.8	15.5
4600	12.2	11.8	11.6	0.6	1.1	1.3	13.6	14.6	15.3
4700	12.0	11.6	11.4	0.6	1.1	1.2	13.4	14.4	15.2
4800	11.8	11.4	11.2	0.6	1.2	1.3	13.2	14.2	15.0
4900	11.6	11.2	10.9	0.6	1.2	1.3	12.9	14.0	14.7
5000	11.4	10.9	10.7	0.6	1.2	1.4	12.7	13.8	14.5
5100	11.1	10.7	10.5	0.7	1.3	1.4	12.6	13.5	14.2
5200	10.9	10.5	10.3	0.7	1.5	1.5	12.4	13.3	14.0
5300	10.7	10.3	10.1	0.8	1.3	1.6	12.1	13.1	13.8
5400	10.5	10.1	9.9	0.8	1.5	1.6	12.0	13.0	13.6
5500	10.3	9.9	9.7	0.8	1.4	1.6	11.9	12.8	13.5
5600	10.1	9.7	9.5	0.8	1.4	1.7	11.7	12.7	13.3
5700	9.9	9.5	9.3	0.9	1.6	1.8	11.6	12.5	13.1
5800	9.7	9.3	9.1	0.9	1.4	1.8	11.4	12.4	12.9
5900	9.5	9.1	8.9	0.9	1.6	1.9	11.2	12.2	12.7
6000	9.3	8.9	8.7	1.0	1.7	1.9	11.1	12.0	12.4

(1) Includes test board loss

*Typical Performance Data*

FREQ (MHz)	OIP3 vs FREQ & TEMPERATURE <sup>(1)</sup> @ V <sub>DS</sub> =+4V, I <sub>DS</sub> =60mA			P1dB vs FREQ & TEMPERATURE <sup>(1,2)</sup> @ V <sub>DS</sub> =+4V, I <sub>DS</sub> =60mA		
	dBm			dBm		
	-45°C	+25°C	+85°C	-45°C	+25°C	+85°C
70	34.0	30.9	30.9	19.2	18.5	19.6
80	34.0	31.6	30.9	19.2	18.5	19.7
90	34.3	31.2	30.9	19.2	18.8	19.7
100	35.2	31.2	31.0	19.1	18.8	19.5
200	35.9	32.1	31.4	19.1	18.7	19.7
300	35.7	31.8	31.4	19.4	18.7	19.9
400	37.3	32.5	31.8	19.4	19.0	20.0
500	36.3	32.6	32.1	19.3	18.7	19.8
600	38.1	32.6	32.4	19.7	19.1	20.2
700	38.2	32.3	32.6	19.7	19.2	20.2
800	38.2	32.3	32.9	19.8	19.2	20.3
900	38.5	32.1	32.8	20.0	19.3	20.5
1000	37.3	32.7	32.9	19.9	19.4	20.5
1100	39.8	32.7	33.7	20.2	19.3	20.7
1200	38.0	32.5	33.7	20.1	19.3	20.7
1300	38.5	32.1	33.8	20.0	19.3	20.5
1400	39.3	32.3	34.1	20.1	19.4	20.6
1500	38.7	32.7	34.8	20.2	19.3	20.8
1600	41.7	33.1	34.4	20.2	19.6	20.7
1700	47.2	32.4	34.9	20.1	19.3	20.5
1800	42.4	34.0	35.1	20.3	19.6	20.8
1900	39.5	33.9	34.4	20.3	19.5	20.9
2000	40.5	32.8	34.7	20.3	19.5	20.8
2100	40.1	33.4	34.9	20.3	19.7	20.8
2200	43.3	33.3	35.3	20.2	19.6	20.8
2300	40.2	33.1	34.9	20.3	19.6	20.8
2400	39.1	33.3	35.1	20.2	19.9	20.6
2500	42.1	32.8	35.1	20.5	19.7	21.0
2600	42.3	33.4	35.5	20.5	19.8	21.0
2700	40.9	33.1	35.5	20.4	19.7	20.9
2800	42.8	32.1	35.6	20.4	19.7	20.9
2900	42.1	34.0	35.4	20.4	19.8	20.8
3000	41.4	34.0	35.6	20.5	19.8	20.9
3100	41.0	33.4	35.7	20.6	19.7	21.0
3200	40.6	34.0	35.4	20.7	19.8	21.2
3300	45.1	34.4	36.0	20.4	20.0	20.9
3400	41.0	34.2	35.7	20.5	19.9	20.8
3500	40.5	33.7	35.6	20.6	19.9	21.1
3600	42.5	33.4	35.8	20.6	20.0	21.1
3700	41.7	33.6	36.0	20.6	19.7	21.2
3800	41.1	32.9	35.8	20.7	19.8	21.2
3900	41.4	33.4	35.9	20.6	19.7	21.1
4000	39.8	32.8	35.9	20.4	19.5	20.9
4100	41.1	33.7	35.9	20.6	19.9	21.0
4200	40.1	33.5	35.8	20.6	19.7	21.1
4300	39.1	33.5	35.7	20.5	19.7	21.0
4400	41.7	33.7	36.1	20.7	19.8	21.1
4500	42.8	33.2	36.4	20.5	19.5	21.0
4600	40.1	33.4	36.3	20.5	19.8	20.9
4700	43.4	33.4	36.7	20.5	19.8	21.0
4800	39.9	33.4	36.3	20.5	19.6	21.1
4900	39.2	33.2	36.6	20.5	19.8	21.1
5000	41.5	34.3	36.6	20.4	19.8	20.9
5100	40.2	33.3	36.7	20.5	19.6	21.0
5200	41.9	33.3	36.8	20.5	19.6	20.9
5300	41.8	33.1	36.8	20.5	19.5	21.0
5400	39.8	33.1	36.6	20.6	19.4	21.0
5500	40.8	32.4	37.1	20.8	19.1	21.3
5600	41.8	32.8	37.0	20.5	19.4	20.9
5700	40.0	33.4	36.8	20.3	19.2	20.7
5800	42.4	33.5	37.1	20.5	19.2	20.9
5900	40.6	32.1	36.9	20.4	19.4	20.8
6000	40.9	33.5	36.9	20.4	19.2	20.8

(1) Includes test board loss

(2) Drain current was allowed to increase during compression measurement