

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
10	0.00	63.0	64.3
100	0.01	49.0	49.5
200	0.01	45.3	45.4
300	0.02	41.7	41.0
500	0.02	39.5	39.5
600	0.03	39.0	38.9
800	0.03	38.9	38.7
900	0.04	39.5	39.3
1000	0.04	40.2	39.8
1200	0.04	44.6	43.3
1400	0.05	57.6	51.9
1600	0.06	48.2	50.9
1800	0.06	40.7	42.3
2000	0.07	37.3	38.1
2200	0.08	35.6	36.0
2400	0.10	34.8	35.0
2600	0.11	35.1	34.7
2800	0.13	36.0	35.4
3000	0.14	38.5	37.5
3500	0.16	44.0	48.1
4000	0.15	31.8	31.5
4500	0.15	27.7	27.2
5000	0.14	27.3	27.1
5500	0.13	31.8	31.7
6000	0.12	43.5	44.9
6500	0.12	30.8	30.7
7000	0.12	30.4	30.2
7500	0.12	40.1	38.8
8000	0.11	33.8	34.2
8500	0.11	28.3	28.3
9000	0.12	29.8	29.3
9500	0.11	46.0	36.2
10000	0.12	27.7	27.7
10500	0.14	22.9	22.8
11000	0.14	23.1	22.7
11500	0.11	29.3	26.8
12000	0.11	32.9	29.3
12500	0.14	22.6	22.7
13000	0.15	20.1	20.3
13500	0.14	21.3	21.6
14000	0.14	28.9	29.6
14500	0.13	28.2	28.9
15000	0.16	22.1	21.8
15500	0.16	22.4	22.2
16000	0.12	31.4	32.1
16500	0.15	27.2	27.3
17000	0.17	20.6	20.9
17500	0.16	20.6	20.8
18000	0.15	25.4	25.7