

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
10	20.04	1.16
50	20.04	1.16
100	20.04	1.16
200	20.04	1.16
300	20.04	1.15
400	20.04	1.15
500	20.04	1.15
1000	20.05	1.14
1500	20.04	1.13
2000	20.02	1.11
2500	20.01	1.09
3000	20.00	1.07
3500	19.99	1.06
4000	20.00	1.05
4500	20.00	1.04
5000	20.02	1.02
5500	20.01	1.02
6000	20.03	1.05
6500	20.04	1.07
7000	20.06	1.08
7500	20.06	1.07
8000	20.08	1.06
8500	20.09	1.05
9000	20.10	1.06
9500	20.12	1.08
10000	20.14	1.09
10500	20.14	1.10
11000	20.14	1.11
11500	20.14	1.10
12000	20.15	1.10
12500	20.16	1.10
13000	20.17	1.11
13500	20.19	1.12
14000	20.20	1.14
14500	20.22	1.16
15000	20.24	1.18
15500	20.27	1.20
16000	20.28	1.19
16500	20.28	1.17
17000	20.27	1.16
17500	20.26	1.17
18000	20.26	1.21