

Typical Performance Data

FREQ.	INSERTION LOSS	INPUT RETURN LOSS (50Ω)	OUTPUT RETURN LOSS (75Ω)
(MHz)	(dB)	(dB)	(dB)
1.00	0.01	13.94	14.74
5.00	0.01	13.92	14.75
10.00	0.02	13.92	14.76
25.00	0.03	13.90	14.80
50.00	0.04	13.89	14.86
100.00	0.09	13.94	14.96
150.00	0.13	14.05	15.03
200.00	0.18	14.21	15.09
250.00	0.22	14.43	15.16
300.00	0.25	14.69	15.21
325.00	0.26	14.85	15.25
350.00	0.27	15.00	15.29
375.00	0.27	15.17	15.35
400.00	0.28	15.34	15.42
425.00	0.27	15.52	15.49
450.00	0.27	15.71	15.57
475.00	0.27	15.89	15.66
500.00	0.26	16.07	15.74
525.00	0.25	16.26	15.81
550.00	0.24	16.43	15.85
575.00	0.23	16.61	15.88
600.00	0.22	16.78	15.90
625.00	0.20	16.94	15.93
650.00	0.19	17.09	15.96
675.00	0.18	17.23	15.99
680.00	0.18	17.26	15.99
685.00	0.18	17.29	15.99
690.00	0.18	17.32	16.00
695.00	0.18	17.34	16.00
700.00	0.18	17.37	16.01
725.00	0.17	17.49	16.04
750.00	0.17	17.59	16.09
800.00	0.19	17.76	16.23
825.00	0.21	17.84	16.32
850.00	0.23	17.90	16.41
875.00	0.26	17.95	16.52
900.00	0.29	17.99	16.65
925.00	0.33	18.02	16.81
950.00	0.36	18.06	16.99
975.00	0.40	18.10	17.19
1000.00	0.43	18.14	17.40
1100.00	0.54	18.40	18.50
1200.00	0.57	18.91	19.87
1300.00	0.55	19.77	21.10
1400.00	0.52	20.97	22.23
1500.00	0.52	22.22	23.50
1600.00	0.54	23.02	25.02
1700.00	0.57	23.10	26.01
1800.00	0.56	22.92	26.07
1900.00	0.52	23.07	25.16
1950.00	0.50	23.38	24.72
2000.00	0.47	23.89	24.15
2050.00	0.45	24.57	23.56
2100.00	0.44	25.43	23.11
2150.00	0.43	26.42	22.63
2200.00	0.44	27.50	22.14
2250.00	0.45	28.53	21.78
2400.00	0.50	30.03	21.02
2450.00	0.51	29.79	21.15
2500.00	0.52	29.13	21.32