

Test Cable, SMA-Male/N-Male

CBL-1.5M-SMNM+

Typical Performance Data

| FREQUENCY (MHz) | INSERTION LOSS (dB) | SMA-MALE RETURN LOSS (dB) | N-MALE RETURN LOSS (dB) |
|--------------------|---------------------------|---------------------------------|-------------------------------|
| 10.0 | 0.06 | 43.61 | 41.74 |
| 50.0 | 0.13 | 42.47 | 43.47 |
| 100.0 | 0.18 | 41.39 | 39.93 |
| 200.0 | 0.26 | 37.88 | 37.79 |
| 300.0 | 0.32 | 48.04 | 42.16 |
| 400.0 | 0.37 | 36.21 | 36.84 |
| 500.0 | 0.42 | 36.33 | 36.03 |
| 600.0 | 0.46 | 42.24 | 42.54 |
| 700.0 | 0.49 | 33.44 | 33.89 |
| 800.0 | 0.53 | 42.92 | 42.72 |
| 900.0 | 0.57 | 32.24 | 33.75 |
| 1000.0 | 0.61 | 33.85 | 33.84 |
| 2000.0 | 0.89 | 30.61 | 31.98 |
| 3000.0 | 1.10 | 42.16 | 36.32 |
| 4000.0 | 1.28 | 41.79 | 39.16 |
| 5000.0 | 1.46 | 32.07 | 32.19 |
| 5500.0 | 1.54 | 34.69 | 38.00 |
| 6000.0 | 1.62 | 36.15 | 36.67 |
| 6500.0 | 1.69 | 33.55 | 33.87 |
| 7000.0 | 1.78 | 32.11 | 34.95 |
| 7500.0 | 1.85 | 29.74 | 30.11 |
| 8000.0 | 1.92 | 29.27 | 30.01 |
| 9000.0 | 2.05 | 40.97 | 40.05 |
| 10000.0 | 2.24 | 26.94 | 27.16 |
| 11000.0 | 2.36 | 25.85 | 27.43 |
| 12000.0 | 2.47 | 31.52 | 28.55 |
| 13000.0 | 2.62 | 29.16 | 23.88 |
| 13500.0 | 2.68 | 24.62 | 21.69 |
| 14000.0 | 2.73 | 22.99 | 21.19 |
| 14500.0 | 2.76 | 23.17 | 21.75 |
| 15000.0 | 2.80 | 24.09 | 22.91 |
| 15500.0 | 2.83 | 25.90 | 23.61 |
| 16000.0 | 2.91 | 30.35 | 27.75 |
| 16500.0 | 2.94 | 46.18 | 28.82 |
| 17000.0 | 3.02 | 36.04 | 31.68 |
| 17500.0 | 3.08 | 36.52 | 33.58 |
| 18000.0 | 3.18 | 39.09 | 31.00 |