

Test Cable, N-Male/N-Male

CBL-1M-NMNM+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
0.3	0.00	50.34	52.38
0.7	0.00	53.08	53.01
1.0	0.01	52.99	52.73
3.0	0.02	49.77	49.65
5.0	0.02	48.12	48.06
7.0	0.03	47.16	47.08
9.0	0.03	46.39	46.45
10.0	0.04	45.83	46.21
30.0	0.06	42.45	42.26
50.0	0.08	40.23	39.86
70.0	0.10	39.50	39.30
90.0	0.11	40.42	40.81
100.0	0.12	41.66	42.46
200.0	0.17	37.52	37.70
300.0	0.22	34.98	34.55
400.0	0.25	33.72	33.36
500.0	0.29	34.25	34.57
600.0	0.31	37.56	37.73
700.0	0.34	39.36	40.32
800.0	0.36	43.74	41.52
900.0	0.38	37.75	37.65
1000.0	0.40	33.19	33.53
1500.0	0.50	29.59	29.16
2000.0	0.59	35.99	32.39
2500.0	0.65	26.88	26.13
3000.0	0.74	30.92	30.24
3500.0	0.79	33.18	29.22
4000.0	0.86	31.00	29.19
4500.0	0.93	29.48	28.89
5000.0	0.98	29.47	28.34
5500.0	1.02	31.72	26.57
6000.0	1.10	26.51	24.21
6500.0	1.13	29.72	28.08
7000.0	1.19	35.46	24.84
7500.0	1.21	34.07	29.70
8000.0	1.25	30.81	26.70
8500.0	1.31	28.68	23.35
9000.0	1.31	34.09	24.84
9500.0	1.38	31.10	24.20
10000.0	1.43	26.50	22.13
10500.0	1.50	28.79	23.00
11000.0	1.50	33.50	38.15
11500.0	1.53	32.28	36.06
12000.0	1.57	27.10	27.94
12500.0	1.65	28.98	26.14
13000.0	1.69	33.68	33.15
13500.0	1.75	24.65	25.37
14500.0	1.86	22.33	19.97
15000.0	1.87	41.88	38.00
15500.0	1.98	25.35	26.50
16000.0	2.02	23.59	24.09
16500.0	1.97	33.29	29.25
17000.0	2.00	29.22	26.96
17500.0	2.19	23.48	22.09
18000.0	2.18	23.03	18.98