

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA MALE 1 RETURN LOSS (dB)	SMA MALE 2 RETURN LOSS (dB)
0.3	0.05	47.0	47.0
1.0	0.07	43.6	43.4
10.0	0.22	36.8	36.3
100.0	0.71	40.1	39.9
200.0	1.03	33.2	33.1
300.0	1.27	36.2	36.2
400.0	1.48	47.1	45.0
500.0	1.66	43.3	41.2
600.0	1.83	33.1	32.9
700.0	1.99	31.4	31.2
800.0	2.13	34.3	34.8
900.0	2.27	50.1	44.5
950.0	2.34	46.3	40.3
1000.0	2.40	33.7	34.1
2000.0	3.49	31.3	31.6
2500.0	3.95	33.2	34.5
3000.0	4.37	40.7	32.7
3500.0	4.76	35.8	39.4
4000.0	5.14	40.3	36.1
4500.0	5.50	41.3	34.3
5000.0	5.84	44.0	32.8
5500.0	6.17	35.8	31.3
6000.0	6.49	40.6	34.2
6500.0	6.80	41.9	33.4
7000.0	7.09	42.3	32.4
7500.0	7.40	40.6	33.3
8000.0	7.68	49.1	29.9
8500.0	7.96	44.4	35.9
9000.0	8.24	44.7	30.0
9500.0	8.50	38.0	33.8
10000.0	8.78	44.9	27.7
10500.0	9.03	35.3	32.1
11000.0	9.30	35.8	27.5
11500.0	9.56	31.1	27.3
12000.0	9.82	30.8	25.5
12500.0	10.08	28.7	27.1
13000.0	10.30	28.5	24.6
13500.0	10.53	28.0	24.7
14000.0	10.75	27.2	23.7
15000.0	11.23	26.3	22.8
15500.0	11.48	25.5	22.7
16000.0	11.68	24.3	22.5
16500.0	11.94	27.4	22.2
17000.0	12.15	27.9	21.6
17500.0	12.38	29.3	21.1
18000.0	12.57	28.3	23.0