

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
100	0.05	49.2	47.3
200	0.06	42.8	45.8
300	0.06	42.0	43.1
400	0.07	39.6	39.5
500	0.08	38.4	39.0
600	0.09	38.9	39.5
700	0.09	39.5	39.1
800	0.11	42.3	39.1
900	0.12	45.1	42.0
1000	0.12	44.5	54.7
1100	0.13	39.7	45.2
1250	0.15	36.4	37.5
1500	0.15	34.8	35.6
1750	0.16	39.7	40.3
2000	0.17	38.9	41.3
2001	0.17	38.8	41.4
2250	0.18	42.8	41.7
2500	0.20	40.3	41.9
2750	0.20	48.4	41.6
3000	0.23	34.5	35.2
3250	0.22	39.4	35.5
3500	0.24	35.1	32.9
3750	0.27	32.5	29.4
4000	0.26	44.2	43.6
4250	0.28	32.6	29.9
4500	0.30	35.8	32.6
5000	0.31	31.5	29.1
5500	0.32	32.9	36.9
6000	0.35	37.9	33.3
6500	0.35	26.0	26.6
7000	0.36	22.4	24.0
7500	0.39	27.4	27.5
8000	0.35	30.6	38.6
8500	0.37	26.9	25.2
9000	0.33	23.3	26.9
9500	0.37	21.8	25.4
10000	0.34	21.4	19.2
10500	0.35	24.8	21.1
11000	0.38	23.7	24.4
11500	0.37	24.9	24.7
12000	0.39	24.3	22.2
12500	0.38	27.7	23.3
13000	0.34	27.3	25.4
13500	0.37	26.4	30.8
14000	0.37	28.0	32.5
14500	0.36	24.2	30.8
15000	0.37	24.4	40.5
15500	0.34	26.2	27.1
16000	0.35	29.1	25.0
16500	0.30	28.4	28.5
17000	0.37	28.3	35.4
17500	0.41	23.2	26.0
18000	0.49	22.5	25.1