

Surface Mount

# Voltage Controlled Oscillator

## MOS-1632-119+

5V Tuning for PLL IC's 1556 to 1632 MHz

### Features

- linear tuning characteristics
- low phase noise
- low pulling
- low pushing
- aqueous washable

### Applications

- wireless communications
- test equipment
- radar & navigation systems



CASE STYLE: CZ682

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Electrical Specifications

MODEL NO.	FREQ. (MHz)		POWER OUTPUT (dBm)	PHASE NOISE dBc/Hz SSB at offset frequencies, kHz				TUNING					NON HARMONIC SPURIOUS (dBc)		HARMONICS (dBc)		PULLING pk-pk @12 dB (MHz)	PUSHING (MHz/V)	DC OPERATING POWER	
	Min.	Max.		Typ.	1	10	100	1000	VOLTAGE RANGE (V)	SENSI- TIVITY (MHz/V)	PORT CAP (pF)	3 dB MODULATION BANDWIDTH (MHz)	Typ.	Max.	Typ.	Max.			Vcc (volts)	Current (mA)
MOS-1632-119+	1556	1632	+4.5	-83	-110	-130	-150	0.5	4.5	31-35	18	60	-90	-19	-10	1	0.3	5	36	

### Pin Connections


RF OUT	5
VCC	3
V-TUNE	1
GROUND	2,4,6,7,8

### Maximum Ratings


Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	6V
Absolute Max. Tuning Voltage (Vtune)	7V
All specifications	50 ohm system

Permanent damage may occur if any of these limits are exceeded.

### Outline Drawing



### Demo Board MCL P/N: TB-128 Suggested PCB Layout (PL-023)



- NOTE: 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

### Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	wt. grams
.375	.375	.131	.188	.035	.033	.154	.050	.425	.183	.060	.425	.028	.154	.060	.60
9.52	9.52	3.33	4.77	0.89	0.84	3.91	1.27	10.80	4.65	1.52	10.80	0.71	3.91	1.52	

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com







REV. B  
M151108  
EDR-8715F1  
MOS-1632-119+  
RAV  
150512  
Page 1 of 2

# Performance Data & Curves\*

# MOS-1632-119+

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			Icc (mA)	HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ. PULL (MHz)	PHASE NOISE (dBc/Hz) at offsets				FREQ OFFSET (KHz)	PHASE NOISE at 1594 MHz (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C		F2	F3	F4			1KHz	10KHz	100KHz	1MHz		
0.00	35.05	1520.4	1514.8	1509.6	5.47	5.02	4.63	30.20	-21.1	-24.1	-39.3	0.81	1.75	-80.8	-108.1	-129.9	-150.1	1.0	-83.46
0.25	32.26	1528.9	1523.5	1518.7	5.42	4.97	4.56	30.19	-21.0	-21.9	-40.5	0.62	1.75	-81.8	-108.0	-130.4	-150.4	2.0	-91.36
0.50	30.75	1536.8	1531.6	1526.9	5.36	4.93	4.52	30.19	-20.9	-24.3	-39.1	0.52	1.61	-82.4	-109.5	-130.4	-149.5	3.5	-98.67
0.75	30.29	1544.4	1539.3	1534.6	5.30	4.87	4.47	30.17	-20.7	-26.0	-37.3	0.43	1.32	-83.6	-109.9	-130.7	-149.7	6.0	-104.78
1.00	30.12	1552.0	1546.9	1542.2	5.24	4.82	4.41	30.18	-20.3	-23.5	-37.6	0.35	0.90	-83.6	-110.0	-130.7	-150.7	8.5	-108.34
1.25	30.27	1559.6	1554.4	1549.8	5.19	4.77	4.36	30.18	-19.9	-25.7	-36.0	0.31	0.38	-83.2	-110.5	-130.8	-150.8	10.0	-109.98
1.50	30.81	1567.2	1562.0	1557.3	5.12	4.73	4.32	30.17	-19.6	-27.9	-35.6	0.28	0.49	-84.3	-109.7	-130.4	-150.6	20.8	-116.90
1.75	31.38	1575.1	1569.7	1564.9	5.03	4.66	4.26	30.17	-19.6	-25.6	-36.3	0.25	1.01	-82.4	-109.2	-130.8	-151.4	35.5	-121.53
2.00	32.05	1583.0	1577.5	1572.6	4.99	4.59	4.17	30.16	-19.1	-27.7	-33.8	0.22	1.41	-81.9	-110.2	-130.1	-149.3	60.7	-125.39
2.25	32.74	1591.1	1585.5	1580.6	4.93	4.56	4.12	30.16	-18.6	-28.2	-35.3	0.22	1.66	-82.4	-109.9	-130.7	-149.9	86.7	-129.27
2.50	33.29	1599.4	1593.7	1588.7	4.85	4.50	4.07	30.16	-18.2	-29.0	-33.0	0.22	1.69	-82.8	-109.8	-130.5	-149.9	100.0	-130.39
2.75	33.92	1607.9	1602.0	1596.9	4.78	4.43	4.00	30.15	-18.1	-30.2	-32.6	0.25	1.58	-81.3	-109.9	-130.3	-150.4	177.0	-134.61
3.00	34.45	1616.5	1610.5	1605.3	4.70	4.38	3.93	30.15	-18.0	-29.6	-32.6	0.28	1.26	-82.8	-110.0	-130.7	-150.6	211.6	-136.45
3.25	34.93	1625.2	1619.1	1613.9	4.62	4.31	3.86	30.14	-17.9	-32.7	-31.1	0.33	0.77	-83.7	-109.8	-130.6	-151.2	302.4	-139.41
3.50	35.32	1634.0	1627.9	1622.5	4.54	4.24	3.78	30.14	-17.8	-30.9	-31.1	0.39	0.26	-82.8	-109.9	-130.9	-149.9	361.5	-141.02
3.75	35.44	1642.9	1636.7	1631.3	4.49	4.17	3.69	30.13	-17.6	-32.2	-29.9	0.45	0.76	-81.3	-108.5	-130.7	-150.8	507.5	-144.16
4.00	35.49	1651.9	1645.5	1640.2	4.43	4.12	3.61	30.13	-17.2	-33.8	-30.5	0.53	1.29	-83.1	-109.2	-130.5	-150.0	606.7	-145.50
4.25	35.30	1660.8	1654.4	1649.0	4.34	4.06	3.55	30.12	-17.1	-32.1	-30.2	0.61	1.62	-81.5	-109.6	-130.3	-149.9	851.6	-148.96
4.50	35.23	1669.6	1663.2	1657.9	4.28	3.98	3.45	30.11	-17.0	-33.9	-29.8	0.68	1.70	-81.2	-109.3	-130.5	-150.3	1000.0	-150.67

\*at 25°C unless mentioned otherwise



**Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

