



SOLID STATE

USB RF SPDT Switch

USB-1SP2T-673

Mini-Circuits

50Ω 0.1 to 67 GHz

THE BIG DEAL

- Super wide bandwidth, solid-state design
- High isolation, 30 dB @ 67 GHz
- USB control and automation
- Daisy-chain control of up to 25 switches
- LED indicator on active port

APPLICATIONS

- RF signal routing / switch matrices
- Satellite communications up to V band
- Military radio, radar & electronic warfare
- Microwave radio / cellular infrastructure
- Test & measurement systems

PRODUCT OVERVIEW

Mini-Circuits' USB-1SP2T-673 is a fast switching solid-state reflective SPDT covering an ultra-wide bandwidth, from 0.1 to 67 GHz. The solid-state design features an impressive combination of high isolation, low insertion loss and good linearity across the entire band. The switch is supplied in a low profile package with precision 1.85 mm RF connectors. LED indicators on the switch package provide a convenient indicator of the current switch state.

The daisy-chain control interface with "dynamic addressing" simplifies control integration, allowing multiple switches to be combined into a Master / Slave chain. Simply connect, then power on and the whole chain of up to 25 compatible switches can be controlled independently through a single USB and software interface.

Full software support is provided, including our user-friendly GUI application for Windows and a full API with programming instructions for Windows and Linux environments (both 32-bit and 64-bit systems).

KEY FEATURES

Feature	Advantages
Fast switching sequences	Program automated switching sequences to run with extremely fast transitions and no external control.
High performance	Solid-state design combining high isolation with low insertion loss from 0.1 to 67 GHz.
Dynamic daisy-chain control	Control up to 25 switches through a single USB interface.
USB control	USB HID interface provides easy compatibility with a wide range of software setups and programming environments.
Full software support	User friendly Windows GUI (graphical user interface) allows manual control straight out of the box, while the comprehensive API (application programming interface) with examples and instructions allows easy automation in most programming environments.



Model No.	USB-1SP2T-673
Case Style	WP3211
Connectors	1.85 mm

DOWNLOAD

SOFTWARE PACKAGE

RoHS Compliant

See our web site for RoHS Compliance methodologies and qualifications

Trademarks:

Windows is a registered trademark of Microsoft Corporation in the United States and other countries; Linux is a registered trademark of Linus Torvalds; Pentium is a registered trademark of Intel Corporation. Neither Mini-Circuits nor the Mini-Circuits products are affiliated with or endorsed by the owners of the referenced trademarks. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation.

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Rev. OR
ECO-012326
EDR-11874
USB-1SP2T-673
MCIL
220316
PAGE 1 OF 10

**SOLID STATE**

USB RF SPDT Switch

USB-1SP2T-673

Mini-Circuits

ELECTRICAL SPECIFICATIONS AT 0 TO 50°C

Parameter	Ports	Condition (GHz)	Min.	Typ.	Max.	Unit
Frequency Range	-	-	0.1		67	GHz
Insertion Loss	COM to any active port	0.1 - 26	-	1.10	3.50	dB
		26 - 40	-	2.20	4.00	
		40 - 60	-	3.00	6.50	
		60 - 67	-	5.10	9.00	
Isolation	Between ports J1 & J2	0.1 - 26	-	45	-	dB
		26 - 40	-	40	-	
		40 - 60	-	30	-	
		60 - 67	-	30	-	
	COM to Inactive port	0.1 - 26	-	45	-	
		26 - 40	-	40	-	
		40 - 60	-	27	-	
		60 - 67	-	27	-	
VSWR	COM port	0.1 - 18	-	1.25	-	:1
		18 - 26	-	1.75	-	
		26 - 60	-	1.85	-	
		60 - 67	-	3.15	-	
	Any port connected to COM	0.1 - 18	-	1.30	-	
		18 - 26	-	1.65	-	
		26 - 60	-	1.85	-	
		60 - 67	-	4.40	-	
Power Input @1 dB Compression ¹	COM to any active port	0.1 - 67	-	27	-	dBm
IP3	COM to any active port	0.5 - 67	-	40	-	dBm
Transition Time ²	-	-	-	5	-	µs
Minimum Dwell Time ³	High speed mode	-	-	10	-	µs
Switching Time (USB) ⁴	-	-	-	2	-	ms
Supply Voltage (Vcc)	USB port	-	4.75	5	5.25	V _{DC}
Supply Current (Icc) ⁵						
Current Pass-through ⁶	-	-	-	-	500	mA
Operating RF Input Power ¹	Through path	Hot switching	-	-	+27	dBm
	Through path	Cold switching	-	-	+27	
	Isolation path	-	-	-	+27	

1. Max power derates linearly from +27 dBm @ 2 GHz to +24 dBm @ 100 MHz.

2. Transition time spec represents the time that the RF signal paths are interrupted during switching and thus is specified without communication delays.

3. Minimum dwell time is the shortest time that can be achieved between 2 switch transitions when programming an automated switch sequence.

4. Switching time (USB) is the time from issuing a single software command via USB to the switch state changing. The most significant factor is the host PC, influenced by CPU load and USB protocol. The time shown is an estimate for a medium CPU load and USB 2.0 connection.

5. USB current draw for a single unit with no slave units.

6. Pass through current is the maximum supply current handling of a unit with slave modules attached. If controlling a large number of slave modules additional power supplies should be included to ensure this limit is not exceeded. See page 5 for details.



SOLID STATE

USB RF SPDT Switch

USB-1SP2T-673

ABSOLUTE MAXIMUM RATINGS

Operating Temperature	0°C to 50°C
Storage Temperature	-20°C to 60°C
DC supply voltage max.	6V
DC voltage @ RF Ports	0V


Permanent damage may occur if any of these limits are exceeded. Operating in the range between operating power limits and absolute maximum ratings for extended periods of time may result in reduced life and reliability.

CONNECTIONS

Port Name	Connector Type
RF Ports (COM, 1 & 2)	1.85 mm female
USB	USB type-C receptacle
Serial In (Digital Control 2 port)	Digital Snap Fit Connector ⁷
Serial Out (Digital Control 1 port)	Digital Snap Fit Connector ⁷

7. Mating connector is Hirose ST40X-10S-CV(30).

BLOCK DIAGRAM






SOLID STATE

USB RF SPDT Switch

USB-1SP2T-673

OUTLINE DRAWING (WP3211)



OUTLINE DIMENSIONS ($\frac{\text{INCH}}$ / MM)


A	B	C	D	E	F	G	H	weight
3.50	0.984	0.925	0.75	0.389	0.50	3.15	0.96	grams
88.90	25.000	23.500	19.00	9.900	12.70	80.00	2.44	94





CONNECTING MULTIPLE MODULES (DAISY CHAIN)

The USB-1SP2T-673 model is designed to connect up to 25 modules in series (daisy chain) using dynamic addressing, meaning there is no need to specifically set the address of the modules. The addresses will be set automatically as part of establishing the communications with the computer. The module connected to the computer's USB port will be assigned address 0 (master), the first module connected to it will get address 1 (slave) and subsequent modules incrementing up to address 24 (slave).



Connections between modules will be made using the serial in/out ports with the module connected to the PC act as a master and all other as slave modules. All control will be through the master module (address 0) which is the only one communicating with the PC. Serial control out port of each module should be connected to the serial control in port of the next module.

Power will be supplied from the PC via the master module up to a maximum of 500 mA. Generally, additional power supply will be needed to keep total current below 500 mA. All power supplies should be connected to the module via the module's USB port. Connecting an additional power supply will automatically cut off power draw from the serial control in port for that module.

The serial master/slave bus allows connecting modules of different types to the same daisy chain as long as all support Mini-Circuits Dynamic addressing setup. To add a new module to the setup, simply connect the module and refresh the address listing, no need to reset any of the existing modules or assign addresses manually.

Note: Different module types may have different current consumption which will change the number of units which can be connected before an additional power supply is needed.




SOLID STATE USB RF SPDT Switch


USB-1SP2T-673

TYPICAL PERFORMANCE CURVES


Insertion Loss over Temperature (J1 Active)




Insertion Loss J1 - J2 Active




Isolation Com to J1 (J2 Active)



Isolation Com to J2 (J1 Active)



Isolation J2 to J1 (J2 Active)






SOLID STATE

USB RF SPDT Switch


USB-1SP2T-673

TYPICAL PERFORMANCE CURVES (CONTINUED)


VSWR @ COM over Temperature (J1 Active)



VSWR @ J1 over Temperature (J1 Active)



VSWR @ J2 over Temperature (J2 Active)





SOLID STATE

USB RF SPDT Switch

USB-1SP2T-673

Mini-Circuits

SOFTWARE SPECIFICATIONS

SOFTWARE & DOCUMENTATION DOWNLOAD:

- Mini-Circuits' full software and support package including user guide, Windows GUI, DLL files, programming manual and examples can be downloaded free of charge from: <https://www.minicircuits.com/softwaredownload/solidstate.html>
- Please contact testsolutions@minicircuits.com for support

MINIMUM SYSTEM REQUIREMENTS:

Parameter	Requirements	
Interface	USB HID or Daisy Chain dynamic addressing	
System Requirements	GUI	Windows 98 or later
	USB API DLL	Windows 98 or later and programming environment with ActiveX or .NET support
	USB Direct Programming	Linux, Windows 98 or later
	Daisy Chain dynamic addressing	An additional Mini-Circuits model supporting dynamic addressing
Hardware	Pentium II or later with 256 MB RAM	

APPLICATION PROGRAMMING INTERFACE (API)

USB SUPPORT (WINDOWS):

- ActiveX COM DLL file for creation of 32-bit programs
- .NET library DLL file for creation of 32 / 64-bit programs
- Supported by most common programming environments (refer to application note AN-49-001 for summary of supported environments)


USB SUPPORT (LINUX):

- Direct USB programming using a series of USB interrupt codes
- Full programming instructions and examples available for a wide range of programming environments / languages.




GRAPHICAL USER INTERFACE (GUI) FOR WINDOWS - KEY FEATURES

- Connect via USB
- Run GUI in "demo mode" to evaluate software without a hardware connection



- View and set switch states at the click of a button
- Control up to 25 units from a single USB control
- Configure and run timed switching sequences
- Set start-up switch state





SOLID STATE

USB RF SPDT Switch


USB-1SP2T-673

Mini-Circuits

ORDERING INFORMATION

Please contact Mini-Circuits' Test Solutions department for price and availability: testsolutions@minicircuits.com

Model	Description
USB-1SP2T-673	USB RF SPDT switch

Included Accessories	Part No.	Description
	USB-CBL-AC-3+	3.3 ft (1.0 m) USB cable: USB type A (Male) to USB type C (Male)

OPTIONAL ACCESSORIES

USB-CBL-AC-3+	3.3 ft (1.0 m) USB Cable: USB type A (Male) to USB type C (Male)
CBL-1.5FT-MMD+	1.5 ft (0.45 m) cable assembly for serial control Daisy Chain with snap fit connectors
USB-AC/DC-5+	AC/DC +5V power adaptor with USB connector ^{8, 9}

8. The power adaptor may be used to provide additional power via USB port when connecting several units in daisy chain.

9. Includes power plugs for US, UK, EU, IL, AU & China. Plugs for other countries are also available. If you need a power cord for a country not listed please contact testsolutions@minicircuits.com

NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>

