

## Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10.0	75.60	0.00
50.0	66.08	0.01
100.0	60.88	0.04
200.0	57.73	0.12
400.0	54.53	0.40
500.0	47.28	0.56
600.0	42.56	0.70
800.0	37.44	0.85
1000.0	36.86	0.90
1100.0	36.69	0.94
1140.0	35.76	0.96
1160.0	35.00	0.98
1180.0	33.97	1.01
1200.0	32.72	1.03
1240.0	29.61	1.10
1260.0	27.84	1.14
1280.0	25.98	1.19
1300.0	24.06	1.25
1400.0	14.40	1.86
1500.0	6.63	4.01
1600.0	2.91	8.85
1700.0	1.84	13.35
1800.0	1.50	15.66
1820.0	1.45	16.01
1840.0	1.42	16.33
1860.0	1.39	16.67
1880.0	1.36	17.01
1900.0	1.33	17.39
1980.0	1.26	19.14
2000.0	1.24	19.53
2080.0	1.23	20.12
2100.0	1.23	19.89
2180.0	1.27	18.04
2200.0	1.29	17.51
2280.0	1.36	15.87
2300.0	1.38	15.63
2380.0	1.44	15.31
2400.0	1.46	15.42
2480.0	1.51	16.24
2500.0	1.53	16.39
2580.0	1.66	15.33
2600.0	1.72	14.52
2620.0	1.79	13.60
2660.0	1.97	11.67
2700.0	2.23	9.83
2760.0	2.74	7.55
2800.0	3.17	6.34
2880.0	4.17	4.56
2900.0	4.44	4.22
2980.0	5.63	3.14
3000.0	5.96	2.93
3080.0	7.45	2.23
3200.0	10.70	1.49
3280.0	14.03	1.20
3400.0	21.52	1.05
3480.0	29.16	1.11
3600.0	31.48	1.36
3640.0	29.39	1.49
3680.0	28.03	1.65
3800.0	27.02	2.23
3840.0	27.55	2.42
3880.0	28.58	2.59
4000.0	35.80	2.66
4080.0	41.30	2.40
4200.0	32.29	1.91
4280.0	29.65	1.65
4400.0	27.87	1.38
4600.0	27.96	1.15
4800.0	31.20	1.04
5000.0	41.94	1.02
5400.0	23.11	1.12