



Coaxial Cable

141-7SM+

50Ω 7 inch DC to 18 GHz SMA-Male

THE BIG DEAL

- Wideband frequency coverage, DC to 18 GHz
- Low Loss, 0.7 dB at 18 GHz
- Excellent Return Loss, 29 dB at 18 GHz
- Hand formable to almost any custom shape without special bending tools
- 8mm bend radius for tight installations
- Anti-torque nut prevents cable stress during installation
- Insulated outer jacket standard¹
- Ideal for interconnect of assembled systems

*Generic photo used for illustration purposes only*

Model No.	141-7SM+
Case Style	KQ1506-7
Connectors	SMA-Male

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Replacement for custom bent 0.141" semi-rigid cables
- Communication receivers and transmitters
- Military and aerospace system
- Environmental and test chambers

PRODUCT OVERVIEW

The 141 Series Hand-Flex™ Coaxial Cables are ideal for interconnection of coaxial components or sub-systems. The construction includes a silver-plated copper-clad steel center conductor which maintains the shape after bending. The outer shield is copper braid, tin soaked, which minimizes signal leakage and at the same time flexible for easy bend. Dielectric is low loss PTFE. Connectors have passivated stainless-steel coupling nut over a gold plated connector body and Silver Plated Copper Clad Steel.

KEY FEATURES

Features	Advantages
Hand-Formable RF Cables	The 141 Series Hand-Flex™ cables are hand formable making them ideal for use integrating coaxial components and sub-assemblies without the need for special cable-bending tools and alleviating the risk of damage during the bending process typical of semi-rigid coaxial cable assemblies.
Tight Bend Radius	Capable of only 8mm bend radius, the 141 Hand-Flex™ series is able to make connections in tight spaces making these cables ideal for dense system integration
Excellent Return Loss	Supporting typical return loss of 30 dB to 6 GHz and 21 dB to 18 GHz, the 141 Series Hand-Flex Cables are ideally suited for interconnecting a wide variety of RF components while minimizing VSWR ripple contribution due to mating cables & connectors.
Good Power Handling Capability: • 546W at 0.5 GHz • 90W at 18 GHz	Mini-Circuits 141 Cable series can support medium to high RF power levels enabling these cables to be used in the transmit path. NOTE: power rating is at sea-level altitudes.
Built-in Anti-torque nut	Mini-Circuits' 141 Series Hand-Flex™ cables include an anti-torque feature to support the connector body during installation alleviating risk of stress to the connector/cable interface.
Jacketed and Unjacketed options	Standard 141 Series cables include a blue FEP insulator jacket reducing the risk of accidental shorting of DC power lines or active pins during installation and operation. Un-jacketed versions are available upon request.



Mini-Circuits

HAND
FLEX™

Coaxial Cable

141-7SM+

50Ω 7 inch DC to 18 GHz SMA-Male

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		DC		18	GHz
Length ²		7			inches
Insertion Loss	DC - 2	—	0.10	0.22	dB
	2 - 6	—	0.20	0.39	
	6 - 10	—	0.33	0.52	
	10 - 18	—	0.47	0.80	
Return Loss	DC - 2	23	52	—	dB
	2 - 6	23	43	—	
	6 - 10	17	37	—	
	10 - 18	17	35	—	

1. Unjacketed cable also available upon request.

2. Custom sizes available, consult factory.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-55°C to +105°C
Storage Temperature	-55°C to +105°C
Power Handling at +25°C, Sea Level	546W at 0.5 GHz 387W at 1 GHz 273W at 2 GHz 156W at 6 GHz 121W at 10 GHz 90W at 18 GHz

Permanent damage may occur if any of these limits are exceeded.





Mini-Circuits

**HAND
FLEX™**

Coaxial Cable

141-7SM+

50Ω 7 inch DC to 18 GHz SMA-Male


CABLE CONSTRUCTION



- Center Conductor: Silver Plated Copper Clad Steel
- Dielectric: Solid PTFE
- Outer Shield: Copper Braid, Tin Soaked
- Jacket: FEP, Blue (Unjacketed cable also available upon request)

Connectors:
Coupling Nut: Stainless Steel Passivated
Body: Stainless Steel Gold Plated
Center Pin: Silver Plated Copper Clad Steel

OUTLINE DRAWING



OUTLINE DIMENSIONS (Inch/mm)

A	B	C1	C2	D	E1	E2	F	T	wt grams
7.0	.36	.315	.250	.36	.315	.250	.163±.004	.10	
177.80	9.14	8.00	6.35	9.14	8.00	6.35	4.14±0.10	2.54	12.6





Mini-Circuits

HAND
FLEX™

Coaxial Cable

141-7SM+

50Ω 7 inch DC to 18 GHz SMA-Male

TYPICAL PERFORMANCE DATA AND CHARTS

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	
		SMA-Male	SMA-Male
10.0	0.01	61.97	53.91
1000.0	0.08	40.86	40.10
2000.0	0.12	52.49	39.94
2500.0	0.14	41.59	38.62
4000.0	0.21	30.43	28.41
5000.0	0.24	30.00	28.55
6000.0	0.27	29.34	33.71
7000.0	0.32	26.75	26.23
8000.0	0.36	31.10	25.28
9000.0	0.38	29.76	26.80
10000.0	0.41	23.50	25.17
12000.0	0.49	21.80	20.74
13000.0	0.48	23.61	31.58
15000.0	0.53	31.54	18.57
18000.0	0.71	33.44	26.95

HAND
FLEX™
Coaxial Cable

50Ω 7 inch DC to 18 GHz SMA-Male

141-7SM+

THE BIG DEAL

- Wideband frequency coverage, DC to 18 GHz
- Low Loss, 0.7 dB at 18 GHz
- Excellent Return Loss, 29 dB at 18 GHz
- Hand formable to almost any custom shape without special bending tools
- 8mm bend radius for tight installations
- Anti-torque nut prevents cable stress during installation
- Insulated outer jacket standard¹
- Ideal for interconnect of assembled systems



Generic photo used for illustration purposes only

Model No.	141-7SM+
Case Style	RQ1506-7
Connectors	SMA-Male

+RoHS Compliant

The RoHS identifies RoHS Compliance. See our website for restricted design and qualifications

APPLICATIONS

- Replacement for custom bent 0.141" semi-rigid cables
- Communication receivers and transmitters
- Military and aerospace system
- Environmental and test chambers

PRODUCT OVERVIEW

The 141 Series Hand-Flex™ Coaxial Cables are ideal for interconnection of coaxial components or sub-systems. The construction includes a silver-plated copper-clad steel center conductor which maintains the shape after bending. The outer shield is copper

HAND
FLEX™
Coaxial Cable

50Ω 7 inch DC to 18 GHz SMA-Male

141-7SM+

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		DC		18	GHz
Length ¹			7		inches
Insertion Loss	DC - 2	—	0.10	0.22	dB
	2 - 6	—	0.20	0.39	
	6 - 10	—	0.33	0.52	
	10 - 18	—	0.47	0.80	
Return Loss	DC - 2	23	52	—	dB
	2 - 6	23	43	—	
	6 - 10	17	37	—	
	10 - 18	17	35	—	

1. Unjacketed cable also available upon request.

ABSOLUTE MAXIMUM RATINGS

Parameter	Rating
Operating Temperature	-55°C to +105°C






PROPER CABLE CONNECTION USING ANTI-TORQUE NUT


Mini-Circuits 141-series HandFlex™ interconnect cables are constructed with an anti-torque nut adjacent to the connector coupling nut. When used properly, this feature prevents possible damage to the cable due to torquing and twisting when tightening the cable connector.

TO PROPERLY TIGHTEN THE CABLE CONNECTOR:

1) The cable connector includes a coupling nut which rotates to fasten the connector, and an anti-torque nut, which is fixed to prevent the cable from twisting during connection.



2) To properly tighten the cable, use a standard 1/4-inch open end wrench to brace the anti-torque nut.



3) Using a 5/16-inch open end wrench, rotate the coupling nut clockwise to tighten the cable connector.

*NOTE: Mini-Circuits recommends using a 5/16-inch open end wrench calibrated to 8 inch-pounds maximum torque to prevent damage due to over-torquing the connector.




NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
10.0	0.01	61.97	53.91
50.0	0.02	53.69	57.20
100.0	0.02	50.90	50.93
200.0	0.03	44.48	45.54
300.0	0.04	42.40	44.12
400.0	0.04	42.67	43.24
500.0	0.05	43.75	43.94
600.0	0.06	50.24	48.86
700.0	0.06	57.56	49.09
800.0	0.07	45.22	44.23
900.0	0.07	42.23	41.29
1000.0	0.08	40.86	40.10
1100.0	0.08	42.16	41.21
1250.0	0.09	49.23	45.14
1500.0	0.10	42.98	41.88
1750.0	0.11	42.50	40.79
2000.0	0.12	52.49	39.94
2001.0	0.12	52.67	40.03
2250.0	0.13	50.01	43.43
2500.0	0.14	41.59	38.62
2750.0	0.15	41.85	35.01
3000.0	0.16	42.12	56.46
3250.0	0.17	34.95	31.08
3500.0	0.18	34.03	33.39
3750.0	0.19	35.81	33.94
4000.0	0.21	30.43	28.41
4250.0	0.21	33.27	38.06
4500.0	0.23	28.43	26.72
5000.0	0.24	30.00	28.55
5500.0	0.26	32.56	35.28
6000.0	0.27	29.34	33.71
6500.0	0.29	26.96	28.61
7000.0	0.32	26.75	26.23
7500.0	0.34	28.05	25.46
8000.0	0.36	31.10	25.28
8500.0	0.38	30.22	25.17
9000.0	0.38	29.76	26.80
9500.0	0.40	26.81	27.26
10000.0	0.41	23.50	25.17
10500.0	0.43	23.82	23.15
11000.0	0.47	23.73	21.14
11500.0	0.48	23.25	20.00
12000.0	0.49	21.80	20.74
13000.0	0.48	23.61	31.58
13500.0	0.52	22.51	25.52
14000.0	0.54	30.45	21.69
14500.0	0.54	39.17	19.12
15000.0	0.53	31.54	18.57
15500.0	0.57	41.04	19.93
16000.0	0.59	39.59	27.08
16500.0	0.60	29.62	26.90
17000.0	0.62	26.16	22.75
17500.0	0.66	25.67	23.22
18000.0	0.71	33.44	26.95

Typical Performance Curves



Outline Dimensions



KQ1506 SERIES
SMA MALE (CONN-1)
SMA MALE (CONN-2)

CASE STYLE #	A		B	C1	C2	D	E1	E2	F		T		WEIGHT GRAMS
	INCH	MM							141U-ASM+	141-ASM+	INCH	MM	
KQ1506-2	2.00	50.80	.36 (9.14)	.315 (8.00)	.250 (6.35)	.36 (9.14)	.315 (8.00)	.250 (6.35)	.141±.003 (3.58±0.07)	.163±.004 (4.14±0.10)	.05	1.27	6.89
KQ1506-3	3.00	76.20									.05	1.27	8.03
KQ1506-4	4.00	101.60									.05	1.27	9.17
KQ1506-5	5.00	127.00									.05	1.27	10.32
KQ1506-6	6.00	152.40									.05	1.27	11.46
KQ1506-7	7.00	177.80									.10	2.54	12.60
KQ1506-8	8.00	203.20									.10	2.54	13.74
KQ1506-9	9.00	228.60									.10	2.54	14.89
KQ1506-10	10.00	254.00									.10	2.54	16.03
KQ1506-11	11.00	279.40									.10	2.54	17.17
KQ1506-12	12.00	304.80									.10	2.54	18.32
KQ1506-13	13.00	330.20									.15	3.81	19.46
KQ1506-14	14.00	355.60									.15	3.81	20.60
KQ1506-15	15.00	381.00									.15	3.81	21.75
KQ1506-16	16.00	406.40									.15	3.81	22.89
KQ1506-17	17.00	431.80									.15	3.81	24.03
KQ1506-18	18.00	457.20									.15	3.81	25.17
KQ1506-19	19.00	482.60									.15	3.81	26.32
KQ1506-19.7	19.69	500.00									.15	3.81	27.12
KQ1506-20	20.00	508.00									.15	3.81	27.45
KQ1506-22	22.00	558.80									.15	3.81	29.75
KQ1506-24	24.00	609.60									.15	3.81	32.03

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. 141 Hand-Flex™ Coaxial Cable.
2. "A" Represents Length of Cable.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Case Style

KQ

KQ1506

Outline Dimensions

KQ1506 SERIES
SMA MALE (CONN-1)
SMA MALE (CONN-2)

CASE STYLE #	A		B	C1	C2	D	E1	E2	F		T		WEIGHT GRAMS						
	INCH	MM							141U-ASM+	141-ASM+	INCH	MM							
KQ1506-26	26.00	660.40	.36 (9.14)	.315 (8.00)	.250 (6.35)	.36 (9.14)	.315 (8.00)	.250 (6.35)	.141 $\pm$.003 (3.58 $\pm$ 0.07)	.163 $\pm$.004 (4.14 $\pm$ 0.10)	.20	5.08	34.32						
KQ1506-30	30.00	762.00									.20	5.08	38.89						
KQ1506-32	32.00	812.80									.20	5.08	41.18						
KQ1506-36	36.00	914.40									.30	7.62	45.75						
KQ1506-39.4	39.37	1000.00									.30	7.62	49.63						
KQ1506-40	40.00	1016.00									.30	7.62	50.32						
KQ1506-48	48.00	1219.20									.40	10.16	61.75						
KQ1506-50	50.0	1270.00									.40	10.16	72.15						
KQ1506-59.1	59.06	1500.00									.40	10.16	73.18						
KQ1506-60	60.00	1524.00									.40	10.16	73.18						
KQ1506-72	72.00	1828.80									.40	10.16	86.90						
KQ1506-78.7	78.74	2000.00									.40	10.16	94.55						



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 105° C or -55° to 85° C (see datasheet) Ambient Environment	Individual Model Data sheet
Storage Temperature	-55° to 105° C or -55° to 85° C (see data sheet) Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 Cycles	MIL-STD-202F; Method 107G
Multiple Bend Radius	40 mm, 5 times for 141 series cables 30 mm, 5 times for 086 series cables	
Single Bend Radius	8 mm for 141 series cables 6 mm for 086 series cables	