

# Bandpass Filter

## SMT

BFCN-ED13661/9

**Important Note**

This model has been designed, built and tested in our engineering department. Performance data represents model capability.  
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : FV1206-4


| ELECTRICAL SPECIFICATIONS 50Ω @ +25°C |                  |       |                 |      |      |      |       |
|---------------------------------------|------------------|-------|-----------------|------|------|------|-------|
| Parameters                            |                  | F#    | Frequency (MHz) | Min. | Typ. | Max. | Units |
| Pass Band                             | Center Frequency |       |                 |      | 8000 |      | MHz   |
|                                       | Insertion Loss   | F1-F2 | 7900-8100       |      | 2.0  | 3.5  | dB    |
|                                       | VSWR             | F1-F2 | 7900-8100       |      | 1.6  |      | :1    |
| Stop Band, Lower                      | Insertion Loss   | DC-F5 | DC-6800         | 17   | 22   |      | dB    |
|                                       |                  | F5-F3 | 6800-7000       |      | 20   |      | dB    |
|                                       | VSWR             | DC-F3 | DC-7000         |      | 30   |      | :1    |
| Stop Band, Upper                      | Insertion Loss   | F4-F6 | 9300-10000      |      | 20   |      | dB    |
|                                       |                  | F6-F7 | 10000-15000     | 15   | 20   |      | dB    |
|                                       | VSWR             | F4-F7 | 9300-15000      |      | 30   |      | :1    |

| MAXIMUM RATINGS       |                |
|-----------------------|----------------|
| Operating Temperature | -55°C to 100°C |
| Storage Temperature   | -55°C to 100°C |
| RF Power Input*       | 2W max. @ 25°C |

\*Passband rating, derate linearly to 0.5W at 100°C ambient

| PIN CONNECTIONS |     |
|-----------------|-----|
| RF IN           | 1   |
| RF OUT          | 3   |
| GROUND          | 2,4 |

Functional Schematic






# Ceramic Bandpass Filter BFCN-ED13661/9

## Typical Performance Data

| FREQUENCY<br>(MHz) | INSERTION LOSS<br>(dB) | RETURN<br>LOSS<br>(dB) | GROUP DELAY<br>(ns) |
|--------------------|------------------------|------------------------|---------------------|
| 100.0              | 48.36                  | 0.01                   | 0.27                |
| 450.0              | 35.43                  | 0.06                   | 0.27                |
| 800.0              | 30.61                  | 0.10                   | 0.26                |
| 1500.0             | 25.82                  | 0.19                   | 0.26                |
| 2200.0             | 23.60                  | 0.26                   | 0.26                |
| 2900.0             | 22.67                  | 0.30                   | 0.25                |
| 3600.0             | 22.46                  | 0.34                   | 0.24                |
| 4300.0             | 22.58                  | 0.39                   | 0.24                |
| 5000.0             | 23.04                  | 0.45                   | 0.25                |
| 5700.0             | 24.83                  | 0.49                   | 0.26                |
| 6400.0             | 32.90                  | 0.54                   | 0.33                |
| 6750.0             | 29.49                  | 0.66                   | 0.69                |
| 7100.0             | 14.65                  | 1.22                   | 0.44                |
| 7200.0             | 11.25                  | 1.75                   | 0.51                |
| 7300.0             | 8.04                   | 2.84                   | 0.66                |
| 7400.0             | 5.21                   | 5.18                   | 0.80                |
| 7500.0             | 3.19                   | 10.37                  | 0.87                |
| 7600.0             | 2.24                   | 18.92                  | 0.82                |
| 7700.0             | 2.03                   | 13.12                  | 0.71                |
| 7775.0             | 2.05                   | 10.52                  | 0.65                |
| 7800.0             | 2.06                   | 10.05                  | 0.64                |
| 7875.0             | 2.06                   | 9.50                   | 0.60                |
| 7900.0             | 2.05                   | 9.52                   | 0.60                |
| 7925.0             | 2.03                   | 9.65                   | 0.60                |
| 7975.0             | 1.98                   | 10.22                  | 0.60                |
| 8000.0             | 1.95                   | 10.69                  | 0.60                |
| 8025.0             | 1.92                   | 11.32                  | 0.61                |
| 8050.0             | 1.89                   | 12.10                  | 0.62                |
| 8075.0             | 1.87                   | 13.01                  | 0.62                |
| 8100.0             | 1.86                   | 14.07                  | 0.64                |
| 8200.0             | 1.97                   | 17.81                  | 0.66                |
| 8275.0             | 2.30                   | 13.86                  | 0.66                |
| 8300.0             | 2.46                   | 12.30                  | 0.66                |
| 8375.0             | 3.09                   | 8.71                   | 0.63                |
| 8400.0             | 3.34                   | 7.83                   | 0.62                |
| 8500.0             | 4.52                   | 5.27                   | 0.56                |
| 8600.0             | 5.84                   | 3.77                   | 0.50                |
| 8700.0             | 7.18                   | 2.85                   | 0.45                |
| 8800.0             | 8.45                   | 2.27                   | 0.42                |
| 8900.0             | 9.67                   | 1.88                   | 0.40                |
| 9000.0             | 10.84                  | 1.63                   | 0.37                |
| 9100.0             | 11.95                  | 1.43                   | 0.36                |
| 9200.0             | 13.00                  | 1.29                   | 0.35                |
| 9300.0             | 14.01                  | 1.19                   | 0.35                |
| 9800.0             | 19.23                  | 0.98                   | 0.34                |
| 10300.0            | 26.14                  | 1.03                   | 0.34                |
| 10800.0            | 41.03                  | 1.21                   | 0.57                |
| 11300.0            | 32.83                  | 1.39                   | 0.43                |
| 11800.0            | 27.92                  | 1.48                   | 0.31                |
| 12300.0            | 26.36                  | 1.59                   | 0.20                |
| 12800.0            | 23.47                  | 1.71                   | 0.26                |
| 13300.0            | 22.16                  | 1.69                   | 0.35                |
| 13800.0            | 23.92                  | 1.69                   | 0.22                |
| 14300.0            | 25.69                  | 1.74                   | 0.13                |
| 15050.0            | 19.69                  | 2.84                   | 0.17                |

## Typical Performance Curves





# Tape & Reel Packaging

# TR-F75

## DEVICE ORIENTATION IN T&R




ILLUSTRATION 1




ILLUSTRATION 2




ILLUSTRATION 3

| Applicable Case Styles |
|------------------------|
| FV1206-1               |
| FV1206-3               |

| Applicable Case Styles |
|------------------------|
| FV1206-4               |
| FV1206-5               |
| FV1206-6               |
| FV1206-7               |
| FV1206-9               |
| JC0603C-1              |

| Applicable Case Styles |
|------------------------|
| NL1008C-6              |
| FV1206-12              |
| NL1008C-9              |
| NL1008C-10             |

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |      |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 8              | 4                       | 7                 | Small quantity standards (see note) | 20   |
|                |                         |                   |                                     | 50   |
|                |                         |                   |                                     | 100  |
|                |                         |                   |                                     | 200  |
|                |                         |                   |                                     | 500  |
|                |                         |                   |                                     | 1000 |
|                |                         |                   | Standard                            | 3000 |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)

Mini-Circuits ISO 9001 & ISO 14001 Certified

**Mini-Circuits®**


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


## THIRD ANGLE PROJECTION



## REVISIONS

| REV | ECN No. | DESCRIPTION | DATE     | DR | AUTH |
|-----|---------|-------------|----------|----|------|
| OR  | M123589 | NEW RELEASE | 01/15/09 | AV | ABD  |
|     |         |             |          |    |      |
|     |         |             |          |    |      |


**SUGGESTED MOUNTING CONFIGURATION  
FOR FV1206-4 CASE STYLE, "04FL01" PIN CODE**



- NOTE:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .020" ± .0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS ±

3 PL DECIMALS ± .005

ANGLES ±

FRACTIONS ±

DRAWN

AV

07/10/09

CHECKED

IL

01/15/09

APPROVED

ABD

01/15/09

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235

PL, 04FL01, FV1206-4, BFCN, TB-518+

SIZE  
ACODE IDENT  
15542

DRAWING NO:

98-PL-305

REV:

OR


FILE: 98PL305

SCALE: 12:1


SHEET:

1 OF 1

# Evaluation Board and Circuit



**TB-518+**



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition                                                           | Reference/Spec                                                                                       |
|----------------------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature      | -55° to 100°C<br>Ambient Environment                                                | Individual Model Data Sheet                                                                          |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment                                               | Individual Model Data Sheet                                                                          |
| Humidity                   | 90 to 95% RH, 240 hours, 50°C                                                       | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Solder Reflow Heat         | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak              | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability              | 10X Magnification                                                                   | J-STD-002, Para 4.2.5, Test S, 95% Coverage                                                          |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock           | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                   | MIL-STD-202, Method 213, Condition A                                                                 |