



Mini-Circuits®

SURFACE MOUNT

Power Splitter/Combiner

ADQ-32+

2 Way-90° 50Ω 160 to 327 MHz

FEATURES

- Low Insertion Loss, 0.3 dB typ.
- High Isolation, 22 dB typ.
- Excellent VSWR, 1.22 typ.
- Small size



Generic photo used for illustration purposes only

CASE STYLE: CJ725

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Point to point microwave link

ELECTRICAL SPECIFICATIONS


Parameter		Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		—	160	—	327	MHz
Insertion Loss Avg. of Coupled Outputs above 3 dB		160-327	—	0.3	0.7	dB
Isolation		160-327	18	22	—	dB
Phase Unbalance		160-327	—	1	5	Degree
Amplitude Unbalance		160-327	—	0.6	1.6	dB
VSWR	S-Port	160-327	—	1.22	—	:1
	Output	160-327	—	1.22	—	

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C
Power Input (as a splitter)	1W Max.

Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SCHEMATIC



Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. C
ECO-019621
ADQ-32+
MCL NY
231017

PAGE 1 OF 3



Mini-Circuits

SURFACE MOUNT

Power Splitter/Combiner


ADQ-32+

2 Way-90° 50Ω 160 to 327 MHz

PIN CONNECTIONS


SUM PORT	1
PORT 1 (0°)	5
PORT 2 (+90°)	8
GROUND EXTERNAL	2,3,6,7
50 OHM TERM EXTERNAL	4

OUTLINE DRAWING




PRODUCT MARKING: N/A

DEMO BOARD MCL P/N: TB-83
SUGGESTED PCB LAYOUT (PL-063)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS $0.020" \pm 0.0015"$. COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK



 METALLIZATION

Weight: .40 gram
Dimensions are in inches [mm]. Tolerances: 2 Pl. $\pm .01$; 3Pl. $\pm .005$ Inch

- Notes:
1. Case material: Plastic.
2. Termination Finish: Tin plate over Nickel plate.

TAPE & REEL INFORMATION: F10



Mini-Circuits

SURFACE MOUNT

Power Splitter/Combiner




ADQ-32+

2 Way-90° 50Ω 160 to 327 MHz

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR (:1)		
	S-1	S-2				S	1	2
160.00	2.70	3.85	1.15	20.36	88.66	1.23	1.23	1.25
170.00	2.86	3.65	0.80	20.38	88.75	1.22	1.23	1.25
180.00	3.01	3.49	0.48	20.45	88.84	1.22	1.22	1.24
190.00	3.14	3.35	0.21	20.53	88.94	1.21	1.21	1.24
200.00	3.26	3.23	0.02	20.63	89.05	1.20	1.20	1.23
220.00	3.45	3.07	0.38	20.89	89.29	1.19	1.19	1.21
240.00	3.57	2.97	0.60	21.19	89.57	1.18	1.18	1.20
260.00	3.62	2.95	0.67	21.62	89.91	1.17	1.17	1.19
270.00	3.62	2.96	0.65	21.89	90.11	1.16	1.16	1.18
280.00	3.59	3.00	0.59	22.21	90.33	1.15	1.15	1.17
290.00	3.53	3.05	0.48	22.60	90.58	1.15	1.15	1.17
300.00	3.46	3.14	0.32	23.02	90.88	1.14	1.14	1.16
310.00	3.37	3.26	0.10	23.45	91.24	1.13	1.13	1.15
320.00	3.25	3.42	0.18	23.87	91.66	1.12	1.12	1.14
327.00	3.15	3.56	0.41	24.12	92.01	1.11	1.12	1.13

1. Total Loss = Insertion Loss + 3dB splitter loss.



- NOTES**
- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



2 Way-90° Power Splitter/Combiner

ADQ-32+

Typical Performance Data

FREQUENCY (MHz)	TOTAL LOSS ¹		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB) 1-2	PHASE UNBALANCE (deg.)	FREQUENCY (MHz)	VSWR		
	(dB)						(:1)		
	S-1	S-2					S	1	2
160.0	2.70	3.85	1.15	20.36	88.66	160.0	1.23	1.23	1.25
170.0	2.86	3.65	0.80	20.38	88.75	170.0	1.22	1.23	1.25
180.0	3.01	3.49	0.48	20.45	88.84	180.0	1.22	1.22	1.24
190.0	3.14	3.35	0.21	20.53	88.94	190.0	1.21	1.21	1.24
200.0	3.26	3.23	0.02	20.63	89.05	200.0	1.20	1.20	1.23
210.0	3.36	3.14	0.22	20.75	89.17	210.0	1.20	1.20	1.22
220.0	3.45	3.07	0.38	20.89	89.29	220.0	1.19	1.19	1.21
230.0	3.52	3.01	0.51	21.03	89.42	230.0	1.19	1.18	1.21
235.0	3.55	2.99	0.56	21.10	89.49	235.0	1.18	1.18	1.20
240.0	3.57	2.97	0.60	21.19	89.57	240.0	1.18	1.18	1.20
245.0	3.59	2.95	0.63	21.29	89.64	245.0	1.18	1.18	1.20
250.0	3.60	2.95	0.66	21.39	89.73	250.0	1.17	1.17	1.19
255.0	3.61	2.94	0.67	21.51	89.81	255.0	1.17	1.17	1.19
260.0	3.62	2.95	0.67	21.62	89.91	260.0	1.17	1.17	1.19
265.0	3.62	2.95	0.67	21.75	90.00	265.0	1.16	1.16	1.18
270.0	3.62	2.96	0.65	21.89	90.11	270.0	1.16	1.16	1.18
275.0	3.60	2.98	0.63	22.05	90.21	275.0	1.16	1.16	1.18
280.0	3.59	3.00	0.59	22.21	90.33	280.0	1.15	1.15	1.17
285.0	3.56	3.02	0.54	22.40	90.46	285.0	1.15	1.15	1.17
290.0	3.53	3.05	0.48	22.60	90.58	290.0	1.15	1.15	1.17
295.0	3.50	3.09	0.40	22.80	90.72	295.0	1.14	1.14	1.16
300.0	3.46	3.14	0.32	23.02	90.88	300.0	1.14	1.14	1.16
305.0	3.42	3.20	0.22	23.24	91.04	305.0	1.13	1.13	1.16
310.0	3.37	3.26	0.10	23.45	91.24	310.0	1.13	1.13	1.15
315.0	3.31	3.34	0.03	23.68	91.43	315.0	1.12	1.13	1.14
320.0	3.25	3.42	0.18	23.87	91.66	320.0	1.12	1.12	1.14
327.0	3.15	3.56	0.41	24.12	92.01	327.0	1.11	1.12	1.13

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS



REV. X2

ADQ-32+






8/4/2010


Page 1 of 1

2 Way-90° Power Splitter/Combiner


ADQ-32+

Typical Performance Curves





PCB Land Pattern



METALLIZATION

Weight: .40 gram

Dimensions are in inches [mm]. Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$ Inch

Notes:

1. Case material: Plastic.
2. Termination finish:
Tin plate over Nickel plate.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F10



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	16	7	10,20,50,100,200
		13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Note: Please consult individual model data sheet to determine device per reel availability.




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82272	NEW RELEASE	08/06/02	GF	DJ
A	M102713	UPDATED NOTES, ADDED "...WITH SMOBC"	01/16/06	GT	IL

SUGGESTED MOUNTING CONFIGURATION FOR CJ725 CASE STYLE, "ma", "nf" PIN CONNECTIONS



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $0.020'' \pm 0.0015''$. COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

GF

07/18/02

TOLERANCES ON:

CHECKED

HY

08/01/02

2 PL DECIMALS $\pm$

APPROVED

DJ

08/06/02

3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$
 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, ma/nf, CJ725, AD3PS/ADQ, TB-83


SIZE
ACODE IDENT
15542DRAWING NO:
98-PL-063REV:
A

FILE: 98PL063


SCALE: 6:1

SHEET: 1 OF 1

Evaluation Board and Circuit



TB-83



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215