

Surface Mount Band Stop Filter

BSF-C174223+

50Ω 174 to 223 MHz

The Big Deal

- High rejection, 44 dB typical
- Good VSWR, 1.3:1 typical in passband
- Stopband (174 to 223 MHz)
- Miniature shielded package



CASE STYLE: HU1186

Product Overview

The BSF-C174223+ is stopband filter fabricated using SMT Technology. Covering 174 to 223 MHz stopband, this units offer good rejection. This unit uses a miniature high Q capacitors and wire welded inductors for high reliability. It has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages
High rejection, 44 dB typical	BSF-C174223+ enables the filter to attenuate spurious signals and reject harmonics for broadband of frequencies.
Good VSWR, 1.3:1 typical in the pass-band	This filter maintains typical VSWR over a passband frequency range which provided good interface when used with other devices.
Shielded package	Shielded package (Size of .087" x 0.80" x 0.25") reduced interface with and from the surrounding components.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Surface Mount Band Stop Filter

50Ω 174 to 223 MHz

BSF-C174223+



CASE STYLE: HU1186

Features

- High rejection, 44 dB typical
- Good VSWR, 1.3:1 typical in passband
- Aqueous washable
- Miniature shield package

Applications

- FM radio
- Receivers / Transmitters
- Lab use

Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band, Lower	Insertion Loss	DC-F1	DC - 130	-	0.6	dB
	VSWR	DC-F1	DC - 130	-	1.3	:1
Stop Band	Rejection	F4-F5	174-223	30	44	dB
	VSWR	F4-F5	174-223	-	6	:1
Pass Band, Upper	Insertion Loss	F2-F3	330-1000	-	0.6	dB
	VSWR	F2-F3	330-1000	-	1.3	:1

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	250 mW max.

Permanent damage may occur if any of these limits are exceeded.

Functional Schematic



Typical Frequency Response





Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
1.0	0.02	1.00
5.0	0.02	1.01
30.0	0.08	1.03
88.0	0.16	1.03
114.0	0.30	1.13
130.0	0.58	1.26
150.0	3.67	2.58
160.0	15.42	8.77
168.0	30.86	13.81
174.0	48.66	16.72
200.0	57.09	14.50
223.0	61.29	22.29
228.0	41.06	18.30
238.0	15.37	7.73
254.0	3.66	2.90
280.0	1.42	1.52
330.0	0.61	1.20
500.0	0.32	1.08
800.0	0.33	1.11
1000.0	0.39	1.18

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com


REV. A
M160153
BSF-C174223+
EDU1290
URJ/NY
161230
Page 2 of 3

Pin Connections	
INPUT	2
OUTPUT	13
NOT CONNECTED	6,9
GROUND	1,3,4,5,7,8,10,11,12,14


Demo Board MCL P/N: TB-378+
Suggested PCB Layout (PL-347)



Outline Drawing



PCB Land Pattern



Outline Dimensions (inch)

A	B	C	D	E	F	G	H
.870	.800	.25	.100	.097	--	.060	.040
22.10	20.32	6.35	2.54	2.46	--	1.52	1.02
J	K	L	M	N	P		wt
.105	.910	--	.060	.060	--		grams
2.67	23.11	--	1.52	1.52	--		2.85

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp







Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
0.5	0.01	0.02	0.02	64.71	60.94	58.49	64.36	60.39	58.04
1.0	0.01	0.02	0.02	59.91	57.29	55.66	59.93	57.27	55.56
10.0	0.03	0.04	0.04	43.98	41.92	40.94	43.85	41.81	40.89
30.0	0.04	0.06	0.07	36.21	34.50	33.49	36.08	34.37	33.47
50.0	0.07	0.09	0.09	32.89	31.70	30.87	32.56	31.51	30.83
70.0	0.10	0.12	0.13	31.78	31.46	31.15	31.22	31.07	30.97
80.0	0.13	0.14	0.15	32.30	32.79	33.04	31.38	31.94	32.45
88.0	0.14	0.17	0.18	33.60	35.38	36.66	32.08	33.36	34.65
100.0	0.18	0.21	0.23	38.08	44.66	47.00	33.70	35.01	35.45
120.0	0.34	0.39	0.43	28.66	27.00	25.71	27.65	25.97	24.69
130.0	0.52	0.60	0.66	23.82	23.47	23.01	23.20	22.42	21.62
140.0	1.05	1.18	1.29	16.52	16.57	16.60	15.35	15.04	14.69
150.0	4.62	5.11	5.54	5.32	5.16	5.00	4.62	4.42	4.23
160.0	17.73	18.49	19.24	1.70	1.76	1.78	1.28	1.33	1.35
168.0	34.69	35.71	36.68	1.19	1.27	1.32	0.88	0.95	0.99
170.0	40.53	41.59	42.78	1.12	1.20	1.24	0.84	0.91	0.95
172.0	47.45	48.69	49.79	1.07	1.15	1.19	0.80	0.87	0.91
174.0	55.45	56.55	56.82	1.03	1.11	1.15	0.77	0.84	0.89
176.0	60.82	60.30	59.45	0.98	1.06	1.12	0.76	0.84	0.88
180.0	55.24	54.62	53.53	0.93	1.01	1.07	0.80	0.90	0.97
184.0	49.35	49.49	50.13	0.92	1.01	1.08	1.11	1.16	1.16
190.0	51.53	51.16	50.84	1.07	1.18	1.29	0.58	0.66	0.70
194.0	52.91	52.69	52.98	1.58	1.80	2.03	0.51	0.59	0.64
196.0	55.44	55.27	55.02	2.38	2.75	3.12	0.50	0.57	0.63
200.0	50.26	50.13	50.46	3.19	2.93	2.65	0.46	0.54	0.60
206.0	58.69	59.45	60.81	0.75	0.84	0.89	0.45	0.52	0.59
210.0	71.57	70.43	71.16	0.58	0.68	0.75	0.45	0.53	0.59
216.0	73.35	67.68	65.78	0.55	0.65	0.72	0.48	0.59	0.65
220.0	58.31	57.48	56.63	0.58	0.68	0.76	0.56	0.67	0.75
223.0	53.06	52.34	51.30	0.63	0.74	0.81	0.66	0.78	0.87
228.0	39.65	38.29	36.87	0.75	0.87	0.96	1.00	1.16	1.30
230.0	33.67	32.45	31.17	0.85	0.96	1.07	1.25	1.45	1.63
238.0	14.51	13.92	13.29	1.82	2.04	2.24	5.74	6.61	7.58
250.0	5.09	5.14	5.12	4.41	4.50	4.63	7.04	6.88	6.82
254.0	4.24	4.30	4.30	5.14	5.22	5.34	6.22	6.18	6.21
260.0	3.22	3.30	3.32	6.64	6.68	6.78	6.60	6.58	6.63
280.0	1.45	1.52	1.56	13.92	13.90	13.82	11.09	11.08	11.03
300.0	0.90	0.95	0.99	21.53	21.99	21.99	15.08	15.11	15.03
320.0	0.69	0.74	0.77	24.76	24.57	24.81	17.48	17.33	17.22
330.0	0.63	0.68	0.71	25.05	24.16	24.17	18.35	18.03	17.85
350.0	0.53	0.59	0.63	25.38	23.52	23.00	19.83	19.13	18.76
400.0	0.42	0.48	0.51	27.40	24.26	22.76	23.07	21.56	20.59
500.0	0.35	0.40	0.43	31.85	28.72	25.80	29.17	26.99	24.81
600.0	0.34	0.39	0.43	32.37	31.39	28.99	38.31	34.11	30.00
700.0	0.34	0.39	0.43	29.26	29.25	28.55	47.77	49.37	36.64
800.0	0.35	0.41	0.45	26.58	26.65	26.32	35.39	42.17	48.69
900.0	0.37	0.44	0.47	24.40	24.76	24.50	30.84	36.57	40.64
1000.0	0.39	0.46	0.51	22.92	23.42	23.22	29.16	34.44	36.13
1200.0	0.44	0.52	0.57	21.85	22.01	21.81	29.93	33.34	33.52
1400.0	0.49	0.59	0.66	21.85	21.85	21.68	33.33	34.55	35.14
1600.0	0.58	0.69	0.76	23.19	22.84	22.62	35.40	37.28	40.28
1800.0	0.68	0.80	0.89	25.70	24.83	23.93	32.52	34.06	32.37
2000.0	0.82	0.96	1.06	27.33	25.54	23.53	28.07	27.54	25.78



Typical Performance Data

FREQ. (MHz)	GROUP DELAY-1 (nsec)			FREQ. (MHz)	GROUP DELAY-2 (nsec)		
	@-40°C	@+25°C	@+85°C		@-40°C	@+25°C	@+85°C
0.5	1.84	1.90	2.04	330.0	2.16	2.14	2.13
1.0	1.86	1.91	2.02	350.0	1.73	1.71	1.71
5.0	1.82	1.82	1.79	370.0	1.48	1.45	1.44
10.0	1.80	1.83	1.80	400.0	1.20	1.19	1.18
30.0	1.90	1.87	1.84	450.0	0.97	0.95	0.93
32.0	1.88	1.88	1.88	500.0	0.81	0.82	0.81
34.0	1.90	1.88	1.90	550.0	0.75	0.73	0.74
36.0	1.91	1.92	1.90	600.0	0.70	0.69	0.69
38.0	1.91	1.93	1.92	650.0	0.66	0.65	0.65
40.0	1.97	1.94	1.94	700.0	0.63	0.63	0.62
42.0	1.97	1.99	1.97	750.0	0.62	0.61	0.60
44.0	1.99	2.01	2.01	800.0	0.60	0.59	0.58
46.0	2.03	2.02	2.05	850.0	0.59	0.58	0.57
48.0	2.04	2.05	2.07	900.0	0.58	0.57	0.56
50.0	2.06	2.05	2.08	950.0	0.57	0.56	0.56
52.0	2.08	2.09	2.10	955.0	0.57	0.56	0.55
54.0	2.10	2.10	2.11	960.0	0.57	0.56	0.55
56.0	2.15	2.15	2.15	965.0	0.57	0.55	0.55
58.0	2.16	2.17	2.19	970.0	0.57	0.56	0.55
60.0	2.20	2.21	2.22	975.0	0.56	0.56	0.55
62.0	2.26	2.28	2.27	980.0	0.57	0.56	0.55
64.0	2.33	2.32	2.33	985.0	0.56	0.55	0.55
66.0	2.34	2.36	2.34	990.0	0.56	0.55	0.55
68.0	2.37	2.39	2.39	995.0	0.56	0.55	0.55
70.0	2.45	2.46	2.46	1000.0	0.56	0.56	0.55
72.0	2.47	2.48	2.49	1200.0	0.55	0.54	0.53
74.0	2.52	2.53	2.56	1300.0	0.54	0.53	0.53
76.0	2.60	2.61	2.60	1325.0	0.54	0.53	0.53
78.0	2.64	2.65	2.64	1350.0	0.54	0.53	0.53
80.0	2.72	2.71	2.71	1375.0	0.54	0.53	0.52
82.0	2.79	2.79	2.82	1400.0	0.54	0.53	0.52
84.0	2.88	2.89	2.89	1425.0	0.54	0.53	0.53
86.0	2.93	2.94	2.96	1450.0	0.54	0.53	0.52
88.0	3.05	3.06	3.05	1475.0	0.54	0.53	0.52
90.0	3.11	3.12	3.13	1500.0	0.54	0.53	0.52
92.0	3.19	3.23	3.23	1525.0	0.53	0.52	0.52
94.0	3.33	3.35	3.35	1550.0	0.54	0.53	0.52
96.0	3.42	3.44	3.45	1575.0	0.53	0.52	0.52
98.0	3.51	3.52	3.55	1600.0	0.54	0.53	0.52
100.0	3.68	3.67	3.71	1625.0	0.54	0.53	0.52
102.0	3.82	3.84	3.85	1650.0	0.53	0.53	0.52
104.0	3.96	3.98	4.02	1675.0	0.54	0.53	0.53
106.0	4.11	4.13	4.16	1700.0	0.54	0.53	0.52
108.0	4.29	4.30	4.35	1725.0	0.54	0.53	0.52
110.0	4.50	4.52	4.55	1750.0	0.54	0.53	0.53
112.0	4.67	4.71	4.76	1775.0	0.53	0.53	0.52
114.0	4.93	4.98	5.02	1800.0	0.54	0.53	0.52
116.0	5.19	5.21	5.26	1825.0	0.54	0.53	0.52
118.0	5.47	5.50	5.55	1850.0	0.54	0.53	0.52
120.0	5.74	5.80	5.86	1875.0	0.54	0.53	0.53
122.0	6.16	6.19	6.26	1900.0	0.54	0.53	0.53
124.0	6.52	6.60	6.67	1925.0	0.54	0.53	0.53
126.0	6.97	7.05	7.13	1950.0	0.54	0.53	0.53
128.0	7.50	7.60	7.67	1975.0	0.54	0.53	0.53
130.0	8.12	8.23	8.31	2000.0	0.54	0.52	0.52

Typical Performance Curves




Typical Performance Curves




Outline Dimensions

HU1186



PCB Land Pattern



Suggested Layout,
Tolerance to be within ± 0.002

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT, GRAM
HU1186	.870 (22.10)	.800 (20.32)	.25 (6.35)	.100 (2.54)	.097 (2.46)	- -	.060 (1.52)	.040 (1.02)	.105 (2.67)	.910 (23.11)	- -	.060 (1.52)	.060 (1.52)	- -	2.85

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F21




Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	32	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION	
	

REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M132023	NEW RELEASE	MAY 11	MD	KG

SUGGESTED MOUNTING CONFIGURATION FOR
HU1186 CASE STYLE "14FL05" PIN CODE





- NOTES:
- TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030"±.003". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED		INITIALS		DATE		Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235							
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005" ANGLES ± FRACTIONS ± 	DRAWN	MD	24 MAY 11	PL, 14FL05, HU1186, BSF-C, TB-378S+, 50Ω									
	CHECKED	MD	24 MAY 11										
	APPROVED	AKR	24 MAY 11										
Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.						SIZE A		CODE IDENT 15542		DRAWING NO: 98-PL-347		REV: OR	
ASHEETA1.DWG REV:A DATE:01/12/95						FILE: 98PL347		SCALE: 2:1		SHEET: 1 OF 1			

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: ROGERS R04350 or equivalent, Dielectric Constant=3.48, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D