

Coaxial Bandpass Filter

NON-CATALOG

BIF-21.4+
BIF-21.4

50Ω Constant Impedance 18 to 25 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Features

- low VSWR in pass & stopbands, 1.3:1 typ.
- rugged shielded case
- custom to models available

Applications

- harmonic rejection
- lab use



CASE STYLE: FF55

Connectors	Model	Price	Qty.
BNC	BIF-21.4(+)	Contact Sales Dept.	


+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.

Bandpass Filter Electrical Specifications

MODEL NO.	CENTER FREQ. (MHz)	PASSBAND (MHz)	STOPBANDS	VSWR, 1.3:1 Typ. TOTAL BAND (MHz)
		(loss<1 dB)	(loss > 10 dB) at MHz (loss > 20 dB) at MHz	
BIF-21.4(+)	21.4	18-25	4.9 & 85 1.3 & 150	DC-220


Outline Drawing




Outline Dimensions (inch/mm)

B	D	wt
.54	2.59	grams
13.72	65.79	40.0

typical frequency response





Electrical Schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	$\bar{x}$	σ		
1.00	25.27	0.20	1.20	4.399
1.10	24.91	0.20	1.30	6.493
1.10	24.55	0.20	1.40	5.803
1.20	24.24	0.20	2.60	6.877
1.20	23.93	0.20	3.70	7.658
1.30	23.64	0.20	4.90	8.204
1.40	23.17	0.20	5.00	8.142
3.70	15.71	0.10	7.90	9.473
4.90	13.27	0.10	11.00	11.528
6.00	11.38	0.10	14.00	14.015
8.70	7.85	0.10	15.00	14.909
11.30	5.18	0.10	17.90	16.385
14.00	2.92	0.10	18.80	16.348
18.00	0.72	0.10	19.80	16.309
20.30	0.14	0.10	20.90	15.915
21.50	0.01	0.10	21.60	15.629
23.80	0.05	0.10	22.40	15.139
40.00	2.02	0.20	23.20	14.502
55.00	7.93	0.20	24.00	13.843
70.00	10.88	0.20	24.80	13.162
85.00	13.23	0.20	26.20	11.927
100.00	15.41	0.20	32.70	6.934
116.70	17.64	0.20	33.90	6.349
133.30	19.87	0.10	51.30	2.263
150.00	22.27	0.10	67.60	1.347
175.00	26.56	0.20	84.60	0.959
186.30	28.96	0.20	86.10	0.936
197.50	31.82	0.30	107.80	0.693
208.80	35.24	0.60	128.10	0.484
220.00	38.08	1.40	147.10	0.321



Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

REV. A
M98898
BIF-21.4
070509

Coaxial Band Pass Filter(Constant Impedance) BIF-21.4+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.00	25.27	52.20	1.2	4.399
1.10	24.55	51.70	1.3	6.493
1.12	24.91	51.60	1.4	5.803
1.20	23.93	51.20	2.6	6.877
1.22	24.24	51.40	3.7	7.658
1.30	23.64	50.90	4.9	8.204
1.40	23.17	50.10	5.0	8.142
3.70	15.71	41.80	7.9	9.473
4.90	13.27	39.00	11.0	11.528
6.00	11.38	36.80	14.0	14.015
8.70	7.85	32.80	15.0	14.909
11.30	5.18	29.50	17.9	16.385
14.00	2.92	27.20	18.8	16.348
18.00	0.72	26.50	19.8	16.309
20.30	0.14	26.20	20.9	15.915
21.50	0.01	25.80	21.6	15.629
23.80	0.05	26.00	22.4	15.139
40.00	2.02	31.00	23.2	14.502
55.00	7.93	34.80	24.0	13.843
70.00	10.88	35.60	24.8	13.162
85.00	13.23	34.40	26.2	11.927
100.00	15.41	32.90	32.7	6.934
116.70	17.64	31.40	33.9	6.349
133.30	19.87	30.20	51.3	2.263
150.00	22.27	29.20	67.6	1.347
175.00	26.56	27.70	84.6	0.959
186.30	28.96	27.10	86.1	0.936
197.50	31.82	26.60	107.8	0.693
208.80	35.24	26.00	128.1	0.484
220.00	38.08	25.60	147.1	0.321

REV. X1
BIF-21.4+
060724
Page 1 of 1






Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Coaxial Band Pass Filter(Constant Impedance) BIF-21.4+

Typical Performance Curves



REV. X1
BIF-21.4+
060724
Page 1 of 1



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF55	--	.57 (14.47)	--	2.59 (65.79)	--	40.0

Dimensions are in inches (mm). Tolerances: 2Pl. +.03/-.04; 3Pl. ± .015

Note:

- Case material: Stainless steel.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I