

Power Splitter/Combiner

BP2G+



Generic photo used for illustration purposes only

CASE STYLE: XX211


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-65°C to 150°C
Power Input (as a splitter)	1.5W max.
Internal Dissipation	0.75W max.
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

SUM PORT	2
PORT 1	8
PORT 2	5
GROUND	1,3,4,6,7

Outline Drawing




Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.163	.210	.077	.250	.220	.050	.017
4.14	5.33	1.96	6.35	5.59	1.27	0.43

H	J	K	M	N	P	wt
.009	.025	.030	.050	.030	.270	grams
0.23	0.64	0.76	1.27	0.76	6.86	0.10

Demo Board MCL P/N: TB-37 Suggested PCB Layout (PL-053)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Features

- low insertion loss, 0.4 dB typ.
- high isolation, 28 dB typ.
- good output VSWR, 1.15:1 typ.
- good input VSWR, 1.2:1 typ.
- excellent power handling, 1.5W
- low profile, 0.077"

Applications

- GPS
- PDC
- mobile satellite
- defense & aeronautical

Electrical Specifications




FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) ABOVE 3.0 dB		PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)	VSWR (:1)	
	Typ.	Min.*	Typ.	Max.			S-Port Typ.	Output Ports Typ.
1420-1660	28	20	0.6	1.0	3.0	0.2	1.15	1.15

* 17 dB over 1420-1500 MHz

Typical Performance Data at 25°C

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
1420.00	3.30	3.23	0.07	18.76	0.46	1.09	1.18	1.17
1440.00	3.30	3.23	0.07	19.68	0.47	1.08	1.17	1.16
1460.00	3.30	3.24	0.06	20.71	0.51	1.08	1.16	1.15
1480.00	3.31	3.24	0.07	21.88	0.52	1.08	1.16	1.15
1500.00	3.32	3.24	0.08	23.24	0.54	1.09	1.16	1.14
1520.00	3.32	3.25	0.07	24.76	0.55	1.11	1.16	1.14
1540.00	3.33	3.25	0.08	26.62	0.59	1.13	1.16	1.14
1560.00	3.34	3.26	0.08	28.87	0.60	1.15	1.17	1.15
1580.00	3.35	3.27	0.08	31.75	0.64	1.17	1.18	1.16
1600.00	3.36	3.28	0.08	35.01	0.66	1.20	1.20	1.17
1620.00	3.37	3.29	0.08	36.48	0.68	1.23	1.21	1.18
1640.00	3.39	3.30	0.09	33.93	0.71	1.25	1.23	1.20
1660.00	3.41	3.32	0.09	30.75	0.74	1.28	1.25	1.22

1. Total Loss = Insertion Loss + 3dB splitter loss.



electrical schematic



ESD Rating

Human Body Model (HBM): Class 1A (250 v to <500 v) in accordance with ANSI/ESD STM 5.1 - 2001
Machine Model (MM): Class M1 (< 100 v) in accordance with ANSI/ESD STM 5.2 - 1999 (pass 50V)

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



2 Way-0° Power Splitter/Combiner

BP2G+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10dBm @ Temperature = +25°C

FREQUENCY (MHz)	Total Loss ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB)	PHASE UNBALANCE (Deg)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
1420.0	3.30	3.23	0.07	18.76	0.46	1420.0	1.09	1.18	1.17
1425.0	3.30	3.24	0.06	18.97	0.48	1425.0	1.08	1.17	1.17
1430.0	3.30	3.24	0.06	19.21	0.47	1430.0	1.08	1.17	1.17
1435.0	3.30	3.24	0.06	19.44	0.47	1435.0	1.08	1.17	1.17
1440.0	3.30	3.23	0.07	19.68	0.47	1440.0	1.08	1.17	1.16
1445.0	3.30	3.24	0.07	19.93	0.48	1445.0	1.08	1.16	1.16
1450.0	3.31	3.24	0.07	20.19	0.49	1450.0	1.08	1.16	1.16
1455.0	3.30	3.23	0.07	20.46	0.49	1455.0	1.08	1.16	1.16
1460.0	3.30	3.24	0.06	20.71	0.51	1460.0	1.08	1.16	1.15
1465.0	3.31	3.24	0.07	20.97	0.49	1465.0	1.08	1.16	1.15
1470.0	3.31	3.24	0.07	21.28	0.52	1470.0	1.08	1.16	1.15
1475.0	3.31	3.24	0.07	21.59	0.52	1475.0	1.08	1.16	1.15
1480.0	3.31	3.24	0.07	21.88	0.52	1480.0	1.08	1.16	1.15
1485.0	3.31	3.24	0.07	22.20	0.52	1485.0	1.08	1.16	1.14
1490.0	3.31	3.24	0.07	22.53	0.53	1490.0	1.09	1.16	1.14
1495.0	3.31	3.24	0.07	22.88	0.54	1495.0	1.09	1.16	1.14
1500.0	3.32	3.24	0.08	23.24	0.54	1500.0	1.09	1.16	1.14
1505.0	3.32	3.24	0.08	23.58	0.54	1505.0	1.10	1.16	1.14
1510.0	3.32	3.25	0.07	23.97	0.56	1510.0	1.10	1.16	1.14
1515.0	3.32	3.24	0.08	24.35	0.55	1515.0	1.10	1.16	1.14
1520.0	3.32	3.25	0.07	24.76	0.55	1520.0	1.11	1.16	1.14
1525.0	3.32	3.25	0.08	25.20	0.57	1525.0	1.11	1.16	1.14
1530.0	3.32	3.25	0.07	25.67	0.57	1530.0	1.12	1.16	1.14
1535.0	3.33	3.25	0.08	26.11	0.58	1535.0	1.12	1.16	1.14
1540.0	3.33	3.25	0.08	26.62	0.59	1540.0	1.13	1.16	1.14
1545.0	3.33	3.25	0.08	27.14	0.59	1545.0	1.13	1.17	1.14
1550.0	3.33	3.26	0.08	27.70	0.60	1550.0	1.14	1.17	1.15
1555.0	3.33	3.26	0.08	28.29	0.59	1555.0	1.14	1.17	1.15
1560.0	3.34	3.26	0.08	28.87	0.60	1560.0	1.15	1.17	1.15
1565.0	3.34	3.26	0.08	29.56	0.62	1565.0	1.16	1.18	1.15
1570.0	3.34	3.26	0.08	30.25	0.62	1570.0	1.16	1.18	1.15
1575.0	3.35	3.27	0.08	30.97	0.63	1575.0	1.17	1.18	1.15
1580.0	3.35	3.27	0.08	31.75	0.64	1580.0	1.17	1.18	1.16
1585.0	3.35	3.27	0.08	32.55	0.64	1585.0	1.18	1.19	1.16
1590.0	3.35	3.27	0.08	33.36	0.64	1590.0	1.19	1.19	1.16
1595.0	3.35	3.27	0.08	34.19	0.65	1595.0	1.19	1.19	1.16
1600.0	3.36	3.28	0.08	35.01	0.66	1600.0	1.20	1.20	1.17
1605.0	3.36	3.28	0.09	35.67	0.66	1605.0	1.21	1.20	1.17
1610.0	3.37	3.28	0.08	36.24	0.66	1610.0	1.21	1.20	1.18
1615.0	3.37	3.29	0.08	36.51	0.67	1615.0	1.22	1.21	1.18
1620.0	3.37	3.29	0.08	36.48	0.68	1620.0	1.23	1.21	1.18
1625.0	3.38	3.29	0.08	36.11	0.69	1625.0	1.23	1.22	1.19
1630.0	3.38	3.30	0.09	35.58	0.69	1630.0	1.24	1.22	1.19
1635.0	3.39	3.30	0.09	34.79	0.71	1635.0	1.25	1.23	1.20
1640.0	3.39	3.30	0.09	33.93	0.71	1640.0	1.25	1.23	1.20
1645.0	3.39	3.30	0.09	33.11	0.70	1645.0	1.26	1.23	1.20
1650.0	3.39	3.31	0.08	32.28	0.74	1650.0	1.27	1.24	1.21
1655.0	3.40	3.31	0.09	31.44	0.72	1655.0	1.28	1.24	1.21
1660.0	3.41	3.32	0.09	30.75	0.74	1660.0	1.28	1.25	1.22

¹Total Loss = Insertion Loss + 3dB Splitter Loss



REV. X3

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site BP2G+



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

2/17/2011

IF/RF MICROWAVE COMPONENTS

Page 1 of 3

2 Way-0° Power Splitter/Combiner

BP2G+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10dBm @ Temperature = -45°C

FREQUENCY (MHz)	Total Loss ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB)	PHASE UNBALANCE (Deg)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
1420.0	3.18	3.11	0.07	18.03	0.62	1420.0	1.09	1.19	1.20
1425.0	3.18	3.11	0.07	18.23	0.64	1425.0	1.09	1.19	1.19
1430.0	3.18	3.11	0.07	18.43	0.65	1430.0	1.08	1.19	1.19
1435.0	3.18	3.11	0.07	18.65	0.65	1435.0	1.08	1.19	1.19
1440.0	3.18	3.10	0.08	18.85	0.64	1440.0	1.08	1.19	1.19
1445.0	3.18	3.11	0.07	19.08	0.65	1445.0	1.08	1.19	1.18
1450.0	3.18	3.11	0.08	19.30	0.66	1450.0	1.07	1.18	1.18
1455.0	3.18	3.11	0.08	19.53	0.67	1455.0	1.07	1.18	1.18
1460.0	3.18	3.11	0.07	19.76	0.68	1460.0	1.07	1.18	1.18
1465.0	3.18	3.11	0.07	19.98	0.67	1465.0	1.07	1.18	1.18
1470.0	3.18	3.11	0.08	20.24	0.69	1470.0	1.07	1.18	1.17
1475.0	3.19	3.11	0.08	20.51	0.70	1475.0	1.07	1.18	1.17
1480.0	3.18	3.10	0.08	20.75	0.69	1480.0	1.07	1.18	1.17
1485.0	3.19	3.11	0.08	21.02	0.70	1485.0	1.07	1.18	1.17
1490.0	3.19	3.11	0.08	21.30	0.72	1490.0	1.08	1.18	1.17
1495.0	3.19	3.11	0.08	21.59	0.70	1495.0	1.08	1.18	1.17
1500.0	3.19	3.11	0.08	21.89	0.72	1500.0	1.08	1.18	1.17
1505.0	3.19	3.11	0.08	22.17	0.71	1505.0	1.09	1.18	1.17
1510.0	3.19	3.11	0.08	22.48	0.73	1510.0	1.09	1.18	1.17
1515.0	3.19	3.11	0.08	22.78	0.72	1515.0	1.09	1.18	1.17
1520.0	3.19	3.11	0.08	23.11	0.73	1520.0	1.10	1.19	1.17
1525.0	3.19	3.11	0.08	23.46	0.75	1525.0	1.10	1.19	1.17
1530.0	3.19	3.11	0.08	23.82	0.74	1530.0	1.11	1.19	1.17
1535.0	3.20	3.11	0.08	24.17	0.76	1535.0	1.11	1.19	1.17
1540.0	3.20	3.11	0.08	24.56	0.77	1540.0	1.12	1.19	1.17
1545.0	3.20	3.12	0.08	24.96	0.77	1545.0	1.12	1.19	1.17
1550.0	3.20	3.12	0.08	25.38	0.79	1550.0	1.13	1.20	1.17
1555.0	3.20	3.12	0.08	25.82	0.78	1555.0	1.14	1.20	1.18
1560.0	3.21	3.12	0.08	26.24	0.79	1560.0	1.14	1.20	1.18
1565.0	3.21	3.12	0.09	26.73	0.80	1565.0	1.15	1.21	1.18
1570.0	3.21	3.12	0.09	27.20	0.80	1570.0	1.15	1.21	1.18
1575.0	3.21	3.13	0.08	27.69	0.81	1575.0	1.16	1.21	1.18
1580.0	3.22	3.13	0.08	28.24	0.82	1580.0	1.17	1.21	1.19
1585.0	3.22	3.13	0.09	28.77	0.81	1585.0	1.17	1.22	1.19
1590.0	3.22	3.13	0.09	29.32	0.82	1590.0	1.18	1.22	1.19
1595.0	3.22	3.13	0.09	29.90	0.84	1595.0	1.19	1.22	1.20
1600.0	3.23	3.14	0.09	30.50	0.85	1600.0	1.19	1.23	1.20
1605.0	3.23	3.14	0.09	31.03	0.84	1605.0	1.20	1.23	1.20
1610.0	3.23	3.14	0.09	31.63	0.85	1610.0	1.21	1.24	1.21
1615.0	3.24	3.15	0.09	32.17	0.87	1615.0	1.21	1.24	1.21
1620.0	3.24	3.15	0.09	32.64	0.88	1620.0	1.22	1.24	1.21
1625.0	3.24	3.15	0.09	33.00	0.87	1625.0	1.23	1.25	1.22
1630.0	3.24	3.15	0.09	33.34	0.89	1630.0	1.24	1.25	1.22
1635.0	3.25	3.16	0.09	33.45	0.90	1635.0	1.24	1.26	1.23
1640.0	3.25	3.16	0.09	33.33	0.90	1640.0	1.25	1.26	1.23
1645.0	3.25	3.16	0.09	33.12	0.90	1645.0	1.26	1.27	1.23
1650.0	3.25	3.16	0.09	32.83	0.93	1650.0	1.27	1.27	1.24
1655.0	3.26	3.17	0.10	32.34	0.92	1655.0	1.27	1.28	1.24
1660.0	3.27	3.17	0.10	31.91	0.93	1660.0	1.28	1.28	1.25

¹Total Loss = Insertion Loss + 3dB Splitter Loss



REV. X3

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site BP2G+
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

2/17/2011
 Page 2 of 3

2 Way-0° Power Splitter/Combiner

BP2G+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10dBm @ Temperature = +85°C

FREQUENCY (MHz)	Total Loss ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB)	PHASE UNBALANCE (Deg)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
1420.0	3.37	3.32	0.05	19.43	0.35	1420.0	1.08	1.17	1.16
1425.0	3.37	3.32	0.06	19.67	0.37	1425.0	1.07	1.16	1.16
1430.0	3.37	3.32	0.06	19.92	0.37	1430.0	1.07	1.16	1.16
1435.0	3.38	3.32	0.06	20.18	0.38	1435.0	1.07	1.16	1.15
1440.0	3.38	3.32	0.06	20.43	0.37	1440.0	1.07	1.15	1.15
1445.0	3.38	3.32	0.06	20.72	0.37	1445.0	1.07	1.15	1.15
1450.0	3.38	3.32	0.06	20.99	0.37	1450.0	1.07	1.15	1.14
1455.0	3.38	3.32	0.06	21.30	0.39	1455.0	1.07	1.15	1.14
1460.0	3.38	3.32	0.06	21.60	0.39	1460.0	1.07	1.14	1.14
1465.0	3.38	3.32	0.06	21.87	0.39	1465.0	1.07	1.14	1.14
1470.0	3.39	3.33	0.06	22.22	0.41	1470.0	1.08	1.14	1.13
1475.0	3.39	3.33	0.06	22.57	0.41	1475.0	1.08	1.14	1.13
1480.0	3.39	3.32	0.06	22.90	0.41	1480.0	1.08	1.14	1.13
1485.0	3.39	3.33	0.06	23.27	0.41	1485.0	1.08	1.14	1.13
1490.0	3.39	3.33	0.06	23.66	0.42	1490.0	1.09	1.14	1.13
1495.0	3.39	3.33	0.06	24.06	0.42	1495.0	1.09	1.14	1.12
1500.0	3.39	3.33	0.06	24.49	0.42	1500.0	1.09	1.13	1.12
1505.0	3.40	3.33	0.06	24.90	0.44	1505.0	1.10	1.13	1.12
1510.0	3.39	3.33	0.06	25.35	0.44	1510.0	1.10	1.13	1.12
1515.0	3.40	3.33	0.06	25.81	0.44	1515.0	1.10	1.13	1.12
1520.0	3.40	3.34	0.06	26.30	0.44	1520.0	1.11	1.13	1.12
1525.0	3.40	3.34	0.06	26.84	0.46	1525.0	1.11	1.13	1.12
1530.0	3.40	3.34	0.06	27.42	0.45	1530.0	1.12	1.14	1.12
1535.0	3.41	3.34	0.06	27.97	0.46	1535.0	1.13	1.14	1.12
1540.0	3.41	3.35	0.07	28.64	0.47	1540.0	1.13	1.14	1.12
1545.0	3.41	3.35	0.06	29.31	0.47	1545.0	1.14	1.14	1.12
1550.0	3.41	3.35	0.06	30.07	0.49	1550.0	1.14	1.14	1.12
1555.0	3.42	3.35	0.06	30.89	0.49	1555.0	1.15	1.14	1.12
1560.0	3.42	3.35	0.07	31.67	0.48	1560.0	1.15	1.14	1.12
1565.0	3.42	3.35	0.07	32.66	0.51	1565.0	1.16	1.15	1.13
1570.0	3.42	3.36	0.07	33.71	0.50	1570.0	1.16	1.15	1.13
1575.0	3.43	3.36	0.07	34.79	0.51	1575.0	1.17	1.15	1.13
1580.0	3.43	3.36	0.07	35.93	0.52	1580.0	1.18	1.16	1.13
1585.0	3.43	3.36	0.07	37.13	0.51	1585.0	1.18	1.16	1.14
1590.0	3.44	3.37	0.07	38.18	0.52	1590.0	1.19	1.16	1.14
1595.0	3.44	3.37	0.07	39.09	0.53	1595.0	1.19	1.16	1.14
1600.0	3.44	3.37	0.07	39.48	0.55	1600.0	1.20	1.17	1.14
1605.0	3.45	3.38	0.07	39.17	0.55	1605.0	1.21	1.17	1.15
1610.0	3.45	3.38	0.07	38.53	0.54	1610.0	1.21	1.18	1.15
1615.0	3.45	3.38	0.07	37.37	0.56	1615.0	1.22	1.18	1.15
1620.0	3.46	3.39	0.07	36.25	0.56	1620.0	1.23	1.18	1.16
1625.0	3.46	3.39	0.07	35.09	0.56	1625.0	1.23	1.19	1.16
1630.0	3.47	3.39	0.07	34.06	0.58	1630.0	1.24	1.19	1.16
1635.0	3.47	3.40	0.07	32.94	0.58	1635.0	1.25	1.20	1.17
1640.0	3.47	3.40	0.07	32.04	0.59	1640.0	1.25	1.20	1.17
1645.0	3.47	3.40	0.07	31.16	0.59	1645.0	1.26	1.20	1.18
1650.0	3.48	3.41	0.07	30.36	0.61	1650.0	1.27	1.21	1.18
1655.0	3.49	3.41	0.08	29.61	0.61	1655.0	1.27	1.21	1.19
1660.0	3.49	3.41	0.08	28.95	0.62	1660.0	1.28	1.22	1.19

¹Total Loss = Insertion Loss + 3dB Splitter Loss



REV. X3

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site BP2G+



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

2/17/2011






IF/RF MICROWAVE COMPONENTS

Page 3 of 3

2 Way-0° Power Splitter/Combiner

BP2G+

Typical Performance Curves



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




IF/RF MICROWAVE COMPONENTS

REV. X3
BP2G+
2/17/2011
Page 1 of 2

2 Way-0° Power Splitter/Combiner

BP2G+

Typical Performance Curves



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




IF/RF MICROWAVE COMPONENTS


minicircuits.com

REV. X3
BP2G+
2/17/2011
Page 2 of 2

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P
XX211	.163 (4.14)	.210 (5.33)	.077 (1.96)	.250 (6.35)	.220 (5.59)	.050 (1.27)	.017 (0.43)	.009 (0.23)	.025 (0.64)	.030 (0.76)	-- --	.050 (1.27)	.030 (0.76)	.270 (6.86)

CASE #	Q	R	S	WT. GRAM
XX211	-- --	-- --	-- --	.10

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Plastic.
 - Termination finish:
For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier. All models, (+) suffix. ☉
For RoHS-5 Case Styles: Tin-Lead plate. All models, No (+) suffix.
 - Special Tolerances: Termination width $\pm .005$ inch, termination thickness $\pm .003$ inch.
- ☉ Model BP4C+ will be supplied with either Tin finish or Tin-Silver-Nickel finish until Tin finish inventory is depleted.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F16



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
				50
				100
				200
				500
			Standard	1000*
		13	Standard	2000**

Note : Please Consult individual model data sheet to determine device per reel availability

* BP models only

** MSW and MSWA models

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82272	NEW RELEASE	08/06/02	GF	DJ
A	M102713	UPDATED NOTES, ADDED "...WITH SMOBC"	01/16/06	GT	IL

SUGGESTED MOUNTING CONFIGURATION FOR XX211 CASE STYLE, "jm" PIN CONNECTION



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $0.020'' \pm 0.0015''$. COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

GF

07/17/02

TOLERANCES ON:

CHECKED

HY

08/06/02

2 PL DECIMALS $\pm$

APPROVED

DJ

08/06/02

3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$
 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, jm, XX211, BP2, TB-37

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-053

REV:

A

FILE: 98PL053


SCALE:

8:1


SHEET:

1 OF 1

Evaluation Board and Circuit



TB-37



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D