

Surface Mount Directional Coupler

75Ω, 20dB coupling, 5 to 1250 MHz


DBTC-20-4+

Features

- very flat coupling
- very broadband, multi octave
- temperature stable, LTCC base
- all welded construction
- leads attached for better solderability
- micro miniature coupler
- aqueous washable
- protected by US Patents 6,140,887 & 6,784,521

Applications

- CATV



Generic photo used for illustration purposes only

CASE STYLE: AT790-1

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost	
Reel Size	Devices/Reel
7"	20, 50, 100, 200, 500
13"	1000, 2000

Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		5		1250	MHz
Mainline Loss ¹	5-50		0.4	0.7	dB
	50-500		0.6	0.9	
	500-1000		0.8	1.2	
	1000-1250		1.1	1.5	
Nominal Coupling	5-1250		20.5 ±0.5		dB
Coupling Flatness(±)	5-1250			±0.9	dB
Directivity	5-50	16	20		dB
	50-500	13	19		
	500-1000	7	11		
	1000-1250	6	9		
VSWR ²	5-1000		1.4		dB
Input Power	5-50			0.5	W
	50-500			1.0	
	500-1000			1.0	
	1000-1250			1.0	

1. Includes theoretical coupled power loss of 0.04 dB at 20 dB coupling.

2. For coupled port VSWR above 500 MHz, 1.6:1 typ.

Maximum Ratings


Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

Function	Pin Number
INPUT	3
OUTPUT	4
COUPLED	1
GROUND	2
ISOLATE (DO NOT USE)	6

Electrical Schematic




* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) THAT ROUTES DC FROM RF PORTS TO GROUND.




DBTC-20-4+

Outline Drawing




PCB Land Pattern



Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H	J	K	wt
.150	.150	.150	.050	.030	.025	.028	.050	.160	.030	grams
3.81	3.81	3.81	1.27	0.76	0.64	0.71	1.27	4.06	0.76	0.10

Demo Board MCL P/N: TB-279
Suggested PCB Layout (PL-150)






- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
				In	Out	Cpl
20.00	0.33	20.30	19.79	28.00	30.48	26.85
100.00	0.35	20.25	22.11	29.28	31.80	27.18
200.00	0.38	20.28	23.36	29.12	30.13	24.16
300.00	0.41	20.32	24.66	27.95	28.09	21.44
400.00	0.43	20.36	25.00	27.01	26.54	19.23
500.00	0.48	20.40	23.74	26.41	25.97	17.30
600.00	0.53	20.43	21.33	25.99	25.74	15.69
700.00	0.58	20.50	19.06	25.78	26.00	14.31
800.00	0.63	20.59	17.10	26.16	26.88	13.07
1000.00	0.70	20.94	14.20	28.41	29.64	11.03



Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Directional Coupler

DBTC-20-4+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +25°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
5.0	0.30	20.07	23.25	28.99	31.76	26.24
10.0	0.30	20.06	23.40	29.76	33.03	26.98
15.0	0.29	20.04	23.51	30.37	34.03	27.55
20.0	0.29	20.04	23.52	30.51	34.28	27.67
50.0	0.31	20.06	23.55	31.05	34.92	27.78
100.0	0.32	20.09	23.93	31.49	35.94	27.30
150.0	0.33	20.11	24.54	31.85	37.09	26.31
200.0	0.34	20.12	25.40	32.12	38.45	25.08
250.0	0.35	20.14	26.45	32.43	40.40	23.86
300.0	0.36	20.15	27.94	32.77	42.98	22.67
350.0	0.38	20.16	29.79	32.79	44.62	21.55
400.0	0.39	20.17	32.01	33.31	44.59	20.56
450.0	0.40	20.17	33.80	33.45	41.62	19.66
500.0	0.42	20.19	33.34	33.88	38.03	18.84
525.0	0.43	20.19	32.12	34.06	36.47	18.45
550.0	0.44	20.20	30.78	34.13	35.18	18.09
600.0	0.46	20.21	28.18	34.48	33.16	17.39
650.0	0.48	20.24	25.97	34.52	31.25	16.75
700.0	0.51	20.27	24.12	34.24	29.47	16.18
750.0	0.53	20.30	22.51	33.98	28.12	15.65
800.0	0.56	20.35	21.14	33.52	26.93	15.14
850.0	0.59	20.39	19.99	32.80	25.82	14.66
900.0	0.62	20.45	18.98	31.67	24.73	14.22
950.0	0.65	20.52	18.10	30.72	23.66	13.80
1000.0	0.68	20.59	17.36	29.83	22.89	13.41
1050.0	0.71	20.66	16.67	28.93	22.13	13.05
1100.0	0.74	20.75	16.06	27.99	21.34	12.70
1150.0	0.78	20.85	15.57	27.01	20.62	12.37
1200.0	0.82	20.95	15.05	26.24	19.94	12.06
1250.0	0.86	21.06	14.61	25.41	19.31	11.78
1300.0	0.89	21.18	14.23	24.58	18.69	11.51
1400.0	0.97	21.45	13.54	23.08	17.62	11.00
1500.0	1.06	21.76	12.89	21.69	16.55	10.55
1600.0	1.15	22.12	12.24	20.53	15.69	10.16
1700.0	1.26	22.54	11.43	19.36	14.77	9.79
1800.0	1.37	23.01	10.48	18.42	14.02	9.48
1900.0	1.50	23.57	9.15	17.45	13.25	9.20
2000.0	1.64	24.19	7.57	16.64	12.59	8.95
2100.0	1.79	24.92	5.58	15.83	11.98	8.72
2200.0	1.97	25.80	3.35	15.02	11.35	8.52
2300.0	2.17	26.81	0.88	14.33	10.81	8.33
2400.0	2.41	27.93	1.74	13.59	10.25	8.18
2500.0	2.69	29.20	4.46	12.95	9.74	8.01
2600.0	3.01	30.53	7.20	12.33	9.24	7.86
2700.0	3.38	31.09	9.11	11.71	8.80	7.72
2800.0	3.83	30.58	9.87	11.16	8.35	7.55
2900.0	4.36	29.06	9.55	10.63	7.95	7.43
3000.0	4.96	27.14	8.74	10.14	7.61	7.24
3100.0	5.67	25.21	7.84	9.70	7.30	7.08
3200.0	6.47	23.52	7.08	9.25	7.02	6.88
3300.0	7.35	21.98	6.37	8.88	6.84	6.65
3400.0	8.27	20.69	5.80	8.53	6.69	6.45
3500.0	9.09	19.57	5.29	8.23	6.61	6.19



P.O. Box 350166, Brooklyn, New York 11235-0003 • (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
DBTC-20-4+
6/27/2013
Page 1 of 3

Directional Coupler

DBTC-20-4+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = -40°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
5.0	0.38	20.23	21.33	24.93	26.29	21.97
10.0	0.30	20.06	23.61	27.75	29.98	24.56
15.0	0.25	19.92	25.43	30.06	33.19	26.71
20.0	0.24	19.90	25.86	30.87	35.00	27.56
50.0	0.24	19.89	26.22	32.12	40.15	29.42
100.0	0.24	19.91	26.32	34.00	38.68	28.80
150.0	0.24	19.92	26.76	35.52	39.39	26.99
200.0	0.25	19.92	27.72	34.20	41.03	25.92
250.0	0.26	19.93	28.94	34.68	40.14	24.41
300.0	0.27	19.94	30.71	34.52	42.44	23.08
350.0	0.28	19.95	32.84	34.28	40.99	22.04
400.0	0.29	19.96	35.09	35.12	40.95	20.94
450.0	0.30	19.97	36.38	34.88	38.48	20.08
500.0	0.31	19.99	34.53	35.61	36.63	19.26
525.0	0.32	20.00	32.77	35.57	35.41	18.85
550.0	0.33	20.01	31.19	35.28	34.03	18.50
600.0	0.34	20.04	28.32	35.98	32.76	17.80
650.0	0.36	20.07	26.22	37.42	31.82	17.14
700.0	0.38	20.11	24.44	37.62	30.23	16.62
750.0	0.40	20.15	22.88	38.00	29.04	16.10
800.0	0.42	20.20	21.48	37.38	27.59	15.64
850.0	0.45	20.25	20.21	37.36	26.63	15.21
900.0	0.48	20.32	19.16	36.36	25.67	14.77
950.0	0.50	20.40	18.20	35.47	24.61	14.39
1000.0	0.53	20.48	17.42	34.74	24.02	13.98
1050.0	0.55	20.58	16.65	33.18	23.08	13.61
1100.0	0.59	20.68	15.95	32.16	22.26	13.32
1150.0	0.62	20.80	15.31	30.46	21.41	12.99
1200.0	0.66	20.93	14.67	29.33	20.52	12.68
1250.0	0.69	21.07	14.13	28.70	20.11	12.42
1300.0	0.73	21.22	13.62	27.28	19.34	12.16
1400.0	0.81	21.56	12.62	25.77	18.06	11.67
1500.0	0.90	21.94	11.56	24.43	17.19	11.32
1600.0	1.00	22.42	10.44	22.28	15.73	10.96
1700.0	1.10	22.94	9.13	21.28	14.97	10.66
1800.0	1.22	23.55	7.61	20.09	14.06	10.39
1900.0	1.36	24.28	5.81	18.87	13.10	10.13
2000.0	1.50	25.09	3.81	18.14	12.49	9.92
2100.0	1.67	26.06	1.55	17.05	11.64	9.73
2200.0	1.83	27.04	0.82	16.73	11.45	9.59
2300.0	2.07	28.28	3.44	15.67	10.56	9.44
2400.0	2.29	29.36	5.87	15.22	10.20	9.27
2500.0	2.59	30.19	8.02	14.45	9.59	9.09
2600.0	2.90	30.02	9.19	13.94	9.22	9.01
2700.0	3.27	28.92	9.32	13.32	8.80	8.87
2800.0	3.75	27.24	8.81	12.61	8.20	8.69
2900.0	4.27	25.31	8.01	11.92	7.85	8.49
3000.0	4.87	23.64	7.36	11.31	7.53	8.21
3100.0	5.57	21.92	6.56	10.96	7.14	7.92
3200.0	6.32	20.54	6.07	10.49	6.95	7.71
3300.0	7.13	19.26	5.54	10.16	6.76	7.38
3400.0	7.95	18.14	5.08	9.82	6.63	7.04
3500.0	8.70	17.22	4.70	9.36	6.58	6.63



P.O. Box 350166, Brooklyn, New York 11235-0003 • (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR
DBTC-20-4+
6/27/2013
Page 2 of 3

Directional Coupler

DBTC-20-4+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +85°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
5.0	0.40	20.30	21.38	26.76	28.94	24.74
10.0	0.39	20.27	21.58	27.42	29.77	25.39
15.0	0.39	20.25	21.73	27.96	30.43	25.90
20.0	0.39	20.25	21.75	28.13	30.55	26.00
50.0	0.40	20.27	21.95	28.93	30.58	25.96
100.0	0.42	20.31	22.53	29.08	31.89	25.78
150.0	0.43	20.34	23.37	28.97	33.74	25.53
200.0	0.44	20.37	24.51	29.59	34.58	24.48
250.0	0.45	20.39	25.89	30.00	36.90	23.39
300.0	0.46	20.42	27.87	30.34	40.28	22.41
350.0	0.47	20.45	30.56	30.68	43.70	21.33
400.0	0.49	20.48	33.75	31.29	52.92	20.34
450.0	0.51	20.52	34.00	31.51	46.77	19.48
500.0	0.53	20.56	30.56	32.01	40.06	18.64
525.0	0.54	20.59	28.60	32.16	37.63	18.23
550.0	0.55	20.61	26.88	32.22	35.90	17.86
600.0	0.57	20.67	24.06	32.49	33.29	17.14
650.0	0.60	20.73	21.89	32.47	31.08	16.44
700.0	0.63	20.80	20.08	32.06	29.06	15.81
750.0	0.65	20.88	18.59	31.76	27.76	15.22
800.0	0.68	20.96	17.30	31.12	26.56	14.65
850.0	0.71	21.05	16.21	30.20	25.34	14.12
900.0	0.74	21.14	15.29	29.10	24.22	13.62
950.0	0.76	21.23	14.42	28.20	23.21	13.14
1000.0	0.79	21.33	13.72	27.41	22.51	12.70
1050.0	0.82	21.43	13.07	26.53	21.76	12.30
1100.0	0.85	21.55	12.49	25.70	21.01	11.91
1150.0	0.88	21.66	11.99	24.95	20.43	11.54
1200.0	0.92	21.77	11.53	24.23	19.80	11.21
1250.0	0.95	21.90	11.12	23.45	19.14	10.90
1300.0	0.98	22.02	10.76	22.83	18.66	10.61
1400.0	1.05	22.29	10.17	21.54	17.72	10.06
1500.0	1.13	22.59	9.69	20.30	16.71	9.57
1600.0	1.20	22.93	9.29	19.30	15.95	9.15
1700.0	1.30	23.33	8.95	18.14	14.98	8.73
1800.0	1.39	23.77	8.68	17.41	14.37	8.38
1900.0	1.50	24.28	8.30	16.65	13.75	8.08
2000.0	1.62	24.84	7.81	15.88	13.09	7.83
2100.0	1.75	25.56	6.88	15.21	12.55	7.58
2200.0	1.91	26.39	5.66	14.35	11.83	7.35
2300.0	2.08	27.35	3.87	13.70	11.34	7.15
2400.0	2.28	28.53	1.54	13.01	10.81	6.99
2500.0	2.51	30.09	1.36	12.42	10.30	6.80
2600.0	2.79	32.16	4.80	11.72	9.70	6.65
2700.0	3.11	34.80	8.87	11.07	9.22	6.50
2800.0	3.48	37.91	13.33	10.52	8.77	6.33
2900.0	3.91	38.88	15.62	10.06	8.36	6.25
3000.0	4.44	35.63	13.61	9.57	7.91	6.11
3100.0	5.06	31.94	11.10	9.11	7.59	6.02
3200.0	5.80	29.06	9.28	8.56	7.18	5.86
3300.0	6.67	26.69	7.89	8.08	6.84	5.72
3400.0	7.63	24.81	6.90	7.62	6.56	5.61
3500.0	8.62	23.23	6.13	7.27	6.37	5.47



REV. OR
DBTC-20-4+
6/27/2013
Page 3 of 3

P.O. Box 350166, Brooklyn, New York 11235-0003 • (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




IF/RF MICROWAVE COMPONENTS

Directional Coupler


Typical Performance Curves

DBTC-20-4+


Insertion Loss




Insertion Loss vs. TEMPERATURE



Coupling Loss vs. TEMPERATURE



Directivity vs. TEMPERATURE




Directional Coupler


Typical Performance Curves

DBTC-20-4+


Return Loss




Return Loss In vs. TEMPERATURE



Return Loss Out vs. TEMPERATURE



Return Loss Cpl vs. TEMPERATURE



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com





IF/RF MICROWAVE COMPONENTS




REV. OR
DBTC-20-4+
6/27/2013
Page 2 of 2

Outline Dimensions

AT790-1



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	WT. GRAMS
AT790-1	.150 (3.81)	.150 (3.81)	.150 (3.81)	.050 (1.27)	.030 (0.76)	.025 (0.64)	.028 (0.71)	.050 (1.27)	.160 (4.06)	.030 (0.76)	-- --	.10

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Open style, Ceramic base.
2. Termination finish: Palladium Silver.



P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F17

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
12	8	7	Small quantity standards (see note)	20
				50
				100
				200
				500
		13	Standard	1000
				2000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M90454	NEW RELEASE	01/16/04	AV	WP
A	M93049	AT1030 WAS AT1029	07/02/04	MMG	WP
B	M102713	ADDED "...WITH SMOBC"	01/17/06	MMG	IL


SUGGESTED MOUNTING CONFIGURATION FOR AT1030 CASE STYLE, "na" PIN CONNECTION



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS $0.020'' \pm 0.0015''$; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

DRAWN

AV

01/08/04

CHECKED

IL

01/16/04

APPROVED

WP

01/16/04



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, na, AT1030, DBTC, TB-278

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-150

REV:

B

FILE:

98PL150

SCALE:

10:1

SHEET:


1 OF 1

Mini-Circuits®


THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit



TB-278



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers R04350B or its equivalent,  Mini-Circuits®
Dielectric Constant=3.5, Thickness=.020"



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215