



Mini-Circuits

MMIC SURFACE MOUNT


Power Splitter/Combiner

GP2Y1+

2 Way-0° 50Ω 1550 to 4400 MHz

FEATURES

- Wide bandwidth, 1550 to 4400 MHz
- Excellent isolation, 20 dB typ.
- Excellent amplitude unbalance, 0.04 dB typ.
- Good phase unbalance, 0.6 deg. typ.
- Small size, 0.118"x0.118"x0.035"
- High ESD level
- Aqueous washable



Generic photo used for illustration purposes only

CASE STYLE: DQ1225

+RoHS CompliantThe +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- WCDMA
- DCS
- Radar
- Navigation
- Instrumentation
- Korea PCS
- WiMax

ELECTRICAL SPECIFICATIONS AT 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Frequency Range		1550		4400	MHz
Insertion Loss* (above 3.0 dB)	1550-4400	—	1.0	1.9	dB
Isolation	1550-4400	12	20	—	dB
Amplitude Unbalance	1550-4400	—	—	0.3	dB
Phase Unbalance	1550-4400	—	—	6.0	deg.
VSWR (Port S)	1550-4400	—	1.4	—	:1
VSWR (Ports 1,2)	1550-4400	—	1.4	—	

* De-embedded from demo board loss.

MAXIMUM RATINGS

Parameter	Ratings
Operating temperature	-40°C to 85°C
Storage temperature	-65°C to 150°C
Power Input (as a splitter)	1.5W max.
Internal Dissipation	0.75W max.

Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SCHEMATIC



Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. D
ECO-015315
GP2Y1+
MCL NY
220912

PAGE 1 OF 3



GP2Y1+



Mini-Circuits

MMIC SURFACE MOUNT

Power Splitter/Combiner




GP2Y1+

2 Way-0° 50Ω 1550 to 4400 MHz

TYPICAL PERFORMANCE DATA AND CHARTS

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
1470.00	4.45	4.44	0.01	16.20	0.33	1.73	1.30	1.31
1690.00	3.84	3.83	0.01	35.04	0.41	1.07	1.15	1.15
1870.00	3.74	3.74	0.00	24.68	0.47	1.16	1.14	1.15
2140.00	3.70	3.72	0.02	21.93	0.54	1.31	1.17	1.19
2320.00	3.67	3.69	0.02	22.75	0.57	1.30	1.16	1.17
2490.00	3.64	3.66	0.02	24.97	0.59	1.23	1.12	1.15
2670.00	3.62	3.63	0.01	29.75	0.51	1.13	1.08	1.10
2940.00	3.64	3.65	0.00	33.00	0.45	1.10	1.09	1.08
3120.00	3.70	3.70	0.00	25.78	0.45	1.21	1.17	1.15
3300.00	3.77	3.78	0.01	21.67	0.49	1.36	1.24	1.24
3490.00	3.85	3.88	0.03	18.91	0.64	1.51	1.31	1.33
3680.00	3.93	3.97	0.04	17.04	0.71	1.63	1.38	1.40
3870.00	3.98	4.05	0.07	15.77	0.85	1.71	1.44	1.51
4240.00	4.07	4.12	0.05	14.38	1.01	1.77	1.66	1.71
4430.00	4.11	4.13	0.01	14.09	0.95	1.77	1.83	1.83

1. Total Loss = Insertion Loss + 3dB splitter loss.

GP2X+
TOTAL LOSSGP2X+
ISOLATIONGP2X+
VSWR

ESD RATING

Human Body Model (HBM): Class 1A (250 to < 500V) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M2 (100V to < 250V) in accordance with ANSI/ESD STM 5.2 - 1999

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



2 Way-0° Power Splitter/Combiner

GP2Y1+

Typical Performance Data

FREQUENCY (MHz)	TOTAL LOSS ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB)	PHASE UNBALANCE (deg.)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
1470.0	4.45	4.44	0.01	16.20	0.33	1470.0	1.73	1.30	1.31
1600.0	3.99	3.98	0.01	26.03	0.38	1600.0	1.26	1.19	1.21
1610.0	3.97	3.96	0.01	27.08	0.39	1610.0	1.23	1.19	1.20
1690.0	3.84	3.83	0.01	35.04	0.41	1690.0	1.07	1.15	1.15
1780.0	3.77	3.77	0.00	28.31	0.44	1780.0	1.07	1.13	1.14
1870.0	3.74	3.74	0.00	24.68	0.47	1870.0	1.16	1.14	1.15
1960.0	3.72	3.73	0.01	22.92	0.47	1960.0	1.24	1.15	1.16
2050.0	3.71	3.73	0.01	22.14	0.50	2050.0	1.29	1.16	1.18
2140.0	3.70	3.72	0.02	21.93	0.54	2140.0	1.31	1.17	1.19
2230.0	3.69	3.71	0.02	22.14	0.58	2230.0	1.32	1.17	1.19
2320.0	3.67	3.69	0.02	22.75	0.57	2320.0	1.30	1.16	1.17
2410.0	3.66	3.67	0.02	23.75	0.58	2410.0	1.27	1.14	1.16
2490.0	3.64	3.66	0.02	24.97	0.59	2490.0	1.23	1.12	1.15
2580.0	3.63	3.64	0.01	26.91	0.55	2580.0	1.18	1.10	1.12
2670.0	3.62	3.63	0.01	29.75	0.51	2670.0	1.13	1.08	1.10
2760.0	3.62	3.63	0.01	33.79	0.51	2760.0	1.08	1.07	1.09
2850.0	3.63	3.63	0.00	36.64	0.47	2850.0	1.06	1.07	1.07
2940.0	3.64	3.65	0.00	33.00	0.45	2940.0	1.10	1.09	1.08
3030.0	3.67	3.67	0.00	28.80	0.45	3030.0	1.15	1.13	1.12
3120.0	3.70	3.70	0.00	25.78	0.45	3120.0	1.21	1.17	1.15
3210.0	3.73	3.73	0.00	23.47	0.46	3210.0	1.29	1.20	1.19
3300.0	3.77	3.78	0.01	21.67	0.49	3300.0	1.36	1.24	1.24
3310.0	3.77	3.78	0.01	21.51	0.50	3310.0	1.37	1.24	1.24
3490.0	3.85	3.88	0.03	18.91	0.64	3490.0	1.51	1.31	1.33
3680.0	3.93	3.97	0.04	17.04	0.71	3680.0	1.63	1.38	1.40
3870.0	3.98	4.05	0.07	15.77	0.85	3870.0	1.71	1.44	1.51
4060.0	4.02	4.10	0.08	14.91	0.83	4060.0	1.75	1.54	1.59
4240.0	4.07	4.12	0.05	14.38	1.01	4240.0	1.77	1.66	1.71
4430.0	4.11	4.13	0.01	14.09	0.95	4430.0	1.77	1.83	1.83

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. X2

GP2Y1+






6/21/2010

Page 1 of 1

2 Way-0° Power Splitter/Combiner

GP2Y1+

Typical Performance Curves



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 • (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




IF/RF MICROWAVE COMPONENTS


minicircuits.com

REV. X2
GP2Y1+
6/21/2010
Page 1 of 1

Outline Dimensions



PCB Land Pattern



SUGGESTED LAYOUT,
TOLERANCE TO BE WITHIN $\pm .002$

Weight: .02 Grams

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .004$

Notes:

- Case material: Plastic.
- Termination finish:
 - For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix. See Data sheet.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Tape & Reel Packaging TR-F66



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.


Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

Evaluation Board and Circuit



TB-453-GP2Y1+



Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

Schematic Diagram

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D