

Surface Mount Bandpass Filter

CBP-1228C+

50Ω 1217 to 1238 MHz

The Big Deal

- Narrow bandwidth
- Excellent Rejection
- High power handling
- Miniature shielded package



Generic photo used for illustration purposes only
CASE STYLE: MP1766

Product Overview

CBP-1228C+ is a ceramic-coaxial-resonator based bandpass filter in a shielded package fabricated using SMT technology. This filter offers outstanding close in rejection, low insertion loss and high power handling for use in space and military applications

Key Features

Feature	Advantages
High Selectivity	The CBP-1228C+ filter incorporates High-Q ceramic resonators that enables sharp rejection near passband.
Low Passband VSWR	This filter maintains typical VSWR over passband frequency range making this filter easier to integrate into receiver and transmitter RF chains with less concerns for in band frequency ripple.
Rugged construction	The CBP-1228C+ has been qualified over wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Surface Mount Bandpass Filter

50Ω 1217 to 1238 MHz

CBP-1228C+



Generic photo used for illustration purposes only
CASE STYLE: MP1766

Features

- Narrow bandwidth
- Excellent rejection
- High selectivity
- High power handling
- Miniature shielded package

Applications

- Space operation and space research
- GPS
- Military

Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	—	—	1228	—	MHz
	Insertion Loss	F1-F2	—	1.30	3.00	dB
	VSWR	F1-F2	—	1.50	2.32	:1
Stop Band, Lower	Insertion Loss	DC-F3	20	30	—	dB
	VSWR	DC-F3	—	20	—	:1
Stop Band, Upper	Insertion Loss	F4-F5	20	29	—	dB
	VSWR	F4-F5	—	20	—	:1

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	10W

Permanent damage may occur if any of these limits are exceeded.

Functional Schematic



Typical Frequency Response







Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	107.94	347.44	1217	10.80
750	79.85	173.72	1218	10.68
1140	32.06	37.77	1219	10.61
1144	30.03	34.75	1220	10.56
1160	20.98	23.49	1221	10.55
1174	11.52	11.24	1222	10.54
1180	7.29	6.28	1223	10.47
1188	3.03	2.43	1224	10.50
1217	1.11	1.04	1225	10.42
1228	1.07	1.07	1226	10.42
1238	1.09	1.16	1227	10.40
1268	3.00	2.72	1228	10.37
1277	7.10	7.63	1229	10.36
1286	12.06	17.39	1230	10.35
1304	20.74	42.38	1232	10.32
1330	30.08	72.39	1233	10.32
1550	71.88	102.19	1234	10.33
2200	54.26	91.43	1235	10.30
2600	47.02	82.73	1237	10.33
3000	42.69	59.91	1238	10.40

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.B
M174392
CBP-1228C+
EDU1819
URJ
200811
Page 2 of 3

Pad Connections

INPUT	1
OUTPUT	10
GROUND	2,3,4,5,6,7,8,9,11,12,13


Demo Board MCL P/N: TB-684+
Suggested PCB Layout (PL-373)



- NOTES:
- TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS .022"±.0015". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H	J	K	L	M	N
.750	.750	.210	.139	.157	.215	.160	.218	.157	.100	.060	.069	.149
19.05	19.05	5.33	3.53	3.99	5.46	4.06	5.54	3.99	2.54	1.52	1.75	3.78
P	Q	R	S	T	U	V	W	X	Y	Z	wt.	
.790	.541	.790	.499	.384	.203	.080	.069	.630	.630	.145		grams
20.07	13.74	20.07	12.67	9.75	5.16	2.03	1.75	16.00	16.00	3.68		4.6

Note: Please refer to case style drawing for details

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1.0	101.99	107.94	110.94	0.05	0.05	0.05	0.05	0.05	0.05
200.0	114.88	120.90	102.38	0.02	0.03	0.04	0.02	0.03	0.03
330.0	101.01	95.26	100.97	0.02	0.04	0.05	0.01	0.04	0.04
440.0	89.79	95.83	93.33	0.02	0.05	0.06	0.01	0.04	0.05
570.0	85.11	86.66	84.87	0.03	0.07	0.08	0.03	0.06	0.07
680.0	80.51	82.39	82.52	0.04	0.08	0.10	0.04	0.08	0.10
800.0	77.61	77.21	78.13	0.06	0.11	0.13	0.06	0.11	0.13
920.0	72.11	71.87	72.04	0.09	0.15	0.17	0.10	0.15	0.18
990.0	70.37	69.35	69.51	0.11	0.18	0.20	0.13	0.19	0.21
1015.0	71.98	72.39	71.85	0.13	0.19	0.22	0.14	0.21	0.23
1100.0	49.99	49.74	49.83	0.22	0.30	0.33	0.24	0.32	0.36
1140.0	32.41	32.06	32.03	0.35	0.46	0.53	0.39	0.50	0.56
1143.0	30.90	30.55	30.51	0.37	0.49	0.56	0.41	0.53	0.60
1146.0	29.35	28.99	28.95	0.39	0.52	0.59	0.43	0.55	0.63
1161.0	20.77	20.36	20.32	0.59	0.76	0.87	0.64	0.81	0.92
1185.0	4.29	4.31	4.56	4.47	5.16	5.29	4.62	5.32	5.41
1187.0	3.30	3.40	3.67	5.95	6.69	6.72	6.13	6.88	6.87
1190.0	2.21	2.42	2.69	9.05	9.76	9.53	9.35	10.06	9.73
1203.0	1.03	1.27	1.42	25.90	31.13	31.73	27.11	31.11	30.46
1208.0	0.97	1.19	1.34	25.32	31.39	39.84	25.16	29.30	33.04
1216.0	0.89	1.12	1.26	31.82	35.71	35.74	31.22	34.49	37.05
1217.0	0.89	1.11	1.25	32.69	35.20	34.97	32.43	35.27	37.92
1228.0	0.85	1.07	1.22	29.38	29.01	27.26	39.45	41.22	31.68
1238.0	0.85	1.09	1.25	25.90	22.57	19.81	29.92	24.09	20.52
1241.0	0.85	1.10	1.27	24.48	21.20	18.62	26.72	22.15	19.10
1256.0	0.97	1.24	1.42	36.22	39.01	34.48	26.30	26.45	26.06
1260.0	1.13	1.45	1.67	18.99	18.12	17.72	17.87	17.18	16.87
1267.0	2.11	2.69	3.12	8.31	7.59	7.11	8.14	7.46	7.00
1271.0	3.35	4.13	4.72	5.07	4.63	4.31	5.00	4.57	4.26
1285.0	10.47	11.52	12.32	1.02	1.08	1.08	1.02	1.07	1.08
1305.0	20.29	21.16	21.87	0.28	0.39	0.44	0.28	0.39	0.44
1319.0	25.74	26.49	27.13	0.18	0.28	0.32	0.19	0.29	0.34
1320.0	26.09	26.84	27.46	0.17	0.27	0.32	0.19	0.29	0.33
1330.0	29.41	30.08	30.67	0.14	0.24	0.28	0.15	0.25	0.29
1333.0	30.33	30.99	31.57	0.13	0.23	0.27	0.15	0.24	0.28
1343.0	33.22	33.83	34.36	0.12	0.21	0.25	0.14	0.22	0.26
1370.0	39.85	40.36	40.84	0.10	0.18	0.22	0.11	0.20	0.23
1395.0	44.91	45.42	45.83	0.09	0.17	0.20	0.11	0.19	0.22
1425.0	50.25	50.64	51.10	0.09	0.17	0.20	0.12	0.19	0.22
1480.0	59.02	59.49	59.92	0.10	0.16	0.19	0.12	0.19	0.22
1495.0	61.17	61.68	62.12	0.10	0.16	0.19	0.12	0.19	0.22
1540.0	68.98	69.03	69.69	0.10	0.17	0.19	0.13	0.20	0.23
1560.0	73.61	72.84	71.38	0.10	0.17	0.19	0.14	0.20	0.23
1600.0	67.74	67.64	67.08	0.11	0.17	0.20	0.14	0.21	0.23
1640.0	65.08	65.07	64.29	0.11	0.18	0.20	0.14	0.21	0.23
1685.0	61.99	61.91	61.75	0.11	0.18	0.20	0.15	0.21	0.23
1730.0	60.47	60.41	60.10	0.12	0.18	0.21	0.15	0.21	0.24
1765.0	59.18	59.00	59.16	0.12	0.18	0.21	0.16	0.22	0.24
1840.0	60.52	60.68	60.67	0.13	0.19	0.21	0.16	0.22	0.24
1990.0	57.65	57.69	57.40	0.13	0.19	0.21	0.17	0.22	0.25
2060.0	55.47	55.42	55.22	0.13	0.19	0.22	0.16	0.22	0.24
2120.0	56.22	56.15	55.96	0.12	0.19	0.22	0.16	0.23	0.25
2200.0	54.52	54.26	54.02	0.12	0.19	0.22	0.16	0.22	0.25
2320.0	53.50	53.26	52.97	0.12	0.19	0.23	0.15	0.22	0.25
2370.0	50.49	50.14	49.91	0.13	0.20	0.24	0.15	0.23	0.26
2390.0	49.05	48.97	48.82	0.12	0.20	0.24	0.15	0.23	0.26
2450.0	50.05	49.67	48.67	0.11	0.20	0.23	0.14	0.22	0.25
2620.0	45.61	45.62	45.83	0.10	0.20	0.25	0.13	0.23	0.27
2890.0	44.19	44.38	44.11	0.12	0.25	0.31	0.14	0.26	0.33
3000.0	42.63	42.69	42.43	0.15	0.29	0.37	0.15	0.29	0.37







Typical Performance Data

FREQ.	GROUP DELAY		
(MHz)	(nsec)		
	@-40°C	@+25°C	@+85°C
1217.0	10.87	10.80	10.81
1217.1	10.83	10.83	10.87
1217.2	10.84	10.78	10.79
1217.3	10.82	10.78	10.85
1217.4	10.77	10.76	10.78
1217.5	10.74	10.70	10.78
1217.6	10.75	10.74	10.77
1217.7	10.78	10.74	10.81
1217.8	10.78	10.74	10.80
1217.9	10.78	10.76	10.80
1218.0	10.71	10.68	10.73
1218.1	10.72	10.71	10.73
1218.2	10.71	10.66	10.73
1218.3	10.74	10.72	10.80
1218.4	10.68	10.67	10.70
1218.5	10.67	10.68	10.75
1218.6	10.67	10.66	10.70
1218.7	10.66	10.67	10.74
1218.8	10.65	10.65	10.69
1218.9	10.65	10.63	10.68
1219.0	10.60	10.61	10.65
1220.0	10.56	10.56	10.62
1221.0	10.53	10.55	10.60
1222.0	10.55	10.54	10.60
1223.0	10.49	10.47	10.55
1224.0	10.47	10.50	10.54
1225.0	10.41	10.42	10.49
1226.0	10.41	10.42	10.50
1227.0	10.38	10.40	10.47
1228.0	10.36	10.37	10.45
1229.0	10.34	10.36	10.44
1230.0	10.32	10.35	10.43
1231.0	10.30	10.32	10.40
1232.0	10.26	10.32	10.35
1233.0	10.26	10.32	10.40
1234.0	10.29	10.33	10.38
1235.0	10.24	10.30	10.36
1236.0	10.27	10.31	10.39
1236.1	10.25	10.31	10.38
1236.2	10.26	10.33	10.39
1236.3	10.27	10.33	10.36
1236.4	10.25	10.34	10.38
1236.5	10.27	10.34	10.39
1236.6	10.27	10.33	10.39
1236.7	10.26	10.31	10.36
1236.8	10.28	10.36	10.39
1236.9	10.33	10.37	10.44
1237.0	10.30	10.33	10.38
1237.1	10.31	10.35	10.42
1237.2	10.32	10.36	10.43
1237.3	10.32	10.38	10.41
1237.4	10.35	10.38	10.44
1237.5	10.35	10.37	10.43
1237.6	10.33	10.38	10.46
1237.7	10.33	10.37	10.43
1237.8	10.32	10.35	10.41
1237.9	10.34	10.38	10.46
1238.0	10.35	10.40	10.48

Band Pass Filter

CBP-1228C+

Typical Performance Curves



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS




REV. OR
CBP-1228C+
140204
Page 1 of 2

Band Pass Filter


CBP-1228C+

Typical Performance Curves




Outline Dimensions

MP1766



PCB Land Pattern



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
MP1766	.750 (19.05)	.750 (19.05)	.210 (5.33)	.139 (3.53)	.157 (3.99)	.215 (5.46)	.160 (4.06)	.218 (5.54)	.157 (3.99)	.100 (2.54)	.060 (1.52)	.069 (1.75)	.149 (3.78)

CASE#	P	Q	R	S	T	U	V	W	X	Y	Z	WT.GRAMS
MP1766	.790 (20.07)	.541 (13.74)	.790 (20.07)	.499 (12.67)	.384 (9.75)	.203 (5.16)	.080 (2.03)	.069 (1.75)	.630 (16.00)	.630 (16.00)	.145 (3.68)	4.6

Dimensions are in inches (mm). Tolerances: 2PL. $\pm .03$; 3PL. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F111



Applicable Case styles:

Applicable Case styles: RS1539

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	24	13	250


Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M137721	NEW RELEASE	JUN 12	DDR	KG

**SUGGESTED MOUNTING CONFIGURATION FOR
MP1766 CASE STYLE "13FL01" PIN CODE**



NOTES:

- TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS $.022 \pm .0015$. COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	DDR
TOLERANCES ON:	CHECKED	MD
2 PL DECIMALS $\pm$	APPROVED	GM
3 PL DECIMALS $\pm$.005"		
ANGLES $\pm$		
FRACTIONS $\pm$		

 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95





Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

**PL, 13FL01, MP1766, BPF,
TB-684+, 50 Ohm**

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-373	OR
FILE:	98PL373	SCALE:	SHEET:
		4:1	1 OF 1

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: OAK-602 OR Equivalent
Dielectric Constant= $2.50 \pm .04$, Thickness=.022 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 96 hours, 40°C	MIL-STD-202, Method 103B, Condition B, Except 50°C
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A