

High Pass Filter

50Ω 5500 to 10000 MHz

Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

RF Power Input* 7W max. at 25°C

Max. DC Voltage at pins 1&3 25 VDC

*Passband rating, derate linearly to 3W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.


Pin Connections

RF IN 1


RF OUT 3

GROUND 2,4,5,6

Outline Drawing



PCB Land Pattern




Suggested Layout,
Tolerance to be within ±.002

Outline Dimensions (inch)

A	B	C	D	E	F
.126	.063	.035	.024	.022	.011
3.20	1.60	0.89	0.61	0.56	0.28
G	H	J	K	wt	
.039	.024	.042	.123	grams	
0.99	0.61	1.07	3.12	.020	

Demo Board MCL P/N: TB-285 Suggested PCB Layout (PL-158)



NOTE: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350 WITH DIELECTRIC THICKNESS: .020 ± .0015; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT
 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com

ISO 9001 ISO 14001 AS 9100 CERTIFIED

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp.

Features

- Low cost
- Small size
- 5 sections
- Temperature stable
- Excellent power handling, 7W
- Hermetically sealed
- LTCC construction
- Protected by US Patent 7,760,485

Applications


- Sub-harmonic rejection and DC blocking
- Transmitters / receivers

Electrical Specifications¹ at 25°C


STOPBAND (MHz)	fco, MHz Nom.	PASSBAND (MHz)	VSWR Typ. Frequency (MHz)	POWER INPUT (W)	NO. OF SECTIONS
(Loss > 30dB) Typ.	(Loss > 20dB) Min.	(Loss < 1.5dB) Typ.	(Loss < 2dB) Max.	Stopband	1.5:1
3600	4200	5050	5650-9700	5500-10000	20:1
			5200-10000	7	5

1. DC Resistance to ground is 100 Mohms min.

typical frequency response





electrical schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
50	61.01	868.59
1000	35.93	347.44
3600	32.03	48.26
4200	31.40	32.79
4700	13.75	14.38
4800	9.47	9.38
4950	4.60	4.01
5050	2.70	2.35
5200	1.55	1.40
5500	1.29	1.51
5650	1.27	1.55
9700	0.65	1.16
10000	0.72	1.34
10700	1.24	1.94
12000	3.06	3.42
14000	3.02	3.21
15000	7.56	3.00



Mini-Circuits
ISO 9001 ISO 14001 AS 9100 CERTIFIED

IF/RF MICROWAVE COMPONENTS

Ceramic High Pass Filter

HFCN-5050D+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	62.02	59.47	60.41	0.02	0.02	0.02	0.01	0.00	0.00
100	55.06	54.34	54.53	0.05	0.04	0.03	0.02	0.01	0.01
200	49.19	49.01	48.87	0.04	0.02	0.02	0.01	0.01	0.02
500	41.15	41.23	41.24	0.05	0.02	0.00	0.04	0.01	0.00
1000	35.81	35.84	35.93	0.05	0.01	0.05	0.03	0.01	0.03
2000	33.05	33.28	33.44	0.07	0.15	0.18	0.03	0.10	0.13
2500	35.56	36.10	36.39	0.10	0.18	0.20	0.09	0.16	0.19
3000	48.43	50.22	51.83	0.12	0.21	0.25	0.13	0.23	0.26
3600	32.21	31.87	31.45	0.22	0.34	0.41	0.22	0.34	0.41
4000	28.09	28.45	28.63	0.24	0.38	0.51	0.30	0.43	0.52
4200	29.60	30.58	31.40	0.28	0.45	0.61	0.35	0.50	0.60
4400	36.21	34.45	31.82	0.36	0.55	0.75	0.42	0.59	0.73
4500	28.81	26.10	23.98	0.46	0.67	0.89	0.47	0.67	0.84
4600	21.50	19.59	18.04	0.57	0.82	1.08	0.59	0.83	1.05
4700	15.92	14.42	13.18	0.76	1.08	1.43	0.79	1.11	1.43
4800	11.21	10.02	9.04	1.22	1.68	2.20	1.23	1.72	2.23
4950	5.62	4.93	4.43	3.03	4.03	5.04	3.15	4.16	5.22
5000	4.28	3.79	3.45	4.30	5.56	6.77	4.36	5.69	7.05
5050	3.16	2.88	2.69	5.91	7.44	8.88	6.13	7.77	9.47
5200	1.49	1.58	1.67	14.18	16.31	17.40	15.17	19.23	23.79
5400	1.09	1.30	1.47	18.86	16.48	15.68	19.23	17.35	16.65
5500	1.09	1.32	1.49	15.97	14.60	14.22	15.77	14.85	14.68
5650	1.04	1.27	1.43	14.25	13.53	13.42	13.75	13.45	13.57
6000	1.00	1.16	1.33	15.70	15.60	15.38	14.55	15.22	15.65
6500	0.78	0.94	1.09	20.87	24.11	24.01	20.28	24.55	27.08
7000	0.66	0.89	1.05	24.95	23.24	22.18	37.16	26.38	22.27
8000	0.77	0.93	1.07	14.71	16.84	18.17	14.29	16.34	17.65
9000	0.48	0.70	0.87	20.56	21.24	21.94	18.19	19.81	22.42
9700	0.37	0.62	0.80	22.61	26.63	30.22	21.04	24.81	34.50
10000	0.40	0.68	0.85	17.57	17.79	19.74	17.67	18.28	21.45
10700	0.78	1.22	1.48	10.68	10.16	9.84	11.23	10.31	10.21
12000	2.54	3.02	3.40	5.21	5.00	4.89	5.30	5.02	4.70
13000	4.06	3.80	3.83	3.34	4.04	4.42	3.16	4.07	4.35
14000	3.75	3.06	2.65	4.01	6.22	9.26	3.89	5.97	8.56
15000	5.61	7.53	8.41	6.56	6.00	5.78	6.48	6.31	6.87
16000	10.79	12.52	13.45	4.05	4.25	3.86	4.75	3.55	3.23
17000	12.83	12.28	12.33	2.25	3.35	4.38	2.46	2.74	2.39
18000	8.45	7.23	6.99	3.80	4.18	4.68	1.99	3.72	4.33
19000	4.14	5.32	6.79	16.91	7.85	5.12	5.66	8.07	8.26
20000	8.48	8.23	7.88	4.47	5.59	5.95	3.37	4.32	5.88

REV. X1

HFCN-5050D+

071010

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE




OUTPUT RETURN LOSS vs. TEMPERATURE



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT. GRAM
FV1206-1	.126 (3.20)	.063 (1.60)	.035 (0.89)	.024 (0.61)	.022 (0.56)	.011 (0.28)	.039 (0.99)	.024 (0.61)	.042 (1.07)	.123 (3.12)	--	--	--	--	.020

Dimensions are in inches (mm). Tolerances: 2 PL. $\pm .01$; 3 PL. $\pm .005$

Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



ISO 9001 ISO 14001 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging

TR-F75

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1




ILLUSTRATION 2




ILLUSTRATION 3

Applicable Case Styles
FV1206-1
FV1206-3

Applicable Case Styles
FV1206-4
FV1206-5
FV1206-6
FV1206-7
FV1206-9
JC0603C-1

Applicable Case Styles
NL1008C-6
FV1206-12
NL1008C-9
NL1008C-10

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits ISO 9001 & ISO 14001 Certified

Mini-Circuits®



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A