

Surface Mount

# Power Splitter/Combiner CDP-2-122W-75+

2 Way-0° 75Ω 1 to 1250 MHz



CASE STYLE: TT1491-1

## The Big Deal

- Wideband, 1 to 1250 MHz
- Low insertion loss, 0.8 dB
- High isolation, 21 dB
- Aqueous washable

## Product Overview

Mini-Circuits' CDP-2-122W-75+ is a 75Ω 2-way 0° surface-mount splitter/combiner covering the 1 to 1250 MHz frequency range, supporting bandwidth requirements for DOCSIS® 3.1 systems and equipment as well as other broadband applications. This model can handle up to 1W RF input power as a splitter and provides low insertion loss, high isolation, and low phase and amplitude unbalance. It features core and wire construction mounted on a six-lead printed laminate base (0.26 x 0.31 x 0.13") with wrap-around terminations for excellent solderability. It also features Mini-Circuits' TopHat® feature for faster, more accurate pick-and-place assembly and easier visual inspection.

## Key Features

Feature	Advantages
Wideband, 1 to 1250 MHz	Suitable for many broadband applications; meets upstream and downstream bandwidth requirements for DOCSIS® 3.1 systems and equipment.
Low insertion loss, 0.8 dB	The combination of 1W power handling and low insertion loss makes this model a suitable candidate for distributing signals while maintaining excellent transmission of signal power.
Low unbalance: <ul style="list-style-type: none"><li>• 0.6 dB amplitude unbalance</li><li>• 4° phase unbalance</li></ul>	CDP-2-122W-75+ produces nearly equal output signals, ideal for parallel path / multichannel systems.
Good isolation, 21 dB	Minimizes interference between input ports.
Good VSWR, 1.2:1 typ.	Provides excellent matching with minimal signal reflection.
TopHat® feature	Improves speed and accuracy of pick-and-place assembly and provides easier visual inspection.



# Surface Mount <sup>top hat</sup> Power Splitter/Combiner CDP-2-122W-75+

2 Way-0° 75Ω 1 to 1250 MHz

## Features

- wideband, 1 to 1250 MHz
- low insertion loss, 0.8 dB typ.
- good isolation, 21 dB typ.
- aqueous washable

## Applications

- DOCSIS® 3.1 Systems
- cellular
- VHF/UHF
- communication systems



Generic photo used for illustration purposes only

CASE STYLE: TT1491-1

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200
13"	500

## Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		1		1250	MHz
Insertion Loss Above 3.0 dB	1-10	—	0.4	0.9	dB
	10-870	—	0.8	1.6	
	870-1000	—	1.1	1.8	
	1000-1250	—	1.5	2.2	
Isolation	1-10	17	23.0	—	dB
	10-870	15	21.0	—	
	870-1000	15	19.0	—	
	1000-1250	15	19.0	—	
Phase Unbalance	1-10	—	2.0	5.0	Degree
	10-870	—	1.5	4.0	
	870-1000	—	1.5	4.0	
	1000-1250	—	1.0	4.0	
Amplitude Unbalance	1-10	—	0.25	0.6	dB
	10-870	—	0.20	0.5	
	870-1000	—	0.25	0.6	
	1000-1250	—	0.30	0.7	
VSWR (Port S)	1-10	—	1.16	1.35	:1
	10-870	—	1.15	1.4	
	870-1000	—	1.20	1.45	
	1000-1250	—	1.20	1.45	
VSWR (Port 1-2)	1-10	—	1.25	1.50	:1
	10-870	—	1.15	1.35	
	870-1000	—	1.25	1.40	
	1000-1250	—	1.30	1.60	

1. Mainline loss includes theoretical power loss at coupled port.

## Maximum Ratings


Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.125W max.

Permanent damage may occur if any of these limits are exceeded.

## Pin Connections

Function	Pin Number
SUM PORT	1
PORT 1	3
PORT 2	4
GROUND	6
NOT USED	2,5


## Product Marking



## Electrical Schematic




## Outline Drawing



## Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	wt.
.255	.310	.133	.100	.050	.055	.044	.090	.310	.050	grams
6.48	7.87	3.38	2.54	1.27	1.40	1.12	2.29	7.87	1.27	0.35

## Demo Board MCL P/N: TB-565+ Suggested PCB Layout (PL-327)






- NOTES:**
- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
  - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

## Typical Performance Data

Frequency (MHz)	Total Loss <sup>1</sup> (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
1	3.26	3.54	0.28	19.84	1.75	1.25	1.24	1.36
10	3.18	3.33	0.15	24.46	0.32	1.17	1.05	1.08
50	3.22	3.37	0.15	24.29	0.16	1.16	1.03	1.06
100	3.27	3.43	0.16	23.79	0.32	1.15	1.02	1.06
150	3.31	3.48	0.16	23.45	0.42	1.14	1.02	1.05
200	3.35	3.51	0.16	23.15	0.54	1.14	1.03	1.05
250	3.39	3.55	0.16	22.85	0.64	1.15	1.03	1.03
300	3.42	3.58	0.15	22.51	0.76	1.15	1.04	1.02
400	3.50	3.63	0.13	21.76	0.93	1.15	1.06	1.01
550	3.64	3.74	0.10	20.41	1.14	1.13	1.09	1.05
700	3.82	3.88	0.07	19.04	1.26	1.18	1.12	1.12
850	4.04	4.05	0.01	18.09	1.18	1.24	1.16	1.18
1000	4.27	4.21	0.06	17.83	0.88	1.24	1.19	1.23
1100	4.41	4.30	0.11	18.12	0.60	1.26	1.22	1.26
1250	4.63	4.41	0.21	19.72	0.06	1.21	1.26	1.28

1. Total Loss = Insertion Loss + 3dB splitter loss.



## Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

# 2 Way-0° Power Splitter/Combiner

# CDP-2-122W-75+

## Typical Performance Data

FREQ. (MHz)	TOTAL LOSS <sup>1</sup> (dB)		AMP. UNBAL. (dB)	ISOLATION (dB)	PHASE UNBAL. (Deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
0.7	3.24	3.56	0.32	18.50	2.32	0.7	1.27	1.33	1.48
0.8	3.25	3.56	0.31	19.07	2.08	0.8	1.26	1.29	1.43
0.9	3.26	3.55	0.29	19.50	1.89	0.9	1.25	1.26	1.39
1.0	3.26	3.54	0.28	19.84	1.75	1.0	1.25	1.24	1.36
2.0	3.25	3.48	0.23	21.48	1.13	2.0	1.22	1.16	1.24
3.0	3.22	3.42	0.20	22.42	0.89	3.0	1.20	1.12	1.18
4.0	3.20	3.39	0.18	23.09	0.75	4.0	1.19	1.10	1.15
5.0	3.20	3.37	0.17	23.56	0.63	5.0	1.18	1.08	1.13
6.0	3.19	3.35	0.16	23.88	0.55	6.0	1.18	1.07	1.11
7.0	3.19	3.34	0.16	24.11	0.46	7.0	1.18	1.06	1.10
8.0	3.18	3.33	0.15	24.27	0.41	8.0	1.17	1.06	1.09
9.0	3.18	3.33	0.15	24.38	0.35	9.0	1.17	1.05	1.09
10	3.18	3.33	0.15	24.46	0.32	10	1.17	1.05	1.08
20	3.19	3.33	0.14	24.66	0.07	20	1.17	1.03	1.06
30	3.20	3.34	0.14	24.56	0.04	30	1.16	1.03	1.06
40	3.21	3.36	0.15	24.43	0.11	40	1.16	1.02	1.06
50	3.22	3.37	0.15	24.29	0.16	50	1.16	1.03	1.06
60	3.23	3.39	0.16	24.17	0.20	60	1.16	1.03	1.06
70	3.24	3.40	0.16	24.06	0.23	70	1.16	1.03	1.06
80	3.25	3.41	0.16	23.96	0.27	80	1.15	1.03	1.06
90	3.26	3.42	0.16	23.86	0.29	90	1.15	1.02	1.06
100	3.27	3.43	0.16	23.79	0.32	100	1.15	1.02	1.06
125	3.29	3.45	0.16	23.60	0.43	125	1.15	1.02	1.06
150	3.31	3.48	0.16	23.45	0.42	150	1.14	1.02	1.05
175	3.33	3.49	0.16	23.30	0.49	175	1.14	1.03	1.05
200	3.35	3.51	0.16	23.15	0.54	200	1.14	1.03	1.05
225	3.37	3.53	0.16	23.01	0.58	225	1.14	1.03	1.04
250	3.39	3.55	0.16	22.85	0.64	250	1.15	1.03	1.03
275	3.41	3.56	0.16	22.68	0.70	275	1.15	1.04	1.03
300	3.42	3.58	0.15	22.51	0.76	300	1.15	1.04	1.02
325	3.44	3.59	0.15	22.33	0.79	325	1.15	1.05	1.02
350	3.46	3.60	0.14	22.14	0.84	350	1.15	1.05	1.02
375	3.48	3.62	0.14	21.95	0.89	375	1.15	1.06	1.01
400	3.50	3.63	0.13	21.76	0.93	400	1.15	1.06	1.01
425	3.52	3.65	0.13	21.56	0.98	425	1.15	1.06	1.01
450	3.54	3.66	0.12	21.33	1.01	450	1.14	1.07	1.02
475	3.56	3.68	0.12	21.10	1.04	475	1.13	1.07	1.03
500	3.58	3.70	0.11	20.86	1.07	500	1.13	1.08	1.04
525	3.61	3.72	0.11	20.63	1.11	525	1.13	1.08	1.04
550	3.64	3.74	0.10	20.41	1.14	550	1.13	1.09	1.05
575	3.66	3.76	0.10	20.18	1.17	575	1.13	1.09	1.06
600	3.69	3.78	0.09	19.94	1.19	600	1.13	1.10	1.07
625	3.72	3.80	0.09	19.71	1.22	625	1.14	1.10	1.09
650	3.75	3.83	0.08	19.48	1.24	650	1.16	1.11	1.09
675	3.78	3.86	0.07	19.26	1.26	675	1.17	1.11	1.10
700	3.82	3.88	0.07	19.04	1.26	700	1.18	1.12	1.12
725	3.85	3.91	0.06	18.86	1.26	725	1.20	1.13	1.13
750	3.89	3.94	0.05	18.69	1.24	750	1.21	1.14	1.14
775	3.93	3.97	0.04	18.53	1.24	775	1.22	1.14	1.14
800	3.96	3.99	0.03	18.37	1.23	800	1.22	1.14	1.15
825	4.00	4.02	0.02	18.22	1.21	825	1.23	1.15	1.17
850	4.04	4.05	0.01	18.09	1.18	850	1.24	1.16	1.18
870	4.07	4.07	0.00	18.01	1.16	870	1.24	1.17	1.19
900	4.12	4.11	0.01	17.89	1.11	900	1.24	1.17	1.20
925	4.15	4.13	0.02	17.81	1.06	925	1.25	1.18	1.21
950	4.19	4.16	0.03	17.78	1.00	950	1.25	1.18	1.22
975	4.23	4.18	0.04	17.80	0.94	975	1.25	1.19	1.23
1000	4.27	4.21	0.06	17.83	0.88	1000	1.24	1.19	1.23
1025	4.30	4.23	0.07	17.86	0.80	1025	1.24	1.20	1.24
1050	4.34	4.25	0.08	17.89	0.73	1050	1.25	1.20	1.25
1075	4.37	4.28	0.10	17.98	0.67	1075	1.26	1.21	1.26
1100	4.41	4.30	0.11	18.12	0.60	1100	1.26	1.22	1.26
1125	4.45	4.32	0.13	18.26	0.52	1125	1.25	1.23	1.26
1150	4.48	4.34	0.14	18.44	0.44	1150	1.25	1.23	1.27
1175	4.51	4.35	0.16	18.67	0.34	1175	1.25	1.23	1.28
1200	4.55	4.37	0.18	18.98	0.25	1200	1.24	1.24	1.28
1225	4.59	4.39	0.19	19.34	0.15	1225	1.22	1.25	1.28
1250	4.63	4.41	0.21	19.72	0.06	1250	1.21	1.26	1.28
1275	4.66	4.43	0.23	20.17	0.06	1275	1.19	1.27	1.30
1300	4.70	4.45	0.25	20.70	0.17	1300	1.17	1.27	1.31
1350	4.79	4.50	0.28	22.10	0.38	1350	1.13	1.29	1.30
1400	4.89	4.57	0.32	24.15	0.67	1400	1.09	1.30	1.33
1450	5.00	4.66	0.34	26.76	0.88	1450	1.06	1.33	1.34
1500	5.15	4.78	0.37	29.59	1.13	1500	1.06	1.35	1.40





<sup>1</sup>Total Loss = Insertion Loss + 3dB Splitter Loss




# 2 Way-0° Power Splitter/Combiner

# CDP-2-122W-75+


## Typical Performance Curves





### Outline Dimensions



### PCB Land Pattern



SUGGESTED LAYOUT  
TOLERANCE TO BE WITHIN  $\pm.002$

 DENOTES METALLIZATION  
 DENOTES SOLDER RESIST

CASE #	A	B	C	D	E	F	G	H	J	K	WT GRAMS
TT1491-1	.255 (6.48)	.310 (7.87)	.133 (3.38)	.100 (2.54)	.050 (1.27)	.055 (1.40)	.044 (1.12)	.090 (2.29)	.310 (7.87)	.050 (1.27)	.35

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

#### Notes:

- Open style, Base material: Printed wiring laminate.
- Termination finish: 3-5  $\mu$  inch (.08-.13 microns) Gold over 120-240  $\mu$  inch (3.05-6.10 microns) Nickel plate. All models, (+) suffix.
- Top-Hat total thickness: .013 inches MAX.
- Orientation Dot on Top Hat & PCB corresponds to Pin #1.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F2



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel See note
16	12	7	10
			20
			50
			100
			200
		13	500
			1000

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M125940	NEW RELEASE	06/28/10	AV	JC


**SUGGESTED MOUNTING CONFIGURATION FOR TT1491 CASE STYLE, "06SP01" PIN CODE**



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN AV	06/22/10
TOLERANCES ON:	CHECKED MMG	06/28/10
2 PL DECIMALS ±	APPROVED JC	06/28/10
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		



**Mini-Circuits®**

13 Neptune Avenue  
Brooklyn NY 11235



PL, 06SP01, 75, TT1491, TB-565+

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-327	REV: OR
FILE: 98PL327	SCALE: 8:1	SHEET: 1 OF 1	




# Evaluation Board and Circuit



## Notes:

1. 75 Ohm BNC connectors.
2. PCB Material: R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215