

# Surface Mount Directional Coupler

75Ω 10 dB 5 to 1000 MHz


## DBTC-10-4-75+

### Features

- very flat coupling
- very broadband, multi octave
- temperature stable, LTCC base
- all welded construction
- leads attached for better solderability
- micro miniature coupler
- aqueous washable
- protected by US Patents 6,140,887 & 6,784,521

### Applications

- cable tv



Generic photo used for illustration purposes only

CASE STYLE: AT790-1

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

| Available Tape and Reel at no extra cost |                       |
|------------------------------------------|-----------------------|
| Reel Size                                | Devices/Reel          |
| 7"                                       | 20, 50, 100, 200, 500 |
| 13"                                      | 1000, 2000            |

### Electrical Specifications at 25°C

| Parameter                  | Condition (MHz) | Min. | Typ.     | Max. | Unit |
|----------------------------|-----------------|------|----------|------|------|
| Frequency Range            |                 | 5    |          | 1000 | MHz  |
| Mainline Loss <sup>1</sup> | 5-50            | —    | 1.5      | 2.2  | dB   |
|                            | 50-500          | —    | 1.4      | 2.0  |      |
|                            | 500-1000        | —    | 1.5      | 2.0  |      |
| Nominal Coupling           | 5-1000          | —    | 10.5±0.5 | —    | dB   |
| Coupling Flatness(±)       | 5-1000          | —    | —        | 0.7  | dB   |
| Directivity                | 5-50            | 16   | 21       | —    | dB   |
|                            | 50-500          | 13   | 20       | —    |      |
|                            | 500-1000        | —    | 16       | —    |      |
| VSWR <sup>2</sup>          | 5-1000          | —    | 1.3      | —    | dB   |
| Input Power                | 5-500           | —    | —        | 0.5  | W    |
|                            | 500-1000        | —    | —        | 1.0  |      |

1. Includes theoretical coupled power loss of 0.4 dB at 10 dB coupling.

2. For coupled port VSWR above 500 MHz, 1.6:1 typ.

### Maximum Ratings


| Parameter             | Ratings        |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |

Permanent damage may occur if any of these limits are exceeded.

### Pin Connections

| Function             | Pin Number |
|----------------------|------------|
| INPUT                | 3          |
| OUTPUT               | 4          |
| COUPLED              | 1          |
| GROUND               | 2          |
| ISOLATE (DO NOT USE) | 6          |

### Electrical Schematic




\* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) THAT ROUTES DC FROM RF PORTS TO GROUND.



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. L  
M151107  
ED-8953A/1  
DBTC-10-4-75+  
WZ/CP/AM  
210401  
Page 1 of 2


## Outline Drawing




## Outline Dimensions (inch/mm)

| A    | B    | C    | D    | E    | F    | G    | H    | J    | K    | wt    |
|------|------|------|------|------|------|------|------|------|------|-------|
| .150 | .150 | .150 | .050 | .030 | .025 | .028 | .050 | .160 | .030 | grams |
| 3.81 | 3.81 | 3.81 | 1.27 | 0.76 | 0.64 | 0.71 | 1.27 | 4.06 | 0.76 | 0.10  |

## PCB Land Pattern






Demo Board MCL P/N: TB-279  
Suggested PCB Layout (PL-151)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

## Typical Performance Data

| Frequency (MHz) | Mainline Loss (dB) In-Out | Coupling (dB) In-Cpl | Directivity (dB) | In    | Return Loss (dB) Out | Cpl   |
|-----------------|---------------------------|----------------------|------------------|-------|----------------------|-------|
| 5.00            | 1.53                      | 10.44                | 21.95            | 12.96 | 18.66                | 14.22 |
| 7.00            | 1.45                      | 10.32                | 21.83            | 13.63 | 20.55                | 15.21 |
| 10.00           | 1.39                      | 10.24                | 21.71            | 14.11 | 22.29                | 15.95 |
| 30.00           | 1.37                      | 10.21                | 21.54            | 14.66 | 25.03                | 16.80 |
| 50.00           | 1.38                      | 10.21                | 21.49            | 14.79 | 25.45                | 16.88 |
| 70.00           | 1.38                      | 10.22                | 21.42            | 14.86 | 25.51                | 16.83 |
| 100.00          | 1.39                      | 10.24                | 21.31            | 14.98 | 25.34                | 16.64 |
| 500.00          | 1.33                      | 10.35                | 19.83            | 16.88 | 19.74                | 11.59 |
| 700.00          | 1.34                      | 10.46                | 19.25            | 18.06 | 18.15                | 9.84  |
| 1000.00         | 1.41                      | 10.70                | 18.57            | 16.64 | 18.44                | 8.57  |



## Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

# Directional Coupler

# DBTC-10-4-75+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0 dBm @ Temperature = +25°C

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | COUPLING<br>LOSS<br>(dB) | DIRECTIVITY<br>(dB) | RETURN LOSS<br>(dB) |       |       |
|--------------------|---------------------------|--------------------------|---------------------|---------------------|-------|-------|
|                    |                           |                          |                     | IN                  | OUT   | CPL   |
| 5.0                | 1.53                      | 10.24                    | 20.26               | 16.21               | 22.03 | 16.09 |
| 10.0               | 1.51                      | 10.24                    | 20.48               | 16.48               | 23.17 | 16.36 |
| 15.0               | 1.49                      | 10.23                    | 20.70               | 16.75               | 24.29 | 16.63 |
| 20.0               | 1.50                      | 10.24                    | 20.70               | 16.76               | 24.36 | 16.64 |
| 25.0               | 1.50                      | 10.25                    | 20.69               | 16.77               | 24.43 | 16.64 |
| 50.0               | 1.52                      | 10.27                    | 20.64               | 16.81               | 24.47 | 16.64 |
| 75.0               | 1.52                      | 10.29                    | 20.61               | 16.90               | 24.55 | 16.66 |
| 100.0              | 1.53                      | 10.31                    | 20.64               | 17.00               | 24.61 | 16.68 |
| 150.0              | 1.53                      | 10.32                    | 20.57               | 17.16               | 24.44 | 16.53 |
| 200.0              | 1.52                      | 10.34                    | 20.46               | 17.25               | 24.02 | 16.30 |
| 250.0              | 1.51                      | 10.36                    | 20.37               | 17.34               | 23.50 | 15.98 |
| 300.0              | 1.51                      | 10.38                    | 20.24               | 17.48               | 22.86 | 15.61 |
| 350.0              | 1.50                      | 10.40                    | 20.07               | 17.56               | 22.23 | 15.21 |
| 400.0              | 1.50                      | 10.42                    | 19.96               | 17.58               | 21.64 | 14.81 |
| 450.0              | 1.49                      | 10.45                    | 19.73               | 17.66               | 21.13 | 14.41 |
| 475.0              | 1.49                      | 10.46                    | 19.73               | 17.76               | 20.92 | 14.21 |
| 500.0              | 1.49                      | 10.48                    | 19.44               | 17.82               | 20.71 | 14.03 |
| 550.0              | 1.49                      | 10.51                    | 19.26               | 17.92               | 20.38 | 13.68 |
| 600.0              | 1.49                      | 10.54                    | 19.18               | 18.08               | 20.17 | 13.39 |
| 650.0              | 1.50                      | 10.58                    | 18.96               | 18.40               | 20.04 | 13.13 |
| 700.0              | 1.50                      | 10.61                    | 18.82               | 18.77               | 20.02 | 12.90 |
| 750.0              | 1.49                      | 10.64                    | 18.78               | 19.03               | 20.03 | 12.68 |
| 800.0              | 1.49                      | 10.68                    | 18.82               | 19.44               | 20.18 | 12.48 |
| 850.0              | 1.48                      | 10.72                    | 18.97               | 20.08               | 20.45 | 12.33 |
| 900.0              | 1.48                      | 10.75                    | 18.90               | 20.71               | 20.79 | 12.20 |
| 950.0              | 1.48                      | 10.81                    | 18.42               | 21.22               | 21.18 | 12.05 |
| 1000.0             | 1.48                      | 10.87                    | 18.00               | 21.76               | 21.55 | 11.90 |
| 1050.0             | 1.48                      | 10.92                    | 17.57               | 22.33               | 22.01 | 11.72 |
| 1100.0             | 1.48                      | 10.99                    | 17.01               | 22.90               | 22.56 | 11.56 |
| 1150.0             | 1.48                      | 11.06                    | 16.28               | 23.36               | 23.12 | 11.39 |
| 1200.0             | 1.50                      | 11.17                    | 15.11               | 23.66               | 23.59 | 11.19 |
| 1250.0             | 1.51                      | 11.25                    | 14.06               | 23.79               | 23.96 | 10.94 |
| 1300.0             | 1.54                      | 11.35                    | 13.10               | 23.61               | 24.38 | 10.69 |
| 1350.0             | 1.57                      | 11.43                    | 12.12               | 23.35               | 24.55 | 10.43 |
| 1400.0             | 1.61                      | 11.53                    | 11.22               | 23.27               | 24.61 | 10.15 |
| 1450.0             | 1.65                      | 11.61                    | 10.68               | 22.96               | 24.41 | 9.82  |
| 1500.0             | 1.69                      | 11.70                    | 10.33               | 22.32               | 24.10 | 9.51  |
| 1600.0             | 1.82                      | 11.90                    | 9.45                | 21.61               | 22.91 | 8.94  |
| 1700.0             | 1.97                      | 12.12                    | 9.05                | 20.56               | 21.26 | 8.38  |
| 1800.0             | 2.18                      | 12.36                    | 9.23                | 19.85               | 19.51 | 7.90  |
| 1900.0             | 2.36                      | 12.69                    | 9.29                | 18.87               | 17.69 | 7.52  |
| 2000.0             | 2.49                      | 13.04                    | 9.82                | 18.26               | 16.15 | 7.19  |
| 2100.0             | 2.58                      | 13.47                    | 9.59                | 17.33               | 14.74 | 6.95  |
| 2200.0             | 2.59                      | 13.92                    | 9.21                | 16.47               | 13.30 | 6.81  |
| 2300.0             | 2.52                      | 14.47                    | 7.88                | 15.53               | 11.95 | 6.71  |
| 2400.0             | 2.58                      | 14.97                    | 6.56                | 14.87               | 10.94 | 6.65  |
| 2500.0             | 2.98                      | 15.25                    | 5.19                | 14.35               | 10.15 | 6.67  |
| 2750.0             | 4.47                      | 15.73                    | 4.30                | 13.82               | 8.70  | 6.78  |
| 3000.0             | 5.84                      | 15.71                    | 6.68                | 13.01               | 7.71  | 6.89  |
| 3250.0             | 5.29                      | 15.46                    | 9.29                | 12.77               | 7.54  | 6.71  |
| 3500.0             | 4.33                      | 17.47                    | 3.04                | 11.61               | 6.59  | 6.43  |
| 3750.0             | 6.56                      | 18.26                    | 0.25                | 10.96               | 6.27  | 6.26  |
| 4000.0             | 9.64                      | 15.96                    | 3.42                | 10.95               | 5.72  | 6.33  |



P.O. Box 350166, Brooklyn, New York 11235-0003 • (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



IF/RF MICROWAVE COMPONENTS

REV. OR  
DBTC-10-4-75+  
3/15/2013  
Page 1 of 3

# Directional Coupler

# DBTC-10-4-75+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = -40°C

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | COUPLING<br>LOSS<br>(dB) | DIRECTIVITY<br>(dB) | RETURN LOSS |       |       |
|--------------------|---------------------------|--------------------------|---------------------|-------------|-------|-------|
|                    |                           |                          |                     | IN          | OUT   | CPL   |
| 5.0                | 1.76                      | 10.39                    | 18.53               | 13.90       | 16.35 | 13.58 |
| 10.0               | 1.55                      | 10.23                    | 19.07               | 15.74       | 20.04 | 15.24 |
| 15.0               | 1.33                      | 10.07                    | 19.62               | 17.57       | 23.73 | 16.90 |
| 20.0               | 1.32                      | 10.06                    | 19.72               | 17.95       | 25.14 | 17.26 |
| 25.0               | 1.30                      | 10.05                    | 19.82               | 18.34       | 26.55 | 17.62 |
| 50.0               | 1.29                      | 10.06                    | 20.06               | 19.30       | 28.78 | 18.53 |
| 75.0               | 1.29                      | 10.07                    | 20.09               | 19.53       | 29.36 | 18.77 |
| 100.0              | 1.29                      | 10.09                    | 20.12               | 18.95       | 29.40 | 18.31 |
| 150.0              | 1.30                      | 10.09                    | 20.09               | 18.48       | 28.43 | 17.31 |
| 200.0              | 1.31                      | 10.11                    | 20.10               | 18.97       | 27.14 | 17.39 |
| 250.0              | 1.31                      | 10.12                    | 19.98               | 18.09       | 25.95 | 16.43 |
| 300.0              | 1.31                      | 10.14                    | 19.93               | 17.93       | 24.57 | 15.61 |
| 350.0              | 1.31                      | 10.16                    | 19.81               | 17.73       | 23.31 | 15.28 |
| 400.0              | 1.31                      | 10.18                    | 19.76               | 17.11       | 22.07 | 14.45 |
| 450.0              | 1.31                      | 10.20                    | 19.63               | 17.01       | 21.01 | 13.92 |
| 475.0              | 1.30                      | 10.20                    | 19.63               | 16.96       | 20.59 | 13.73 |
| 500.0              | 1.31                      | 10.23                    | 19.42               | 16.84       | 20.16 | 13.50 |
| 550.0              | 1.31                      | 10.26                    | 19.35               | 16.89       | 19.50 | 12.98 |
| 600.0              | 1.32                      | 10.27                    | 19.37               | 17.08       | 19.08 | 12.70 |
| 650.0              | 1.32                      | 10.30                    | 19.26               | 17.33       | 18.82 | 12.46 |
| 700.0              | 1.32                      | 10.31                    | 19.29               | 17.85       | 18.77 | 12.33 |
| 750.0              | 1.31                      | 10.34                    | 19.31               | 18.45       | 18.85 | 12.27 |
| 800.0              | 1.31                      | 10.35                    | 19.46               | 19.55       | 19.20 | 12.27 |
| 850.0              | 1.30                      | 10.36                    | 19.70               | 20.77       | 19.75 | 12.39 |
| 900.0              | 1.30                      | 10.38                    | 19.67               | 22.24       | 20.42 | 12.47 |
| 950.0              | 1.29                      | 10.41                    | 19.14               | 23.92       | 21.22 | 12.59 |
| 1000.0             | 1.29                      | 10.45                    | 18.46               | 25.63       | 22.13 | 12.60 |
| 1050.0             | 1.27                      | 10.50                    | 17.75               | 26.07       | 23.36 | 12.43 |
| 1100.0             | 1.27                      | 10.54                    | 16.93               | 24.51       | 24.85 | 12.25 |
| 1150.0             | 1.27                      | 10.60                    | 16.06               | 22.79       | 26.51 | 11.76 |
| 1200.0             | 1.28                      | 10.69                    | 14.73               | 20.98       | 28.07 | 11.21 |
| 1250.0             | 1.29                      | 10.76                    | 13.61               | 20.05       | 28.99 | 10.65 |
| 1300.0             | 1.31                      | 10.84                    | 12.58               | 19.06       | 29.70 | 10.00 |
| 1350.0             | 1.33                      | 10.93                    | 11.55               | 17.98       | 29.21 | 9.41  |
| 1400.0             | 1.36                      | 11.02                    | 10.62               | 17.75       | 28.47 | 8.90  |
| 1450.0             | 1.38                      | 11.09                    | 10.10               | 17.90       | 27.41 | 8.49  |
| 1500.0             | 1.42                      | 11.16                    | 9.79                | 18.44       | 26.23 | 8.17  |
| 1600.0             | 1.52                      | 11.35                    | 8.99                | 18.56       | 23.51 | 7.78  |
| 1700.0             | 1.66                      | 11.57                    | 8.75                | 20.58       | 20.61 | 7.90  |
| 1800.0             | 1.88                      | 11.79                    | 9.15                | 22.21       | 18.40 | 8.17  |
| 1900.0             | 2.07                      | 12.10                    | 9.40                | 28.98       | 16.60 | 8.56  |
| 2000.0             | 2.21                      | 12.41                    | 10.23               | 27.54       | 15.57 | 8.42  |
| 2100.0             | 2.28                      | 12.77                    | 9.93                | 20.17       | 14.74 | 7.67  |
| 2200.0             | 2.26                      | 13.23                    | 9.24                | 16.15       | 13.58 | 6.63  |
| 2300.0             | 2.16                      | 13.79                    | 7.58                | 13.10       | 12.15 | 5.45  |
| 2400.0             | 2.21                      | 14.27                    | 6.12                | 11.30       | 10.97 | 4.65  |
| 2500.0             | 2.63                      | 14.65                    | 4.65                | 9.68        | 9.99  | 4.32  |
| 2750.0             | 4.21                      | 15.32                    | 4.00                | 9.44        | 8.06  | 5.51  |
| 3000.0             | 5.82                      | 15.17                    | 7.16                | 13.90       | 6.95  | 8.85  |
| 3250.0             | 5.17                      | 14.90                    | 9.85                | 17.59       | 6.93  | 7.24  |
| 3500.0             | 3.80                      | 17.17                    | 1.38                | 9.30        | 6.12  | 3.70  |
| 3750.0             | 5.97                      | 17.85                    | 0.94                | 5.87        | 6.17  | 2.96  |
| 4000.0             | 8.97                      | 15.03                    | 3.25                | 5.70        | 5.92  | 4.83  |



P.O. Box 350166, Brooklyn, New York 11235-0003 • (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



IF/RF MICROWAVE COMPONENTS

REV. OR  
DBTC-10-4-75+  
3/15/2013  
Page 2 of 3

# Directional Coupler

# DBTC-10-4-75+

## Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0 dBm @ Temperature = +85°C

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | COUPLING<br>LOSS<br>(dB) | DIRECTIVITY<br>(dB) | RETURN LOSS |       |       |
|--------------------|---------------------------|--------------------------|---------------------|-------------|-------|-------|
|                    |                           |                          |                     | IN          | OUT   | CPL   |
| 5.0                | 1.87                      | 10.47                    | 19.79               | 14.68       | 18.96 | 14.83 |
| 10.0               | 1.85                      | 10.46                    | 19.96               | 14.92       | 19.73 | 15.06 |
| 15.0               | 1.83                      | 10.46                    | 20.14               | 15.16       | 20.50 | 15.29 |
| 20.0               | 1.83                      | 10.47                    | 20.11               | 15.10       | 20.55 | 15.24 |
| 25.0               | 1.83                      | 10.48                    | 20.08               | 15.05       | 20.60 | 15.20 |
| 50.0               | 1.84                      | 10.51                    | 20.03               | 14.77       | 20.69 | 14.89 |
| 75.0               | 1.85                      | 10.53                    | 20.01               | 14.83       | 20.75 | 14.84 |
| 100.0              | 1.84                      | 10.54                    | 20.03               | 15.28       | 20.79 | 15.12 |
| 150.0              | 1.83                      | 10.56                    | 19.94               | 15.83       | 20.89 | 15.63 |
| 200.0              | 1.82                      | 10.59                    | 19.76               | 15.76       | 21.00 | 15.34 |
| 250.0              | 1.80                      | 10.61                    | 19.68               | 16.46       | 21.04 | 15.50 |
| 300.0              | 1.79                      | 10.64                    | 19.47               | 16.78       | 21.07 | 15.59 |
| 350.0              | 1.78                      | 10.67                    | 19.25               | 16.94       | 21.02 | 15.25 |
| 400.0              | 1.76                      | 10.71                    | 19.03               | 17.44       | 20.92 | 15.14 |
| 450.0              | 1.76                      | 10.76                    | 18.74               | 17.71       | 20.87 | 15.04 |
| 475.0              | 1.75                      | 10.77                    | 18.66               | 17.84       | 20.89 | 14.86 |
| 500.0              | 1.75                      | 10.81                    | 18.36               | 17.94       | 20.81 | 14.69 |
| 550.0              | 1.74                      | 10.86                    | 18.11               | 18.22       | 20.75 | 14.45 |
| 600.0              | 1.74                      | 10.91                    | 17.96               | 18.33       | 20.74 | 14.20 |
| 650.0              | 1.73                      | 10.97                    | 17.71               | 18.50       | 20.68 | 13.84 |
| 700.0              | 1.73                      | 11.03                    | 17.52               | 18.74       | 20.56 | 13.53 |
| 750.0              | 1.73                      | 11.09                    | 17.42               | 18.65       | 20.41 | 13.16 |
| 800.0              | 1.72                      | 11.14                    | 17.42               | 18.68       | 20.27 | 12.71 |
| 850.0              | 1.72                      | 11.20                    | 17.51               | 19.11       | 20.26 | 12.40 |
| 900.0              | 1.72                      | 11.26                    | 17.42               | 19.33       | 20.27 | 12.19 |
| 950.0              | 1.72                      | 11.34                    | 17.09               | 19.60       | 20.28 | 11.90 |
| 1000.0             | 1.72                      | 11.43                    | 16.79               | 19.90       | 20.26 | 11.69 |
| 1050.0             | 1.73                      | 11.50                    | 16.68               | 20.38       | 20.38 | 11.51 |
| 1100.0             | 1.73                      | 11.59                    | 16.31               | 21.35       | 20.66 | 11.33 |
| 1150.0             | 1.75                      | 11.68                    | 15.75               | 22.44       | 21.10 | 11.26 |
| 1200.0             | 1.77                      | 11.79                    | 14.85               | 23.74       | 21.60 | 11.26 |
| 1250.0             | 1.79                      | 11.89                    | 13.95               | 25.41       | 22.12 | 11.20 |
| 1300.0             | 1.84                      | 11.98                    | 13.10               | 26.96       | 22.85 | 11.17 |
| 1350.0             | 1.88                      | 12.08                    | 12.21               | 27.91       | 23.49 | 11.13 |
| 1400.0             | 1.92                      | 12.17                    | 11.37               | 28.15       | 24.21 | 11.00 |
| 1450.0             | 1.98                      | 12.25                    | 10.87               | 26.50       | 24.88 | 10.76 |
| 1500.0             | 2.03                      | 12.34                    | 10.50               | 24.45       | 25.37 | 10.47 |
| 1600.0             | 2.18                      | 12.54                    | 9.51                | 21.53       | 24.83 | 9.79  |
| 1700.0             | 2.32                      | 12.78                    | 9.09                | 19.01       | 22.55 | 8.75  |
| 1800.0             | 2.50                      | 12.99                    | 9.10                | 17.72       | 20.17 | 7.90  |
| 1900.0             | 2.66                      | 13.34                    | 9.05                | 16.48       | 17.69 | 7.25  |
| 2000.0             | 2.75                      | 13.68                    | 9.45                | 16.17       | 15.70 | 6.82  |
| 2100.0             | 2.82                      | 14.09                    | 9.36                | 15.97       | 14.24 | 6.70  |
| 2200.0             | 2.83                      | 14.50                    | 9.24                | 16.04       | 12.97 | 6.91  |
| 2300.0             | 2.79                      | 14.99                    | 8.16                | 16.35       | 11.91 | 7.32  |
| 2400.0             | 2.86                      | 15.44                    | 7.05                | 17.28       | 11.39 | 7.56  |
| 2500.0             | 3.24                      | 15.64                    | 5.69                | 17.83       | 10.96 | 7.81  |
| 2750.0             | 4.59                      | 16.00                    | 4.57                | 16.39       | 10.05 | 7.15  |
| 3000.0             | 5.76                      | 16.01                    | 6.43                | 12.44       | 8.25  | 6.18  |
| 3250.0             | 5.13                      | 15.61                    | 9.34                | 11.43       | 7.49  | 6.22  |
| 3500.0             | 4.13                      | 17.25                    | 4.05                | 11.67       | 6.71  | 7.07  |
| 3750.0             | 6.05                      | 18.31                    | 0.39                | 12.66       | 6.87  | 7.24  |
| 4000.0             | 9.32                      | 16.35                    | 3.29                | 12.92       | 6.27  | 6.34  |



P.O. Box 350166, Brooklyn, New York 11235-0003 • (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



IF/RF MICROWAVE COMPONENTS


REV. OR  
DBTC-10-4-75+  
3/15/2013  
Page 3 of 3

# Directional Coupler


## Typical Performance Curves

DBTC-10-4-75+


Insertion Loss




Insertion Loss vs. TEMPERATURE



Coupling Loss vs. TEMPERATURE



Directivity vs. TEMPERATURE




# Directional Coupler


## Typical Performance Curves

**DBTC-10-4-75+**


**Return Loss**




**Return Loss In vs. TEMPERATURE**



**Return Loss Out vs. TEMPERATURE**





**Return Loss Cpl vs. TEMPERATURE**




## Outline Dimensions

AT790-1



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE #  | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | L        | WT. GRAMS |
|---------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|-----------|
| AT790-1 | .150<br>(3.81) | .150<br>(3.81) | .150<br>(3.81) | .050<br>(1.27) | .030<br>(0.76) | .025<br>(0.64) | .028<br>(0.71) | .050<br>(1.27) | .160<br>(4.06) | .030<br>(0.76) | --<br>-- | .10       |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

1. Open style, Ceramic base.
2. Termination finish: Palladium Silver.



P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F17

## DEVICE ORIENTATION IN T&R



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |      |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 12             | 8                       | 7                 | Small quantity standards (see note) | 20   |
|                |                         |                   |                                     | 50   |
|                |                         |                   |                                     | 100  |
|                |                         |                   |                                     | 200  |
|                |                         |                   |                                     | 500  |
|                |                         | 13                | Standard                            | 1000 |
|                |                         |                   |                                     | 2000 |

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)


RF/IF MICROWAVE COMPONENTS

THIRD ANGLE PROJECTION

| REVISIONS |         |                       |          |     |      |
|-----------|---------|-----------------------|----------|-----|------|
| REV/      | ECN No. | DESCRIPTION           | DATE     | DR  | AUTH |
| OR        | M90455  | NEW RELEASE           | 01/16/04 | AV  | WP   |
| A         | M102713 | ADDED "...WITH SMOBC" | 01/17/06 | MMG | IL   |
|           |         |                       |          |     |      |
|           |         |                       |          |     |      |

SUGGESTED MOUNTING CONFIGURATION FOR

AT1029 CASE STYLE, "na" PIN CONNECTION




- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC  
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED                                                                                       | INITIALS |    | DATE     |
|------------------------------------------------------------------------------------------------------------------|----------|----|----------|
| DIMENSIONS ARE IN INCHES<br>TOLERANCES ON:<br>2 PL DECIMALS ±<br>3 PL DECIMALS ± .005<br>ANGLES ±<br>FRACTIONS ± | DRAWN    | AV | 01/07/04 |
|                                                                                                                  | CHECKED  | IL | 01/16/04 |
|                                                                                                                  | APPROVED | WP | 01/16/04 |
|                                                                                                                  |          |    |          |



Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235

PL, na, 75, AT1029, DBTC, TB-279



| SIZE   | CODE IDENT | DRAWING NO: | REV: |
|--------|------------|-------------|------|
| A      | 15542      | 98-PL-151   | A    |
| FILE:  | 98PL151    | SCALE:      | 10:1 |
| SHEET: |            | 1 OF 1      |      |

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

# Evaluation Board and Circuit



Schematic Diagram

## Notes:

1. BNC Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec                                                                                       |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature          | -40° to 85°C<br>Ambient Environment                                                                                                                             | Individual Model Data Sheet                                                                          |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Humidity                       | 90 to 95% RH, 240 hours, 50°C                                                                                                                                   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                                                       | MIL-STD-202, Method 107, Condition A-3, except +100°C                                                |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak                                                                                          | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability                  | 10X Magnification                                                                                                                                               | J-STD-002, 95% Coverage                                                                              |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                                                             | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                                                               | MIL-STD-202, Method 213, Condition A                                                                 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215                                                                              |