

Electronic Line Stretcher

50Ω 360° Voltage Variable 750 to 1300 MHz

ELS-1300



CASE STYLE: K18

Connectors Model
SMA ELS-1300-S
BRACKET (OPTION "B")

Maximum Ratings

Operating Temperature	0°C to 50 °C
Storage Temperature	-40°C to 100°C
RF Input Power	13dBm
Control Voltage	0.5V to 30V
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

RF IN	1
MONITOR OUT*	2
CONTROL	3

* Monitor out port should be connected to a 50-ohm load

Features

- over 360° phase shift of the reflected signal
- normalized and stable magnitude of the reflected signal
- voltage controlled for automated applications
- protected under US Patent 6,479,977

Applications


- automated load-pull measurement of oscillators¹

Electrical Specifications

FREQUENCY RANGE (MHz)	INPUT POWER (dBm)	PHASE RANGE (Degrees)	RETURN LOSS (dB)	CONTROL VOLTAGE (V)
f_L - f_U	Max.	Min.	Typ.	
750-1300	10	360	10-12	1-25

1. See Application Note AN-45-002 on our web site.

Outline Drawing




Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
1.25	1.25	.75	.63	.38	1.00	.125	1.000
31.75	31.75	19.05	16.00	9.65	25.40	3.18	25.40
J	K	L	M	N	P	Q	wt
--	--	.125	1.688	2.18	.75	.07	grams
--	--	3.18	42.88	55.37	19.05	1.78	70.0


Typical Performance Data

FREQ. (MHz)	PHASE SHIFT (Deg.)		RETURN LOSS (dBr)					
			Vc=0.5V @ 0°C	Vc=10V @ 0°C	Vc=25V @ 0°C	Vc=0.5V @ +50°C	Vc=10V @ +50°C	Vc=25V @ +50°C
600	310.91	302.56	-11.32	-10.01	-9.88	-11.15	-9.91	-9.88
700	368.80	357.25	-11.63	-10.42	-9.79	-11.33	-10.27	-9.77
740	402.57	390.39	-11.81	-10.68	-9.83	-11.50	-10.51	-9.80
820	450.97	440.76	-11.61	-11.23	-9.98	-11.17	-11.02	-9.93
900	472.51	464.41	-11.28	-11.46	-10.27	-11.14	-11.26	-10.19
980	477.28	470.45	-11.09	-11.22	-10.74	-10.96	-11.10	-10.59
1060	466.16	460.26	-11.22	-11.19	-11.33	-11.05	-11.05	-11.10
1140	430.97	424.98	-11.87	-11.38	-11.78	-11.54	-11.17	-11.60
1220	396.57	386.46	-12.73	-11.50	-11.49	-12.25	-11.28	-11.37
1260	390.00	379.35	-12.77	-11.46	-11.45	-12.35	-11.26	-11.29
1340	381.80	373.28	-12.13	-11.21	-11.51	-11.90	-11.06	-11.29
1420	367.17	361.69	-11.45	-10.99	-11.46	-11.29	-10.91	-11.23
1500	345.54	342.13	-10.95	-10.96	-11.25	-10.84	-10.91	-11.08


Maximum Phase Shift vs. Frequency at temperature extremes @ Pin = +7 dBm



Return Loss vs. Frequency at temperature extremes @ Pin = +7 dBm



Application Block Diagram



Notes



- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




Typical Performance Data

FREQUENCY (MHz)	PHASE SHIFT		RETURN LOSS					
	(Deg.)		(dBr)					
	0°C	+50°C	Vc=1V @ 0°C	Vc=10V @ 0°C	Vc=25V @ 0°C	Vc=1V @ +50°C	Vc=10V @ +50°C	Vc=25V @ +50°C
600.0	310.91	302.56	-11.32	-10.01	-9.88	-11.15	-9.91	-9.88
700.0	368.80	357.25	-11.63	-10.42	-9.79	-11.33	-10.27	-9.77
740.0	402.57	390.39	-11.81	-10.68	-9.83	-11.50	-10.51	-9.80
820.0	450.97	440.76	-11.61	-11.23	-9.98	-11.17	-11.02	-9.93
900.0	472.51	464.41	-11.28	-11.46	-10.27	-11.14	-11.26	-10.19
980.0	477.28	470.45	-11.09	-11.22	-10.74	-10.96	-11.10	-10.59
1060.0	466.16	460.26	-11.22	-11.19	-11.33	-11.05	-11.05	-11.10
1140.0	430.97	424.98	-11.87	-11.38	-11.78	-11.54	-11.17	-11.60
1220.0	396.57	386.46	-12.73	-11.50	-11.49	-12.25	-11.28	-11.37
1260.0	390.00	379.35	-12.77	-11.46	-11.45	-12.35	-11.26	-11.29
1340.0	381.80	373.28	-12.13	-11.21	-11.51	-11.90	-11.06	-11.29
1420.0	367.17	361.69	-11.45	-10.99	-11.46	-11.29	-10.91	-11.23
1500.0	345.54	342.13	-10.95	-10.96	-11.25	-10.84	-10.91	-11.08

Typical Performance Curves



Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
K18	1.25 (31.75)	1.25 (31.75)	.75 (19.05)	.63 (16.00)	.38 (9.65)	1.000 (25.40)	.125 (3.18)	1.000 (25.40)	--	--	.125 (3.18)	1.688 (42.88)	2.18 (55.37)

CASE#	P	Q	WT. GRAMS
K18	.75 (19.05)	.07 (1.78)	70.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Mounting bracket available on request. Add suffix B to part number.
- For port marking 1, 2, and 3 see specifications data sheet.
- For bracket version, option B, dimension "C" changes from .75 to .94 inches when connectors are type N.
- Refer to the individual model data sheet for the type of connectors available.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-0° to 50° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-40° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I