

JYPQ-160+



CASE STYLE: BJ293

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.

Permanent damage may occur if any of these limits are exceeded.

SUM PORT	8
PORT 1 (+90°)	1
PORT 2 (0°)	4
GROUND	2,3,6,7
50 OHM TERM EXTERNAL	5

Suggested Layout,
Tolerance to be within $\pm.002$

A	B	C	D	E	F	G
.395	.500	--	.100	.230	.100	.100
10.03	12.70	--	2.54	5.84	2.54	2.54
H	J	K	L			wt
.047	.065	.065	.425			grams
1.19	1.65	1.65	10.80			0.80

Figure 1: Dimensions of the 16-pin package. The diagram shows a top-down view of a square package with dimensions in inches. Key dimensions include: overall width .560, pin pitch 5X .100, pin width .030, pin height .200 TYP, package thickness .040 TYP, mounting hole diameter .145, mounting hole pitch .074, mounting hole offset .036, pin 1 location .163, pin width .035 TYP, and trace width .066 (4 PL). The package has 16 pins, with 16X #.020 PTH FOR GROUND indicated.

NOTE: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350 WITH DIELECTRIC THICKNESS .030" ± .002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT

 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK




- low insertion loss, 0.25 dB typ.
- good isolation, 24 dB typ.

- VHF
- signal processing
- modulators
- image rejection mixers

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) Avg. of Coupled Outputs ABOVE 3 dB		PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)
f_L - f_U	Typ.	Min.	Typ.	Max.	Max.	Max.
105-160	24	17	0.25	0.6	3	1.5

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
105.00	3.71	2.70	1.01	30.06	89.85	1.088	1.101	1.097
110.00	3.60	2.80	0.79	29.77	89.92	1.090	1.104	1.101
120.00	3.42	2.98	0.45	28.89	90.09	1.098	1.112	1.110
125.00	3.36	3.04	0.32	28.26	90.15	1.104	1.117	1.116
127.00	3.34	3.07	0.28	28.00	90.22	1.106	1.119	1.118
131.00	3.31	3.11	0.20	27.40	90.29	1.111	1.124	1.124
135.00	3.29	3.13	0.16	26.76	90.36	1.117	1.130	1.131
139.00	3.29	3.16	0.12	26.05	90.49	1.124	1.137	1.138
141.00	3.29	3.16	0.12	25.70	90.54	1.128	1.140	1.142
145.00	3.29	3.18	0.12	24.96	90.68	1.136	1.148	1.151
151.00	3.33	3.17	0.16	23.79	90.89	1.151	1.163	1.166
155.00	3.37	3.16	0.21	22.98	91.12	1.162	1.174	1.178
160.00	3.45	3.13	0.32	21.94	91.37	1.179	1.191	1.195

1. Total Loss = Insertion Loss + 3dB splitter loss



Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

REV. E
ECO-006036
JYPQ-160+
HY/TD/CP/AM
210202
Page 1 of 1

2 Way-90° Power Splitter/Combiner

JYPQ-160+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS ¹			AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)	VSWR		
	S-1	S-2	AVG.				S	(:1) 1	2
50	6.83	1.17	4.00	5.66	89.37	24.05	1.14	1.13	1.16
55	6.27	1.34	3.81	4.93	89.38	23.64	1.15	1.14	1.17
60	5.78	1.52	3.65	4.26	89.41	23.30	1.15	1.14	1.17
65	5.36	1.70	3.53	3.66	89.45	23.03	1.16	1.14	1.18
70	5.01	1.87	3.44	3.14	89.48	22.83	1.16	1.15	1.18
75	4.69	2.04	3.37	2.65	89.54	22.65	1.16	1.15	1.18
80	4.42	2.20	3.31	2.22	89.59	22.51	1.16	1.15	1.18
85	4.19	2.36	3.27	1.83	89.67	22.40	1.16	1.15	1.18
90	3.98	2.51	3.25	1.47	89.73	22.33	1.16	1.14	1.18
95	3.80	2.65	3.23	1.15	89.82	22.27	1.16	1.14	1.18
100	3.64	2.78	3.21	0.86	89.87	22.26	1.16	1.14	1.18
105	3.51	2.90	3.21	0.61	89.98	22.22	1.15	1.14	1.17
110	3.40	3.02	3.21	0.38	90.05	22.19	1.15	1.14	1.17
115	3.30	3.11	3.20	0.19	90.20	22.17	1.15	1.14	1.17
120	3.22	3.20	3.21	0.02	90.30	22.14	1.15	1.14	1.17
125	3.16	3.28	3.22	0.12	90.41	22.12	1.15	1.14	1.17
130	3.11	3.34	3.22	0.23	90.55	22.07	1.15	1.14	1.16
135	3.08	3.39	3.24	0.31	90.66	22.02	1.15	1.14	1.16
140	3.06	3.42	3.24	0.36	90.80	21.95	1.15	1.14	1.16
145	3.05	3.45	3.25	0.40	90.99	21.85	1.15	1.14	1.16
150	3.06	3.45	3.25	0.39	91.13	21.78	1.15	1.14	1.17
155	3.08	3.45	3.26	0.37	91.33	21.67	1.15	1.15	1.17
160	3.12	3.43	3.27	0.31	91.53	21.55	1.16	1.16	1.17
165	3.17	3.39	3.28	0.22	91.75	21.40	1.16	1.16	1.18
170	3.25	3.34	3.29	0.09	92.00	21.24	1.17	1.17	1.18
175	3.35	3.28	3.31	0.07	92.31	21.03	1.18	1.19	1.19
180	3.48	3.20	3.34	0.28	92.60	20.79	1.19	1.20	1.20
185	3.62	3.11	3.36	0.51	93.00	20.52	1.21	1.22	1.21
190	3.81	3.00	3.40	0.81	93.43	20.20	1.23	1.24	1.23
195	4.02	2.88	3.45	1.14	93.96	19.86	1.25	1.26	1.25
200	4.29	2.74	3.51	1.55	94.54	19.47	1.27	1.28	1.27
205	4.61	2.60	3.61	2.01	95.25	19.04	1.30	1.31	1.30
210	5.00	2.45	3.73	2.55	96.16	18.58	1.33	1.34	1.33
215	5.48	2.29	3.88	3.19	97.27	18.07	1.37	1.38	1.36
220	6.06	2.13	4.10	3.93	98.73	17.55	1.41	1.42	1.40

¹Total Loss = Insertion Loss + 3dB Splitter Loss

REV. X2
JYPQ-160+
100623
Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



2 Way-90° Power Splitter/Combiner

JYPQ-160+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = -40°C

FREQ. (MHz)	TOTAL LOSS ¹			AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB) 1-2	VSWR		
	S-1	S-2	AVG.				S	(:1) 1	2
50	6.83	1.12	3.97	5.71	89.49	24.71	1.11	1.12	1.13
55	6.26	1.29	3.78	4.97	89.50	24.26	1.12	1.12	1.13
60	5.77	1.47	3.62	4.30	89.51	23.88	1.12	1.12	1.14
65	5.35	1.64	3.49	3.71	89.53	23.53	1.12	1.13	1.14
70	4.99	1.82	3.40	3.17	89.55	23.23	1.13	1.13	1.14
75	4.67	1.99	3.33	2.68	89.59	22.97	1.14	1.14	1.15
80	4.40	2.15	3.28	2.25	89.62	22.74	1.14	1.14	1.15
85	4.16	2.31	3.23	1.85	89.67	22.55	1.15	1.14	1.16
90	3.95	2.46	3.21	1.49	89.72	22.43	1.15	1.14	1.16
95	3.77	2.60	3.18	1.17	89.78	22.32	1.15	1.14	1.17
100	3.62	2.73	3.17	0.89	89.85	22.29	1.15	1.14	1.17
105	3.48	2.85	3.16	0.63	89.94	22.26	1.15	1.14	1.17
110	3.37	2.96	3.16	0.41	90.00	22.25	1.15	1.14	1.17
115	3.27	3.05	3.16	0.22	90.16	22.28	1.15	1.14	1.17
120	3.18	3.14	3.16	0.04	90.25	22.31	1.15	1.13	1.16
125	3.11	3.21	3.16	0.10	90.37	22.35	1.14	1.13	1.15
130	3.06	3.28	3.17	0.22	90.49	22.36	1.14	1.13	1.15
135	3.02	3.33	3.17	0.31	90.61	22.35	1.13	1.13	1.14
140	2.99	3.36	3.17	0.37	90.73	22.34	1.13	1.13	1.14
145	2.98	3.38	3.18	0.40	90.86	22.29	1.13	1.13	1.14
150	2.98	3.39	3.19	0.41	90.99	22.21	1.13	1.14	1.13
155	3.01	3.40	3.21	0.39	91.17	22.09	1.13	1.14	1.14
160	3.04	3.37	3.20	0.33	91.32	21.93	1.14	1.15	1.14
165	3.09	3.34	3.21	0.25	91.51	21.74	1.14	1.15	1.15
170	3.16	3.29	3.23	0.13	91.72	21.52	1.15	1.16	1.15
175	3.25	3.23	3.24	0.02	91.98	21.25	1.16	1.18	1.17
180	3.37	3.15	3.26	0.22	92.24	20.95	1.18	1.19	1.18
185	3.51	3.06	3.28	0.45	92.60	20.61	1.20	1.21	1.20
190	3.69	2.95	3.32	0.74	92.99	20.25	1.22	1.23	1.22
195	3.89	2.83	3.36	1.06	93.48	19.86	1.24	1.25	1.24
200	4.15	2.69	3.42	1.46	94.03	19.43	1.27	1.28	1.27
205	4.45	2.55	3.50	1.90	94.69	18.98	1.30	1.31	1.29
210	4.82	2.39	3.61	2.43	95.52	18.50	1.33	1.35	1.33
215	5.28	2.24	3.76	3.04	96.54	17.98	1.37	1.38	1.36
220	5.83	2.07	3.95	3.76	97.87	17.45	1.41	1.42	1.40

¹Total Loss = Insertion Loss + 3dB Splitter Loss

REV. X2
JYPQ-160+
100623
Page 2 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



2 Way-90° Power Splitter/Combiner

JYPQ-160+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +85°C

FREQ. (MHz)	TOTAL LOSS ¹			AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB) 1-2	VSWR		
	S-1	S-2	AVG.				S	(:1) 1	2
50	6.85	1.20	4.02	5.65	89.28	23.57	1.16	1.15	1.19
55	6.30	1.37	3.84	4.93	89.28	23.18	1.18	1.16	1.20
60	5.82	1.55	3.69	4.27	89.31	22.88	1.19	1.16	1.21
65	5.40	1.72	3.56	3.68	89.37	22.68	1.19	1.16	1.22
70	5.05	1.90	3.48	3.15	89.44	22.54	1.19	1.16	1.22
75	4.73	2.07	3.40	2.66	89.52	22.46	1.19	1.16	1.22
80	4.46	2.23	3.35	2.23	89.58	22.40	1.18	1.15	1.21
85	4.22	2.38	3.30	1.84	89.69	22.38	1.18	1.15	1.21
90	4.01	2.53	3.27	1.48	89.78	22.38	1.17	1.14	1.20
95	3.83	2.67	3.25	1.16	89.87	22.38	1.16	1.14	1.19
100	3.67	2.79	3.23	0.88	89.96	22.39	1.16	1.14	1.18
105	3.54	2.91	3.23	0.63	90.06	22.35	1.15	1.14	1.18
110	3.43	3.03	3.23	0.40	90.13	22.29	1.15	1.13	1.17
115	3.34	3.13	3.24	0.21	90.28	22.23	1.15	1.13	1.17
120	3.26	3.21	3.24	0.05	90.38	22.15	1.15	1.14	1.17
125	3.19	3.29	3.24	0.10	90.49	22.04	1.15	1.14	1.17
130	3.15	3.35	3.25	0.20	90.63	21.92	1.15	1.14	1.17
135	3.12	3.40	3.26	0.28	90.76	21.78	1.16	1.14	1.18
140	3.10	3.44	3.27	0.34	90.89	21.66	1.16	1.14	1.18
145	3.10	3.46	3.28	0.36	91.09	21.53	1.17	1.15	1.19
150	3.12	3.47	3.29	0.35	91.26	21.40	1.17	1.15	1.20
155	3.15	3.47	3.31	0.32	91.50	21.26	1.18	1.16	1.20
160	3.19	3.45	3.32	0.26	91.73	21.14	1.18	1.17	1.21
165	3.25	3.41	3.33	0.16	92.00	20.99	1.19	1.18	1.21
170	3.33	3.36	3.34	0.03	92.29	20.86	1.20	1.19	1.22
175	3.43	3.30	3.37	0.13	92.63	20.68	1.21	1.20	1.22
180	3.56	3.22	3.39	0.34	92.99	20.49	1.22	1.22	1.23
185	3.71	3.13	3.42	0.58	93.41	20.26	1.24	1.23	1.24
190	3.90	3.03	3.47	0.87	93.87	20.00	1.25	1.25	1.25
195	4.12	2.91	3.51	1.21	94.42	19.70	1.27	1.27	1.26
200	4.39	2.77	3.58	1.62	95.07	19.34	1.29	1.29	1.28
205	4.72	2.62	3.67	2.10	95.81	18.93	1.31	1.32	1.30
210	5.13	2.47	3.80	2.66	96.79	18.48	1.34	1.35	1.32
215	5.62	2.32	3.97	3.30	97.99	17.99	1.38	1.38	1.36
220	6.23	2.16	4.20	4.07	99.56	17.48	1.42	1.42	1.39

¹Total Loss = Insertion Loss + 3dB Splitter Loss

REV. X2
JYPQ-160+
100623
Page 3 of 3



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits®




2 Way-90° Power Splitter/Combiner


JYPQ-160+

Typical Performance Curves


Total Loss




Average Total Loss vs. TEMPERATURE




Amplitude Unbalance vs. TEMPERATURE



Phase Unbalance vs. TEMPERATURE



Isolation 1-2 vs. TEMPERATURE



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




REV. X2
JYPQ-160+
100623
Page 1 of 2

2 Way-90° Power Splitter/Combiner

JYPQ-160+

Typical Performance Curves



REV. X2
JYPQ-160+
100623
Page 2 of 2




Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Outline Dimensions

BJ293
BJ398



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	WT. GRAMS
BJ293	.395 (10.03)	.500 (12.70)	-- --	.100 (2.54)	.230 (5.84)	.100 (2.54)	.100 (2.54)	.047 (1.19)	.065 (1.65)	.065 (1.65)	.425 (10.80)	.80
BJ398	.305 (7.75)	.390 (9.91)	-- --	.100 (2.54)	.105 (2.67)	.045 (1.14)	.100 (2.54)	.047 (1.19)	.065 (1.65)	.065 (1.65)	.325 (8.26)	.20

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Base material: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F10



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	16	7	10,20,50,100,200
		13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Note: Please consult individual model data sheet to determine device per reel availability.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82549	NEW RELEASE	11/15/02	MMG	HY
A	M102713	MODIFIED NOTES, ADDED "...WITH SMOBC"	01/16/06	GT	IL

**SUGGESTED MOUNTING CONFIGURATION
FOR BJ293 CASE STYLE, "kx" PIN CONNECTION.**



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" $\pm$.002".
COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:
2 PL DECIMALS $\pm$
3 PL DECIMALS $\pm$.005
ANGLES $\pm$
FRACTIONS $\pm$

INITIALS

DRAWN

MMG

DATE

11/05/02

CHECKED

AV

11/14/02

APPROVED

HY


11/15/02



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, kx, BJ293, JYPQ, TB-216



THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-100

REV:

A

FILE:

98PL100


SCALE:

6:1


SHEET:

1 OF 1

Evaluation Board and Circuit



TB-216



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215