

Dual Low Pass Filter

LPFD-7080+

50Ω Passband DC to 70 MHz & DC to 80 MHz

Maximum Ratings*


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W Max

*Ratings are for each of the two filters in the package.
Permanent damage may occur if any of these limits are exceeded.

Pin Connections


RF IN 1	2 (Filter 1)
RF OUT 1	14 (Filter 1)
RF IN 2	6 (Filter 2)
RF OUT 2	10 (Filter 2)
GROUND	1,3,4,5,7,8,9,11,12,13,15,16

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J
.500	.500	.195	.100	.080	.115	.060	.040	.540
12.70	12.70	4.95	2.54	2.03	2.92	1.52	1.02	13.72
K	L	M	N	P	Q	R	S	wt.
.060	.100	.135	.135	.115	.140	.070	.150	grams
1.52	2.54	3.43	3.43	2.92	3.56	1.78	3.81	1.0

Demo Board MCL P/N: TB-686
Suggested PCB Layout (PL-374)

NOTES:

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- High rejection
- Sharp insertion loss roll off
- Good VSWR, 1.2:1 typ. @ passband
- Small size dual filter, 0.5" x 0.5"
- Aqueous washable

Applications

- Wireless communications
- Receivers / Transmitters




CASE STYLE: DV874

+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Low Pass Filter Electrical Specifications (T_{AMB} = 25°C)

STRUCTURE	PASSBAND (MHz)	f _{co} , MHz Nom.	STOPBAND (MHz)		CROSS OVER ISOLATION (dB) Typ.	VSWR (:1)	
	(Loss < 2dB)	(Loss 3dB)	(Loss > 20dB)	(Loss > 40dB)		Passband Typ.	Stopband Typ.
Filter 1	DC - 70	80	135 - 200	200 - 2500	60	1.2	20
Filter 2	DC - 80	93	155 - 250	250 - 2500		1.2	20


Typical Frequency Response
(for each of filter)

Functional Schematic




Typical Performance Data at 25°C

Freq. (MHz)	Filter 1			Filter 2			Cross Over	Freq. (MHz)	Filter 1	Filter 2
	I. Loss (dB)	R. Loss (dB)		I. Loss (dB)	R. Loss (dB)	Isolation (dB)	Group Delay (nSec)			
	$\bar{x}$	σ		$\bar{x}$	σ	between filters 1 & 2				
0.5	0.25	0.01	29.65	0.23	0.01	30.43	91.07	1.0	8.71	7.70
10.0	0.31	0.01	24.16	0.26	0.01	28.06	85.80	3.5	7.24	6.22
70.0	1.01	0.03	16.31	0.70	0.01	23.57	62.72	5.0	7.26	6.21
80.0	2.77	0.18	5.81	0.93	0.02	20.26	60.18	10.0	7.16	6.16
93.0	8.78	0.36	1.59	2.99	0.15	5.76	61.51	15.0	7.22	6.20
95.0	9.87	0.37	1.36	3.63	0.17	4.73	62.07	20.0	7.29	6.24
100.0	12.58	0.37	0.99	5.58	0.21	2.94	63.67	25.0	7.39	6.31
135.0	28.39	0.32	0.39	20.92	0.20	0.53	71.02	30.0	7.54	6.39
140.0	30.25	0.32	0.36	22.79	0.19	0.48	71.15	35.0	7.72	6.51
155.0	35.43	0.30	0.29	27.92	0.17	0.36	71.62	40.0	7.94	6.63
200.0	48.59	0.27	0.20	40.20	0.15	0.22	70.58	45.0	8.20	6.78
250.0	61.85	0.26	0.17	50.46	0.37	0.18	69.69	50.0	8.51	6.93
300.0	79.88	0.69	0.14	58.56	0.82	0.13	68.75	55.0	8.94	7.13
500.0	74.18	2.26	0.14	80.02	3.37	0.09	66.98	60.0	9.62	7.36
1000.0	67.53	0.49	0.21	78.51	0.58	0.16	67.67	66.0	10.89	7.81
1500.0	66.18	2.87	0.26	71.46	1.54	0.23	50.65	70.0	12.01	8.28
2000.0	60.25	4.58	0.27	57.38	1.46	0.26	43.79	75.0	13.20	9.10
2500.0	56.20	7.32	0.31	47.80	1.38	0.29	39.95	80.0	13.27	10.14




Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp

LOW PASS FILTER 1
GROUP DELAY



LOW PASS FILTER 2
GROUP DELAY



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Low Pass Filter

LPFD-7080+





Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS		RETURN LOSS		Cross Over Isolation between F1 & F2 (dB)	FREQUENCY (MHz)	GROUP DELAY	
	Filter 1 (dB)	Filter 2 (dB)	Filter 1 (dB)	Filter 2 (dB)			Filter 1 (nsec)	Filter 2 (nsec)
0.5	0.25	0.23	29.65	30.43	91.07	1.0	8.71	7.70
10.0	0.31	0.26	24.16	28.06	85.80	3.5	7.24	6.22
70.0	1.01	0.70	16.31	23.57	62.72	5.0	7.26	6.21
80.0	2.77	0.93	5.81	20.26	60.18	10.0	7.16	6.16
93.0	8.78	2.99	1.59	5.76	61.51	15.0	7.22	6.20
95.0	9.87	3.63	1.36	4.73	62.07	20.0	7.29	6.24
100.0	12.58	5.58	0.99	2.94	63.67	25.0	7.39	6.31
135.0	28.39	20.92	0.39	0.53	71.02	30.0	7.54	6.39
140.0	30.25	22.79	0.36	0.48	71.15	35.0	7.72	6.51
155.0	35.43	27.92	0.29	0.36	71.62	40.0	7.94	6.63
200.0	48.59	40.20	0.20	0.22	70.58	45.0	8.20	6.78
250.0	61.85	50.46	0.17	0.18	69.69	50.0	8.51	6.93
300.0	79.88	58.56	0.14	0.13	68.75	55.0	8.94	7.13
500.0	74.18	80.02	0.14	0.09	66.98	60.0	9.62	7.36
1000.0	67.53	78.51	0.21	0.16	67.67	66.0	10.89	7.81
1500.0	66.18	71.46	0.26	0.23	50.65	70.0	12.01	8.28
2000.0	60.25	57.38	0.27	0.26	43.79	75.0	13.20	9.10
2500.0	56.20	47.80	0.31	0.29	39.95	80.0	13.27	10.14

Low Pass Filter


LPFD-7080+

Typical Performance Data



Outline Dimensions

DV874



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
DV874	.500 (12.70)	.500 (12.70)	.195 (4.95)	.100 (2.54)	.080 (2.03)	.115 (2.92)	.060 (1.52)	.040 (1.02)	.540 (13.72)	.060 (1.52)	.100 (2.54)	.135 (3.43)

CASE#	N	P	Q	R	S	WT.GRAM
DV874	.135 (3.43)	.115 (2.92)	.140 (3.56)	.070 (1.78)	.150 (3.81)	1.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F37



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
24	16	7	Small quantity standards (see note)	10
				20
				50
				100
		13	Standard	200
				500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M137753	NEW RELEASE	JUN 12	DDR	KG
A	M142821	ADDED PIN CODE "16FL01"	08/07/13	GF	IL

**SUGGESTED MOUNTING CONFIGURATION FOR
DV874 CASE STYLE, 16AV01/16FL01 PIN
CODES**



NOTES:

1. TRACE WIDTH IS SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS .030"±.002". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:
2 PL DECIMALS ±
3 PL DECIMALS ± .005"
ANGLES ±
FRACTIONS ±

DRAWN

DDR

28 JUN 12

CHECKED

MD

28 JUN 12

APPROVED

ASJ

28 JUN 12

 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

**PL, 16AV01/16FL01, DV874,
TB-686+**

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-374

REV:

A

FILE:

98PL374



SCALE:

4:1

SHEET:

1 OF 1

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: ROGERS (R04350B) OR Equivalent
Dielectric Constant= 3.48 ± 0.05 , Thickness= $.030$ inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 85° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215