


Ceramic

NON-CATALOG

Frequency Mixer WIDE BAND

Level 13 (LO Power+13 dBm) 300 to 2400 MHz

MCA1T-24MH+



CASE STYLE: DZ885-2

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-40°C to 85°C
RF Power	200 mW
IF Current	40 mA
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

LO	10
RF	5
IF	3
GROUND	1,2,4,6,7,8,9

Features

- wide bandwidth, 300 to 2400 MHz
- low conversion loss, 6.1 dB typ.
- excellent L-R isolation, 40 dB typ.
- LTCC double balanced mixer
- aqueous washable
- low cost
- low profile, 0.095"
- protected by US Patent 7,027,795 & 8,749,989


Applications

- cellular
- PCN
- defense & weather radar
- UHF TV
- WCDMA
- defense communications

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	E	F	G
.350	.280	.095	.075	.050	.030
8.89	7.11	2.41	1.91	1.27	0.76
H	K	L	M	wt	
.074	.096	.321	.030	grams	
1.88	2.44	8.15	0.76	0.21	

Demo Board MCL P/N: TB-493+ Suggested PCB Layout (PL-288)



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Electrical Specifications (T_{AMB}=-55°C to 100°C)


FREQUENCY (MHz)		CONVERSION LOSS (dB)			LO-RF ISOLATION (dB)		LO-IF ISOLATION (dB)		IP3 at center band (dBm)
LO/RF f _L -f _U	IF	$\bar{X}$	σ	Max.	Typ.	Min.	Typ.	Min.	Typ.
300-2400	DC-700	6.1	0.1	8.9	40	20	25	14	13

1 dB COMPR. +9 dBm typ.









Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +13dBm	LO +13dBm	LO +13dBm	LO +13dBm	LO +13dBm
300.00	330.00	5.82	49.37	21.78	1.81	8.01
400.00	430.00	5.10	42.20	23.99	1.56	2.46
500.00	530.00	6.84	40.15	27.27	3.96	1.34
700.00	730.00	6.58	46.19	27.35	3.69	2.12
1000.00	1030.00	7.41	43.92	24.46	4.01	2.74
1200.00	1230.00	7.45	39.35	31.83	4.28	3.82
1500.00	1530.00	5.74	39.15	28.78	1.91	2.66
1700.00	1730.00	5.13	36.63	25.65	1.04	1.79
2000.00	2030.00	6.17	32.38	21.69	2.26	2.44
2200.00	2230.00	7.25	33.19	20.62	3.48	3.62
2400.00	2430.00	7.16	30.70	25.44	3.42	7.44

Electrical Schematic



REV. C
M151777
MCA1T-24MH+
DJ/RS/CP/AM
160816



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Frequency Mixer

MCA1T-24MH+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)		
		@LO (dBm)		
		+10	+13	+16
220.0	250.0	27.70	14.43	7.73
300.0	330.0	7.10	5.51	5.29
380.0	410.0	5.25	4.84	4.63
460.0	490.0	6.90	5.93	5.37
540.0	570.0	7.37	6.44	5.97
620.0	650.0	6.40	6.20	6.05
700.0	730.0	6.10	5.83	5.77
780.0	810.0	6.66	6.06	5.79
860.0	890.0	6.97	6.53	6.27
940.0	970.0	6.78	6.41	6.23
1020.0	1050.0	6.70	6.46	6.32
1100.0	1130.0	7.12	6.65	6.41
1180.0	1210.0	7.91	6.91	6.37
1260.0	1290.0	8.74	7.49	6.80
1340.0	1370.0	6.96	6.47	6.18
1420.0	1450.0	6.55	5.85	5.42
1500.0	1530.0	6.23	5.57	5.11
1580.0	1610.0	5.47	4.81	4.71
1660.0	1690.0	5.25	4.85	4.79
1740.0	1770.0	5.34	5.06	5.02
1820.0	1850.0	5.72	5.21	5.11
1900.0	1930.0	5.67	5.09	4.96
1980.0	2010.0	6.90	5.86	5.36
2060.0	2090.0	7.84	6.68	6.04
2140.0	2170.0	8.13	6.83	6.25
2200.0	2230.0	8.08	6.61	6.20
2280.0	2310.0	8.98	6.60	6.14
2340.0	2370.0	10.83	6.53	6.14
2420.0	2450.0	11.80	6.71	6.33
2480.0	2510.0	10.67	7.17	6.88
2560.0	2590.0	11.95	7.87	7.20
2620.0	2650.0	11.56	8.41	7.49
2700.0	2730.0	9.59	8.49	7.97
2760.0	2790.0	8.81	8.48	8.39
2840.0	2870.0	8.50	7.84	7.62
2900.0	2930.0	9.01	8.28	7.87
2980.0	3010.0	8.75	8.24	8.05
3040.0	3070.0	9.52	9.15	8.94
3120.0	3150.0	10.91	10.29	9.92
3180.0	3210.0	11.68	10.85	10.37

RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)		
		@LO (dBm)		
		+10	+13	+16
220.0	250.0	-4.93	2.43	12.69
300.0	330.0	8.92	14.10	18.25
380.0	410.0	13.71	18.56	22.38
460.0	490.0	11.04	14.23	16.71
540.0	570.0	13.00	16.37	18.09
620.0	650.0	15.41	14.47	15.50
700.0	730.0	14.93	17.60	16.92
780.0	810.0	20.42	18.36	15.36
860.0	890.0	22.43	27.09	28.04
940.0	970.0	17.00	19.54	22.78
1020.0	1050.0	22.13	23.17	23.99
1100.0	1130.0	22.88	21.12	21.16
1180.0	1210.0	16.21	19.25	21.56
1260.0	1290.0	15.72	16.66	17.23
1340.0	1370.0	19.03	14.93	13.68
1420.0	1450.0	12.63	13.48	13.73
1500.0	1530.0	9.74	10.21	13.51
1580.0	1610.0	14.81	19.63	19.83
1660.0	1690.0	18.08	22.23	20.11
1740.0	1770.0	15.41	20.85	22.60
1820.0	1850.0	23.25	16.18	20.10
1900.0	1930.0	11.77	15.71	21.23
1980.0	2010.0	13.69	15.22	17.24
2060.0	2090.0	13.70	17.17	19.86
2140.0	2170.0	13.08	14.85	16.72
2200.0	2230.0	12.42	14.87	18.19
2280.0	2310.0	11.22	14.52	21.27
2340.0	2370.0	7.40	18.21	21.83
2420.0	2450.0	7.35	22.02	24.51
2480.0	2510.0	9.70	18.89	23.24
2560.0	2590.0	9.01	24.81	23.27
2620.0	2650.0	11.16	25.56	22.04
2700.0	2730.0	15.92	22.84	23.02
2760.0	2790.0	14.95	17.24	25.27
2840.0	2870.0	14.84	15.18	16.06
2900.0	2930.0	19.88	18.57	17.73
2980.0	3010.0	15.65	18.28	20.24
3040.0	3070.0	20.64	23.32	25.27
3120.0	3150.0	20.64	22.47	24.63
3180.0	3210.0	19.47	22.68	24.10

RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+9dBm (dB)		
		@LO (dBm)		
		+10	+13	+16
220.0	250.0	-14.43	-3.87	0.55
300.0	330.0	2.65	2.01	1.30
380.0	410.0	3.31	2.83	2.52
460.0	490.0	2.60	2.74	2.70
540.0	570.0	1.55	1.69	1.63
620.0	650.0	1.39	1.18	1.07
700.0	730.0	1.16	0.87	0.63
780.0	810.0	0.87	0.85	0.77
860.0	890.0	0.84	0.59	0.50
940.0	970.0	1.02	0.72	0.54
1020.0	1050.0	0.93	0.63	0.49
1100.0	1130.0	1.21	0.91	0.75
1180.0	1210.0	1.30	1.27	1.16
1260.0	1290.0	1.18	1.36	1.35
1340.0	1370.0	1.96	1.64	1.46
1420.0	1450.0	1.68	1.40	1.39
1500.0	1530.0	1.76	1.60	1.52
1580.0	1610.0	2.01	1.19	0.89
1660.0	1690.0	1.83	1.04	0.74
1740.0	1770.0	1.83	1.01	0.74
1820.0	1850.0	1.77	1.27	0.96
1900.0	1930.0	1.74	1.28	0.91
1980.0	2010.0	1.43	1.47	1.43
2060.0	2090.0	1.12	1.16	1.23
2140.0	2170.0	1.25	0.95	0.88
2200.0	2230.0	1.10	0.85	0.65
2280.0	2310.0	0.45	0.85	0.60
2340.0	2370.0	-0.96	0.95	0.47
2420.0	2450.0	-1.53	0.98	0.46
2480.0	2510.0	-0.42	0.98	0.48
2560.0	2590.0	-0.85	0.82	0.50
2620.0	2650.0	-0.69	0.51	0.50
2700.0	2730.0	0.44	0.34	0.31
2760.0	2790.0	0.98	0.48	0.31
2840.0	2870.0	1.13	0.93	0.76
2900.0	2930.0	0.61	0.59	0.56
2980.0	3010.0	1.22	0.65	0.38
3040.0	3070.0	0.86	0.47	0.33
3120.0	3150.0	0.63	0.34	0.23
3180.0	3210.0	1.00	0.32	0.17

Frequency Mixer

MCA1T-24MH+

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=1210.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=289.9MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=2410.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+13			+13			+13
770.1	440.0	9.69	10.1	300.0	6.40	830.1	1580.0	10.72
750.1	460.0	9.77	30.1	320.0	5.67	810.1	1600.0	9.85
730.1	480.0	9.53	50.1	340.0	5.61	790.1	1620.0	9.51
710.1	500.0	9.21	70.1	360.0	5.55	770.1	1640.0	9.04
690.1	520.0	8.68	90.1	380.0	5.47	750.1	1660.0	8.75
670.1	540.0	8.16	110.1	400.0	5.41	730.1	1680.0	8.59
650.1	560.0	7.59	130.1	420.0	5.41	710.1	1700.0	8.35
630.1	580.0	6.88	150.1	440.0	5.40	690.1	1720.0	8.29
610.1	600.0	6.19	170.1	460.0	5.56	670.1	1740.0	8.30
590.1	620.0	5.79	190.1	480.0	5.76	650.1	1760.0	8.06
570.1	640.0	5.80	210.1	500.0	5.85	630.1	1780.0	7.78
550.1	660.0	5.85	230.1	520.0	5.92	610.1	1800.0	7.69
530.1	680.0	6.09	250.1	540.0	5.96	590.1	1820.0	7.72
510.1	700.0	6.68	270.1	560.0	6.07	570.1	1840.0	7.58
490.1	720.0	7.23	290.1	580.0	6.09	550.1	1860.0	7.54
470.1	740.0	8.12	310.1	600.0	6.28	530.1	1880.0	7.57
450.1	760.0	8.62	330.1	620.0	6.35	510.1	1900.0	7.79
430.1	780.0	8.49	350.1	640.0	6.31	490.1	1920.0	7.94
410.1	800.0	8.66	370.1	660.0	6.06	470.1	1940.0	7.97
390.1	820.0	8.28	390.1	680.0	5.99	450.1	1960.0	8.03
370.1	840.0	8.20	410.1	700.0	6.15	430.1	1980.0	8.09
350.1	860.0	7.90	430.1	720.0	6.13	410.1	2000.0	8.26
330.1	880.0	7.59	450.1	740.0	6.68	390.1	2020.0	8.33
310.1	900.0	7.40	470.1	760.0	6.54	370.1	2040.0	8.37
290.1	920.0	7.33	490.1	780.0	6.21	350.1	2060.0	8.40
270.1	940.0	7.13	510.1	800.0	6.16	330.1	2080.0	8.43
250.1	960.0	6.88	530.1	820.0	6.05	310.1	2100.0	8.49
230.1	980.0	6.75	550.1	840.0	6.07	290.1	2120.0	8.39
210.1	1000.0	6.65	570.1	860.0	6.00	270.1	2140.0	8.13
190.1	1020.0	6.56	590.1	880.0	5.82	250.1	2160.0	7.91
170.1	1040.0	6.45	610.1	900.0	5.85	230.1	2180.0	7.77
150.1	1060.0	6.38	630.1	920.0	5.95	210.1	2200.0	7.67
130.1	1080.0	6.42	670.1	960.0	5.76	190.1	2220.0	7.31
110.1	1100.0	6.51	690.1	980.0	5.97	170.1	2240.0	7.14
90.1	1120.0	6.57	730.1	1020.0	6.26	150.1	2260.0	7.24
70.1	1140.0	6.57	750.1	1040.0	6.46	130.1	2280.0	7.34
50.1	1160.0	6.55	790.1	1080.0	7.00	90.1	2320.0	6.94
40.1	1170.0	6.60	810.1	1100.0	7.37	70.1	2340.0	6.79
20.1	1190.0	6.63	850.1	1140.0	8.54	30.1	2380.0	6.84
10.1	1200.0	6.69	870.1	1160.0	9.48	10.1	2400.0	6.93

Frequency Mixer

MCA1T-24MH+

Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	+10	+13	+16	+10	+13	+16
250.0	49.05	48.55	51.46	25.78	25.90	25.56
330.0	45.23	47.17	45.74	20.21	21.61	23.83
410.0	40.26	41.20	41.68	20.50	23.30	25.54
490.0	39.14	40.22	41.11	22.31	24.57	26.43
570.0	67.09	57.41	53.00	25.41	28.15	29.98
650.0	46.01	44.48	44.18	28.00	28.13	27.49
730.0	43.60	42.39	41.15	27.82	26.55	25.60
810.0	42.47	41.84	41.37	33.45	31.83	30.30
890.0	40.70	41.33	41.71	28.81	30.17	31.18
970.0	40.60	41.25	41.79	23.43	24.93	26.16
1050.0	42.68	42.60	42.60	24.37	25.05	25.22
1130.0	44.11	43.24	42.78	28.42	28.23	27.79
1210.0	43.28	42.96	41.84	32.23	32.48	31.89
1290.0	46.68	45.21	43.16	33.72	35.89	35.91
1370.0	36.97	34.39	34.94	31.33	34.32	37.04
1450.0	50.16	46.47	43.14	29.18	31.75	34.95
1530.0	41.54	39.59	37.23	27.09	29.03	31.96
1610.0	38.36	35.16	33.12	26.12	29.74	33.83
1690.0	36.86	32.92	30.86	26.35	29.03	32.05
1770.0	38.40	36.46	34.41	22.99	25.05	27.45
1850.0	35.62	33.36	31.84	21.30	22.98	25.24
1930.0	34.46	33.07	32.06	20.21	21.95	24.03
2010.0	35.00	32.75	31.40	21.30	22.66	24.63
2090.0	38.53	34.83	32.70	24.25	27.00	29.88
2170.0	36.90	33.59	31.59	21.22	22.56	23.73
2230.0	38.58	34.94	32.17	21.03	22.24	22.95
2310.0	38.85	38.05	35.15	21.32	22.02	22.00
2370.0	37.84	36.82	34.95	23.21	24.84	24.35
2450.0	37.49	35.60	32.35	31.10	32.36	28.52
2510.0	41.15	35.60	30.30	39.48	35.17	29.11
2590.0	45.83	37.00	32.47	40.78	30.64	25.22
2650.0	46.38	36.45	32.55	36.40	27.27	23.35
2730.0	41.93	34.66	32.23	29.52	23.88	21.66
2790.0	36.74	32.21	30.29	25.59	22.62	21.07
2870.0	39.97	35.71	33.33	22.71	22.00	21.38
2930.0	36.78	35.29	34.12	21.91	22.26	22.24
3010.0	32.00	31.69	31.72	20.91	21.78	22.18
3070.0	31.14	31.16	31.42	19.49	20.88	21.99
3150.0	31.11	31.51	31.89	19.09	20.88	22.40
3210.0	32.64	33.11	33.45	19.35	21.31	23.08

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		+10	+13	+16
220.0	250.0	32.11	27.24	24.41
300.0	330.0	21.55	18.53	18.01
380.0	410.0	16.33	15.74	15.42
460.0	490.0	14.59	14.15	13.92
540.0	570.0	20.22	19.31	18.65
620.0	650.0	28.73	27.72	26.88
700.0	730.0	31.87	30.82	28.79
780.0	810.0	32.83	30.22	28.19
860.0	890.0	30.43	28.80	27.80
940.0	970.0	31.48	30.68	30.18
1020.0	1050.0	38.55	38.17	38.02
1100.0	1130.0	31.26	30.75	30.41
1180.0	1210.0	27.04	26.65	26.38
1260.0	1290.0	23.18	22.41	22.26
1340.0	1370.0	23.65	21.46	19.97
1420.0	1450.0	22.25	21.91	21.78
1500.0	1530.0	23.44	22.50	21.97
1580.0	1610.0	22.94	23.14	23.33
1660.0	1690.0	23.24	22.73	22.56
1740.0	1770.0	23.02	22.74	22.51
1820.0	1850.0	23.42	22.80	22.59
1900.0	1930.0	22.07	20.97	20.68
1980.0	2010.0	30.30	28.83	27.37
2060.0	2090.0	26.56	25.79	25.12
2140.0	2170.0	28.80	24.28	22.65
2200.0	2230.0	40.08	40.57	32.20
2280.0	2310.0	26.28	25.15	23.74
2340.0	2370.0	26.15	24.46	23.20
2420.0	2450.0	30.11	28.13	25.78
2480.0	2510.0	21.93	21.70	20.76
2560.0	2590.0	17.83	18.96	18.53
2620.0	2650.0	17.82	18.06	17.72
2700.0	2730.0	17.69	16.95	16.55
2760.0	2790.0	16.97	16.21	15.74
2840.0	2870.0	16.63	16.15	15.75
2900.0	2930.0	16.82	16.37	15.92
2980.0	3010.0	15.84	15.42	15.07
3040.0	3070.0	15.09	14.81	14.58
3120.0	3150.0	14.52	14.23	14.00
3180.0	3210.0	14.35	14.03	13.72

Frequency Mixer

MCA1T-24MH+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)			LO (MHz)	LO VSWR (:1)			IF (OUT) (MHz)	IF VSWR @LO=2400MHz (:1)		
		@LO (dBm)				@LO (dBm)				@LO (dBm)		
		+10	+13	+16		+10	+13	+16		+10	+13	+16
220.0	250.0	15.96	8.12	3.93	250.0	28.96	28.03	20.95	10.0	2.49	1.08	1.22
300.0	330.0	2.26	1.97	1.99	330.0	13.49	7.00	6.28	30.0	2.56	1.10	1.21
380.0	410.0	1.69	1.55	1.46	410.0	2.59	2.95	3.82	50.0	2.62	1.14	1.18
460.0	490.0	3.31	2.92	2.68	490.0	1.34	1.88	2.62	70.0	2.55	1.17	1.23
540.0	570.0	4.42	3.95	3.69	570.0	1.36	1.38	1.93	90.0	2.65	1.21	1.21
620.0	650.0	3.83	3.63	3.52	650.0	1.77	1.62	2.09	110.0	2.69	1.25	1.25
700.0	730.0	3.82	3.35	2.99	730.0	1.99	2.08	2.65	130.0	2.84	1.31	1.24
780.0	810.0	4.16	3.67	3.31	810.0	2.31	2.78	3.58	150.0	2.91	1.36	1.28
860.0	890.0	4.24	3.88	3.65	890.0	2.58	3.27	4.25	170.0	3.03	1.42	1.32
940.0	970.0	3.94	3.63	3.47	970.0	2.40	3.31	4.45	190.0	3.09	1.43	1.34
1020.0	1050.0	3.76	3.55	3.42	1050.0	2.47	3.43	4.62	210.0	3.28	1.50	1.36
1100.0	1130.0	4.23	3.88	3.65	1130.0	3.23	3.92	4.91	230.0	3.44	1.56	1.38
1180.0	1210.0	4.55	4.09	3.80	1210.0	3.97	4.24	4.95	250.0	3.60	1.64	1.44
1260.0	1290.0	4.67	4.10	3.83	1290.0	4.63	4.31	4.61	270.0	3.72	1.64	1.42
1340.0	1370.0	3.46	3.01	2.62	1370.0	4.66	4.20	4.32	290.0	3.91	1.71	1.45
1420.0	1450.0	2.97	2.63	2.32	1450.0	4.32	3.43	3.52	310.0	4.13	1.77	1.44
1500.0	1530.0	2.41	1.93	1.50	1530.0	3.56	2.31	2.23	330.0	4.35	1.88	1.52
1580.0	1610.0	1.48	1.17	1.07	1610.0	3.54	2.21	2.03	350.0	4.48	1.92	1.52
1660.0	1690.0	1.34	1.11	1.06	1690.0	3.11	1.92	1.78	370.0	4.59	1.96	1.54
1740.0	1770.0	1.21	1.09	1.14	1770.0	2.48	1.56	1.59	390.0	4.70	2.03	1.55
1820.0	1850.0	1.50	1.32	1.32	1850.0	2.50	1.84	1.88	410.0	4.79	2.09	1.60
1900.0	1930.0	1.65	1.36	1.26	1930.0	2.70	2.21	2.28	430.0	4.98	2.17	1.65
1980.0	2010.0	2.27	1.94	1.72	2010.0	3.30	2.59	2.59	450.0	4.93	2.15	1.63
2060.0	2090.0	2.86	2.49	2.25	2090.0	4.35	3.00	2.77	470.0	5.07	2.21	1.66
2140.0	2170.0	3.26	2.83	2.59	2170.0	5.97	3.30	2.63	490.0	5.10	2.20	1.65
2200.0	2230.0	3.26	2.75	2.57	2230.0	7.02	3.63	2.63	510.0	5.27	2.28	1.71
2280.0	2310.0	3.63	2.71	2.47	2310.0	8.95	4.41	2.63	530.0	5.19	2.21	1.66
2340.0	2370.0	4.23	2.72	2.52	2370.0	10.31	5.95	2.98	550.0	5.19	2.24	1.69
2420.0	2450.0	4.50	2.74	2.49	2450.0	10.96	6.07	3.02	570.0	5.17	2.18	1.66
2480.0	2510.0	3.72	2.58	2.34	2510.0	10.31	5.10	2.71	590.0	5.19	2.20	1.69
2560.0	2590.0	4.33	3.35	3.09	2590.0	9.58	4.63	2.75	610.0	5.12	2.16	1.70
2620.0	2650.0	4.78	3.91	3.60	2650.0	8.68	4.08	2.72	630.0	5.04	2.12	1.70
2700.0	2730.0	4.45	4.01	3.79	2730.0	6.03	3.33	2.92	650.0	4.98	2.11	1.76
2760.0	2790.0	4.15	3.89	3.76	2790.0	4.30	3.20	3.24	670.0	4.84	2.10	1.83
2840.0	2870.0	4.18	3.84	3.62	2870.0	3.31	3.21	3.58	690.0	4.78	2.17	1.97
2900.0	2930.0	4.34	3.97	3.68	2930.0	2.92	3.23	3.73	710.0	4.53	2.16	2.08
2980.0	3010.0	3.81	3.51	3.33	3010.0	2.52	2.98	3.53	730.0	4.39	2.28	2.29
3040.0	3070.0	4.03	3.82	3.67	3070.0	2.26	2.82	3.38	750.0	4.14	2.42	2.58
3120.0	3150.0	4.50	4.27	4.09	3150.0	2.41	2.85	3.27	790.0	3.77	2.92	3.30
3180.0	3210.0	4.70	4.43	4.23	3210.0	2.75	3.06	3.36	810.0	3.64	3.19	3.63

Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	9	21	8	24	20	26	40	46	44	51
1	-	16	+0	21	39	27	39	46	35	46	41	48
2	66	51	60	42	53	55	48	54	57	61	63	57
3	>90	51	68	56	67	53	57	68	66	69	62	65
4	>90	>78	>78	>78	>78	71	73	>78	>78	>78	78	76
5	>90	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78
6	>90	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78
7	>90	>78	>78	>78	>78	>78	>78	>78	>78	77	>78	>78
8	>90	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78
9	>90	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78
10	>90	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78
RF CAL	0	1	2	3	4	5	6	7	8	9	10	

Test conditions:

RF IN: 1350 MHz; -6.00 dBm.
LO IN: 1380 MHz; +13.00 dBm
IF OUT: 30 MHz; -12.21 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	20	35	20	38	32	37	57	66	55	67
1	-	15	+0	26	33	30	45	54	46	62	55	61
2	46	41	53	37	44	46	41	50	52	55	77	61
3	>90	33	41	41	30	39	51	56	69	65	56	57
4	>90	66	57	56	57	51	53	67	56	62	64	72
5	>90	55	59	46	61	58	44	52	53	58	61	67
6	>90	60	62	81	67	61	67	69	60	83	63	78
7	>90	64	60	71	71	59	63	79	54	65	60	63
8	>90	77	81	60	71	73	81	71	>88	67	69	83
9	>90	78	86	>88	71	74	75	73	71	87	62	78
10	>90	>88	87	>88	>88	76	87	81	83	84	>88	82
RF CAL	0	1	2	3	4	5	6	7	8	9	10	

LO HARMONICS ORDER

Test conditions:

RF IN: 1350 MHz; 4.00 dBm.
LO IN: 1380 MHz; +13.00 dBm
IF OUT: 30 MHz; -2.3 dBm


- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

Frequency Mixer


MCA1T-24MH+

Typical Performance Curves


Conversion Loss @ IF=30MHz




Conversion Loss vs. IF @ RF=1210.1MHz




Conversion Loss vs. IF @ RF=289.9MHz




Conversion Loss vs. IF @ RF=2410.1MHz



IP3 Input




Compression @ RF IN=+9dBm




Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	9	21	8	24	20	26	40	46	44	51
1	-	16	+0	21	39	27	39	46	35	46	41	48
2	66	51	60	42	53	55	48	54	57	61	63	57
3	>90	51	68	56	67	53	57	68	66	69	62	65
4	>90	>78	>78	>78	>78	71	73	>78	>78	>78	78	76
5	>90	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78
6	>90	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78
7	>90	>78	>78	>78	>78	>78	>78	>78	>78	77	>78	>78
8	>90	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78
9	>90	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78
10	>90	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78	>78
RF CAL	0	1	2	3	4	5	6	7	8	9	10	

Test conditions:

RF IN: 1350 MHz; -6.00 dBm.
LO IN: 1380 MHz; +13.00 dBm
IF OUT: 30 MHz; -12.21 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	20	35	20	38	32	37	57	66	55	67
1	-	15	+0	26	33	30	45	54	46	62	55	61
2	46	41	53	37	44	46	41	50	52	55	77	61
3	>90	33	41	41	30	39	51	56	69	65	56	57
4	>90	66	57	56	57	51	53	67	56	62	64	72
5	>90	55	59	46	61	58	44	52	53	58	61	67
6	>90	60	62	81	67	61	67	69	60	83	63	78
7	>90	64	60	71	71	59	63	79	54	65	60	63
8	>90	77	81	60	71	73	81	71	>88	67	69	83
9	>90	78	86	>88	71	74	75	73	71	87	62	78
10	>90	>88	87	>88	>88	76	87	81	83	84	>88	82
RF CAL	0	1	2	3	4	5	6	7	8	9	10	

LO HARMONICS ORDER


Test conditions:

RF IN: 1350 MHz; 4.00 dBm.
LO IN: 1380 MHz; +13.00 dBm
IF OUT: 30 MHz; -2.3 dBm


- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

DZ885-2

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm.002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
DZ885-2	.350 (8.89)	.280 (7.11)	.095 (2.41)	-- --	.075 (1.91)	.050 (1.27)	.030 (0.76)	.074 (1.88)	-- --	.096 (2.44)	.321 (8.15)	.030 (0.76)	0.21

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Plastic encapsulation on Ceramic base, mounted on PCB carrier board.
- Termination finish:
For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F34



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
				100
				200
		13	Standard	500
				1000

Note: Availability of small reel quantity varies by model.
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M119455	NEW RELEASE	09/08/08	AV	DJ

**SUGGESTED MOUNTING CONFIGURATION FOR
DZ885-2/DZ1383-2 CASE STYLES
"10MX01" PIN CODE**



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .020" $\pm$.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

INITIALS

DATE

DRAWN

AV

09/05/08

CHECKED

MMG

09/08/08

APPROVED

DJ

09/08/08



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, 10MX01, DZ885-2/DZ1383-2, TB-493

SIZE
ACODE IDENT
15542DRAWING NO:
98-PL-288REV:
OR

FILE: 98PL288

SCALE: 8:1

SHEET: 1 OF 1


Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit

For Pin Connections refer to Data Sheet of the DUT



TB-493+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Case Temperature	Individual Model Data Sheet
Storage Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process: 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215