

Non-Catalog Model

Frequency Mixer

LRMS-2UHJ

Level 17 (LO Power +17 dBm)

Important Note

This is a non-catalog model and can be manufactured on specific request.
Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : QQQ569

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	10		1000	MHz
	RF (fL to fU)	10		1000	MHz
	IF	10		750	MHz
Conversion Loss	mid band		7.1	9.2	dB
	Total Range			9.9	dB
LO-RF Isolation	Low Range	40	50		dB
	Mid Range	30	38		dB
	Upper Range	23	30		dB
LO-IF Isolation	Low Range	30	50		dB
	Mid Range	25	40		dB
	Upper Range	22	34		dB
1 dB Comp. Input Power			+14		dBm

Notes: Low Range = [fL to 10fL]
mid band = [2fL to fU/2]

Mid Range = [10fL to fU/2]


Upper Range = [fU/2 to fU]

Phase detection, positive polarity
Aqueous washable.

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA

PIN CONNECTIONS	
LO	1
RF	4
IF	5
GROUND	2, 3, 6

Electrical Schematics



Frequency Mixer

LRMS-2UHJ

Typical Performance Data

RF (MHz)	LO (MHz)	CONVERSION LOSS (dB)			LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
		@LO (dBm)				@LO (dBm)			@LO (dBm)		
		+14	+17	+20		+14	+17	+20	+14	+17	+20
10.0	40.0	7.08	6.57	6.19	10.0	65.1	63.8	61.3	57.8	57.0	56.1
20.0	50.0	7.08	6.50	6.13	20.0	60.5	60.6	59.6	56.0	55.1	54.3
50.0	80.0	7.01	6.37	5.98	50.0	54.1	55.2	55.6	54.7	52.6	50.7
97.4	67.4	6.91	6.33	5.95	97.4	48.3	50.0	51.1	54.3	49.2	46.4
100.0	70.0	6.91	6.34	5.96	100.0	48.1	49.8	50.9	54.4	49.2	46.3
184.7	154.7	7.06	6.58	6.34	184.7	43.5	46.0	46.0	60.4	46.9	42.0
200.0	170.0	7.03	6.61	6.36	200.0	42.9	44.2	45.3	55.8	46.3	41.5
272.1	242.1	7.67	7.05	6.61	272.1	40.4	41.6	43.0	45.8	42.3	38.6
359.4	329.4	8.57	7.68	6.91	359.4	38.0	39.9	41.6	40.2	39.6	36.3
446.8	416.8	9.29	8.11	7.36	446.8	36.8	39.1	41.1	37.3	36.2	34.5
475.9	445.9	9.40	8.07	7.24	475.9	37.1	39.7	41.7	36.9	35.2	33.3
500.0	470.0	9.46	8.04	7.20	500.0	37.1	39.8	42.2	36.3	35.2	33.3
534.1	504.1	9.34	8.08	7.27	534.1	36.8	39.4	41.7	35.6	35.2	33.5
621.5	591.5	9.70	8.27	7.45	621.5	36.4	37.9	39.7	34.5	34.6	33.8
708.8	678.8	10.44	8.76	7.79	708.8	35.9	37.2	38.1	36.5	34.5	33.1
796.2	766.2	10.20	8.91	8.00	796.2	35.3	36.1	36.4	43.5	36.9	34.2
883.5	853.5	10.34	9.44	8.77	883.5	36.1	36.2	36.2	40.3	42.6	37.5
941.8	911.8	10.27	9.54	8.98	941.8	36.5	36.4	36.2	34.5	38.8	37.3
970.9	940.9	9.94	9.32	8.90	970.9	36.9	36.8	36.4	32.0	35.4	35.5
1000.0	970.0	10.18	9.47	9.22	1000.0	36.4	36.4	36.1	29.8	32.6	33.0

REV. X1
LRMS-2UHJ
060612
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Frequency Mixer

LRMS-2UHJ

Typical Performance Data

RF/LO (MHz)	RF VSWR (:1)			LO VSWR (:1)			IF (MHz)	IF VSWR (:1)		
	@LO (dBm)			@LO (dBm)				@LO (dBm)		
	+14	+17	+20	+14	+17	+20		+14	+17	+20
10.0	1.49	1.46	1.45	1.54	1.86	2.56	10.0	1.85	1.80	1.80
20.0	1.29	1.25	1.23	1.26	1.74	2.49	20.0	1.43	1.40	1.44
50.0	1.26	1.20	1.16	1.16	1.80	2.56	50.0	1.21	1.12	1.19
100.0	1.41	1.34	1.30	1.17	1.68	2.34	100.0	1.24	1.05	1.10
115.0	1.46	1.39	1.35	1.18	1.68	2.35	115.0	1.27	1.09	1.11
190.0	1.83	1.73	1.69	1.44	1.64	2.11	190.0	1.43	1.24	1.18
200.0	1.90	1.80	1.75	1.49	1.64	2.08	200.0	1.46	1.26	1.19
280.0	2.34	2.19	2.11	1.68	1.58	1.87	280.0	1.60	1.35	1.23
370.0	3.00	2.71	2.54	1.85	1.52	1.68	370.0	1.69	1.38	1.21
460.0	3.18	2.81	2.58	1.82	1.40	1.50	460.0	1.60	1.30	1.13
490.0	3.21	2.82	2.56	1.82	1.36	1.45	490.0	1.57	1.28	1.14
500.0	3.17	2.77	2.52	1.82	1.33	1.49	500.0	1.54	1.26	1.14
550.0	2.97	2.53	2.26	1.70	1.29	1.47	550.0	1.46	1.33	1.35
640.0	2.49	2.14	1.96	1.54	1.25	1.56	640.0	1.37	1.46	1.60
730.0	2.29	2.01	1.85	1.41	1.35	1.78	730.0	1.50	1.78	2.02
820.0	2.57	2.28	2.13	1.49	1.58	1.98	820.0	1.87	2.24	2.56
910.0	3.14	2.83	2.64	1.78	1.83	2.19	910.0	2.26	2.59	2.92
970.0	3.81	3.45	3.21	2.12	2.04	2.34	970.0	2.52	2.82	3.11
985.0	4.26	3.82	3.54	2.28	2.11	2.34	985.0	2.64	2.93	3.21
1000.0	4.39	3.91	3.67	2.49	2.20	2.35	1000.0	2.65	2.91	3.16

REV. X1
LRMS-2UHJ
060612
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


Conversion Loss




LO-RF Isolation




LO-IF Isolation




RF VSWR



LO VSWR



IF VSWR



REV. X1

LRMS-2UHJ

060612

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$


CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT, GRAM
QQQ569	.390 (9.90)	.31 (7.87)	.225 (5.72)	.060 (1.52)	-	.100 (2.54)	.045 (1.14)	.420 (10.67)	.120 (3.05)	.060 (1.52)	.100 (2.54)	-	.50

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Ceramic.
- Termination finish:
 - For RoHS Case Styles: Tin plate over Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.

Tape & Reel Packaging TR-F5



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82272	NEW RELEASE	08/02/02	AV	DJ
A	M102713	UPDATED NOTES	01/14/06	GF	IL

SUGGESTED MOUNTING CONFIGURATION FOR QQQ569 CASE STYLE, "w" PIN CONNECTION



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030" $\pm$ 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

AV

07/19/02

TOLERANCES ON:

CHECKED

WL

08/02/02

2 PL DECIMALS $\pm$.005

APPROVED

DJ

08/02/02

ANGLES $\pm$

FRACTIONS $\pm$

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, w, QQQ569, LRMS-J, TB-44

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-083

REV:

A

FILE: 98PL083


SCALE:

6:1


SHEET:

1 OF 1

Evaluation Board and Circuit



TB-44+



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215