

Surface Mount

Power Splitter/Combiner

LRPS-2-11

2 Way-0° 50Ω 20 to 2000 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.125W max.


Pin Connections

SUM PORT	6
PORT 1	4
PORT 2	3
GROUND	1,2,5

Outline Drawing




PCB Land Pattern



Outline Dimensions (inch mm)

A	B	C	D	E	F	G
.400	.31	.200	.10	.010	.100	.050
10.16	7.87	5.08	2.54	0.25	2.54	1.27
H	J	K	L	M		wt
.420	.120	.060	.100	.020		grams
10.67	3.05	1.52	2.54	0.51		0.55

Demo Board MCL P/N: TB-100 Suggested PCB Layout (PL-057)



Features

- very wideband, 20 to 2000 MHz
- low insertion loss, 0.7 dB typ.
- good isolation, 21 dB typ.

Applications

- cellular
- GPS
- communications systems



CASE STYLE: QQQ130



Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)						INSERTION LOSS (dB) ABOVE 3.0 dB						PHASE UNBALANCE (Degrees)			AMPLITUDE UNBALANCE (dB)		
	L		M		U		L		M		U		L		M		U	
	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Max.	Max.	Max.	Max.	Max.	Max.
20-2000	19	15	21	15	30	15	0.6	0.8	0.7	1.0	0.8	1.5	2.0	3.0	5.0	0.2	0.3	0.7


L = 20-200 MHz M = 200-1000 MHz U = 1000-2000 MHz

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
20.00	3.57	3.55	0.01	18.82	0.10	1.98	1.58	1.58
60.00	3.58	3.57	0.01	18.71	0.18	1.96	1.58	1.57
100.00	3.59	3.59	0.01	18.70	0.29	1.95	1.58	1.58
160.00	3.61	3.59	0.02	18.72	0.45	1.94	1.58	1.58
300.00	3.63	3.64	0.01	18.84	0.77	1.91	1.58	1.59
600.00	3.65	3.65	0.00	19.55	1.46	1.84	1.57	1.59
800.00	3.65	3.63	0.02	20.59	1.76	1.76	1.56	1.59
950.00	3.65	3.60	0.05	21.89	1.90	1.71	1.55	1.58
1150.00	3.65	3.56	0.09	24.73	1.89	1.62	1.53	1.56
1300.00	3.67	3.64	0.03	28.68	1.70	1.53	1.52	1.54
1450.00	3.72	3.60	0.12	37.99	1.45	1.46	1.50	1.51
1600.00	3.78	3.73	0.05	34.62	1.03	1.42	1.49	1.48
1850.00	3.94	3.83	0.11	22.22	0.16	1.45	1.47	1.40
1950.00	4.01	3.94	0.07	19.58	0.70	1.51	1.46	1.36
2000.00	4.03	4.02	0.01	18.65	0.98	1.55	1.46	1.34



electrical schematic



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. A
M120055
LRPS-2-11
ED-2361
DJ/TD/CP/AM
090119

2 Way-0° Power Splitter/Combiner

LRPS-2-11

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +25°C

FREQ. (MHz)	INSERTION LOSS (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB) 1-2	VSWR (:1)		
	S-1	S-2				S	1	2
10	3.54	3.54	0.00	0.03	18.03	1.99	1.54	1.53
20	3.55	3.55	0.00	0.08	18.11	1.98	1.54	1.53
30	3.55	3.55	0.00	0.12	18.10	1.98	1.54	1.54
40	3.56	3.56	0.00	0.15	18.10	1.98	1.54	1.54
50	3.57	3.57	0.00	0.18	18.12	1.97	1.54	1.54
100	3.59	3.59	0.00	0.36	18.25	1.96	1.55	1.55
150	3.61	3.60	0.01	0.56	18.38	1.95	1.56	1.56
200	3.61	3.61	0.00	0.75	18.50	1.94	1.57	1.57
250	3.63	3.62	0.01	0.94	18.65	1.93	1.57	1.57
300	3.64	3.62	0.02	1.11	18.84	1.92	1.58	1.58
350	3.65	3.63	0.02	1.28	19.03	1.92	1.58	1.58
400	3.66	3.63	0.03	1.43	19.22	1.91	1.59	1.59
450	3.67	3.63	0.04	1.56	19.44	1.90	1.59	1.59
500	3.68	3.63	0.05	1.71	19.70	1.90	1.60	1.60
550	3.69	3.64	0.05	1.85	19.98	1.89	1.60	1.60
600	3.70	3.64	0.06	2.00	20.28	1.88	1.61	1.60
650	3.71	3.63	0.08	2.08	20.63	1.87	1.62	1.61
700	3.72	3.63	0.09	2.17	20.99	1.87	1.63	1.61
750	3.73	3.63	0.10	2.27	21.46	1.86	1.63	1.62
800	3.74	3.63	0.11	2.33	21.93	1.85	1.64	1.62
850	3.75	3.62	0.13	2.46	22.48	1.83	1.65	1.63
900	3.76	3.61	0.15	2.45	23.06	1.82	1.66	1.63
950	3.77	3.60	0.17	2.42	23.74	1.81	1.66	1.64
1000	3.79	3.60	0.19	2.48	24.51	1.80	1.67	1.64
1050	3.79	3.59	0.20	2.46	25.38	1.78	1.68	1.65
1100	3.80	3.58	0.22	2.44	26.35	1.76	1.69	1.65
1150	3.82	3.57	0.25	2.39	27.48	1.75	1.69	1.65
1200	3.83	3.55	0.28	2.33	28.75	1.73	1.70	1.66
1250	3.83	3.55	0.28	2.27	30.38	1.71	1.71	1.66
1300	3.84	3.53	0.31	2.13	32.15	1.69	1.71	1.65
1350	3.85	3.53	0.32	2.05	34.11	1.67	1.71	1.65
1400	3.86	3.52	0.34	1.92	35.37	1.65	1.72	1.65
1450	3.87	3.52	0.35	1.82	35.00	1.62	1.72	1.65
1500	3.87	3.50	0.37	1.55	33.60	1.60	1.72	1.64
1550	3.88	3.50	0.38	1.35	31.55	1.58	1.72	1.64
1600	3.89	3.49	0.40	1.07	29.57	1.55	1.72	1.63
1650	3.89	3.48	0.41	0.85	27.62	1.53	1.72	1.63
1700	3.90	3.47	0.43	0.52	26.09	1.50	1.72	1.62
1750	3.93	3.47	0.46	0.25	24.71	1.48	1.70	1.61
1800	3.92	3.48	0.44	0.06	23.28	1.46	1.70	1.60
1850	3.93	3.48	0.45	0.40	22.13	1.44	1.70	1.59
1900	3.95	3.47	0.48	0.89	21.18	1.42	1.69	1.58
1950	3.95	3.49	0.46	1.20	20.15	1.40	1.68	1.56
2000	3.96	3.51	0.45	1.48	19.20	1.39	1.66	1.55
2050	3.97	3.53	0.44	2.11	18.40	1.39	1.66	1.53
2100	3.97	3.55	0.42	2.54	17.59	1.39	1.64	1.52
2150	4.00	3.58	0.42	3.02	16.84	1.39	1.62	1.50
2200	4.00	3.62	0.38	3.77	16.17	1.41	1.62	1.48
2250	4.04	3.66	0.38	4.52	15.49	1.43	1.60	1.46
2300	4.06	3.70	0.36	4.86	14.84	1.46	1.58	1.44
2400	4.17	3.82	0.35	6.10	13.70	1.53	1.54	1.40
2500	4.22	3.96	0.26	7.04	12.64	1.63	1.51	1.36
2600	4.29	4.16	0.13	8.71	11.63	1.77	1.51	1.32



INTERNET <http://www.minicircuits.com>
 Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
 Mini-Circuits ISO 9001 & ISO 14001 Certified



REV. X1
 LRPS-2-11
 080204
 Page 1 of 3

2 Way-0° Power Splitter/Combiner

LRPS-2-11

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = -40°C

FREQ. (MHz)	INSERTION LOSS (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB) 1-2	VSWR (:1)		
	S-1	S-2				S	1	2
10	3.53	3.53	0.00	0.04	17.18	1.99	1.55	1.54
20	3.54	3.54	0.00	0.11	18.68	1.99	1.58	1.58
30	3.54	3.54	0.00	0.15	19.13	1.99	1.59	1.60
40	3.55	3.55	0.00	0.20	19.38	1.99	1.60	1.61
50	3.56	3.56	0.00	0.25	19.53	1.98	1.61	1.62
100	3.57	3.56	0.01	0.50	19.84	1.96	1.62	1.62
150	3.58	3.57	0.01	0.79	19.93	1.95	1.63	1.62
200	3.59	3.58	0.01	1.06	19.93	1.95	1.63	1.64
250	3.60	3.57	0.03	1.33	19.99	1.94	1.63	1.63
300	3.60	3.57	0.03	1.61	20.16	1.93	1.63	1.64
350	3.61	3.57	0.04	1.87	20.37	1.92	1.64	1.64
400	3.61	3.57	0.04	2.12	20.52	1.92	1.64	1.64
450	3.63	3.57	0.06	2.37	20.70	1.91	1.65	1.65
500	3.64	3.57	0.07	2.60	20.92	1.91	1.65	1.65
550	3.64	3.56	0.08	2.85	21.23	1.90	1.65	1.65
600	3.65	3.56	0.09	3.09	21.52	1.89	1.66	1.65
650	3.66	3.55	0.11	3.29	21.87	1.88	1.66	1.66
700	3.67	3.54	0.13	3.45	22.24	1.87	1.67	1.66
750	3.67	3.53	0.14	3.67	22.74	1.87	1.68	1.67
800	3.68	3.53	0.15	3.83	23.27	1.86	1.68	1.67
850	3.69	3.51	0.18	4.05	23.84	1.84	1.69	1.67
900	3.70	3.51	0.19	4.18	24.49	1.83	1.70	1.68
950	3.71	3.49	0.22	4.33	25.23	1.82	1.70	1.68
1000	3.72	3.49	0.23	4.41	26.18	1.80	1.71	1.69
1050	3.73	3.47	0.26	4.58	27.11	1.79	1.72	1.69
1100	3.73	3.45	0.28	4.59	28.35	1.78	1.72	1.69
1150	3.75	3.45	0.30	4.79	29.71	1.76	1.73	1.70
1200	3.74	3.44	0.30	4.78	31.66	1.74	1.74	1.70
1250	3.76	3.42	0.34	4.81	33.49	1.73	1.74	1.70
1300	3.76	3.41	0.35	4.78	35.92	1.71	1.75	1.70
1350	3.77	3.40	0.37	4.86	37.51	1.69	1.75	1.69
1400	3.77	3.39	0.38	4.81	36.84	1.67	1.75	1.69
1450	3.78	3.37	0.41	4.71	34.51	1.65	1.76	1.68
1500	3.79	3.36	0.43	4.66	31.99	1.62	1.76	1.68
1550	3.79	3.35	0.44	4.58	29.69	1.60	1.76	1.67
1600	3.79	3.34	0.46	4.41	27.79	1.57	1.76	1.67
1650	3.80	3.32	0.48	4.26	26.21	1.55	1.76	1.66
1700	3.80	3.32	0.48	4.13	24.63	1.53	1.75	1.66
1750	3.82	3.30	0.52	3.81	23.51	1.50	1.74	1.65
1800	3.80	3.31	0.49	3.78	22.10	1.47	1.74	1.64
1850	3.83	3.30	0.52	3.80	21.06	1.45	1.71	1.63
1900	3.82	3.30	0.52	3.28	20.20	1.43	1.72	1.62
1950	3.83	3.32	0.51	3.18	19.28	1.41	1.69	1.61
2000	3.85	3.33	0.52	3.07	18.44	1.39	1.68	1.59
2050	3.81	3.34	0.47	2.38	17.60	1.39	1.69	1.57
2100	3.85	3.36	0.49	1.85	16.91	1.39	1.68	1.55
2150	3.84	3.39	0.45	1.66	16.19	1.39	1.65	1.54
2200	3.87	3.42	0.45	0.96	15.56	1.40	1.64	1.52
2250	3.91	3.45	0.46	0.64	14.87	1.42	1.61	1.49
2300	3.91	3.50	0.42	0.30	14.21	1.44	1.60	1.47
2400	3.98	3.60	0.38	1.12	13.04	1.50	1.57	1.42
2500	4.01	3.73	0.27	2.07	12.08	1.59	1.54	1.38
2600	4.12	3.89	0.23	3.28	11.23	1.71	1.52	1.34



INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified



REV. X1
LRPS-2-11
080204
Page 2 of 3

2 Way-0° Power Splitter/Combiner

LRPS-2-11

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +85°C

FREQ. (MHz)	INSERTION LOSS (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB) 1-2	VSWR (:1)		
	S-1	S-2				S	1	2
10	3.54	3.54	0.00	0.03	15.75	1.98	1.42	1.42
20	3.55	3.55	0.00	0.10	15.80	1.98	1.42	1.42
30	3.55	3.55	0.00	0.13	15.79	1.97	1.42	1.42
40	3.56	3.57	0.01	0.18	15.80	1.97	1.43	1.42
50	3.57	3.57	0.00	0.21	15.81	1.97	1.43	1.42
100	3.60	3.60	0.00	0.41	15.93	1.96	1.44	1.44
150	3.62	3.62	0.00	0.57	16.09	1.95	1.44	1.45
200	3.63	3.63	0.00	0.75	16.28	1.93	1.45	1.45
250	3.64	3.64	0.00	0.92	16.49	1.93	1.46	1.47
300	3.65	3.65	0.00	1.08	16.69	1.92	1.47	1.47
350	3.66	3.67	0.01	1.24	16.89	1.91	1.48	1.48
400	3.68	3.67	0.01	1.38	17.09	1.91	1.49	1.49
450	3.69	3.68	0.01	1.51	17.33	1.90	1.50	1.50
500	3.70	3.69	0.01	1.63	17.59	1.89	1.50	1.50
550	3.72	3.69	0.03	1.75	17.91	1.89	1.51	1.51
600	3.72	3.70	0.02	1.86	18.23	1.88	1.52	1.52
650	3.73	3.70	0.03	1.93	18.60	1.87	1.53	1.52
700	3.75	3.70	0.05	1.97	18.97	1.86	1.54	1.53
750	3.76	3.70	0.06	2.08	19.41	1.85	1.55	1.54
800	3.77	3.71	0.06	2.10	19.85	1.84	1.56	1.55
850	3.78	3.70	0.08	2.19	20.34	1.82	1.57	1.55
900	3.79	3.70	0.09	2.18	20.86	1.81	1.58	1.56
950	3.80	3.70	0.10	2.20	21.44	1.79	1.59	1.57
1000	3.81	3.70	0.11	2.17	22.09	1.78	1.60	1.57
1050	3.83	3.69	0.14	2.17	22.75	1.76	1.60	1.58
1100	3.84	3.69	0.15	2.06	23.54	1.74	1.61	1.58
1150	3.85	3.68	0.16	2.10	24.45	1.72	1.62	1.59
1200	3.85	3.69	0.16	2.02	25.41	1.70	1.62	1.59
1250	3.86	3.67	0.19	1.90	26.45	1.68	1.63	1.59
1300	3.87	3.67	0.20	1.75	27.72	1.66	1.63	1.59
1350	3.88	3.67	0.21	1.73	29.13	1.63	1.64	1.58
1400	3.89	3.67	0.22	1.58	30.79	1.61	1.64	1.58
1450	3.90	3.65	0.25	1.37	32.50	1.58	1.64	1.57
1500	3.92	3.64	0.28	1.20	34.21	1.56	1.64	1.57
1550	3.92	3.65	0.27	1.04	35.03	1.53	1.64	1.56
1600	3.93	3.65	0.29	0.76	34.52	1.51	1.64	1.56
1650	3.94	3.64	0.30	0.50	32.79	1.48	1.64	1.55
1700	3.94	3.65	0.29	0.30	30.62	1.45	1.63	1.54
1750	3.97	3.64	0.33	0.09	29.10	1.43	1.62	1.54
1800	3.96	3.66	0.30	0.22	27.02	1.41	1.62	1.53
1850	3.97	3.67	0.30	0.32	25.30	1.38	1.61	1.52
1900	3.99	3.66	0.33	0.89	24.34	1.37	1.61	1.51
1950	4.00	3.69	0.31	1.19	23.04	1.35	1.59	1.50
2000	4.04	3.70	0.34	1.21	22.02	1.33	1.56	1.49
2050	4.00	3.73	0.27	1.87	20.92	1.33	1.57	1.47
2100	4.03	3.76	0.27	2.38	20.04	1.32	1.56	1.46
2150	4.06	3.78	0.27	2.77	19.24	1.33	1.54	1.44
2200	4.06	3.81	0.25	3.37	18.41	1.34	1.54	1.43
2250	4.09	3.85	0.24	3.57	17.63	1.35	1.50	1.41
2300	4.12	3.89	0.22	4.18	16.96	1.37	1.50	1.40
2400	4.15	4.02	0.13	5.58	15.60	1.44	1.49	1.37
2500	4.20	4.14	0.06	6.53	14.45	1.51	1.47	1.34
2600	4.26	4.30	0.04	7.68	13.42	1.60	1.45	1.31



INTERNET <http://www.minicircuits.com>
 Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
 Mini-Circuits ISO 9001 & ISO 14001 Certified




REV. X1
 LRPS-2-11
 080204
 Page 3 of 3

2 Way-0° Power Splitter/Combiner


LRPS-2-11

Typical Performance Curves


Insertion Loss




Insertion Loss S-1 vs. TEMPERATURE




Amplitude Unbalance vs. TEMPERATURE



Phase Unbalance vs. TEMPERATURE






Isolation 1-2 vs. TEMPERATURE



2 Way-0° Power Splitter/Combiner

LRPS-2-11

Typical Performance Curves




Case Style


QQQ

Outline Dimensions

QQQ130 (non-waterproof)
QQQ828 (washable)



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT, GRAM
QQQ130	.400 (10.16)	.31 (7.87)	.200 (5.08)	.10 (2.54)	.010 (.25)	.100 (2.54)	.050 (1.27)	.420 (10.67)	.120 (3.05)	.060 (1.52)	.100 (2.54)	.020 (.51)	.55
QQQ828			.050 (1.27)										.20

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Ceramic.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Tape & Reel Packaging TR-F10



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	16	7	10,20,50,100,200
		13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Note: Please consult individual model data sheet to determine device per reel availability.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82272	NEW RELEASE	08/05/02	GF	DJ
A	M102713	ADDED NOTE 2 & "...WITH SMOBC",	01/18/06	MMG	LC
		QQQ130/828 WAS QQQ569/828 CASE STYLE			


SUGGESTED MOUNTING CONFIGURATION FOR QQQ130/828 CASE STYLE, "gn" PIN CONNECTION



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" $\pm$.002"; COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

GF

07/17/02

TOLERANCES ON:

CHECKED

HY


08/01/02

2 PL DECIMALS $\pm$

APPROVED

DJ

08/05/02

3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$ 

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, gn, QQQ130/828, LRPS/SCL, TB-100

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-057


REV:
A

FILE: 98PL057


SCALE: 6:1

SHEET: 1 OF 1

Evaluation Board and Circuit



TB-100



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215