



Mini-Circuits®

CERAMIC BALUN

## RF Transformer

NCS2-771-75+

75Ω 240 to 770 MHz 1:2 Ratio

## FEATURES

- Wideband, 240 to 770 MHz
- Low phase unbalance, 7 deg. and amplitude unbalance, 0.3 dB typ
- Miniature size 0805, 0.079"x0.049"x0.033"
- LTCC construction
- Low cost
- Aqueous washable

## APPLICATIONS

- VHF/UHF
- Signal process
- Instrumentation



Generic photo used for illustration purposes only

CASE STYLE: GE0805C-9

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## ELECTRICAL SPECIFICATIONS AT 25°C

| Parameter                           | Frequency (MHz) | Min. | Typ. | Max. | Units  |
|-------------------------------------|-----------------|------|------|------|--------|
| Impedance Ratio (Secondary/Primary) |                 | 2    |      |      |        |
| Frequency Range                     |                 | 240  |      | 770  | MHz    |
| Insertion Loss <sup>1</sup>         | 240 - 770       | —    | 0.8  | 1.2  | dB     |
| Amplitude Unbalance                 | 240 - 770       | —    | 0.3  | 1.0  | dB     |
| Phase Unbalance <sup>2</sup>        | 240 - 770       | —    | 7    | 10   | Degree |

1. Reference Demo Board TB-626+

2. Relative to 180°


## MAXIMUM RATINGS

| Parameter             | Ratings        |
|-----------------------|----------------|
| Operating Temperature | -55°C to 100°C |
| Storage Temperature   | -55°C to 100°C |
| RF Power <sup>3</sup> | 2W             |

3. Passband rating, derate linearly to 1W at 100°C ambient.

Permanent damage may occur if any of these limits are exceeded.

## CONFIGURATION J



\*Internal open circuit

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. C  
ECO-010420  
NCS2-771-75+  
MCL NY  
211112

PAGE 1 OF 3



Mini-Circuits

CERAMIC BALUN

# RF Transformer


NCS2-771-75+

## PAD CONNECTIONS

|                               |     |
|-------------------------------|-----|
| PRIMARY DOT (Unbalanced Port) | 2   |
| PRIMARY (GND)                 | 1,3 |
| SECONDARY DOT (Balanced)      | 4   |
| SECONDARY (Balanced)          | 6   |
| NO CONNECTION                 | 5   |

PRODUCT MARKING: N/A


## DEMO BOARD MCL P/N: TB-626+ SUGGESTED PCB LAYOUT (PL-348)




### NOTES:

1. TRACE WIDTH IS SHOWN FOR REFERENCE ONLY.
  2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)  
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

## OUTLINE DRAWING



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

## OUTLINE DIMENSIONS (Inches/mm)

| A    | B    | C    | D    | E     | F    |
|------|------|------|------|-------|------|
| .079 | .049 | .033 | .014 | .012  | .012 |
| 2.0  | 1.24 | 0.84 | 0.36 | 0.30  | 0.30 |
| G    | H    | J    | K    | wt    |      |
| .026 | .014 | .039 | .110 | grams |      |
| 0.66 | 0.36 | 1.00 | 2.80 | .008  |      |




## TAPE & REEL INFORMATION: F74



TYPICAL PERFORMANCE DATA<sup>3</sup>

| Frequency (MHz) | Insertion Loss (dB) | Input Return Loss (dB) | Amplitude Unbalance (dB) | Phase Unbalance (deg) |
|-----------------|---------------------|------------------------|--------------------------|-----------------------|
| 240             | 0.66                | 18.76                  | 0.21                     | 4.45                  |
| 300             | 0.58                | 20.33                  | 0.17                     | 5.57                  |
| 370             | 0.63                | 16.43                  | 0.14                     | 6.29                  |
| 420             | 0.67                | 15.22                  | 0.12                     | 6.26                  |
| 500             | 0.72                | 14.73                  | 0.10                     | 5.34                  |
| 570             | 0.74                | 15.18                  | 0.10                     | 3.40                  |
| 620             | 0.75                | 16.01                  | 0.08                     | 1.41                  |
| 670             | 0.76                | 17.24                  | 0.06                     | 1.10                  |
| 710             | 0.77                | 18.58                  | 0.04                     | 3.65                  |
| 770             | 0.79                | 21.67                  | 0.04                     | 7.99                  |

3. Measured with Agilent E5071B network analyzer using impedance conversion and port extension.



## NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

# RF Transformer

# NCS2-771-75+

## Typical Performance Data

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS*<br>(dB) | INPUT<br>RETURN LOSS<br>(dB) | AMPLITUDE<br>UNBALANCE<br>(dB) | PHASE<br>UNBALANCE**<br>(deg) |
|--------------------|----------------------------|------------------------------|--------------------------------|-------------------------------|
| 140                | 3.09                       | 4.19                         | 0.26                           | 1.51                          |
| 150                | 2.48                       | 5.23                         | 0.26                           | 1.91                          |
| 160                | 2.00                       | 6.38                         | 0.26                           | 2.27                          |
| 170                | 1.63                       | 7.63                         | 0.25                           | 2.59                          |
| 180                | 1.35                       | 8.98                         | 0.24                           | 2.90                          |
| 190                | 1.14                       | 10.44                        | 0.24                           | 3.19                          |
| 200                | 0.98                       | 11.97                        | 0.23                           | 3.47                          |
| 210                | 0.86                       | 13.60                        | 0.23                           | 3.75                          |
| 220                | 0.77                       | 15.31                        | 0.22                           | 3.98                          |
| 230                | 0.71                       | 17.06                        | 0.22                           | 4.23                          |
| 240                | 0.66                       | 18.76                        | 0.21                           | 4.45                          |
| 260                | 0.61                       | 21.37                        | 0.20                           | 4.90                          |
| 280                | 0.59                       | 21.67                        | 0.19                           | 5.24                          |
| 300                | 0.58                       | 20.33                        | 0.17                           | 5.57                          |
| 320                | 0.59                       | 18.91                        | 0.16                           | 5.84                          |
| 340                | 0.60                       | 17.73                        | 0.15                           | 6.08                          |
| 360                | 0.62                       | 16.80                        | 0.14                           | 6.18                          |
| 380                | 0.64                       | 16.11                        | 0.14                           | 6.30                          |
| 400                | 0.65                       | 15.61                        | 0.13                           | 6.31                          |
| 420                | 0.67                       | 15.22                        | 0.12                           | 6.26                          |
| 440                | 0.68                       | 14.98                        | 0.12                           | 6.16                          |
| 460                | 0.70                       | 14.82                        | 0.11                           | 5.96                          |
| 480                | 0.71                       | 14.73                        | 0.11                           | 5.70                          |
| 500                | 0.72                       | 14.73                        | 0.10                           | 5.34                          |
| 520                | 0.73                       | 14.78                        | 0.10                           | 4.93                          |
| 540                | 0.74                       | 14.89                        | 0.10                           | 4.39                          |
| 560                | 0.74                       | 15.07                        | 0.10                           | 3.76                          |
| 580                | 0.75                       | 15.32                        | 0.09                           | 3.08                          |
| 600                | 0.75                       | 15.63                        | 0.09                           | 2.29                          |
| 620                | 0.75                       | 16.01                        | 0.08                           | 1.41                          |
| 640                | 0.76                       | 16.44                        | 0.08                           | 0.48                          |
| 660                | 0.76                       | 16.95                        | 0.07                           | 0.54                          |
| 680                | 0.76                       | 17.54                        | 0.06                           | 1.71                          |
| 700                | 0.77                       | 18.20                        | 0.05                           | 2.99                          |
| 720                | 0.77                       | 18.99                        | 0.03                           | 4.30                          |
| 730                | 0.78                       | 19.45                        | 0.02                           | 5.04                          |
| 740                | 0.78                       | 19.94                        | 0.01                           | 5.75                          |
| 750                | 0.78                       | 20.49                        | 0.00                           | 6.50                          |
| 760                | 0.79                       | 21.05                        | 0.02                           | 7.24                          |
| 770                | 0.79                       | 21.67                        | 0.04                           | 7.99                          |
| 780                | 0.80                       | 22.31                        | 0.05                           | 8.79                          |
| 790                | 0.81                       | 22.97                        | 0.07                           | 9.61                          |
| 800                | 0.82                       | 23.62                        | 0.09                           | 10.42                         |
| 810                | 0.83                       | 24.26                        | 0.10                           | 11.27                         |
| 820                | 0.84                       | 24.83                        | 0.12                           | 12.13                         |
| 830                | 0.85                       | 25.33                        | 0.13                           | 13.04                         |
| 840                | 0.86                       | 25.63                        | 0.16                           | 13.95                         |
| 850                | 0.87                       | 25.84                        | 0.18                           | 14.86                         |

\* Reference Demo Board TB-626+

\*\*Phase Unbalance is relative to 180°







P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)




IF/RF MICROWAVE COMPONENTS

REV. A  
 NCS2-771-75+  
 2/5/2015  
 Page 1 of 1


## Typical Performance Data



## Outline Dimensions



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

| CASE #    | A              | B              | C              | D              | E              | F              | G              | H              | J              | K              | WT.GRAM |
|-----------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|---------|
| GE0805C-9 | .079<br>(2.00) | .049<br>(1.25) | .037<br>(0.95) | .014<br>(0.35) | .012<br>(0.30) | .012<br>(0.30) | .026<br>(0.65) | .014<br>(0.35) | .039<br>(1.00) | .110<br>(2.80) | .008    |

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

- Open style, ceramic base.
- Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.  
For RoHS-5 Case Styles: Tin-Lead plate over Nickel plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F114

## DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

| Applicable Case Styles |           |
|------------------------|-----------|
| GE0805C                | JC0603C   |
| GE0805C-1              | JC0603C-4 |
| GE0805C-1AP            | JC0603C-6 |
| GE0805C-7              |           |
| GE0805C-9              |           |
| GE0805C-10             |           |
| GE0805C-11             |           |
| GE0805C-12             |           |




ILLUSTRATION 2

| Applicable Case Styles |           |
|------------------------|-----------|
| GE0805C-2              | JC0603C-1 |
| GE0805C-3              | JC0603C-2 |
| GE0805C-4              | JC0603C-3 |
| GE0805C-5              | JC0603C-5 |
| GE0805C-6              | JC0603C-7 |
| GE0805C-8              | JV1210C-1 |
| GE0805C-15             |           |

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |      |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 8              | 4                       | 7                 | Small quantity standards (see note) | 20   |
|                |                         |                   |                                     | 50   |
|                |                         |                   |                                     | 100  |
|                |                         |                   |                                     | 200  |
|                |                         |                   |                                     | 500  |
|                |                         |                   |                                     | 1000 |
|                |                         |                   | Standard                            | 4000 |

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


## THIRD ANGLE PROJECTION



## REVISIONS

| REV | ECN No. | DESCRIPTION              | DATE     | DR | AUTH |
|-----|---------|--------------------------|----------|----|------|
| OR  | M132367 | NEW RELEASE              | 07/20/11 | GF | ABD  |
| A   | M151441 | UPDATED TRACE WIDTH INFO | 06/05/15 | GF | WP   |
|     |         |                          |          |    |      |


SUGGESTED MOUNTING CONFIGURATION FOR  
GE0805C-1 CASE STYLE, "06TJ01" PIN CODE

**NOTES:**

1. TRACE WIDTH IS SHOWN FOR REFERENCE ONLY.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC  
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED | INITIALS     | DATE     |
|----------------------------|--------------|----------|
| DIMENSIONS ARE IN INCHES   | DRAWN GF     | 06/20/11 |
| TOLERANCES ON:             | CHECKED IL   | 07/20/11 |
| 2 PL DECIMALS ±            | APPROVED ABD | 07/20/11 |
| 3 PL DECIMALS ± .005       |              |          |
| ANGLES ±                   |              |          |
| FRACTIONS ±                |              |          |

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95





**Mini-Circuits®**

13 Neptune Avenue  
Brooklyn NY 11235

PL, 06TJ01, GE0805C-1, TB-626+

| SIZE  | CODE IDENT | DRAWING NO: | REV:   |
|-------|------------|-------------|--------|
| A     | 15542      | 98-PL-348   | A      |
| FILE: | 98PL348    | SCALE:      | 20:1   |
|       |            | SHEET:      | 1 OF 1 |

# Evaluation Board and Circuit



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.010 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition                                                           | Reference/Spec                                                                                       |
|----------------------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature      | -55° to 100°C<br>Ambient Environment                                                | Individual Model Data Sheet                                                                          |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment                                               | Individual Model Data Sheet                                                                          |
| Humidity                   | 90 to 95% RH, 240 hours, 50°C                                                       | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Solder Reflow Heat         | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak              | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1                                                        |
| Solderability              | 10X Magnification                                                                   | J-STD-002, Para 4.2.5, Test S, 95% Coverage                                                          |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock           | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                   | MIL-STD-202, Method 213, Condition A                                                                 |