

3 Way-0° 50Ω 10 to 300 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.375W max.
Permanent damage may occur if any of these limits are exceeded.	


Pin Connections

SUM PORT	6
PORT 1	1
PORT 2	2
PORT 3	3
GROUND	4,5

Outline Drawing




PCB Land Pattern

Suggested Layout,
Tolerance to be within ±.002

Outline Dimensions (inch mm)

A	B	C	D	E	F	G
.390	.31	.225	.060	--	.100	.045
9.91	7.87	5.72	1.52	--	2.54	1.14
H	J	K	L	M	wt	
.420	.120	.060	.100	--	grams	
10.67	3.05	1.52	2.54	--	0.50	

Demo Board MCL P/N: TB-225
Suggested PCB Layout (PL-170)

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Features

- low insertion loss, 0.3 dB typ.
- good isolation, 25 dB typ.
- aqueous washable
- J-leads for strain relief & excellent solderability

Applications

- VHF
- defense & federal communications



Generic photo used for illustration purposes only

CASE STYLE: QQQ569

Electrical Specifications




FREQ. RANGE (MHz)	ISOLATION (dB)						INSERTION LOSS (dB) ABOVE 4.8 dB						PHASE UNBALANCE (Degrees)			AMPLITUDE UNBALANCE (dB)		
	L		M		U		L		M		U		L		M		U	
	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Max.	Max.	Max.	Max.	Max.	Max.
10-300	25	20	25	20	25	20	0.2	0.6	0.3	0.8	0.5	1.2	2	3	4	0.1	0.3	0.7

L = low range [f_L to $10 f_L$] M = mid range [$10 f_L$ to $f_U/2$] U = upper range [$f_U/2$ to f_U]


Typical Performance Data

Freq. (MHz)	Total Loss ¹ (dB)			Amp. Unbal. (dB)	Isolation (dB)			Phase Unbal. (deg.)	VSWR S	VSWR 1	VSWR 2	VSWR 3
	S-1	S-2	S-3		1-2	1-3	2-3					
10.00	5.09	5.10	5.10	0.01	25.23	25.70	25.35	0.12	1.29	1.08	1.09	1.08
20.00	5.09	5.10	5.10	0.01	25.12	25.56	25.20	0.21	1.27	1.06	1.07	1.07
30.00	5.09	5.10	5.10	0.01	24.91	25.32	24.94	0.31	1.26	1.06	1.06	1.06
45.00	5.09	5.10	5.10	0.01	24.63	25.03	24.63	0.42	1.25	1.05	1.06	1.06
60.00	5.10	5.12	5.11	0.01	24.44	24.82	24.38	0.58	1.25	1.05	1.06	1.06
75.00	5.12	5.13	5.13	0.01	24.26	24.64	24.15	0.69	1.25	1.05	1.05	1.06
90.00	5.13	5.14	5.14	0.01	24.12	24.53	23.97	0.82	1.24	1.05	1.05	1.06
110.00	5.15	5.17	5.17	0.01	23.97	24.38	23.75	1.00	1.24	1.05	1.05	1.06
140.00	5.20	5.21	5.21	0.02	23.85	24.26	23.52	1.18	1.23	1.05	1.05	1.06
180.00	5.26	5.28	5.27	0.02	23.91	24.29	23.41	1.48	1.21	1.04	1.04	1.06
210.00	5.31	5.33	5.31	0.02	24.17	24.50	23.53	1.70	1.19	1.04	1.04	1.06
240.00	5.37	5.40	5.38	0.03	24.72	24.91	23.89	1.84	1.16	1.05	1.04	1.06
270.00	5.44	5.47	5.44	0.03	25.65	25.60	24.56	2.00	1.12	1.06	1.05	1.06
290.00	5.49	5.52	5.49	0.03	26.59	26.28	25.26	2.06	1.10	1.07	1.05	1.06
300.00	5.53	5.55	5.52	0.04	27.22	26.71	25.71	2.09	1.09	1.07	1.06	1.06

1. Total Loss = Insertion Loss + 4.8dB splitter loss.



electrical schematic



3 Way-0° Power Splitter/Combiner

LRPS-3-1J+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)			AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)			
	S-1	S-2	S-3			1-2	1-3	2-3	S	1	2	3
10	5.03	5.04	5.04	0.01	0.12	24.43	24.59	24.42	1.27	1.10	1.11	1.11
20	5.04	5.05	5.05	0.01	0.17	24.36	24.55	24.37	1.25	1.08	1.08	1.08
30	5.04	5.05	5.05	0.01	0.27	24.20	24.39	24.18	1.25	1.08	1.08	1.08
40	5.04	5.05	5.05	0.01	0.33	24.08	24.30	24.06	1.24	1.07	1.07	1.07
50	5.06	5.06	5.06	0.00	0.43	23.99	24.21	23.95	1.24	1.07	1.07	1.07
60	5.07	5.08	5.07	0.01	0.50	23.91	24.14	23.84	1.24	1.07	1.07	1.07
70	5.07	5.08	5.08	0.01	0.57	23.84	24.08	23.76	1.23	1.07	1.07	1.07
80	5.09	5.09	5.09	0.00	0.65	23.78	24.03	23.68	1.23	1.06	1.06	1.07
90	5.10	5.10	5.10	0.00	0.74	23.73	23.99	23.60	1.23	1.06	1.06	1.06
100	5.11	5.11	5.11	0.00	0.81	23.70	23.95	23.53	1.23	1.06	1.06	1.06
110	5.12	5.13	5.12	0.01	0.90	23.66	23.91	23.46	1.22	1.06	1.06	1.06
120	5.13	5.14	5.13	0.01	0.97	23.61	23.88	23.40	1.22	1.06	1.05	1.06
130	5.15	5.15	5.14	0.01	1.04	23.59	23.85	23.34	1.22	1.06	1.05	1.05
140	5.16	5.16	5.14	0.02	1.13	23.58	23.85	23.31	1.22	1.06	1.05	1.05
150	5.17	5.17	5.15	0.02	1.20	23.59	23.85	23.28	1.22	1.05	1.05	1.05
160	5.19	5.18	5.16	0.03	1.26	23.60	23.84	23.26	1.21	1.05	1.05	1.05
170	5.19	5.19	5.17	0.02	1.35	23.61	23.83	23.24	1.21	1.05	1.05	1.05
180	5.21	5.21	5.18	0.03	1.43	23.66	23.85	23.25	1.21	1.05	1.05	1.04
190	5.23	5.22	5.19	0.04	1.49	23.72	23.87	23.27	1.20	1.05	1.05	1.04
200	5.24	5.23	5.20	0.04	1.56	23.80	23.91	23.32	1.20	1.06	1.05	1.04
210	5.25	5.24	5.21	0.04	1.63	23.92	23.97	23.39	1.19	1.06	1.05	1.04
220	5.27	5.26	5.22	0.05	1.68	24.04	24.04	23.48	1.19	1.06	1.05	1.04
230	5.29	5.27	5.23	0.06	1.74	24.20	24.12	23.59	1.18	1.06	1.06	1.04
240	5.30	5.28	5.24	0.06	1.81	24.38	24.21	23.72	1.18	1.07	1.06	1.04
250	5.32	5.30	5.25	0.07	1.84	24.61	24.31	23.89	1.17	1.07	1.06	1.04
260	5.34	5.32	5.27	0.07	1.91	24.89	24.45	24.10	1.17	1.08	1.07	1.04
270	5.36	5.34	5.27	0.09	1.97	25.20	24.60	24.35	1.16	1.08	1.08	1.04
280	5.38	5.35	5.29	0.09	2.01	25.57	24.78	24.64	1.16	1.09	1.08	1.05
290	5.40	5.36	5.30	0.10	2.06	26.00	24.95	24.98	1.16	1.09	1.09	1.05
300	5.43	5.38	5.31	0.12	2.11	26.49	25.15	25.38	1.16	1.10	1.10	1.05
310	5.46	5.41	5.33	0.13	2.14	27.12	25.38	25.87	1.16	1.11	1.10	1.06
320	5.49	5.44	5.35	0.14	2.17	27.83	25.64	26.43	1.17	1.12	1.11	1.07
330	5.52	5.46	5.37	0.15	2.21	28.69	25.90	27.13	1.18	1.13	1.12	1.07
340	5.54	5.48	5.39	0.15	2.25	29.73	26.17	27.95	1.19	1.14	1.13	1.08
350	5.58	5.51	5.41	0.17	2.26	31.01	26.41	28.92	1.21	1.15	1.14	1.09
375	5.70	5.61	5.50	0.20	2.31	36.10	26.94	32.73	1.28	1.18	1.17	1.12
400	5.85	5.74	5.60	0.25	2.35	40.83	27.02	42.24	1.37	1.22	1.20	1.14
425	6.05	5.92	5.76	0.28	2.33	32.24	26.31	38.65	1.51	1.26	1.23	1.18
450	6.31	6.14	5.96	0.35	2.25	26.66	24.79	29.55	1.69	1.30	1.26	1.21
475	6.67	6.46	6.26	0.41	2.16	22.85	22.91	24.72	1.93	1.35	1.30	1.25
500	7.13	6.88	6.65	0.48	2.02	20.00	20.99	21.38	2.24	1.41	1.33	1.30
525	7.73	7.43	7.16	0.57	2.24	17.75	19.24	18.84	2.63	1.46	1.36	1.34
550	8.46	8.10	7.79	0.67	2.60	15.95	17.72	16.85	3.14	1.51	1.39	1.38
575	9.37	8.94	8.57	0.80	3.00	14.49	16.43	15.27	3.76	1.56	1.42	1.42

¹Total Loss = Insertion Loss + 4.8dB Splitter Loss

REV. X2
LRPS-3-1J+
100624
Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



3 Way-0° Power Splitter/Combiner

LRPS-3-1J+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = -40°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)			AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)			
	S-1	S-2	S-3			1-2	1-3	2-3	S	1	2	3
10	4.91	4.92	4.92	0.01	0.11	24.39	24.86	24.69	1.28	1.17	1.16	1.16
20	4.98	4.99	4.99	0.01	0.16	25.44	25.74	25.48	1.25	1.08	1.08	1.08
30	4.99	5.00	5.01	0.02	0.25	25.52	25.76	25.48	1.25	1.06	1.05	1.06
40	5.00	5.01	5.02	0.02	0.31	25.45	25.69	25.38	1.24	1.04	1.04	1.05
50	5.01	5.01	5.03	0.02	0.44	25.38	25.61	25.28	1.24	1.04	1.03	1.04
60	5.02	5.02	5.03	0.01	0.51	25.32	25.55	25.18	1.24	1.03	1.02	1.03
70	5.03	5.03	5.04	0.01	0.59	25.26	25.50	25.10	1.23	1.03	1.02	1.03
80	5.04	5.03	5.05	0.02	0.70	25.21	25.45	25.03	1.23	1.02	1.02	1.03
90	5.05	5.04	5.05	0.01	0.77	25.15	25.41	24.94	1.23	1.02	1.02	1.03
100	5.05	5.05	5.06	0.01	0.85	25.11	25.37	24.86	1.23	1.02	1.02	1.02
110	5.07	5.06	5.06	0.01	0.95	25.05	25.32	24.77	1.23	1.01	1.02	1.02
120	5.07	5.07	5.07	0.00	1.04	25.00	25.28	24.69	1.22	1.01	1.01	1.02
130	5.09	5.07	5.08	0.01	1.12	24.95	25.23	24.61	1.22	1.01	1.01	1.02
140	5.09	5.08	5.08	0.01	1.21	24.93	25.20	24.56	1.22	1.01	1.01	1.02
150	5.10	5.09	5.09	0.01	1.27	24.91	25.19	24.51	1.22	1.01	1.02	1.02
160	5.12	5.09	5.10	0.03	1.35	24.90	25.18	24.47	1.22	1.01	1.02	1.01
170	5.13	5.10	5.11	0.03	1.45	24.89	25.14	24.42	1.22	1.01	1.02	1.01
180	5.14	5.12	5.11	0.03	1.53	24.92	25.13	24.40	1.21	1.01	1.02	1.01
190	5.15	5.12	5.12	0.03	1.60	24.97	25.14	24.41	1.21	1.02	1.03	1.01
200	5.16	5.13	5.13	0.03	1.69	25.04	25.17	24.44	1.21	1.02	1.03	1.01
210	5.18	5.14	5.13	0.05	1.75	25.15	25.22	24.50	1.20	1.02	1.03	1.00
220	5.19	5.15	5.14	0.05	1.87	25.27	25.28	24.59	1.20	1.03	1.04	1.00
230	5.20	5.16	5.15	0.05	1.93	25.44	25.35	24.70	1.19	1.03	1.04	1.00
240	5.22	5.17	5.15	0.07	2.00	25.63	25.43	24.83	1.18	1.04	1.05	1.01
250	5.23	5.17	5.16	0.07	2.06	25.88	25.52	25.03	1.18	1.04	1.05	1.01
260	5.25	5.19	5.17	0.08	2.12	26.20	25.67	25.26	1.17	1.05	1.06	1.01
270	5.27	5.21	5.18	0.09	2.21	26.56	25.84	25.55	1.17	1.06	1.07	1.02
280	5.29	5.22	5.18	0.11	2.26	27.00	26.02	25.89	1.16	1.06	1.08	1.02
290	5.30	5.22	5.19	0.11	2.32	27.51	26.20	26.30	1.16	1.07	1.08	1.03
300	5.32	5.24	5.20	0.12	2.39	28.12	26.41	26.77	1.16	1.08	1.09	1.04
310	5.35	5.27	5.22	0.13	2.45	28.89	26.64	27.37	1.16	1.09	1.10	1.04
320	5.37	5.28	5.23	0.14	2.51	29.79	26.89	28.07	1.16	1.10	1.11	1.05
330	5.40	5.30	5.25	0.15	2.55	30.91	27.15	28.95	1.17	1.11	1.12	1.06
340	5.43	5.32	5.26	0.17	2.60	32.34	27.38	30.00	1.18	1.12	1.12	1.07
350	5.46	5.34	5.28	0.18	2.63	34.13	27.58	31.31	1.20	1.13	1.13	1.07
375	5.57	5.43	5.35	0.22	2.74	41.64	27.79	37.00	1.26	1.16	1.16	1.10
400	5.70	5.55	5.45	0.25	2.89	36.65	27.32	49.23	1.36	1.19	1.19	1.13
425	5.88	5.70	5.59	0.30	2.86	29.56	25.98	33.43	1.49	1.23	1.22	1.16
450	6.13	5.91	5.77	0.36	2.87	24.99	24.09	27.20	1.68	1.28	1.25	1.19
475	6.47	6.21	6.05	0.42	2.82	21.66	22.08	23.21	1.92	1.32	1.29	1.23
500	6.90	6.61	6.42	0.48	2.73	19.07	20.16	20.25	2.24	1.38	1.32	1.27
525	7.48	7.14	6.91	0.57	3.07	16.96	18.45	17.91	2.66	1.43	1.36	1.32
550	8.19	7.80	7.54	0.65	3.45	15.26	16.98	16.06	3.19	1.48	1.39	1.37
575	9.08	8.62	8.31	0.77	3.90	13.87	15.75	14.56	3.87	1.53	1.42	1.41

¹Total Loss = Insertion Loss + 4.8dB Splitter Loss

REV. X2
LRPS-3-1J+
100624
Page 2 of 3



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits®



3 Way-0° Power Splitter/Combiner

LRPS-3-1J+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +85°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)			AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)			
	S-1	S-2	S-3			1-2	1-3	2-3	S	1	2	3
10	5.08	5.09	5.09	0.01	0.14	23.10	23.30	23.19	1.27	1.15	1.15	1.15
20	5.08	5.10	5.09	0.02	0.21	22.95	23.17	23.05	1.26	1.14	1.14	1.13
30	5.09	5.11	5.10	0.02	0.31	22.83	23.06	22.91	1.25	1.13	1.13	1.13
40	5.10	5.12	5.11	0.02	0.37	22.75	23.00	22.82	1.25	1.13	1.13	1.13
50	5.11	5.13	5.12	0.02	0.49	22.68	22.93	22.73	1.24	1.13	1.13	1.13
60	5.12	5.15	5.13	0.03	0.56	22.62	22.87	22.64	1.24	1.12	1.13	1.12
70	5.13	5.16	5.15	0.03	0.62	22.56	22.83	22.57	1.24	1.12	1.13	1.12
80	5.15	5.17	5.16	0.02	0.73	22.52	22.79	22.51	1.23	1.12	1.12	1.12
90	5.16	5.18	5.17	0.02	0.80	22.48	22.76	22.44	1.23	1.12	1.12	1.12
100	5.17	5.20	5.18	0.03	0.88	22.45	22.73	22.38	1.23	1.12	1.11	1.11
110	5.19	5.21	5.19	0.02	0.99	22.42	22.71	22.33	1.23	1.11	1.11	1.11
120	5.20	5.23	5.20	0.03	1.08	22.40	22.69	22.28	1.23	1.11	1.10	1.11
130	5.22	5.24	5.22	0.03	1.16	22.39	22.67	22.24	1.22	1.11	1.10	1.11
140	5.23	5.26	5.23	0.03	1.25	22.40	22.68	22.23	1.22	1.11	1.09	1.10
150	5.24	5.27	5.24	0.03	1.33	22.42	22.69	22.21	1.22	1.11	1.09	1.10
160	5.26	5.29	5.25	0.04	1.38	22.45	22.70	22.21	1.21	1.10	1.09	1.10
170	5.28	5.30	5.26	0.04	1.49	22.47	22.71	22.20	1.21	1.10	1.09	1.09
180	5.29	5.32	5.28	0.04	1.56	22.52	22.73	22.22	1.20	1.10	1.09	1.09
190	5.31	5.33	5.29	0.04	1.62	22.59	22.76	22.25	1.20	1.10	1.08	1.09
200	5.32	5.35	5.30	0.05	1.68	22.68	22.81	22.31	1.19	1.10	1.08	1.09
210	5.34	5.37	5.31	0.06	1.73	22.79	22.88	22.38	1.19	1.10	1.08	1.08
220	5.36	5.39	5.33	0.06	1.82	22.91	22.96	22.46	1.18	1.10	1.08	1.08
230	5.38	5.40	5.34	0.06	1.85	23.05	23.04	22.57	1.18	1.10	1.08	1.08
240	5.39	5.42	5.35	0.07	1.92	23.21	23.12	22.69	1.18	1.10	1.08	1.08
250	5.42	5.44	5.36	0.08	1.96	23.41	23.21	22.83	1.17	1.10	1.08	1.08
260	5.44	5.46	5.38	0.08	2.01	23.65	23.34	23.01	1.17	1.11	1.08	1.07
270	5.47	5.49	5.40	0.09	2.07	23.91	23.49	23.23	1.16	1.11	1.09	1.07
280	5.49	5.51	5.42	0.09	2.11	24.21	23.65	23.47	1.16	1.12	1.09	1.08
290	5.51	5.52	5.42	0.10	2.16	24.56	23.80	23.76	1.16	1.12	1.10	1.08
300	5.54	5.55	5.44	0.11	2.21	24.96	23.98	24.07	1.16	1.13	1.10	1.08
310	5.57	5.58	5.47	0.11	2.23	25.46	24.19	24.47	1.17	1.13	1.11	1.08
320	5.61	5.61	5.49	0.12	2.26	26.01	24.42	24.92	1.18	1.14	1.12	1.09
330	5.64	5.64	5.52	0.12	2.28	26.68	24.68	25.47	1.19	1.15	1.13	1.10
340	5.67	5.67	5.54	0.13	2.30	27.46	24.94	26.10	1.20	1.16	1.13	1.10
350	5.72	5.70	5.57	0.15	2.30	28.38	25.19	26.82	1.22	1.17	1.14	1.11
375	5.85	5.82	5.67	0.18	2.34	31.78	25.85	29.49	1.29	1.20	1.17	1.13
400	6.01	5.96	5.79	0.22	2.35	37.70	26.31	34.46	1.39	1.24	1.19	1.16
425	6.23	6.15	5.95	0.27	2.31	36.34	26.26	47.49	1.52	1.28	1.23	1.19
450	6.50	6.40	6.18	0.32	2.22	29.18	25.34	33.66	1.69	1.32	1.26	1.23
475	6.89	6.74	6.48	0.41	2.11	24.60	23.78	27.10	1.92	1.37	1.29	1.27
500	7.36	7.17	6.89	0.47	1.94	21.33	21.95	23.06	2.21	1.43	1.33	1.31
525	7.98	7.73	7.41	0.57	2.18	18.83	20.19	20.16	2.57	1.48	1.36	1.35
550	8.74	8.43	8.06	0.68	2.52	16.86	18.61	17.95	3.03	1.53	1.39	1.40
575	9.66	9.27	8.84	0.82	2.93	15.30	17.26	16.22	3.57	1.58	1.41	1.43

¹Total Loss = Insertion Loss + 4.8dB Splitter Loss

REV. X2
LRPS-3-1J+
100624
Page 3 of 3



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits®




3 Way-0° Power Splitter/Combiner


LRPS-3-1J+

Typical Performance Curves


Total Loss




Total Loss S-1 vs. TEMPERATURE




Amplitude Unbalance vs. TEMPERATURE




Phase Unbalance vs. TEMPERATURE



Isolation



Isolation 1-2 vs. TEMPERATURE



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




REV. X2
LRPS-3-1J+
100624
Page 1 of 2

3 Way-0° Power Splitter/Combiner

LRPS-3-1J+

Typical Performance Curves



REV. X2
LRPS-3-1J+
100624
Page 2 of 2




Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$


CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT, GRAM
QQQ569	.390 (9.90)	.31 (7.87)	.225 (5.72)	.060 (1.52)	-	.100 (2.54)	.045 (1.14)	.420 (10.67)	.120 (3.05)	.060 (1.52)	.100 (2.54)	-	.50

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Ceramic.
- Termination finish:
 - For RoHS Case Styles: Tin plate over Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.

Tape & Reel Packaging TR-F5



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M94650	NEW RELEASE	10/11/04	MMG	HY
A	M100924	CHANGED ORIENTATION PIN 1 TO PIN 6	09/23/05	GT	HY
B	M102713	ADDED "...WITH SMOBC"	01/17/06	MMG	IL

**SUGGESTED MOUNTING CONFIGURATION
FOR QQQ569 CASE STYLE, "gt" PIN CONNECTION**



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" $\pm$.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

MMG

10/07/04

TOLERANCES ON:

CHECKED

AV


10/11/04

2 PL DECIMALS $\pm$

APPROVED

HY

10/11/04

3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$ 

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VEEDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, gt, QQQ569, LRPS-3-1J, TB-225

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-170

REV:

B

FILE:

98PL170


SCALE:

8:1


SHEET:

1 OF 1

Evaluation Board and Circuit



TB-225



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215