

Frequency Mixer WIDE BAND

Level 4 (LO Power+4 dBm) 2800 to 8500 MHz

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	50 mW
IF Current	40 mA

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

LO	10
RF	5
IF	3
GROUND	1,2,4,6,7,8,9

Outline Drawing



PCB Land Pattern




Suggested Layout,
Tolerance to be within $\pm .002$

Outline Dimensions ($\frac{\text{inch}}$)

A	B	C	D	E	F	G
.30	.250	.085	.266	.050	.050	.012
7.62	6.35	2.16	6.76	1.27	1.27	0.30
H	J	K	L	M		wt
.029	.004	.085	.296	.030		grams
0.74	0.10	2.16	7.52	0.76		0.25

Demo Board MCL P/N: TB-144
Suggested PCB Layout (PL-045)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .020" $\pm$.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC
 (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- Notes:**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms_iso

Features

- wide bandwidth, 2800 to 8500 MHz
- high L-R isolation, 35 dB typ.
- IF, DC to 1200 MHz
- LTCC double balanced mixer
- aqueous washable
- low cost
- low profile, 0.08"
- protected by US Patent 7,027,795

Applications

- satellite up and down converters
- line of sight links
- defense radar
- defense communication

Electrical Specifications (T_{AMB}=-55°C to 100°C)

FREQUENCY (MHz)		CONVERSION LOSS (dB)			LO-RF ISOLATION (dB)		LO-IF ISOLATION (dB)		IP3 at center band (dBm)
LO/RF f_L - f_U	IF	$\overline{X}$	σ	Max.	Typ.	Min.	Typ.	Min.	Typ.
2800-8500	DC-1200								
2800-5000	DC-1200	5.7	0.2	8.4*	35	20	13	7	11
5000-7500	DC-1200	6.0	0.3	8.4*	35	20	38	20	7
7500-8500	DC-1200	7.0	0.3	—	31	—	32	—	8



1 dB COMPR. 0 dBm typ.

* Conversion loss at 30 MHz IF. increases with IF frequency.

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +4dBm	LO +4dBm	LO +4dBm	LO +4dBm	LO +4dBm
2800.10	2770.10	6.06	39.50	11.58	2.48	1.91
3000.10	2970.10	5.85	44.16	13.00	2.48	1.84
3500.10	3470.10	5.47	39.32	13.49	2.00	1.86
4000.10	3970.10	6.67	35.79	12.28	2.46	2.08
4500.10	4470.10	6.70	28.08	16.04	2.01	2.43
5000.10	4970.10	6.55	35.79	27.00	2.60	2.28
5500.10	5470.10	6.27	42.78	33.73	2.22	3.31
6000.10	5970.10	6.26	36.23	37.80	2.15	4.41
6500.10	6470.10	5.90	36.41	47.06	2.10	3.13
6700.10	6670.10	5.84	33.42	50.18	2.18	3.06
6800.10	6770.10	5.84	33.65	46.65	2.00	3.62
6900.10	6870.10	5.88	33.84	43.73	2.07	3.35
7000.10	6970.10	5.98	33.85	41.08	2.07	3.19
7500.10	7470.10	6.80	39.32	33.99	1.83	3.16
7600.10	7570.10	7.17	39.67	33.16	1.68	3.99
7700.10	7670.10	7.41	40.86	32.27	1.63	4.00
7800.10	7770.10	7.48	40.67	31.25	1.68	3.52
7900.10	7870.10	7.28	37.86	30.76	1.70	3.52
8000.10	7970.10	7.02	35.05	30.85	1.77	3.68
8500.10	8470.10	6.93	32.51	33.93	2.22	4.99

Electrical Schematic











Generic photo used for illustration purposes only

CASE STYLE: DZ885

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications





Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Frequency Mixer

MCA1-85L+

Typical Performance Data

RF (MHz)	LO (MHz)	CONVERSION LOSS (dB)			LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)			LO (MHz)	RF (MHz)	IP3 Input (dBm)
		@LO (dBm)				@LO (dBm)			@LO (dBm)					@LO (dBm)
		+1	+4	+7		+1	+4	+7	+1	+4	+7			+4
2800.1	2770.1	6.60	6.06	5.89	2770.1	45.69	39.50	36.81	12.36	11.58	10.35	2470.1	2500.1	9.06
3000.1	2970.1	6.28	5.85	5.74	2970.1	49.14	44.16	39.38	14.26	13.00	11.75	2570.1	2600.1	7.53
3500.1	3470.1	5.98	5.47	5.29	3470.1	34.75	39.32	38.41	13.49	13.49	13.58	2950.1	2980.1	8.42
4000.1	3970.1	7.23	6.67	6.48	3970.1	29.94	35.79	40.21	10.39	12.28	13.89	3010.1	3040.1	10.48
4500.1	4470.1	7.62	6.70	6.38	4470.1	25.02	28.08	31.07	14.59	16.04	17.67	3250.1	3280.1	8.86
5000.1	4970.1	7.69	6.55	6.17	4970.1	34.25	35.79	37.03	27.28	27.00	26.23	3770.1	3800.1	13.07
5500.1	5470.1	7.60	6.27	5.85	5470.1	44.87	42.78	40.91	37.93	33.73	31.19	3870.1	3900.1	13.67
6000.1	5970.1	8.02	6.26	5.74	5970.1	34.59	36.23	37.20	38.70	37.80	35.68	4670.1	4700.1	11.27
6500.1	6470.1	7.33	5.90	5.38	6470.1	32.69	36.41	39.09	48.92	47.06	43.95	5670.1	5700.1	8.02
6700.1	6670.1	7.76	5.84	5.40	6670.1	31.88	33.42	36.15	58.91	50.18	48.35	6070.1	6100.1	5.85
6800.1	6770.1	7.56	5.84	5.46	6770.1	31.79	33.65	36.09	50.51	46.65	46.81	6270.1	6300.1	6.34
6900.1	6870.1	7.27	5.88	5.51	6870.1	31.61	33.84	36.10	45.47	43.73	44.52	6470.1	6500.1	6.32
7000.1	6970.1	7.18	5.98	5.59	6970.1	31.74	33.85	36.07	42.13	41.08	42.59	6670.1	6700.1	6.16
7500.1	7470.1	8.34	6.80	6.30	7470.1	39.48	39.32	38.79	33.47	33.99	35.25	6870.1	6900.1	7.29
7600.1	7570.1	8.87	7.17	6.60	7570.1	41.43	39.67	38.05	32.98	33.16	34.31	7070.1	7100.1	8.76
7700.1	7670.1	9.56	7.41	6.86	7670.1	40.67	40.86	37.33	32.74	32.27	33.25	7270.1	7300.1	9.21
7800.1	7770.1	10.22	7.48	6.86	7770.1	38.38	40.67	36.19	32.98	31.25	31.74	7470.1	7500.1	10.23
7900.1	7870.1	10.36	7.28	6.63	7870.1	38.09	37.86	34.32	33.92	30.76	30.19	7670.1	7700.1	9.89
8000.1	7970.1	9.97	7.02	6.31	7970.1	36.83	35.05	32.74	36.56	30.85	29.14	8070.1	8100.1	8.23
8500.1	8470.1	10.33	6.93	6.24	8470.1	32.27	32.51	30.84	31.22	33.93	33.04	8670.1	8700.1	12.12

REV. X1
MCA1-85L+
061022
Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Frequency Mixer

MCA1-85L+

Typical Performance Data

RF/LO (MHz)	RF VSWR (:1)			LO VSWR (:1)			IF (MHz)	IF VSWR (:1)		
	@LO (dBm)			@LO (dBm)				@LO (dBm)		
	+1	+4	+7	+1	+4	+7		+1	+4	+7
2770.1	3.34	2.48	2.20	1.71	1.91	2.37	10.1	1.53	1.06	1.17
2970.1	2.89	2.48	2.17	1.55	1.84	2.36	30.1	1.56	1.06	1.18
3470.1	2.46	2.00	1.75	1.21	1.86	2.57	40.1	1.57	1.07	1.18
3970.1	2.93	2.46	2.33	1.70	2.08	2.71	50.1	1.58	1.07	1.19
4470.1	2.36	2.01	1.86	2.78	2.43	2.62	60.1	1.59	1.08	1.19
4970.1	2.94	2.60	2.34	3.60	2.28	2.21	70.1	1.58	1.09	1.20
5470.1	2.81	2.22	1.88	4.83	3.31	2.81	80.1	1.58	1.10	1.20
5970.1	3.40	2.15	1.94	10.69	4.41	3.00	90.1	1.58	1.11	1.21
6470.1	2.82	2.10	1.83	12.71	3.13	2.16	100.1	1.59	1.12	1.21
6670.1	3.18	2.18	1.90	7.20	3.06	2.20	200.1	1.65	1.19	1.26
6770.1	2.87	2.00	1.78	8.35	3.62	2.38	300.1	1.74	1.29	1.33
6870.1	2.35	2.07	1.81	6.68	3.35	2.32	400.1	1.86	1.38	1.38
6970.1	2.21	2.07	1.80	6.09	3.19	2.29	500.1	2.01	1.47	1.42
7470.1	1.96	1.83	1.65	4.05	3.16	2.25	600.1	2.22	1.57	1.46
7570.1	1.97	1.68	1.53	6.17	3.99	2.67	700.1	2.46	1.67	1.51
7670.1	1.92	1.63	1.48	5.97	4.00	2.70	800.1	2.65	1.77	1.56
7770.1	2.05	1.68	1.50	4.72	3.52	2.50	900.1	2.67	1.93	1.66
7870.1	2.36	1.70	1.51	5.04	3.52	2.44	1000.1	2.49	2.08	1.78
7970.1	2.84	1.77	1.56	6.15	3.68	2.47	1100.1	3.00	2.20	1.93
8470.1	3.52	2.22	1.87	6.68	4.99	3.03	1200.1	3.73	1.97	1.83

REV. X1
MCA1-85L+
061022
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661









The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Frequency Mixer

MCA1-85L+

Typical Performance Curves



IF VSWR



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




REV. X1
MCA1-85L+
061022
Page 1 of 1

Outline Dimensions

DZ885
DZ1034



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
DZ885	.30 (7.62)	.250 (6.35)	.085 (2.16)	.266 (6.76)	.050 (1.27)	.050 (1.27)	.012 (0.30)	.029 (0.74)	.004 (0.10)	.085 (2.16)	.296 (7.52)	.030 (0.76)	0.25
DZ1034			.105 (2.67)										0.3

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Plastic encapsulation on Ceramic base.
- Termination finish:
 - For RoHS Case Styles: Tin plate. All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F34



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
				100
				200
		13	Standard	500
				1000

Note: Availability of small reel quantity varies by model.
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
A	M81781	UPDATED PCB LAYOUT	06/07/02	GF	DJ
B	M82377	UPDATED DRAWING	07/31/02	AV	WL
C	M102713	ADDED NOTE 2 & "...WITH SMOBC"	01/17/06	MMG	IL
D	M135488	ADDED DZ1650, CHANGED PIN CONN.	02/02/12	GF	DJ

SUGGESTED MOUNTING CONFIGURATION FOR DZ883, DZ885 & DZ1650 CASE STYLES, "10MX01" PIN CONNECTION



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" $\pm$.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:
 2 PL DECIMALS $\pm$
 3 PL DECIMALS $\pm$.005
 ANGLES $\pm$
 FRACTIONS $\pm$

DRAWN

AV

05/08/02

CHECKED

DB

05/16/02

APPROVED

WL

05/16/02

 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, 10MX01, DZ883/885/1650, TB-144

 SIZE
A

 CODE IDENT
15542

 DRAWING NO:
98-PL-045


 REV:
D

FILE: 98PL045


SCALE: 8:1

SHEET: 1 OF 1

Evaluation Board and Circuit



TB-144



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process: 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215