

50Ω 40 to 400 MHz

## Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.

## Pin Connections

|             |           |
|-------------|-----------|
| INPUT       | 1         |
| OUTPUT      | 2         |
| COUPLED     | 5         |
| GROUND      | 3,4,6,7,8 |
| CASE GROUND | 3,4,6,7,8 |

## Features

- high power, up to 10W power input
- wideband, 40 to 400 MHz
- low mainline loss, 0.2 dB typ.
- excellent directivity, 30 dB typ.
- rugged welded construction, hermetically sealed

## Applications

- power levelling
- military & defense communications
- VSWR measurement




Generic photo used for illustration purposes only

CASE STYLE: A01

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## Outline Drawing



## Outline Dimensions (inch mm)

| A     | B     | C    | D     | E    | F     |
|-------|-------|------|-------|------|-------|
| .770  | .800  | .385 | .400  | .370 | .400  |
| 19.56 | 20.32 | 9.78 | 10.16 | 9.40 | 10.16 |
| G     | H     | J    | K     |      | wt    |
| .200  | .20   | .14  | .031  |      | grams |
| 5.08  | 5.08  | 3.56 | 0.79  |      | 5.2   |

## Directional Coupler Electrical Specifications

| FREQ.<br>(MHz) | COUPLING<br>(dB)               |      | MAINLINE LOSS <sup>1</sup><br>(dB) |      |      |      |      |      | DIRECTIVITY<br>(dB) |      |      |      |      |      | VSWR<br>(:1) | POWER<br>INPUT, W |      |
|----------------|--------------------------------|------|------------------------------------|------|------|------|------|------|---------------------|------|------|------|------|------|--------------|-------------------|------|
|                |                                |      | L                                  |      | M    |      | U    |      | L                   |      | M    |      | U    |      |              | L                 | MU   |
|                | f <sub>L</sub> -f <sub>U</sub> | Nom. | Flatness                           | Typ. | Max. | Typ. | Max. | Typ. | Max.                | Typ. | Min. | Typ. | Min. | Typ. |              | Min.              | Typ. |
| 40-400         | 21.5±0.5                       | ±0.6 | 0.1                                | 0.3  | 0.2  | 0.4  | 0.2  | 0.5  | 30                  | 20   | 30   | 20   | 27   | 18   | 1.1          | 10.0              | 10.0 |




L = 40-100 MHz M = 100-200 MHz U = 200-400 MHz

1. Mainline loss includes theoretical power loss at coupled port.


External heat sinking is recommended to reduce case temperature

## Typical Performance Data

| Frequency<br>(MHz) | Mainline Loss<br>(dB)<br>In-Out | Coupling<br>(dB)<br>In-Cpl | Directivity<br>(dB) | Return Loss<br>(dB) |       |       |
|--------------------|---------------------------------|----------------------------|---------------------|---------------------|-------|-------|
|                    |                                 |                            |                     | In                  | Out   | Cpl   |
| 40.00              | 0.08                            | 21.91                      | 27.54               | 25.40               | 25.17 | 25.48 |
| 64.00              | 0.12                            | 21.84                      | 35.86               | 30.09               | 31.45 | 29.93 |
| 88.00              | 0.14                            | 21.81                      | 45.58               | 32.95               | 37.18 | 32.12 |
| 120.00             | 0.18                            | 21.84                      | 45.56               | 35.19               | 42.43 | 33.49 |
| 160.00             | 0.19                            | 21.84                      | 40.49               | 36.89               | 40.19 | 34.73 |
| 210.00             | 0.24                            | 21.83                      | 37.31               | 36.89               | 35.12 | 35.99 |
| 260.00             | 0.25                            | 21.81                      | 34.65               | 34.69               | 31.80 | 37.34 |
| 310.00             | 0.30                            | 21.73                      | 33.12               | 31.93               | 29.39 | 39.03 |
| 360.00             | 0.32                            | 21.72                      | 30.76               | 29.36               | 27.46 | 41.34 |
| 400.00             | 0.37                            | 21.62                      | 29.41               | 27.52               | 26.13 | 43.97 |

PDC20-400HP+  
MAINLINE LOSSPDC20-400HP+  
COUPLING & DIRECTIVITYPDC20-400HP+  
RETURN LOSS

## Electrical Schematic



\* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) THAT ROUTES DC FROM RF PORTS TO GROUND.

## Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

# Directional Coupler

PDC20-400HP+

## Typical Performance Data

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | COUPLING<br>(dB) | DIRECTIVITY<br>(dB) | RETURN LOSS |       |       |
|--------------------|---------------------------|------------------|---------------------|-------------|-------|-------|
|                    |                           |                  |                     | IN          | OUT   | CPL   |
| 40.0               | 0.08                      | 21.91            | 27.54               | 25.40       | 25.17 | 25.48 |
| 46.0               | 0.09                      | 21.90            | 29.47               | 26.78       | 26.79 | 26.83 |
| 52.0               | 0.10                      | 21.87            | 31.31               | 28.01       | 28.36 | 28.01 |
| 58.0               | 0.11                      | 21.85            | 33.62               | 29.12       | 29.92 | 29.06 |
| 64.0               | 0.12                      | 21.84            | 35.86               | 30.09       | 31.45 | 29.93 |
| 70.0               | 0.12                      | 21.82            | 38.66               | 30.99       | 32.99 | 30.69 |
| 76.0               | 0.13                      | 21.81            | 40.31               | 31.74       | 34.42 | 31.25 |
| 82.0               | 0.14                      | 21.81            | 42.15               | 32.38       | 35.79 | 31.71 |
| 88.0               | 0.14                      | 21.81            | 45.58               | 32.95       | 37.18 | 32.12 |
| 94.0               | 0.15                      | 21.82            | 45.85               | 33.46       | 38.45 | 32.44 |
| 100.0              | 0.16                      | 21.83            | 47.58               | 33.93       | 39.64 | 32.77 |
| 110.0              | 0.18                      | 21.83            | 46.76               | 34.61       | 41.15 | 33.15 |
| 120.0              | 0.18                      | 21.84            | 45.56               | 35.19       | 42.43 | 33.49 |
| 130.0              | 0.19                      | 21.85            | 44.13               | 35.73       | 42.77 | 33.85 |
| 140.0              | 0.18                      | 21.85            | 42.60               | 36.21       | 42.16 | 34.15 |
| 150.0              | 0.19                      | 21.86            | 40.93               | 36.68       | 41.37 | 34.43 |
| 160.0              | 0.19                      | 21.84            | 40.49               | 36.89       | 40.19 | 34.73 |
| 170.0              | 0.19                      | 21.85            | 39.80               | 37.16       | 39.00 | 35.00 |
| 180.0              | 0.19                      | 21.84            | 39.03               | 37.26       | 37.89 | 35.30 |
| 190.0              | 0.21                      | 21.85            | 38.75               | 37.20       | 36.90 | 35.50 |
| 200.0              | 0.23                      | 21.85            | 37.77               | 37.14       | 36.00 | 35.79 |
| 210.0              | 0.24                      | 21.83            | 37.31               | 36.89       | 35.12 | 35.99 |
| 220.0              | 0.23                      | 21.82            | 36.78               | 36.55       | 34.39 | 36.25 |
| 230.0              | 0.23                      | 21.82            | 35.79               | 36.12       | 33.68 | 36.54 |
| 240.0              | 0.23                      | 21.83            | 35.84               | 35.67       | 33.01 | 36.79 |
| 250.0              | 0.25                      | 21.83            | 34.98               | 35.23       | 32.37 | 37.05 |
| 260.0              | 0.25                      | 21.81            | 34.65               | 34.69       | 31.80 | 37.34 |
| 270.0              | 0.25                      | 21.79            | 34.33               | 34.13       | 31.31 | 37.60 |
| 280.0              | 0.26                      | 21.80            | 33.98               | 33.58       | 30.77 | 37.94 |
| 290.0              | 0.29                      | 21.81            | 33.65               | 32.97       | 30.30 | 38.22 |
| 300.0              | 0.31                      | 21.78            | 33.19               | 32.44       | 29.85 | 38.59 |
| 310.0              | 0.30                      | 21.73            | 33.12               | 31.93       | 29.39 | 39.03 |
| 320.0              | 0.27                      | 21.72            | 32.58               | 31.41       | 28.96 | 39.46 |
| 330.0              | 0.28                      | 21.74            | 32.12               | 30.87       | 28.56 | 39.91 |
| 340.0              | 0.31                      | 21.76            | 31.53               | 30.34       | 28.16 | 40.42 |
| 350.0              | 0.32                      | 21.74            | 31.24               | 29.85       | 27.80 | 40.85 |
| 360.0              | 0.32                      | 21.72            | 30.76               | 29.36       | 27.46 | 41.34 |
| 370.0              | 0.32                      | 21.71            | 30.59               | 28.88       | 27.10 | 41.99 |
| 380.0              | 0.35                      | 21.70            | 30.25               | 28.43       | 26.76 | 42.71 |
| 390.0              | 0.38                      | 21.67            | 29.86               | 27.97       | 26.45 | 43.22 |
| 400.0              | 0.37                      | 21.62            | 29.41               | 27.52       | 26.13 | 43.97 |

REV. X1  
PDC20-400HP  
060718  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661







The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Directional Coupler


## Typical Performance Curves

PDC20-400HP+



A01  
A04  
A05  
A06

## Outline Dimensions



| CASE# | A               | B               | C              | D               | E              | F               | G              | H             | J             | K             | WT,<br>GRAM |
|-------|-----------------|-----------------|----------------|-----------------|----------------|-----------------|----------------|---------------|---------------|---------------|-------------|
| A01   | .770<br>(19.56) | .800<br>(20.32) | .385<br>(9.78) | .400<br>(10.16) | .370<br>(9.40) | .400<br>(10.16) | .200<br>(5.08) | .20<br>(5.08) | .14<br>(3.56) | .031<br>(.79) | 5.2         |
| A04   |                 |                 | .200<br>(5.08) | .210<br>(5.33)  |                |                 |                |               |               |               | 3.7         |
| A05   |                 |                 | .240<br>(6.10) | .250<br>(6.35)  |                |                 |                |               |               |               | 3.7         |
| A06   |                 |                 | .285<br>(7.24) | .310<br>(7.87)  |                |                 |                |               |               |               | 5.2         |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .03$ ; 3 Pl.  $\pm .015$

### Notes:

- Header material: C.R.S.  
Pin material: #52 alloy.  
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver.
- Insulated spacer available. Request P/N B14-045-01.
- Tolerance on pin diameter  $\pm .005$  inch.
- Glass meniscus 0.015 inch max.
- Blue bead indicates Pin 1. Pin numbers do not appear on unit, for reference only.

**Mini-Circuits®**

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec                                                                                       |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature          | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                                                       | MIL-STD-202, Method 107, Condition A-3, except +100°C                                                |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                                                             | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                                                               | MIL-STD-202, Method 213, Condition A                                                                 |
| Moisture Resistance            | 10 cycles, 24 hours per cycle                                                                                                                                   | MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours |
| Solderability                  | 10X Magnification                                                                                                                                               | J-STD-002, 95% Coverage                                                                              |
| Resistance to Solder Heat      | 260°C for 10 seconds                                                                                                                                            | MIL-STD-202, Method 210, Condition B                                                                 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215                                                                              |
| Terminal Strength              | 4 1/2 Pound Pull                                                                                                                                                | MIL-STD-202, Method 211, Condition A                                                                 |



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification       | Test/Inspection Condition | Reference/Spec                       |
|---------------------|---------------------------|--------------------------------------|
| Gross Leak          | 125°C Bubble Test         | MIL-STD-202, Method 112, Condition D |
| Barometric Pressure | 100,000 Feet              | MIL-STD-202, Method 105, Condition D |