

Plug-In

Power Splitter/Combiner

PRSC-2050

2 Way-0° Resistive 50Ω DC to 2000 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.125W max.
Permanent damage may occur if any of these limits are exceeded.	

Pin Connections

SUMPORT	5
PORT 1	3
PORT 2	15
GROUND	1,2,4,8,9,12,13,14,16
CASE GROUND	1,2,4,8,9,12,13,14,16

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E
.770	.810	.380	.410	.030
19.56	20.57	9.65	10.41	0.76
F	G	H		wt
.200	.20	.14		grams
5.08	5.08	3.56		11.0

Features

- wideband, DC to 2000 MHz
- hermetic metal case
- excellent amplitude unbalance 0:2 dB typ.
- excellent VSWR, 1.1:1 typ.

Applications

- test set-ups
- video or cable tv
- military, hi-rel application

Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)			INSERTION LOSS (dB) ABOVE 6.0 dB						PHASE UNBALANCE (Degrees)			AMPLITUDE UNBALANCE (dB)		
	L	M	U	L	M	U	L	M	U	L	M	U	L	M	U
$f_L - f_U$	Typ.	Typ.	Typ.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Max.	Max.	Max.	Max.	Max.	Max.
DC-2000	6.0	6.2	6.5	0.1	0.3	0.2	0.7	0.5	1.0	1	3	5	0.1	0.3	0.5




L = DC-100 MHz M = 100-1000 MHz U = 1000-2000 MHz

This is a resistive power divider to enable frequency coverage from dc to the highest rated frequency. Since resistive power divider do not provide a high degree of isolation (basically isolation equals the insertion loss between ports), an amplifier such as Mini-Circuits' ZFL series is recommended when high isolation is required. Matched power rating 0.75W, internal load dissipation 0.375W.

Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
1.00	6.03	6.03	0.00	6.03	0.02	1.00	1.00	1.00
5.00	6.03	6.04	0.01	6.05	0.06	1.00	1.00	1.00
10.00	6.04	6.04	0.00	6.04	0.09	1.00	1.01	1.01
50.00	6.05	6.06	0.00	6.06	0.04	1.01	1.01	1.01
100.00	6.06	6.05	0.00	6.06	0.10	1.01	1.01	1.01
500.00	6.05	6.04	0.01	6.07	0.13	1.03	1.02	1.03
1000.00	6.10	6.08	0.02	6.13	0.05	1.11	1.08	1.12
1100.00	6.15	6.08	0.07	6.17	0.09	1.13	1.10	1.14
1250.00	6.20	6.15	0.05	6.25	0.06	1.17	1.13	1.18
1400.00	6.26	6.20	0.06	6.33	0.06	1.21	1.17	1.22
1550.00	6.34	6.29	0.05	6.45	0.20	1.25	1.21	1.26
1700.00	6.44	6.38	0.06	6.58	0.40	1.29	1.24	1.29
1850.00	6.55	6.49	0.05	6.72	0.69	1.32	1.27	1.32
1925.00	6.58	6.53	0.05	6.76	0.76	1.33	1.29	1.33
2000.00	6.63	6.59	0.04	6.82	0.98	1.35	1.30	1.34

1. Total Loss = Insertion Loss + 3dB splitter loss.



electrical schematic



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



2 Way-0° Power Splitter/Combiner

PRSC-2050

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	ISOLATION (dB)	PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
1.0	6.03	6.03	0.00	6.03	0.02	1.0	1.00	1.00	1.00
2.0	6.03	6.03	0.00	6.04	0.06	2.0	1.00	1.00	1.00
3.0	6.03	6.04	0.00	6.04	0.06	3.0	1.00	1.00	1.00
4.0	6.04	6.03	0.01	6.03	0.02	4.0	1.00	1.00	1.00
5.0	6.03	6.04	0.01	6.05	0.06	5.0	1.00	1.00	1.00
6.0	6.04	6.04	0.00	6.03	0.06	6.0	1.00	1.00	1.00
7.0	6.05	6.04	0.01	6.04	0.02	7.0	1.00	1.01	1.00
8.0	6.04	6.04	0.00	6.04	0.03	8.0	1.00	1.01	1.00
9.0	6.04	6.04	0.00	6.04	0.06	9.0	1.00	1.01	1.01
10.0	6.04	6.04	0.00	6.04	0.09	10.0	1.00	1.01	1.01
20.0	6.05	6.04	0.01	6.04	0.02	20.0	1.01	1.01	1.01
30.0	6.04	6.04	0.00	6.05	0.05	30.0	1.01	1.01	1.01
40.0	6.05	6.04	0.01	6.04	0.03	40.0	1.01	1.01	1.01
50.0	6.05	6.06	0.00	6.06	0.04	50.0	1.01	1.01	1.01
60.0	6.06	6.03	0.02	6.04	0.05	60.0	1.01	1.01	1.01
70.0	6.04	6.05	0.00	6.05	0.01	70.0	1.01	1.01	1.01
80.0	6.05	6.04	0.00	6.06	0.08	80.0	1.01	1.01	1.01
90.0	6.05	6.05	0.00	6.06	0.09	90.0	1.01	1.01	1.01
100.0	6.06	6.05	0.00	6.06	0.10	100.0	1.01	1.01	1.01
200.0	6.05	6.05	0.00	6.06	0.13	200.0	1.01	1.01	1.01
300.0	6.07	6.05	0.02	6.06	0.18	300.0	1.01	1.01	1.02
400.0	6.06	6.04	0.02	6.06	0.17	400.0	1.02	1.01	1.03
500.0	6.05	6.04	0.01	6.07	0.13	500.0	1.03	1.02	1.03
600.0	6.07	6.04	0.03	6.07	0.24	600.0	1.04	1.02	1.05
700.0	6.06	6.04	0.03	6.08	0.22	700.0	1.05	1.03	1.06
800.0	6.07	6.04	0.03	6.08	0.35	800.0	1.07	1.04	1.08
900.0	6.09	6.05	0.04	6.11	0.14	900.0	1.09	1.06	1.10
1000.0	6.10	6.08	0.02	6.13	0.05	1000.0	1.11	1.08	1.12
1100.0	6.15	6.08	0.07	6.17	0.09	1100.0	1.13	1.10	1.14
1175.0	6.16	6.15	0.01	6.21	0.02	1175.0	1.15	1.11	1.16
1250.0	6.20	6.15	0.05	6.25	0.06	1250.0	1.17	1.13	1.18
1325.0	6.23	6.18	0.05	6.29	0.04	1325.0	1.19	1.15	1.20
1400.0	6.26	6.20	0.06	6.33	0.06	1400.0	1.21	1.17	1.22
1475.0	6.31	6.26	0.05	6.39	0.09	1475.0	1.23	1.19	1.24
1550.0	6.34	6.29	0.05	6.45	0.20	1550.0	1.25	1.21	1.26
1625.0	6.38	6.34	0.04	6.50	0.29	1625.0	1.27	1.23	1.27
1700.0	6.44	6.38	0.06	6.58	0.40	1700.0	1.29	1.24	1.29
1775.0	6.49	6.45	0.03	6.63	0.55	1775.0	1.31	1.26	1.31
1850.0	6.55	6.49	0.05	6.72	0.69	1850.0	1.32	1.27	1.32
1925.0	6.58	6.53	0.05	6.76	0.76	1925.0	1.33	1.29	1.33
2000.0	6.63	6.59	0.04	6.82	0.98	2000.0	1.35	1.30	1.34

¹Total Loss = Insertion Loss + 6dB Splitter Loss

REV. X2
PRSC-2050
100624
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661








The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



2 Way-0° Power Splitter/Combiner

PRSC-2050

Typical Performance Curves



REV. X2
PRSC-2050
100624
Page 1 of 1




Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	WT. GRAM
C145	.770 (19.56)	.810 (20.57)	.380 (9.65)	.410 (10.41)	.030 (.76)	.200 (5.08)	.20 (5.08)	.14 (3.56)	11.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Header material: C.R.S.
Pin material: #52 alloy.
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver.
- Tolerance on pin diameter $\pm .005$ inch.
- Glass meniscus 0.015 inch max.
- Blue bead indicates Pin 1. Pin numbers do not appear on unit, for reference only.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Moisture Resistance	10 cycles, 24 hours per cycle	MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours
Solderability	10X Magnification	J-STD-002, 95% Coverage
Resistance to Solder Heat	260°C for 10 seconds	MIL-STD-202, Method 210, Condition B
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215
Terminal Strength	4 1/2 Pound Pull	MIL-STD-202, Method 211, Condition A



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Gross Leak	125°C Bubble Test	MIL-STD-202, Method 112, Condition D
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D