

Plug-In

# Power Splitter/Combiner

PSCQ-2-51W+

2 Way-90° 50Ω 5 to 50 MHz


## Maximum Ratings

|                                                                 |                |
|-----------------------------------------------------------------|----------------|
| Operating Temperature                                           | -55°C to 100°C |
| Storage Temperature                                             | -55°C to 100°C |
| Power Input (as a splitter)                                     | 0.5W max.      |
| Permanent damage may occur if any of these limits are exceeded. |                |

## Pin Connections

|               |           |
|---------------|-----------|
| SUMPORT       | 1         |
| PORT 1 (0°)   | 5         |
| PORT 2 (+90°) | 6         |
| GROUND        | 2,3,4,7,8 |

## Outline Drawing



## Outline Dimensions (inch/mm)

| A     | B     | C    | D    | E    | F     |       |
|-------|-------|------|------|------|-------|-------|
| .770  | .800  | .285 | .310 | .370 | .400  |       |
| 19.56 | 20.32 | 7.24 | 7.87 | 9.40 | 10.16 |       |
| G     | H     | J    | K    |      |       | wt    |
| .200  | .20   | .14  | .031 |      |       | grams |
| 5.08  | 5.08  | 3.56 | 0.79 |      |       | 5.2   |

## Features

- 10:1 bandwidth
- excellent amplitude unbalance, 0.15 dB typ. and phase unbalance, 1.0 deg. typ.
- very low insertion loss, 0.5 dB typ.
- excellent VSWR, 1.21 typ.
- excellent isolation, 41 dB typ.

## Applications

- short wave
- land mobile


## Electrical Specifications

| FREQ. RANGE (MHz) | ISOLATION (dB) | INSERTION LOSS (dB)<br>Avg. of Coupled Outputs ABOVE 3 dB | PHASE UNBALANCE (Degrees) | AMPLITUDE UNBALANCE (dB) |
|-------------------|----------------|-----------------------------------------------------------|---------------------------|--------------------------|
| $f_L - f_U$       | Typ. Min.      | Typ. Max.                                                 | Max.                      | Max.                     |
| 5-50              | 41 30          | 0.5 1.0                                                   | 5.0                       | 0.5                      |


## Typical Performance Data

| Frequency (MHz) | Total Loss <sup>1</sup> (dB) |      | Amplitude Unbalance (dB) | Isolation (dB) | Phase Unbalance (deg.) | VSWR S | VSWR 1 | VSWR 2 |
|-----------------|------------------------------|------|--------------------------|----------------|------------------------|--------|--------|--------|
|                 | S-1                          | S-2  |                          |                |                        |        |        |        |
| 5.00            | 3.32                         | 3.19 | 0.13                     | 40.09          | 89.18                  | 1.18   | 1.31   | 1.03   |
| 10.00           | 3.36                         | 3.26 | 0.10                     | 57.75          | 87.49                  | 1.15   | 1.21   | 1.08   |
| 15.00           | 3.42                         | 3.32 | 0.10                     | 45.05          | 87.36                  | 1.17   | 1.17   | 1.15   |
| 20.00           | 3.47                         | 3.37 | 0.10                     | 41.67          | 88.47                  | 1.20   | 1.16   | 1.21   |
| 25.00           | 3.52                         | 3.42 | 0.10                     | 40.64          | 89.30                  | 1.23   | 1.18   | 1.25   |
| 30.00           | 3.57                         | 3.47 | 0.10                     | 40.43          | 89.51                  | 1.26   | 1.21   | 1.28   |
| 35.00           | 3.62                         | 3.52 | 0.10                     | 40.57          | 89.16                  | 1.29   | 1.25   | 1.29   |
| 40.00           | 3.67                         | 3.56 | 0.10                     | 40.61          | 88.38                  | 1.32   | 1.28   | 1.28   |
| 41.00           | 3.68                         | 3.57 | 0.10                     | 40.75          | 88.19                  | 1.32   | 1.29   | 1.28   |
| 43.00           | 3.69                         | 3.59 | 0.10                     | 40.75          | 87.78                  | 1.33   | 1.30   | 1.28   |
| 45.00           | 3.71                         | 3.60 | 0.10                     | 40.75          | 87.34                  | 1.34   | 1.31   | 1.27   |
| 47.00           | 3.72                         | 3.62 | 0.10                     | 40.71          | 86.89                  | 1.35   | 1.32   | 1.27   |
| 48.00           | 3.73                         | 3.63 | 0.10                     | 40.70          | 86.65                  | 1.35   | 1.33   | 1.26   |
| 49.00           | 3.74                         | 3.63 | 0.10                     | 40.71          | 86.42                  | 1.35   | 1.34   | 1.26   |
| 50.00           | 3.75                         | 3.64 | 0.10                     | 40.65          | 86.19                  | 1.36   | 1.34   | 1.26   |

1. Total Loss = Insertion Loss + 3dB splitter loss.



## electrical schematic



## Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B  
M151107  
ED-11294-2  
PSCQ-2-51W+  
LC/RS/CP/AM  
150930



Generic photo used for illustration purposes only

CASE STYLE: A06

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

# 2 Way-90° Power Splitter/Combiner

PSCQ-2-51W+

## Typical Performance Data

| FREQUENCY<br>(MHz) | TOTAL LOSS <sup>1</sup><br>(dB) |      | AMPLITUDE<br>UNBALANCE<br>(dB) | ISOLATION<br>(dB) | PHASE<br>UNBALANCE<br>(deg.) | FREQUENCY<br>(MHz) | VSWR<br>(:1) |      |      |
|--------------------|---------------------------------|------|--------------------------------|-------------------|------------------------------|--------------------|--------------|------|------|
|                    | S-1                             | S-2  |                                |                   |                              |                    | S            | 1    | 2    |
| 5.0                | 3.32                            | 3.19 | 0.13                           | 40.09             | 89.18                        | 5.0                | 1.18         | 1.31 | 1.03 |
| 6.0                | 3.32                            | 3.20 | 0.12                           | 42.54             | 89.37                        | 6.0                | 1.17         | 1.28 | 1.02 |
| 7.0                | 3.32                            | 3.21 | 0.11                           | 45.39             | 88.98                        | 7.0                | 1.16         | 1.25 | 1.03 |
| 8.0                | 3.33                            | 3.22 | 0.11                           | 49.03             | 88.44                        | 8.0                | 1.15         | 1.24 | 1.04 |
| 9.0                | 3.35                            | 3.24 | 0.11                           | 54.51             | 87.94                        | 9.0                | 1.15         | 1.22 | 1.06 |
| 10.0               | 3.36                            | 3.26 | 0.10                           | 57.75             | 87.49                        | 10.0               | 1.15         | 1.21 | 1.08 |
| 15.0               | 3.42                            | 3.32 | 0.10                           | 45.05             | 87.36                        | 15.0               | 1.17         | 1.17 | 1.15 |
| 20.0               | 3.47                            | 3.37 | 0.10                           | 41.67             | 88.47                        | 20.0               | 1.20         | 1.16 | 1.21 |
| 25.0               | 3.52                            | 3.42 | 0.10                           | 40.64             | 89.30                        | 25.0               | 1.23         | 1.18 | 1.25 |
| 30.0               | 3.57                            | 3.47 | 0.10                           | 40.43             | 89.51                        | 30.0               | 1.26         | 1.21 | 1.28 |
| 35.0               | 3.62                            | 3.52 | 0.10                           | 40.57             | 89.16                        | 35.0               | 1.29         | 1.25 | 1.29 |
| 40.0               | 3.67                            | 3.56 | 0.10                           | 40.61             | 88.38                        | 40.0               | 1.32         | 1.28 | 1.28 |
| 41.0               | 3.68                            | 3.57 | 0.10                           | 40.75             | 88.19                        | 41.0               | 1.32         | 1.29 | 1.28 |
| 42.0               | 3.68                            | 3.58 | 0.10                           | 40.77             | 87.98                        | 42.0               | 1.33         | 1.29 | 1.28 |
| 43.0               | 3.69                            | 3.59 | 0.10                           | 40.75             | 87.78                        | 43.0               | 1.33         | 1.30 | 1.28 |
| 44.0               | 3.70                            | 3.60 | 0.10                           | 40.81             | 87.57                        | 44.0               | 1.33         | 1.31 | 1.28 |
| 45.0               | 3.71                            | 3.60 | 0.10                           | 40.75             | 87.34                        | 45.0               | 1.34         | 1.31 | 1.27 |
| 46.0               | 3.72                            | 3.61 | 0.10                           | 40.77             | 87.12                        | 46.0               | 1.34         | 1.32 | 1.27 |
| 47.0               | 3.72                            | 3.62 | 0.10                           | 40.71             | 86.89                        | 47.0               | 1.35         | 1.32 | 1.27 |
| 48.0               | 3.73                            | 3.63 | 0.10                           | 40.70             | 86.65                        | 48.0               | 1.35         | 1.33 | 1.26 |
| 49.0               | 3.74                            | 3.63 | 0.10                           | 40.71             | 86.42                        | 49.0               | 1.35         | 1.34 | 1.26 |
| 50.0               | 3.75                            | 3.64 | 0.10                           | 40.65             | 86.19                        | 50.0               | 1.36         | 1.34 | 1.26 |

<sup>1</sup>Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS








REV. X2  
PSCQ-2-51W+  
8/4/2010  
Page 1 of 1

# 2 Way-90° Power Splitter/Combiner


PSCQ-2-51W+

## Typical Performance Curves



A01  
A04  
A05  
A06

## Outline Dimensions



| CASE# | A               | B               | C              | D               | E              | F               | G              | H             | J             | K             | WT,<br>GRAM |
|-------|-----------------|-----------------|----------------|-----------------|----------------|-----------------|----------------|---------------|---------------|---------------|-------------|
| A01   | .770<br>(19.56) | .800<br>(20.32) | .385<br>(9.78) | .400<br>(10.16) | .370<br>(9.40) | .400<br>(10.16) | .200<br>(5.08) | .20<br>(5.08) | .14<br>(3.56) | .031<br>(.79) | 5.2         |
| A04   |                 |                 | .200<br>(5.08) | .210<br>(5.33)  |                |                 |                |               |               |               | 3.7         |
| A05   |                 |                 | .240<br>(6.10) | .250<br>(6.35)  |                |                 |                |               |               |               | 3.7         |
| A06   |                 |                 | .285<br>(7.24) | .310<br>(7.87)  |                |                 |                |               |               |               | 5.2         |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .03$ ; 3 Pl.  $\pm .015$

### Notes:

- Header material: C.R.S.  
Pin material: #52 alloy.  
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver.
- Insulated spacer available. Request P/N B14-045-01.
- Tolerance on pin diameter  $\pm .005$  inch.
- Glass meniscus 0.015 inch max.
- Blue bead indicates Pin 1. Pin numbers do not appear on unit, for reference only.

**Mini-Circuits®**

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec                                                                                       |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature          | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                                                       | MIL-STD-202, Method 107, Condition A-3, except +100°C                                                |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                                                             | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                                                               | MIL-STD-202, Method 213, Condition A                                                                 |
| Moisture Resistance            | 10 cycles, 24 hours per cycle                                                                                                                                   | MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours |
| Solderability                  | 10X Magnification                                                                                                                                               | J-STD-002, 95% Coverage                                                                              |
| Resistance to Solder Heat      | 260°C for 10 seconds                                                                                                                                            | MIL-STD-202, Method 210, Condition B                                                                 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215                                                                              |
| Terminal Strength              | 4 1/2 Pound Pull                                                                                                                                                | MIL-STD-202, Method 211, Condition A                                                                 |



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification       | Test/Inspection Condition | Reference/Spec                       |
|---------------------|---------------------------|--------------------------------------|
| Gross Leak          | 125°C Bubble Test         | MIL-STD-202, Method 112, Condition D |
| Barometric Pressure | 100,000 Feet              | MIL-STD-202, Method 105, Condition D |